Dwg. No. :<u>H21-3627</u>

承認字號

Issued Date: 2021/11/20

Customer :		
(客 戶)		
Part No. :	HBV101M1VTR-0608	
(貴公司糾號)		

# SPECIFICATION FOR APPROVAL

# 承認書

:Organic Conductive Polymer Hybrid Aluminum Electrolytic Capacitors
:HBV Series
.: HBV101M1VTR-0608

## LELON ELECTRONICS CORP.

立隆電子工業股份有限公司

## Headquarters

147, Sec. 1, Guoguang Rd,. Dali District, Taichung, Taiwan TEL: +886-4-24181856 FAX: +886-4-24181906

## Manufacturing Sites

Lelon Electronics Corp.
147, Sec. 1, Guoguang Rd,. Dali District, Taichung, Taiwar
TEL: +886-4-24181856 FAX: +886-4-24181906

Lelon Electronics (Huizhou) Co., Ltd.

Taiyang Industrial Zone, Baihua Town, Huidong County, Huizhou City,
Guangdong, China

TEL: +86-752-8768222 FAX: +86-752-8768199

Lelon Electronics (Suzhou) Co., Ltd.

1220, Zhongshan North Rd., Wujiang Economic and Technological Technological Development Zone Suzhou City, Jiangsu, China

TEL: +86-512-63457588 FAX: +86-512-63457791

## Approval Signatures

貴公司承認印

Approval	Check	Design
核 准	確 認	作 成
R & D	R & D	R & D
NOV. 20. 2021	NOV. 20. 2021	NOV. 20. 2021
H. Y. Huang	J.H.Xiong	Z. X. Sun

Please Return One Copy with Your Approval 承 認 後 請 寄 回 本 圖 一 份

## Part Numbering System

#### **Product Code Guide**

HBW series	100µF	±20%	25V	Carrier Tape		6.3φ×7.7L	Pb-free and	
<b>HBW</b>	<u>101</u>	<u>M</u>	<u>1E</u>	<u>TR</u>	-	<u>0608</u>		
1	2	3	4	<b>⑤</b>	6	7	8	9
Series	Capacitance	Capacitance Tolerance	Rated Voltage	Package Type	Terminal Type	Case size	Lead Wire	Supplement Code

## 1) Series:

Series is represented by a three-letter code. When the series name only has two letters, use a hyphen, "-", to fill the third blank. When the series name has 4 letters, use the following series codes.

OCVZ > OVZ; OCVU > OVU

## 2 Capacitance:

Capacitance in  $\mu F$  is represented by a three-digit code. The first two digits are significant and the third digit indicates the number of zeros following the significant figure. "R" represents the decimal point for capacitance under 10 $\mu F$ .

Example:

Capacitance	22	47	100	220	470	1,000	2,200	4,700
Part number	220	470	101	221	471	102	222	472

## 3 Tolerance:

K = -10% ~ +10%	M = -20% ~ +20%	V = -10% ~ +20%

## 4 Rated voltage:

Rated voltage in volts (V) is represented by a two-digit code

							,						
Voltage (WV)	2.5	4	6.3	10	16	20	25	35	40	50	63	80	100
Code	0E	0G	OJ	1A	1C	1D	1E	1V	1G	1H	1J	1K	2A

## ⑤ Package:

TR = Reel package

#### **6** Terminal:

- = No dummy terminal

#### 7 Case size:

The first two digits indicate case diameter and the last two digits indicate case length in mm.

Į	φD×L	6.3×5.8	6.3×7.7	8×10	8×12	10×10	10×12.5	10×13.5
	Code	0606	0608	0810	0812	1010	1013	1014

Note: When a case size is required and not shown in the table, please contact with us for further discussion.

#### **8** Lead Wire and Coating Type:

None = Pb free wire (Standard design)

K / L = Automotive control code

## Supplement code (Optional):

For special control purpose

<sup>\*</sup> When a supplement code following a blank digit code of lead wire and case coating type (standard design), use a hyphen, "-", to fill the blank digit.

<sup>\*</sup> When the automotive control code is required, please contact with us for further discussion.

Lelon P/N: HBV101M1VTR-0608

## LELON ELECTRONICS CORP.


HBV  $~100~\mu F$  /  $35~V-6.3\phi \times 7.7 L$ 

Page: 1 / 1

## **CUSTOMER**

## CUSTOMER P/N: HBV101M1VTR-0608


## PRODUCT DIMENSIONS




	Unit: mm
φD	6.3
L	$7.7 \pm 0.3$
Α	6.6
В	6.6
С	7.2
W	0.5~0.8
Р	$2.0 \pm 0.2$

Items	Performance									
Rated Voltage $V_R$	35 V									
Capacitance C <sub>R</sub>					100 μF		(120 H	z, 20°ℂ)		
Category Temperature Range				-:	55°C ~ +105°C					
Capacitance Tolerance				-2	20 % ~ +20 %		(120 H	z, 20°ℂ)		
Surge Voltage V <sub>S</sub>					$40.3\;V_{DC}$					
Leakage Current (20°C)					$I_{LEAK} \le 35  \mu A$		After 2	minutes		
Tan δ					≦ 0.12		(120 H	z, 20°C)		
ESR max.					35 m $\Omega$		(100k	Hz, 20°ℂ)		
Ripple Current (I <sub>AC, R</sub> / rms )					1400 mA	١	(100k	Hz, 105°ℂ)		
Ripple Current (mA) and Frequency Multipliers		Frequency (I	Hz)	120 ≤ f < 1k 0.1	$1k \le f < 10k$ $0.3$	10k ≤ f <100k 0.6	100k≦ f <500k 1.0			
Endurance and Moisture Resistance	Items Test Time Cap. Change Tan δ ESR Leakage Current* Shelf Life: After store			Endurance  10,000 Hrs at 105°C; V <sub>R</sub> I <sub>AC,R</sub> 1,000 Hrs at 105°C  Within ±30 % of initial value  Less than 200% of specified value  Within specified value						
Standards					abilized at +20 ° 5101-1, IEC 60					
Remarks				RoHS C	ompliance, Halo	ogen-free				

Marking: Each capacitor shall be marked with the following information.





Month	1	2	3	4	5	6
Code	Α	В	С	D	Е	F
Month	7	8	9	10	11	12
Code	G	Н	I	J	K	L


Marking color: Dark Green

<sup>\*</sup> Please refer to "Precautions and Guidelines for Aluminum Electrolytic Capacitors" section in Lelon's catalog for further details.

Publication Date	November 20, 2021	Approval Signatures:	Approved	Checked	Designed
Revision Date			R & D	R & D	R&D
			NOV. 20. 2021	NOV. 20. 2021	NOV. 20. 2021
Version No.	1	Please return one copy with your approval	H. Y. Huang	J.H.Xiong	Z. X. Sun

## Diagram of Dimensions:

Unit: mm




(\*): For  $6.3\phi$  is 0.4 max.


φD	L	Α	В	С	W	P ± 0.2
6.3	5.8± 0.3	6.6	6.6	7.2	0.5 ~ 0.8	2.0
6.3	$7.7 \pm 0.3$	6.6	6.6	7.2	0.5 ~ 0.8	2.0
8	10.0 ± 0.5	8.3	8.3	9.0	0.7~ 1.1	3.1
8	12.0 ± 0.5	8.3	8.3	9.0	0.7 ~ 1.1	3.1
10	10.0 ± 0.5	10.3	10.3	11.0	0.7~ 1.3	4.7
10	12.5 ± 0.5	10.3	10.3	11.0	0.7 ~ 1.3	4.7


## Marking:

Each capacitor shall be marked with the following information.










## Description of Date Code:



IVIOTILIT O	i illalik	aracur	C			
Month	1	2	3	4	5	6
Code	Α	В	С	D	Е	F
Month	7	8	9	10	11	12
Code	G	Н	I	J	K	L

Origin Code:

Huizhou: A1 , B1 , ... , K1 , L1 Suzhou: 1A , 1B , ... , 1K , 1L


Marking Color: Dark Green

## Taping Specification for SMD Type

## 1. Carrier Tape

Fig. 1-1 Fig. 1-2

Fig. 1-3



φD×L	Α	В	$\phi$ d	F	Р	P1	P2	t1	t2	W	W1	Unit: mm Fig. No.
3~4 ×4.5	4.5	4.5		5.5	8				4.8			4.4
4 ×5.3	4.5	4.5		5.5	8				5.8			1-1
4 ×5.7	4.5	4.5		5.5	8				6.3	12.0		
5 ×4.5	5.5	5.5		5.5	12				4.8			
5 ×5.3	5.5	5.5		5.5	12				5.9			
5 ×5.7 ~ 5.8	5.5	5.5		5.5	12				6.3			
6.3 ×4.5	6.8	6.8		7.5	12			0.4	4.8			
6.3 ×5.3	6.8	6.8							5.9			
6.3 ×5.7 / 5.8	6.8	6.8		7.5	12				6.3	16.0		
6.3 ×7.7	6.8	6.8							8.3			
6.3 ×8.7	6.8	6.8							9.3			4.0
6.3 ×9.5	6.8	6.8		11.5	16			0.5	10.6	24.0		1-2
8 ×6.5	8.7	8.7		7.5	12				6.9	16.0		
8 ×9.5~10									11.0			
8 ×10.5(G)	9.4	9.4		11.5	16				11.4	24.0		
10 ×7.7	10.7	10.7				2.0	4.0		8.7			
10 ×10			1.5						11.0		1.75	
10 ×10.5(G)	11.4	11.4							11.4			
10 ×12.5	10.7	10.7							13.1			
10 ×16.5	10.7	10.7							17.5			
12.5 ×13.5	13.4	13.4							14.5			
12.5 ×13.5(G)	13.7	13.7		14.2	24				15.0	32.0		
12.5 ×16	13.4	13.4							17.0			
12.5 ×16(G)	13.7	13.7						0.5	17.5			
16 ×16.5	17.5	17.5							17.0			1-3
16 ×16.5(G)	17.5	17.5			28				17.5	44.0		
16 ×21.5	17.5	17.5		20.2					23.0			
18 ×16.5	19.5	19.5			22				17.5			
18 ×16.5(G)	19.6	19.6			32				17.5			
18 ×21.5	19.5	19.5							23.0			
Tol.	± 0.2	± 0.2	+0.1/-0	± 0.1	± 0.1	± 0.1	± 0.1	± 0.1	± 0.2	± 0.3	± 0.15	

LELON ELECTRONICS CORP. PAC-SMD

## 2. Reel Package

Fig. 2-1






Fig. 2-2 Reel Polarity



Case size	3 ~ 4 ¢	5φ	$6.3\phi$	8 <b>¢</b> ×6.5	8 <i>φ</i> ×10	10 <i>φ</i>	12.5 <i>ϕ</i>	16 ~ 18 φ
W	14	14	18	18	26	26	34	46
Α	380	380	380	380	380	380	380	380
t	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0

## 3. Packing specification

Fig. 3-1 Carrier Tape



## Unit: pcs

Case size	Q'ty / Reel	Q'ty / Box
3φ	2,000	20,000
$4\phi$	2,000	20,000
5φ	1,000	10,000
$6.3\phi$	1,000	10,000
8 <b>¢ ×</b> 6.5	1,000	10,000
8 <b>¢</b> ×10L	500	5,000
10 φ ×7.7 ~ 10L	500	5,000
10 φ ×12.5L	400	4,000
12.5 φ ×13.5L	200	1,600
12.5 φ ×16L	200	1,600
16 <b>¢</b> ×16.5L	200	1,600
16 φ ×21.5L	100	800
18 <b>¢</b> ×16.5L	150	1,200
18 <b>¢</b> ×21.5L	100	800


Unit: mm

Case size	3 ~ 4 ¢	5φ	$6.3\phi$	$8 \phi \times 6.5$	8 <b>0</b> × 10	10 <i>ϕ</i>	12.5 ¢	16 ~ 18 φ
Н	210	210	250	250	330	330	330	425
W, L	395	395	395	395	395	395	395	395


Ver. 12 -2-

LELON ELECTRONICS CORP. PAC-SMD

Fig. 3-2 Label




## 4. Chip Tray



Dimension and	d packa	ge quai	ntity		Unit: mm			
Case size	Case size W1 H H1 Q'ty / Tray							
12.5 φ ×13.5L	284	21	18.5	120	600			
12.5 φ ×16L	284	21	18.5	120	600			
16 <i>ф</i> ×16.5L	284	28	24.0	80	400			
16 φ ×21.5L	284	28	24.0	80	400			
18 <b>¢</b> ×16.5L	284	28	24.0	60	300			
18 <b>¢</b> ×21.5L	284	28	24.0	60	300			


## 5. Sealing Tape Reel Strength

- 5.1 Peel angle: 165 to 180 ℃ refered to the surface on which the tape is glued.
- 5.2 Peel speed: 300mm per minutes
- 5.3 The peel strength must be  $0.1 \sim 0.7N$  under these conditions.



## 6. Packing Method

- 6.1 The leader length of the tape shall not be less than 400 mm including 10 or more embossed sections in which no parts are contained.
- 6.2 The winding core is provided with an over 160mm long empty section; punched carrier is only suitable for  $\phi$  D  $\leq$  5 mm.



7. Other: Specifications stated above is in accordance with JIS C 0806-3.

Ver. 12 -3-

## ${\tt LELON\ ELECTRONICS\ CORP.}$

## Endurance characteristic:

No.	Item		Condition	S			Specification				
1	Rotational Temperature Test						Capacitance change	Within ±20% of initial value.			
	1030		rated temperature± rated temperature±		-		Tanδ	Less than 200% of specified value			
		Max. transfe	rated temperature±3 er time: 1min o the step1 to step2			Ocycles	Leakage Current	Within specified value			
				•		,	ESR	Less than 200% of specified value			
							Physical	No broken and undamaged			
2	High Temperature	of rated ripp	shall be placed in o			ication	Capacitance change	Within ±30% of initial value			
	Endurance Life	at 105°C.	apacitor shall be sub	niactad t	n etar	ndard	Tanδ	Less than 200% of specified value			
		atmospheri	c conditions for 4 ho				Leakage Current	Within specified value			
		measureme	ents shall be made.				ESR	Less than 200% of specified value			
							Physical	No broken and undamaged			
3	High Temperature	working vol	+48 / -0 hours test a tage. And then the o	capacito	r shal	I	Capacitance change	Within ±30% of initial value			
	Shelf Life Test		d to standard atmos				Tanδ	Less than 200% of specified value			
		for 4 nours,	after which measur	ements	snali	be made.	Leakage Current	Within specified value			
							ESR	Less than 200% of specified value			
							Physical	No broken and undamaged			
4	Un-biased Humidity		shall be exposed fo sphere of 85%±5%				Capacitance change	Within ±30% of initial value.			
			n the capacitor shall be subjected to standard					Less than 200% of specified value			
			c conditions for 4 ho ents shall be made.	ours, afte	er whi	ch	Leakage Current	Within specified value			
							ESR	Less than 200% of specified value			
							Physical	No broken and undamaged			
5.	Vibration Test						Capacitance change	Within ±10% of initial value			
			or is placed in the Pong the acceleration (				Tanδ	Within specified value			
		2000Hz) a	ccording to the test three directions (X-	conditio			Leakage Current	Within specified value			
			(	- –/-			ESR	Within specified value			
	Danistana ta	ID D-fl					Physical	No broken and undamaged			
6.	Resistance to Soldering Heat	IR Reflow		t3 <sub> -</sub>			Capacitance change	Within ±10% of initial value.			
	Test	Т3		7			Tanδ	Within specified value			
		Temperature(C)					Leakage Current	Within specified value			
		Tem	t1	t2			ESR	Within specified value  No broken and undamaged			
							Physical	No broken and undamaged			
					ne(sec)						
		Preheat	Temp.(T1~T2,°C)	1	50 ~ 1	80					
			Time(t1)(Max,secs)	000	120	000					
		Duration	Temp. (T3,°C) Time(t2)(Max,secs)	200 70	217 50	230 40					
			Time(t2)(Max,secs) Temp. (T4,°C)	250	30	260					
		Peak	Time (t3,secs) 5								
			Time (t3,secs) 5  Reflow cycles 2 1			1					
			ntact our represent		our co						
		higher.	•	·							
			sure that the capac			25°C\					
		_	to the room temp second reflow.	erature (	(ວ (~	<b>35</b> ()					
		* Consult wi	th us when performi	ng reflo	w pro	file in					
		IPC / JEDI	EC (J-STD-020)								

No.	Item	Conditions		Specification			
7.	Biased Humidity	Capacitors shall be rated working voltage for 2000	Capacitance change	Within ±30% of initial value.			
		+48/-0 hrs in an atmosphere of 85%±5% R.H.	Tanδ	Less than 200% of specified value			
		at $85\pm3^{\circ}$ C. And then the capacitor shall be subjected to standard	Leakage Current	Within specified value			
		atmospheric conditions for 4 hours, after which measurements shall be made.	ESR	Less than 200% of specified value			
			Physical	No broken and undamaged			
8	Surge Voltage Test	The capacitor shall be subjected to 1000 cycles at 15 ~35 $^{\circ}$ C . Protective series resistor a 1K $\Omega$ each	Capacitance change	Within ±20% of initial value.			
		consisting of a charge period of 30±5 seconds, followed by discharge period of approximately 5.5	Tanδ Leakage	Within specified value			
		minutes.	Current	Within specified value			
			ESR	Less than 200% of specified value			
		Applying voltage:	Physical	No broken and undamaged			
		Rated Voltage(V) 16 20 25 35 50	63 80				
		Surge Voltage(V) 18.4 23.0 28.8 40.3 57.5	+ + + - + - + - + - + - + - + - + - + -				
		21.02 1.05(1) 1.01 2.00 2.00 1.010 01.0					
9.	Board Flex Test	Capacitor is placed in the PCB and pressed to	Capacitance change	Within ±10% of initial value.			
		deviate from Original fulcrum less than 2mm for	Tanδ	Within specified value			
		60 (+5) s.	Leakage Current	Within specified value			
		Pressure rod	ESR	Within specified value			
		R230	Physical	No broken and undamaged			
		Board					
		R5 / 1510 / 1510					
		45±2 45±2					
10.	Terminal Strength	Test condition: Capacitor is placed in the PCB by solder paste and do high temperature test (Reflow)	Capacitance change	Within ±10% of initial value.			
	Test	2 twice to endurance the power of 1.8kg for 60S,no dropping condition.	Tanδ	Within specified value			
		dropping condition.	Leakage Current	Within specified value			
			Physical	No broken and undamaged			
11	Physical Dimension		Within specifie	d value			
12.	Mechanical Shock	Capacitor is placed in the PCB and fixed .Setting the	Capacitance change	Within ±10% of initial value.			
		acceleration (100g)and time(6ms) according to the test condition ,shock 6 times	Tanδ	Within specified value			
		from three directions (X-Y-Z).	Leakage Current	Within specified value			
			ESR	Within specified value			
			Physical	No broken and undamaged			
13	Resistance To Solvents	Step 1:Put the capacitor into IPA(25±5°C); Step 2:the dipping time is 3+0.5/-0 minutes; Step 3:Brush the capacitor for 10 times; Conduct the steps 1~3 for 3 cycles.	The print cann	not fall off or be obscure			
14.	Electrical Characterization	, , , , , , , , , , , , , , , , , , ,					

LEL(	ON ELECTRONICS	SCORP	<u>.</u>								HBV	-APF	₹-03	
No.	Item		Conditions				S	Specifi	cation	)				
15.	Characteristics at				(1)Step.2 Ir	mpedan	nce R	atio (a	at 100	kHz)				
	High and Low	Step	Temperature (°C)	Time(min)	R.V(V.D.C)		16	25	35	50	63	80	$\neg$	
	Temperature	1	20±2	,	Z(-25°C/Z(2		1.5	1.5	1.5	1.5	1.5	1.5		
		2	-25±3, -55±3	30	Z(-55°C/Z(2		2.0	2.0	2.0	2.0	2.0	2.0		
		3	20±2	10~15	2(33 072(2	200)	2.0	2.0	2.0	2.0	2.0	2.0		
		4	105±2	30	(2)Step 4.									
		5	20±2	10~15	(2)0100									
			1						Sp	ecifica	ition			
					Capacitano	ce chang	ge	V	Vithin ±			1		
					Tons				∧/:+hin /	value			-	
			Tanδ     Within specified value       Leakage Current     Less than 500% of specified value       Physical     No broken and undamaged											
16	Venting Test	1 Appli	achla ta tha canacitar	a with against its	200 mm and	lorgor							_	
16.	Venting Test		cable to the capacitor	s with case size i	s op mm and	larger.								
			st condition:											
			AC test: The capacitor shall be connected across a applying 50 or 60 Hz AC which is 0.7 times of											
			d voltage or 250Vrms AC whichever is the lower.  DC test: Applying inverse DC rated voltage with current to the capacitor.											
			ere case diameter: $\varphi$ D $\leq$ 22.4mm: 1 A DC max											
				22.4mm: 10 A D										
		Note:	7 - 1		• • • • • • • • • • • • • • • • • • • •									
			n the pressure relief	vent operated, the	e capacitor sh	nall avoi	id an	v dano	ger of	fire o	r explo	osion	of	
			or element(terminal ar					,	<b>J</b> -					
			n the pressure relief			voltage	appl	ied ov	er 30	minu	tes, th	e tes	t is	
			red to be passed.											
17.	Solderability Test		oility test 1:											
		Pre-cond												
		execution	n according to RDD03		Test Method	l), item 4	4.4.2	-						
			1 (chart 3)											
			ath temperature: 235:	<b>±5</b> ℃										
		Duration	:5+0/-0.5s											
		0	""											
			oility test 2:	oording to DDD0	202 (Saldaral	hility To	oot		Cn io	moro	than (	)E0/	in tha	
		Pre-cond	ditioning: execution ac	n 4.4.2-1 (chart 3		Dility 16	ะรเ		Sn is surfac				ın tne	
		Solder h	netriode), item eath temperature: 215		)				Suriac	e or t	CIIIIII	aı		
			: 5+0/-0.5s	±3 C										
		Duration	. 570/-0.55											
		Solderah	oility test 3:											
			ditioning: execution ac	cording to RDD0	302 (Solderal	bilitv Te	est							
				n 4.4.2-1 (chart 3)		٠, ٠								
		Solder b	ath temperature:260		•									
		Duration	-											
18.	Coating Case	The cold	or of coating case will	turn light khaki fr	om colorless	with lor	ng du	ration	in hig	h ten	nperat	ure.		
			Should there is any concern with the color changing of coating case, please consult with us.											
19.	Land Pattern	Recommended pad pattern and size												
						Case siz	ze			d size				
				× )		2400 012		G	,	Υ	Χ			
			G   -			5φ		1.4	3	.0	1.6			
						6.3φ		1.9	.3	.5	1.6			
				<i>                                      </i>		8φ		3.0		.5	2.5			
												-		
				/ [777] <b>-</b>		10φ		4.0	4	.0	2.5			
			L	/ []: pad										

## Precautions and Guidelines for Aluminum Electrolytic Capacitors

# 1. Guidelines for Circuit Design (General / Application guidelines for using electrolytic capacitors)

Selecting of a right capacitor is a key to a good circuit design.

#### (1) Polarity

Most of the aluminum electrolytic capacitors are polarized. Therefore, they must be installed with the correct polarity. Usage in the reverse polarity results into a short-circuit condition that may damage or even explode the capacitor. In addition, it may influence circuit functionality. A bi-polar electrolytic capacitor should be installed when polarity across a capacitor is unstable / reversible. It should be, however, noted that usage of both polar and bi-polar capacitors are limited to DC applications. They must NOT be used for AC application.

#### (2) Operating Voltage

Applied DC voltage must not exceed rated voltage of the capacitor. Applying higher voltage than its rated voltage across a capacitor terminals cause overheating due to higher leakage currents and capacitor dielectric/insulation deterioration that will ultimately affect a capacitor's performance. The device, however, is capable of working under short-time transient voltages such as DC transients and peak AC ripples. Reverse voltages higher than 1 Volt within a specified temperature limit or AC voltages are not permissible. Overall, using capacitors at recommended operating voltages can prolong its lifespan. Note that the result of DC voltage overlapped with peak ripple voltage should not exceed rated voltage.

#### (3) Ripple Current

One of the key functions of any capacitor is removal of the ripple current i.e. the RMS value of AC flowing through a capacitor. But, a ripple current higher than rated ripple current will drop resultant capacitance, cause undue internal heating and thus reduces life span of the capacitor. In extreme cases, internal high temperature will cause the pressure relief vent to operate while destroying the device. Overall, it is important to note that an electrolytic capacitor must be used within a permissible range of ripple current. Indicators like temperature coefficient of allowable ripple current are generally used to determine life expectancy of the capacitor, but to avoid related complex calculations and for the sake of simplicity, we haven't provided temperature coefficient in the catalogue. But it offers key indicators like maximum operating temperature for calculation of life expectancy at a given temperature.

## (4) Operating Temperature

Capacitors should be used within a permissible range of operating temperatures. Using capacitor at a higher temperature than maximum rated temperature will considerably shorten its life. In the worst-case scenario, high temperature can cause pressure relief vent to operate and the device will get destroyed. Using capacitors at an ambient room temperature assure their longer life.

#### (5) Leakage Current

Leakage current flows through a capacitor when DC voltage is applied across it. Leakage current varies with changes in ambient temperature and applied DC voltage level and its time of application. Overvoltage situation, presence of moisture, and thermal stresses, especially occurring during the soldering process can enhance leakage current. Initial leakage current is usually higher and does not decrease until voltage is applied for a certain period of time. It is recommended to keep initial leakage current within specified levels.

## (6) Charge and Discharge

Regular electrolytic capacitors are not suitable for rapid charging/discharging circuits. Such usage may either cause reduction in overall capacitance or damage due to overheating. Lelon provides special assistance for selecting appropriate capacitors for rapid charging/discharging circuits.

## (7) Surge Voltage

The Surge voltage rating is referred as the maximum DC overvoltage that may be applied to an electrolytic capacitor for a short time interval of 30 seconds at infrequent time intervals not exceeding 5.5minutes with a limiting resistance of  $1k\Omega$ . Unless otherwise described on the catalogue or product specifications, please do not apply a voltage exceeding the capacitor's voltage rating. The rated surge voltages corresponding to rated voltages of electrolytic capacitors are presented as follows:

Rated Voltage(V)	4	6.3	10	16	25	35	50
Surge Voltage(V)	4.6	7.3	11.5	18.4	28.8	40.3	57.5
Rated Voltage(V)	63	80	100	160	200	250	315
Surge Voltage(V)	72.5	92	115	184	230	288	347
							1
Rated Voltage(V)	350	400	420	450	500	525	
Surge Voltage(V)	385	440	462	495	550	578	

#### (8) Condition of Use

The capacitors shall NOT be exposed to:

- (a) Fluids including water, saltwater spray, oil, fumes, highly humid or condensed climates, etc.
- (b) Ambient conditions containing hazardous gases/fumes like hydrogen sulfide, sulfurous acid, nitrous acid, chlorine or bromine gas, ammonia, etc.
- (c) Exposed to ozone, ultraviolet rays and radiation.
- (d) Severe vibrations or physical shocks that exceeds the specifications mentioned in this catalogue.

## (9) Circuit Design Consideration

- (a) Please ensure whether application, operating and mounting conditions satisfy the conditions specified in the catalog before installation of a capacitor. Please consult Lelon, if any of the conditions are beyond the conditions specified in the catalog.
- (b) Heat-generating components or heat sinks should not be placed closer to Aluminum electrolytic capacitors on the PCB to avoid their premature failure. A cooling system is recommended to improve their reliable working.
- (c) Electrical characteristics and performance of aluminum electrolytic capacitors are affected by variation of applied voltage, ripple current, ripple frequency and operating temperature. Therefore, these parameters shall not exceed specified values in the catalog.
- (d) Aluminum capacitors may be connected in the parallel fashion for increasing total capacitance and/or for achieving higher ripple current capability. But, such design may cause unequal current flow through each of the capacitors due to differences in their impedances.
- (e) When two or more capacitors are connected in series, voltage across each capacitor may differ and fall below the applied voltage. A resistor should be placed across each capacitor so as to match applied voltage with voltage across a capacitor.
- (f) Please consult Lelon while selecting a capacitor for highfrequency switching circuit or a circuit that undergoes rapid charging/ discharging
- (g) Standard outer sleeve of the capacitor is not a perfect electrical insulator therefore is unsuitable for the applications that requires perfect electrical insulation. Please consult Lelon, if your application requires perfect electrical insulation.
- (h) Tilting or twisting capacitor body is not recommended once it is soldered to the PCB.

## 2. Caution for Assembling Capacitors

#### (1) Mounting

(a) Aluminum electrolytic capacitors are not recommended to reuse in other circuits once they are mounted and powered in a circuit.

- (b) Aluminum electrolytic capacitors may hold static charge between its anode and cathode, which is recommended to be discharged through a 1kΩ resistor before re-use.
- (c) A long storage of capacitors may result into its insulation deterioration. This can lead to a high leakage current when voltage is applied that may damage the capacitor. Capacitors following a long storage period must undergo voltage treatment/re-forming.

Capacitors are charged by applying rated DC voltage through a resistor of  $1k\Omega$  in series at least for an hour. It is recommended to increase applied voltage gradually using a voltage regulator unit once capacitors are assembled on the board. The charging should be followed by discharging through a  $1K\Omega$  resistor.

- (d) Please check capacitor rated voltage before mounting.
- (e) Please check capacitor polarity before mounting.
- (f) Please don't drop capacitor on the floor / hard object.
- (g) Please don't deform the capacitor during installation.
- (h) Please confirm whether the lead spacing of the capacitors match with its pad spacing / footprint on PCB prior to installation.
- Please avoid excessive mechanical shocks to capacitor during the auto-insertion process, inspection or centering operations.
- (j) Please don't place any wiring or circuit over the capacitor's pressure relief vent. The pressure relief vent may fail to open if adequate clearance space is not provided. Following table shows minimum clearance space required for different case diameters.

Case Diameter	φ6.3 ~ φ16	φ 18 ~ φ 35	$\phi$ 40 or above
Clearance (min)	2 mm	3 mm	5 mm


#### (2) Soldering


- (a) Please confirm that soldering conditions, especially temperature and contact time are within our specifications. Dip or flow soldering temperature should be limited at 260 ± 5°C for 10 ± 1 sec while manual soldering using soldering iron should be limited at 350 ± 5°C for 3 +1/-0 seconds. Please do not dip capacitor body into molten solder. A capacitor's life will be negatively affected if these conditions are violated.
- (b) Storage of capacitors in *high humidity* conditions is likely to *affect* the *solder-ability of lead wires and terminals*.

- (c) Reflow soldering should NOLY be used for SMD type capacitors. The temperature and duration shall not exceed the specified temperature and duration in the specification. If the temperature or duration is higher than the value specified, please consult Lelon before usage.
- (d) Standard aluminum electrolytic capacitors are not designed to withstand multiple reflow processes. Please consult Lelon if repeated reflowing is unavoidable.
- (e) Incorrect mounting on PCB with improper external strength applied on its lead wires or capacitor body after soldering may damage a capacitor's internal structure, cause short circuit, or lead to high leakage current issues. Do not bend or twist the capacitor body after soldering. Referring to the drawings below only case (i) is recommended.
  - (i) Correct soldering
  - (ii) Hole-to-hole spacing on PCB differs from the lead space of lead wires.
  - (iii) Lead wires are bent after soldering.
  - (iv) Capacitor body doesn't stand vertical on PCB after soldering.

#### (3) Cleaning Circuit Boards after Soldering

- (a) Following chemicals are not recommended for cleaning: Solvent containing halogen ions, Alkaline solvent, Xylene, Acetone, Terpene, petro-based solvent.
- (b) Recommended cleaning conditions: Fatty-alcohol - Pine Alpha ST-100S, Clean Through-750H and IPA (isopropyl alcohol) are examples of the most acceptable cleaning agents. Temperature of the cleaning agent must not exceed 60°C. Flux content in the cleaning agents should be limited to 2 Wt. %. Overall length of cleaning process (e.g., immersion, ultrasonic or other) shall be within 5 minutes (5 ~ 7mm height within 3 minutes). CFC substitute cleaning agents such as AK225AES can also be used for cleaning. In this case, its temperature shall not exceed 40 C and cleaning process (e.g., immersion, ultrasonic or other) shall be completed within 2 ~ 3 minutes. After cleaning capacitors should be dried with hot air for at least 10 minutes along with the PCB. Temperature of hot air shall not exceed maximum category temperature of the capacitor. Insufficient drying may cause appearance defects, sleeve shrinkage, and bottom-plate bulging. However, usage of this CFC substitute must completely regulated for protection of environment.





#### 3. Maintenance Inspection

Periodical inspection of aluminum capacitors is absolutely necessary, especially when they are used with industrial equipment. The following items should be checked:

- (1) Appearance: Bloated, vent operated, leaked, etc.
- (2) Electrical characteristic: Capacitance, Tanδ, leakage current, and other specified items listed in specification.

Lelon recommend replacing the capacitors if any of the abovementioned items fail to meet specifications.

#### 4. Storage

- (1) The most suitable conditions for aluminum capacitor storage are 5 °C ~ 35°C and indoor relative humidity less than 75%. High temperature and/or humidity storage is detrimental to the capacitors.
- (2) Capacitors shall not be stored in wet or damp atmospheres containing water, brine, fumes or oil.
- (3) Capacitors storage area shall neither be exposed to hazardous gases such as hydrogen sulfide, sulfurous acid, nitrous acid, chlorine, ammonium, etc. nor to acidic or alkaline solutions.
- (4) Capacitors shall not be exposed to ozone, ultraviolet rays or radiation.

#### 5. Estimation of life time

$$L_r = L_0 \times 2^{\frac{T_{0\max} - T_{r\max}}{10}}$$

L<sub>r</sub>: Estimated lifetime (hours)

L<sub>0</sub>: Base lifetime specified at maximum operating temperature with applied the DC voltage and the ripple current (hours)

T<sub>0 max</sub>: The core temperature that rated ripple current applied at maximum operating temperature.

 $T_{r\,\text{max}}\!\!:$  The core temperature that applied actual ripple current at ambient temperature.

#### 6. Disposal

Please consult with a local industrial waste disposal specialist when disposing of aluminum electrolytic capacitors

#### 7. Environmental Consideration

Lelon already have received ISO 14000 certificate. Cadmium (Cd), Lead (Pb), Mercury (Hg), Hexavalent Chromium (Cr<sup>+6</sup>), PBB, PBDE, DEHP, BBP, DBP and DIBP have never been using in capacitor. If you need "Halogen-free" products, please consult with us.

## 8. AEC-Q200 Compliance

Automotive Electronics Counsel (AEC) has established various electronic component qualification/reliability standards in order to serve automotive electronics industry. AEC-Q200 standard is dedicated for passive components like capacitors, inductors, etc. and is widely adopted domestically as well as internationally. Lelon offers compliant product designs and support services to satisfy customers' product requirements, including the AEC-Q200 required criteria of the reliability tests. Lelon's capacitors are professionally designed to outperform all requirements of AEC-Q200.

For further details, please refer to

IEC 60384-4- Fixed capacitors for use in electronic equipment – Part 4: Sectional specification – Aluminium electrolytic capacitors with solid (MnO<sub>2</sub>) and non-solid electrolyte (Established in January 1995, Revised in March 2007), and

EIAJ RCR-2367B- Guideline of notabilia for fixed aluminium electrolytic capacitors for use in electronic equipment [Technical Standardization Committee on Passive Components (Established in March 1995, Revised in March 2002)].