

|      |         |             |      |       |      |
|------|---------|-------------|------|-------|------|
| REV. | ECN NO. | DESCRIPTION | DRWN | APPD. | DATE |
| REV  | ECN_NO. | DESCRIPTION | DR.  | APPD. | DATE |

SPEC:  
 Current Rating: 3Amps  
 Insulator Resistance: 5000mΩ Min  
 Dielectric Withstanding: AC 500V  
 Operating Temperature: -40° to+105°  
 Contact Material: Copper alloy T=0.25  
 Insulator Material: Polyester, UL 94V-0 LCP  
 Finish :  
 Gold/tin plating on contact area  
 100μ" min. Tin Plating on soldertails  
 50μ" min. nickel under plating over all tin,  
 Max. Processing Temp:  
 230C° for 30-60seconds(260C° for 10 secinds)









Table:

| PRODUCT NO. | ITEM | PART NO.   | PART NAME  | Q' TY | Material             |
|-------------|------|------------|------------|-------|----------------------|
| ST11220101U | 1    | PS00150110 | CONTACT    | 22    | C5191R-H, GOLD FLASH |
|             | 2    | PS00165520 | BOARDLOCKS | 2     | C2680R-H, TIN 100μ"  |
|             | 3    | PP0010BK10 | HOUSING    | 1     | LCP+30%GF, BLACK     |
| ST11220601U | 1    | PS00150610 | CONTACT    | 22    | C5191R-H, GOLD 15μ"  |
| ST11220201U | 1    | PS00150210 | CONTACT    | 22    | C5191R-H, GOLD 30μ"  |

|   |                |                 |               |                    |   |
|---|----------------|-----------------|---------------|--------------------|---|
| UNITS<br>mm   | SCALE<br>SCALE | REV.<br>REV.    | SHEET<br>PAGE | L&X 深圳市连欣科技有限公司    |   |
| DATE<br>D_DATE  |                |                 |               |                    |   |
| GENERAL<br>TOLERANCE<br>0.<br>0.0<br>0.00<br>0°<br>0.0° |                | DR.<br>DESIGNER |               | MATERIAL           |   |
|   |                | CHK.            |               | FINISH             |   |
|   |                | APPD.           |               | DWG.NO.<br>DWG_NO. | C |