







# 客户图

REV.	ECN NO.	DESCRIPTION	DRAW	CHECK	APPL.	DATE
A0	N/A	NEW	DEAN SHEN	✓	JASON	2014.10.20
A1		1. 在接触片密客戶要求修改 2. 增加气孔	DEAN SHEN	✓	JASON	2015.01.13



PCB Layout

SPEC:  
 Current Rating: 3Amps  
 Insulator Resistance: 5000mΩ Min  
 Dielectric Withstanding: AC 500V  
 Operating Temperature: -40° to+105°  
 Contact Material: Copper alloy T=0.30  
 Insulator Material: Polyester, UL 94V-0  
 Finish :  
 Gold/tin plating on contact area  
 100u" min. Tin-lead Plating on soldertails  
 50u" min.nickel under plating over all tin,  
 Max.Processing Temp:  
 230C° for 30-60seconds(260C° for 10 secinds)

ITEM	NAME	Q'TY	MATERIAL / PLATING
D	PAD	2	C2680R-H T=0.30 Contact Plating Au,Solder Area Bright Sn
C	CONTACT	7	C2680R-H T=0.25 Contact Plating Au,Solder Area Bright Sn
B	CONTACT	15	C2680R-H T=0.25 Contact Plating Au,Solder Area Bright Sn
A	HOUSING	1	LCP +30%G.F. BLACK UL94V-0

QUALITY SYMBOLS

GENERAL TOLERANCES (UNLESS SPECIFIED)	MM	INCH
ANGULAR ±1°	±0.35	±
	±0.25	±
	±0.15	±

DRAWN BY DATE  
 Dean Oct.20.2014

CHECKED BY DATE  
 Dean Oct.20.2014

APPROVED BY DATE

TITLE: SAT A 7+15P 公座类板1.0mm (七孔)  
 THIRD ANGLE PROJECTION  
 CUSTOMER COPY  
 PART NO. XJTS-2210-012  
 DWG NO.  
 SHEET NO. 1/1

深圳市连欣科技有限公司