



Features

- ◆ 650V, 7A, $R_{DS(ON)}$ (Typ.) = 0.58Ω@ V_{GS} = 10V.
- ◆ CRM(CQ) Super_Junction technology
- ◆ Much lower $R_{on} \cdot A$ performance for On-state efficiency
- ◆ Much lower FOM for fast switching efficiency



Application

- ◆ Charger
- ◆ Power Supply
- ◆ LED/LCD/PDP TV and monitor Lighting
- ◆ Solar/Renewable/UPS-Micro Inverter System

Absolute Maximum Ratings $T_c = 25^\circ C$ unless otherwise noted

Symbol	Parameter	Limit	Unit
		TO-252	
V_{DS}	Drain-Source Voltage ^a	650	V
V_{GS}	Gate-Source Voltage	± 30	V
I_D	Drain Current-Continuous, $T_c = 25^\circ C$	7	A
	Drain Current-Continuous, $T_c = 100^\circ C$	5	A
I_{DM}	Drain Current-Pulsed ^b	28	A
P_D	Maximum Power Dissipation @ $T_J = 25^\circ C$	75	W
EAS	Single Pulsed Avalanche Energy ^d	245	mJ
T_J , T_{STG}	Operating and Store Temperature Range	-55 to 150	$^\circ C$

Thermal Characteristics

Symbol	Parameter	Value	Unit
$R_{\theta JC}$	Thermal Resistance, Junction-Case Max.	1.66	$^\circ C/W$
$R_{\theta JA}$	Thermal Resistance Junction-Ambient Max.	133	$^\circ C/W$

Electrical Characteristics $T_J = 25^\circ C$ unless otherwise noted

■ Off Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS} = 0V$, $I_D = 250\mu A$	650	-	-	V
I_{DSS}	Zero Gate Voltage Drain Current	$V_{DS} = 650V$, $V_{GS} = 0V$	-	-	1	μA
I_{GSS}	Forward Gate Body Leakage Current	$V_{DS} = 0V$, $V_{GS} = \pm 30V$	-	-	± 100	nA



MJD07N65

N-Channel Power MOSFET

■ On Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
V _{GS(th)}	Gate Threshold Voltage	V _{DS} =V _{GS} , I _D =250μA	2.5	-	4.5	V
R _{DS(on)}	Static Drain-Source On-Resistance ^c	V _{GS} = 10V, I _D =3.5A	-	0.58	0.65	Ω

■ Dynamic Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
C _{iss}	Input Capacitance	V _{DS} = 100V, V _{GS} = 0V, f = 1.0MHz	-	382	-	pF
C _{oss}	Output Capacitance		-	29	-	pF
C _{rss}	Reverse Transfer Capacitance		-	24	-	pF

■ On Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
t _{d(on)}	Turn-On Delay Time	V _{DD} = 400V, I _D =3.5A, R _G =25Ω, V _{GS} =10V	-	7.4	-	ns
t _r	Turn-On Rise Time		-	9.4	-	ns
t _{d(off)}	Turn-Off Delay Time		-	48	-	ns
t _f	Turn-Off Fall Time		-	7.5	-	ns
Q _g	Total Gate Charge	V _{DS} =480V, I _D =3.5A, V _{GS} =10V, f =1MHz	-	12.5	-	nC
Q _{gs}	Gate-Source Charge		-	2.7	-	nC
Q _{gd}	Gate-Drain Charge		-	5.2	-	nC

■ Drain-Source Diode Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
V _{SD}	Drain-Source Diode Forward Voltage	V _{GS} = 0V, I _S = 3.5A	-	0.85	1.2	V
T _{rr}	Body Diode Reverse Recovery Time	di/dt=100A/us. I _S =3.5A	-	189	-	ns
Q _{rr}	Reverse Recovery Charge		-	1500	-	nC

Notes:

- a. T_J=-55 °C to +150 °C.
- b. Repetitive rating; pulse width limited by maximum junction temperature.
- c. Pulse width≤ 300us; duty cycle≤ 2%.
- d. L=10mH, V_{DD}=50V, I_{as}=7A, R_G=25Ω Starting T_J=25 °C.




Figure 1. Typical Output Characteristics




Figure 2. Typical Transfer Characteristics




Figure 3. On- Resistance vs. Drain Current




Figure 4. Body-Diode Characteristics




Figure 5. Gate Charge Characteristics




Figure 6. Capacitance Characteristics




Figure 7. Normalized On-Resistance Variation with Temperature




Figure 8. Typical Threshold Voltage vs Junction Temperature




Figure 9. Normalized Breakdown voltage vs. Junction Temperature




Figure 10. On-Resistance vs Gate Voltage




Figure 11. Maximum Safe Operating Area




Figure 12: Normalized Maximum Transient Thermal Impedance

■ Package Information

TO-252

