


Pin No.	NAME
C1	VCC
C2	RST
C3	CLK
C4	RESERVED
C5	GND
C6	VPP
C7	I/O
C8	RESERVED

- NOTES:
- ELECTRICAL CHARACTERISTICS
    - CONTACT RESISTANCE: 60 Milliohms Max
    - INSULATION RESISTANCE: 1,000 Megohms Min.
    - DIELECTRIC WITHSTANDING VOLTAGE: 500V AC
  - FOR 1 MINUTE.
  - MECHANICAL CHARACTERISTICS
    - OPERATION TEMPERATURE RANGE: -25C~+70C
    - DURABILITY: 5000 CYCLES
  - MATERIAL:
    - HOUSING: THERMOPLASTIC, UL 94-V0
    - TERMINAL: PHOSPHOR BRONZE, T=0.15
    - SHELL: STAINLESS STEEL, T=0.15
    - FINISHED:
  - TERMINAL: NI PLATED UNDERAu PLATED ON CONTACT AREA, G/F PLATED ON SOLDERIAL
  - SHELL: NI PLATED UNDER, G/F PLATED ON SOLDERIAL



REV	变更单号 ECN NO.	变更描述 DESCRIPTION	审批人 APPROVA BY	日期 REV	图号 DRWG NO.
A	??	首次发行			
??	??	变更描述			

名称 TITLE	料号 PART NO.	规格 SPECIFICATION	比例 SCALE	第三角画法 THIRD ANGLE	原图 REV
MICRO SIM 8PIN 掀盖式H1.5MM	XDSE-0182-1508	X ± 0.25 X.X ± 0.20 X.XX ± 0.15 X.XXX ± 0.10	1:1	3	A

深圳市连欣科技有限公司  
<http://www.szliankinkeji.com/>

一般公差 GENERAL TOLERANCE	审核 APPROVED BY	比例 SCALE	单位 UNIT	图号 DRAWN BY
2011年 8月01日	Jeff	1:1	mm	Brick