



REV.	ECN NO.	DESCRIPTION	DRWN	APPD.	DATE
REV	ECN_NO.	DESCRIPTION	DR.	APPD.	DATE

SPEC:
Current Rating: 3Amps
Insulator Resistance: 5000mΩ Min
Dielectric Withstanding: AC 500V
Operating Temperature: -40° to+105°
Contact Material: Copper alloy T=0.25
Insulator Material: Polyester, UL 94V-0 LCP
Finish :
Gold/tin plating on contact area
100m" min. Tin Plating on soldertails
50m" min. nickel under plating over all tin,
Max. Processing Temp:
230C° for 30-60seconds(260C° for 10 secinds)

RECOMMEND PCB LAYOUT
PCB TOLERANCE: ±0.05

UNITS	SCALE	REV.	SHEET	深圳市连欣科技有限公司	
mm	SCALE	REV.	PAGE	TITLE	
				DATE	
GENERAL TOLERANCE				D_DATE	
0. 0.0 0.00 0. 0.0°				DR. DESIGNER	
0.0°				CHK.	
APPD.				MAT'L MATERIAL	
				PART NO. XUTS-2209-1301	
				DWG.NO. DWG_NO.	
				FINISH FINISH	
				SIZE A4	