



MPC13N65



N-Channel Power MOSFET

Features

- ◆ 650V, 13A, $R_{DS(ON)}$ (Typ.) = $0.65\Omega @ V_{GS} = 10V$.
- ◆ Low C_{rss}
- ◆ Fast Switching
- ◆ 100% Avalanche Tested

Application

- ◆ Adapter
- ◆ LCD Panel Power
- ◆ E-Bike Charger
- ◆ Switching Mode Power Supply



Absolute Maximum Ratings $T_c = 25^\circ\text{C}$ unless otherwise noted

Symbol	Parameter	Limit	Unit
V_{DS}	Drain-Source Voltage ^a	650	V
V_{GS}	Gate-Source Voltage	± 30	V
I_D	Drain Current-Continuous, $T_c = 25^\circ\text{C}$	13	A
	Drain Current-Continuous, $T_c = 100^\circ\text{C}$	7.5	A
I_{DM}	Drain Current-Pulsed ^b	48	A
P_D	Maximum Power Dissipation @ $T_J = 25^\circ\text{C}$	150	W
EAS	Single Pulsed Avalanche Energy ^d	500	mJ
T_J, T_{STG}	Operating and Store Temperature Range	-55 to 150	$^\circ\text{C}$

Thermal Characteristics

Symbol	Parameter	Value	Unit
$R_{\theta JC}$	Thermal Resistance, Junction-Case Max.	0.83	$^\circ\text{C/W}$
$R_{\theta JA}$	Thermal Resistance Junction-Ambient Max	62.5	$^\circ\text{C/W}$

Electrical Characteristics $T_J = 25^\circ\text{C}$ unless otherwise noted

Off Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS} = 0V, I_D = 250\mu\text{A}$	650	-	-	V
I_{DSS}	Zero Gate Voltage Drain Current	$V_{DS} = 650V, V_{GS} = 0V$	-	-	1	μA
I_{GSS}	Forward Gate Body Leakage Current	$V_{DS} = 0V, V_{GS} = \pm 30V$	-	-	± 100	nA

On Characteristics



MPC13N65

N-Channel Power MOSFET

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS} = V_{GS}, I_D = 250\mu A$	2	-	4	V
$R_{DS(on)}$	Static Drain-Source On-Resistance ^c	$V_{GS} = 10V, I_D = 6.5A$	-	0.65	0.80	Ω

Dynamic Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
C_{iss}	Input Capacitance	$V_{DS} = 25V,$ $V_{GS} = 0V,$ $f = 1.0MHz$	-	1780	-	pF
C_{oss}	Output Capacitance		-	162	-	pF
C_{rss}	Reverse Transfer Capacitance		-	9.6	-	pF

On Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
$t_{d(on)}$	Turn-On Delay Time	$V_{DD} = 325V, I_D = 13A,$ $R_G = 10\Omega, V_{GS} = 10V$	-	28	-	ns
t_r	Turn-On Rise Time		-	26	-	ns
$t_{d(off)}$	Turn-Off Delay Time		-	64	-	ns
t_f	Turn-Off Fall Time		-	44	-	ns
Q_g	Total Gate Charge	$V_{DS} = 520V, I_D = 13A,$ $V_{GS} = 10V$	-	40.2	-	nC
Q_{gs}	Gate-Source Charge		-	10.3	-	nC
Q_{gd}	Gate-Drain Charge		-	14.4	-	nC

Drain-Source Diode Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
I_S	Drain-Source Diode Forward Continuous Current	$V_{GS} = 0V$	-	-	12	A
I_{SM}	Maximum Pulsed Current	$V_{GS} = 0V$	-	-	48	A
V_{SD}	Drain-Source Diode Forward Voltage	$V_{GS} = 0V, I_S = 13A$	-	-	1.5	V
t_{rr}	Reverse Recovery Time	$I_S = 13A, T_j = 25^\circ C$ $dI_F/dt = 100A/\mu s,$ $V_{GS} = 0V$	-	650	-	ns
Q_{rr}	Reverse Recovery Charge		-	4.29	-	nC

Notes:

- $T_j = +25^\circ C$ to $+150^\circ C$
- Repetitive rating; pulse width limited by maximum junction temperature.
- Pulse width $\leq 300\mu s$; duty cycle $\leq 2\%$
- $L = 10mH, V_{DD} = 50V, I_{as} = 10A, R_G = 25\Omega$ Starting $T_j = 25^\circ C$




Figure 1. Maximum Safe Operating Area




Figure 2. Normalized On-Resistance Variation with Temperature




Figure 3. Gate Threshold Variation with Temperature




Figure 4. Maximum Drain Current with Case Temperature




Figure 8. Typical Drain to Source ON Resistance vs Drain Current




Figure 6. On-State Characteristics




Figure 7. Body Diode Forward Voltage Variation with Source Current




Figure 8. Transfer Characteristics Variation with Source Current




Figure 9. Capacitance Characteristics




Figure 10. Gate Charge Characteristics





Figure 11. Normalized Effective Transient Thermal Impedance With Pulse Duration

■ Package Information





MPC13N65

N-Channel Power MOSFET