




MPC16N65

N-Channel Power MOSFET

Features

- ◆ 650V, 16A, $R_{DS(ON)}$ (Typ.) = 0.45Ω@VGS = 10V.
- ◆ Low Crss
- ◆ Fast Switching
- ◆ 100% Avalanche Tested



Application

- ◆ Adapter
- ◆ Standby Power
- ◆ Switching Mode Power Supply

Absolute Maximum Ratings $T_c = 25^\circ C$ unless otherwise noted

Symbol	Parameter	Limit	Unit
V_{DS}	Drain-Source Voltage ^a	650	V
V_{GS}	Gate-Source Voltage	± 30	V
I_D	Drain Current-Continuous, $T_c = 25^\circ C$	16	A
	Drain Current-Continuous, $T_c = 100^\circ C$	10.6	A
I_{DM}	Drain Current-Pulsed ^b	64	A
P_D	Maximum Power Dissipation @ $T_j = 25^\circ C$	190	W
EAS	Single Pulsed Avalanche Energy ^d	605	mJ
T_j, T_{STG}	Operating and Store Temperature Range	-55 to 150	°C

Thermal Characteristics

Symbol	Parameter	Value	Unit
$R_{\theta J_C}$	Thermal Resistance, Junction-Case Max.	0.66	°C/W
$R_{\theta J_A}$	Thermal Resistance Junction-Ambient Max	62.5	°C/W

Electrical Characteristics $T_j = 25^\circ C$ unless otherwise noted

■ Off Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS} = 0V, I_D = 250\mu A$	650	-	-	
I_{DSS}	Zero Gate Voltage Drain Current	$V_{DS} = 650V, V_{GS} = 0V$	-	-	1	μA
I_{GSS}	Forward Gate Body Leakage Current	$V_{DS} = 0V, V_{GS} = \pm 30V$	-	-	± 100	nA



MPC16N65

N-Channel Power MOSFET

On Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
V _{GS(th)}	Gate Threshold Voltage	V _{DS} = V _{GS} , I _D = 250μA	2	-	4	V
R _{DS(on)}	Static Drain-Source On-Resistance ^c	V _{GS} = 10V, I _D = 8.0A	-	0.45	0.55	Ω

Dynamic Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
g _{fs}	Forward Transconductance ^d	V _{DS} = 15V, I _D = 8.0A V _{GS} = 25V, f = 1.0MHz		15		S
C _{iss}	Input Capacitance		-	2430	-	pF
C _{oss}	Output Capacitance		-	215	-	pF
C _{rss}	Reverse Transfer Capacitance		-	18	-	pF

On Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
t _{d(on)}	Turn-On Delay Time	V _{DD} = 325V, I _D = 16A, R _G = 25Ω, V _{GS} = 10V	-	28	-	ns
t _r	Turn-On Rise Time		-	68	-	ns
t _{d(off)}	Turn-Off Delay Time		-	142	-	ns
t _f	Turn-Off Fall Time		-	73	-	ns
Q _g	Total Gate Charge	V _{DS} = 325V, I _D = 16A, V _{GS} = 10V	-	53		nC
Q _{gs}	Gate-Source Charge		-	11	-	nC
Q _{gd}	Gate-Drain Charge		-	23	-	nC

Drain-Source Diode Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
I _s	Drain-Source Diode Forward Continuous Current	V _{GS} = 0V	-	-	16	A
I _{sM}	Maximum Pulsed Current	V _{GS} = 0V	-	-	64	A
V _{SD}	Drain-Source Diode Forward Voltage	V _{GS} = 0V, I _s = 16A	-	0.9	1.4	V

Notes:

- a. T_J=-55 °C to +150 °C
- b. Repetitive rating; pulse width limited by maximum junction temperature.
- c. Pulse width ≤ 300us; duty cycle ≤ 2%
- d. L=10mH, V_{DD}=50V, I_{as}=11.0A, RG=25 Ω Starting TJ=25 °C




Figure 1 Maximum Safe Operating Area




Figure 2 Normalized On-Resistance Variation with Temperature




Figure 3. Typical Threshold Voltage vs Junction Temperature




Figure 4. Capacitance Characteristics




Figure 5. Gate Charge Characteristics




Figure 6. On-State Characteristics




Figure 7. Typical Body Diode Transfer Characteristics




Figure 8. Typical Breakdown Voltage vs Junction Temperature




Figure 9. Normalized Effective Transient Thermal Impedance With Pulse Duration

■ Package Information

