


Features

- ◆ 650V, 7A, $R_{DS(ON)}$ (Typ.) = 1.1Ω@VGS = 10V.
- ◆ Low Crss
- ◆ Fast Switching
- ◆ 100% Avalanche Tested



Application

- ◆ Adapter
- ◆ LCD Panel Power
- ◆ E-Bike Charger
- ◆ Switching Mode Power Supply



Absolute Maximum Ratings $T_c = 25^\circ\text{C}$ unless otherwise noted

Symbol	Parameter	Limit		Unit
		TO-220F		
V_{DS}	Drain-Source Voltage ^a	650		V
V_{GS}	Gate-Source Voltage	± 30		V
I_D	Drain Current-Continuous, $T_c = 25^\circ\text{C}$	7		A
	Drain Current-Continuous, $T_c = 100^\circ\text{C}$	4		A
I_{DM}	Drain Current-Pulsed ^b	28		A
P_D	Maximum Power Dissipation @ $T_J = 25^\circ\text{C}$	35		W
EAS	Single Pulsed Avalanche Energy ^d	245		mJ
T_J, T_{STG}	Operating and Store Temperature Range	-55 to 150		°C

Thermal Characteristics

Symbol	Parameter	Value	Unit
$R_{\theta JC}$	Thermal Resistance, Junction-Case Max.	3.5	°C/W
$R_{\theta JA}$	Thermal Resistance Junction-Ambient Max.	62.5	°C/W

Electrical Characteristics $T_J = 25^\circ\text{C}$ unless otherwise noted

■ Off Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS} = 0\text{V}, I_D = 250\mu\text{A}$	650	-	-	V
I_{DSS}	Zero Gate Voltage Drain Current	$V_{DS} = 650\text{V}, V_{GS} = 0\text{V}$	-	-	1	μA
I_{GSS}	Forward Gate Body Leakage Current	$V_{DS} = 0\text{V}, V_{GS} = \pm 30\text{V}$	-	-	± 100	nA



MPF07N65

N-Channel Power MOSFET

■ On Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS}=V_{GS}$, $I_D=250\mu A$	2	-	4	V
$R_{DS(on)}$	Static Drain-Source On-Resistance ^c	$V_{GS} = 10V$, $I_D = 3.5A$	-	1.1	1.4	Ω

■ Dynamic Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
C_{iss}	Input Capacitance	$V_{DS} = 25V$, $V_{GS} = 0V$, $f = 1.0MHz$	-	1135	-	pF
C_{oss}	Output Capacitance		-	88	-	pF
C_{rss}	Reverse Transfer Capacitance		-	4.6	-	pF

■ On Characteristics







Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
$t_{d(on)}$	Turn-On Delay Time	$V_{DD} = 325V$, $I_D = 7A$, $R_G = 10\Omega$, $V_{GS} = 10V$	-	19	-	ns
t_r	Turn-On Rise Time		-	21	-	ns
$t_{d(off)}$	Turn-Off Delay Time		-	42	-	ns
t_f	Turn-Off Fall Time		-	19	-	ns
Q_g	Total Gate Charge	$V_{DS} = 520V$, $I_D = 7A$, $V_{GS} = 10V$	-	24	-	nC
Q_{gs}	Gate-Source Charge		-	5.1	-	nC
Q_{gd}	Gate-Drain Charge		-	9.5	-	nC

■ Drain-Source Diode Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
I_s	Drain-Source Diode Forward Continuous Current	$V_{GS} = 0V$	-	-	7	A
I_{SM}	Maximum Pulsed Current	$V_{GS} = 0V$	-	-	28	A
V_{SD}	Drain-Source Diode Forward Voltage	$V_{GS} = 0V$, $I_s = 7A$	-		1.4	V
T_{rr}	Body Diode Reverse Recovery Time	$di/dt = 100A/\mu s$ $I_s = 10A$, $V_{GS} = 0V$	-	370	-	ns
Q_{rr}	Reverse Recovery Charge		-	1920	-	nC

Notes:

- a. $T_J = -55^\circ C$ to $+150^\circ C$.
- b. Repetitive rating; pulse width limited by maximum junction temperature.
- c. Pulse width $\leq 300\mu s$; duty cycle $\leq 2\%$.
- d. $L = 10mH$, $V_{DD} = 50V$, $I_{as} = 7A$, $R_G = 25\Omega$ Starting $T_J = 25^\circ C$.






Figure 7. Typical Body Diode Transfer Characteristics




Figure 8. Typical Breakdown Voltage vs Junction Temperature




Figure 9. Maximum Effective Thermal Impedance , Junction to Case

■ Package Information

