EVERLIGHT

DATASHEET

GENERAL PURPOSE SOLID STATE RELAY 8PIN DIP 2-CHANNEL TYPE FORM A SSR Series



Schematic

Ö

2 0 3 8

0 7

Features

•Compact 8-pin DIP size

•Applicable for 2 Form A use as well as two independent 1 Form A use

- Controls low-level analog signals
- High sensitivity and high speed response
- •Low-level off state leakage current of max. 1uA
- Wide operating temperature range of -40°C to 85°C
- High isolation voltage between input and output (Viso = 5000 Vrms)
- UL 1577 + cUL approved (No. E214129)
- VDE approved (No. 40028391)
- SEMKO approved
- NEMKO approved
- DEMKO approved
- FIMKO approved
- CQC approved


Description

The EL840A and EL860A are solid state relays containing an AlGaAs infrared LEDs on the light emitting side (input side) optically coupled to a high voltage output detector circuit. The detector consists of a photovoltaic diode array and MOSFETs on the output side. The dual channel configuration is equivalent to 1 form A EMR. They are packaged in 8 pin DIP and available in surface mount SMD option.

Applications

- High-speed inspection machines
- •Telephones equipment
- •Computer

1



Pin Configuration 1, 3 LED Anode 2, 4 LED Cathode 8, 7, 6, 5 MOSFET

Absolute Maximum Ratings (T_A=25 °C, unless otherwise specified)

	Doromotor	Cumhal	Ratir	Rating		
	Parameter	Symbol —	EL840A	EL860A		
Input	Forward Current	IF	50		mA	
	Reverse Voltage	VR	5		V	
	Peak Forward Current*1	IFP	1		А	
	Power Dissipation	Pin	75		mW	
Output	Break Down Voltage*2	VL	400	600	V	
	Continuous Load Current* ²	۱L	120	50	mA	
	Pulse Load Current*3	LPeak	0.3	0.15	А	
	Power Dissipation	Pout	800)	mW	
Total Power Dissipation		Pτ	850	850		
Isolation Voltage*4		V _{iso}	500	Vrms		
Storage Temperature		T _{STG}	-40 to	-40 to 125		
Operating Temperature		T _{OPR}	-40 to	85	°C	
Soldering Temperature*5		TSOL	260)	٥C	

Notes:

*1. f =100Hz, Duty Cycle = 0.1%

*2. Indicate the peak AC and DC values


*3.A connection: 100ms (1 shot), V_L = DC or Peak AC

*4.AC for 1 minute, R.H. = 40 ~ 60% R.H. In this test, pins 1, 2 are shorted together, and pins 3, 4 are shorted together. *5.For 10 seconds

Electro-Optical Characteristics (T_A=25 °C)

	Parameter		Symbol	Condition	Min.	Тур.	Max.	Unit
	Forward Voltage		VF	I _F = 10mA	-	1.18	1.5	V
Input	Reverse Current		IR	$V_R = 5V$	-	-	1	μΑ
	Off State leakage Current		lleak	$I_F = 0mA$, $V_L = Max$.	-	-	1	μA
	On Resistance	EL840A	D	$I_F = 10mA$, $I_L = Max$. t = 1s	-	20	30	Ω
Output		EL860A	- R _{d(ON)}		-	40	70	
	Output	EL840A	Cout	$V_L = 0V$, f = 1MHz	-	45	-	pF
	Capacitance	EL860A			-	30	-	
	LED turn on	EL840A	F(on)	I∟= Max.		3.0	5	mA
	Current	EL860A	IF(on)		-	3.0	5	
	LED turn off	EL840A		I∟= Max.	0.4	3.0	-	mA
	current	EL860A	- I _{F(off)}		0.4	3.0	-	
	Turn On Time	EL840A	. т	$I_F = 10 \text{ mA}, I_L = \text{Max}.$	-	0.4	3	me
Transfer		EL860A	– T _{on}		-	1.4	3	ms
Characteristics		EL840A	- T _{off}	$R_L = 200\Omega$,		0.05	0.5	me
	Turn Off Time	EL860A	ιοπ			0.05	0.5	ms
	Isolation Resistance	R _{I-O}	V	I-O = 500V DC	5×10 ¹⁰		-	Ω
	Isolation Capacitance	C _{I-O}	V = 0V, f = 1MHz		1.5	-	-	pF

Turn on/Turn off Time



DATASHEET GENERAL PURPOSE SOLID STATE RELAY 8PIN DIP 2-CHANNEL TYPE FORM A SSR Series

Figure 1. Load current vs Ambient temperature Figure 2. On Resistance vs Ambient Temperature 70 200 180 I = 5mA 60 I = Max. 160 **a** ₅₀ EL860A 140 R_{DS(on)} Load current, l (mA) EL840A 120 40 On Resistance, 100 30 80 EL840A 60 EL860A 20 40 10 20 0 L 40-₀ ∟ -40 -20 0 20 40 60 80 -20 0 20 40 60 80 Ambient temperature, T_A (°C) Ambient Temperature, T_A (°C) Figure 4. Turn On Time vs LED Forward Current Figure 3. Switching Time vs Ambient Temperature 5 3.0 I_= 5mA I = Max. 2.5 l = Max. R = 200Ω 4 R = 200Ω EL860A Turn On Time, T_{on}(mS) T_{on} 2 EL840A EL860A 1 0.5 T_{of} 0.0 └─ -40 EL840A 0 L -20 0 20 40 60 80 30 40 20 10 50 Ambient Temperature, T_A (°C) LED Forward Current, I (mA) Figure 6. LED Operate on Current vs Ambient Temperature Figure 5. Turn Off Time vs LED Forward Current 0.10 I, = Max. I = Max. R = 200Ω 0.08 LED Operate on Current, I_{ron} (mA) Turn Off Time, T_{off} (mS) 0.07 EL840A EL860A EL840A 2 EL860A 0.02 0.00 0 10 20 30 50 0 40 -40 -20 20 40 60 80 0 LED Forward Current, I_c (mA)


EVERLIGHT

Typical Electro-Optical Characteristics Curves

Ambient Temperature, T_A (°C)

DATASHEET GENERAL PURPOSE SOLID STATE RELAY 8PIN DIP 2-CHANNEL TYPE FORM A SSR Series

EVERLIGHT









Figure 9. Load Voltage vs Load Current






Figure 11. Applied Voltage VS Output Capacitance Frequence:1MHz 60 40 20 EL840A EL840A

20

Applied Voltage, (V)

30

40

EL860A

10

0 L 0

Load Voltage, V_L (V)



Order Information

Part Number



Note:

- XX = Part No. (40 or 60)
- Y = Lead form option (S1, or none)
- Z = Tape and reel option (TA, TB, TU, TD or none).


V = VDE safety approved option


Option	Description	Packing quantity
None	Standard DIP-8	45 units per tube
S1 (TA)	Surface mount lead form (low profile) + TA tape & reel option	1000 units per reel
S1 (TB)	Surface mount lead form (low profile) + TB tape & reel option	1000 units per reel




Package Dimension (Dimensions in mm)


Standard DIP Type









Option S1 Type



6.60±0.30










Recommended Pad Layout for Surface Mount Leadform




Device Marking

WW

V

denotes 2 digit Week code


denotes VDE option



EVERLIGHT

 $\Phi \Phi \Phi \Phi \Phi \Phi \Phi$

Tape & Reel Packing Specifications



Direction of feed from reel

Direction of feed from reel


Г

Option TB

0

-🕁

÷



 $\diamond \phi \phi \phi \phi$


Dimension No.	A	В	Do	D1	E	F
Dimension(mm)	10.4±0.1	10.0±0.1	1.5+0.1/-0	1.5±0.25/-0	1.75±0.1	7.5±0.1
Dimension No.	Ро	P1	P2	t	W	к
Dimension(mm)	4.0±0.1	12.0±0.1	2.0±0.05	0.4±0.05	16.0±0.3/	4.5±0.1



Precautions for Use

1. Soldering Condition

1.1 (A) Maximum Body Case Temperature Profile for evaluation of Reflow Profile



Note:

Preheat

Temperature min (T_{smin}) Temperature max (T_{smax}) Time (T_{smin} to T_{smax}) (t_s) Average ramp-up rate (T_{smax} to T_p)

150 °C 200°C 60-120 seconds 3 °C/second max

Reference: IPC/JEDEC J-STD-020D

Other

Liquidus Temperature (TL) Time above Liquidus Temperature (t L) Peak Temperature (TP) Time within 5 °C of Actual Peak Temperature: TP - 5°C Ramp- Down Rate from Peak Temperature Time 25°C to peak temperature Reflow times 217 °C 60-100 sec 260°C 30 s 6°C /second max. 8 minutes max. 3 times

DISCLAIMER

- 1. Above specification may be changed without notice. EVERLIGHT will reserve authority on material changer above specification.
- 2. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
- 3. When using this product, please observe the absolute maximum ratings and the instructions for use outline these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of product which does not comply with the absolute maximum ratings and the instructions included in the specification sheets.
- 4. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in form is prohibited without the specific consent of EVERLIGHT.
- 5. This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life sa applications or any other application which can result in human injury or death. Please contact author Everlight sales agent for special application request.
- 6. Statements regarding the suitability of products for certain types of applications are based on Everlik knowledge of typical requirements that are often placed on Everlight products in generic applications. \$ statements are not binding statements about the suitability of products for a particular application. It is customer's responsibility to validate that a particular product with the properties described in the pro specification is suitable for use in a particular application. Parameters provided in datasheets ar specifications may vary in different applications and performance may vary over time. All operating parame including typical parameters, must be validated for each customer application by the customer's techn experts. Product specifications do not expand or otherwise modify Everlight's terms and conditions of purch including but not limited to the warranty expressed therein.