



MPCM301X, MPCM302X, MPCM305X Series ***SOP4, DC Input, Random-Phase Photo TRIAC Photo Coupler***

■ Features

- High isolation 3750 VRMS
- DC input with random-phase photo triac output
- Operating temperature range - 40 °C to 100 °C
- RoHS & REACH Compliance
- Halogen free
- MSL class 1
- Regulatory Approvals
 - UL - UL1577
 - VDE - EN60747-5-5(VDE0884-5)
 - CQC – GB4943.1-2022

■ Description


The MPCM301X, MPCM302X and MPCM305X series combine an AlGaAs infrared emitting diode as the emitter which is optically coupled to a monolithic silicon random-phase photo triac in a plastic SOP4 package.

With the robust coplanar double mold structure, MPCM301X, MPCM302X and MPCM305X series provide the most stable isolation feature.

■ Applications

- Solenoid/valve controls
- Lighting controls
- Motor controls
- Temperature controls
- Static AC power switches
- Solid state relays
- Interfacing microprocessors to 115 to 240VAC peripherals

■ Schematic





MPCM301X, MPCM302X, MPCM305X Series
SOP4, DC Input, Random-Phase Photo TRIAC Photo Coupler

ABSOLUTE MAXIMUM RATINGS					
PARAMETER		SYMBOL	VALUE	UNIT	NOTE
INPUT					
Forward Current		I_F	60	mA	
Reverse Voltage		V_R	6	V	
Junction Temperature		T_j	125	°C	
Input Power Dissipation		P_i	100	mW	
OUTPUT					
Off-state Output Terminal Voltage	MPCM301X	V_{DRM}	250	V	
	MPCM302X		400		
	MPCM305X		600		
Peak Repetitive Surge Current PW=100μs, 120pps		I_{TSM}	1	A	
Junction Temperature		T_j	125	°C	
Output Power Dissipation		P_o	300	mW	
COMMON					
Total Power Dissipation		P_{tot}	330	mW	
Isolation Voltage		V_{iso}	3750	Vrms	1
Operating Temperature		T_{opr}	-40~100	°C	
Storage Temperature		T_{stg}	-55~125	°C	
Soldering Temperature		T_{sol}	260	°C	2

Note 1. AC For 1 Minute, R.H. = 40 ~ 60%

Note 2. For 10 seconds



MPCM301X, MPCM302X, MPCM305X Series
SOP4, DC Input, Random-Phase Photo TRIAC Photo Coupler

ELECTRICAL OPTICAL CHARACTERISTICS at Ta=25°C							
PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION	NOTE
INPUT							
Forward Voltage	V _F	-	1.24	1.4	V	I _F =10mA	
Reverse Current	I _R	-	-	10	μA	V _R =6V	
Input Capacitance	C _{in}	-	8.5	250	pF	V=0, f=1kHz	
OUTPUT							
Peak Off-state Current, Either Direction	I _{DRM}	-	-	100	nA	V _{DRM} =Rated V _{DRM} I _F =0	3
Peak On-state Current, Either Direction	V _{TM}	-	1.58	2.5	V	I _{TM} =100mA I _F =Rated I _{FT}	
Critical Rate of Rise of Off-state Voltage	dV/dt	1000	-	-	V/μs	V _{PEAK} =Rated V _{DRM}	4
TRANSFER CHARACTERISTICS							
LED Trigger Current	MPCM3010, MPCM3021, MPCM3051	I _{FT}	-	-	15	mA	Terminal Voltage = 3V I _{TM} =100mA
	MPCM3011, MPCM3022, MPCM3052		-	-	10		
	MPCM3012, MPCM3023, MPCM3053		-	-	5		
Holding Current	I _H	-	257	-	μA		
Isolation Resistance	R _{iso}	10 ¹²	10 ¹⁴	-	Ω	DC500V, 40 ~ 60% R.H.	
Floating Capacitance	C _{io}	-	0.4	1	pF	V=0, f=1MHz	

Note3. Test voltage must be applied within dV/dt rating.

Note4. Refer to Fig.15 & Fig.16



MPCM301X, MPCM302X, MPCM305X Series

SOP4, DC Input, Random-Phase Photo TRIAC Photo Coupler

CHARACTERISTIC CURVES




Fig.1 Forward Current vs. Ambient Temperature




Fig.2 On-state Terminal Current vs. Ambient Temperature




Fig.3 Forward Current vs. Forward Voltage




Fig.4 Off-state Terminal Current vs. Ambient Temperature




Fig.5 Normalized Off-state Terminal Voltage vs. Ambient Temperature




Fig.6 Normalized Trigger Current vs. LED Trigger Pulse Width



MPCM301X, MPCM302X, MPCM305X Series

SOP4, DC Input, Random-Phase Photo TRIAC Photo Coupler

CHARACTERISTIC CURVES




Fig.7 Normalized Trigger Current vs. Ambient Temperature




Fig.8 On-state Terminal Voltage vs. Ambient Temperature




Fig.9 On-state Terminal Voltage vs. On-state Terminal Current




Fig.10 Holding Current vs. Ambient Temperature




Fig.11 Turn On Time vs. Forward Current




Fig.12 Turn On Time vs. Ambient Temperature

TEST CIRCUITS

Fig.13 Test Circuits of Turn On Time




Fig.14 Waveforms of Turn On Time




Fig.15 Test Circuits of dV/dt







Fig.16 Waveforms of dV/dt



PACKAGE DIMENSIONS (Dimensions in mm unless otherwise stated)




Recommended Solder Mask (Dimensions in mm unless otherwise stated)




CARRIER TAPE SPECIFICATIONS (Dimensions in mm unless otherwise stated)

Option T1



Option T2





MPCM301X, MPCM302X, MPCM305X Series
SOP4, DC Input, Random-Phase Photo TRIAC Photo Coupler

ORDERING AND MARKING INFORMATION

MARKING INFORMATION

	<p>MPC : Company Abbr.</p> <p>30XX : Part Number & Rank</p> <p>V : VDE Option</p> <p>Y : Fiscal Year</p> <p>A : Manufacturing Code</p> <p>WW : Work Week</p>
--	--

ORDERING INFORMATION

MPCM30XX(Z)-GV


MPC – Company Abbr.
M – Package Type: SOP4
30XX – Part Number & Rank(10/11/12/21/22/23/51/52/53)
Z – Tape and Reel Option (T1/T2)
G – Material Option (G: Green, None: Non-Green)
V – VDE Option (V or None)

PACKING QUANTITY

Option	Quantity	Quantity – Inner box	Quantity – Outer box
T1	3000 Units/Reel	3 Reels/Inner box	5 Inner box/Outer box = 45k Units
T2	3000 Units/Reel	3 Reels/Inner box	5 Inner box/Outer box = 45k Units

REFLOW INFORMATION

REFLOW PROFILE




Profile Feature	Sn-Pb Assembly Profile	Pb-Free Assembly Profile
Temperature Min. (Tsmin)	100	150°C
Temperature Max. (Tsmax)	150	200°C
Time (ts) from (Tsmin to Tsmax)	60-120 seconds	60-120 seconds
Ramp-up Rate (tL to tP)	3°C/second max.	3°C/second max.
Liquidous Temperature (TL)	183°C	217°C
Time (tL) Maintained Above (TL)	60 – 150 seconds	60 – 150 seconds
Peak Body Package Temperature	235°C +0°C / -5°C	260°C +0°C / -5°C
Time (tP) within 5°C of 260°C	20 seconds	30 seconds
Ramp-down Rate (TP to TL)	6°C/second max	6°C/second max
Time 25°C to Peak Temperature	6 minutes max.	8 minutes max.



MPCM301X, MPCM302X, MPCM305X Series
SOP4, DC Input, Random-Phase Photo TRIAC Photo Coupler

TEMPERATURE PROFILE OF SOLDERING

WAVE SOLDERING (JESD22-A111 COMPLIANT)



HAND SOLDERING BY SOLDERING IRON

Soldering Temperature	380+0/-5°C
Soldering Time	3 sec max.

- One time soldering is recommended for all soldering method.
- Do not solder more than three times for IR reflow soldering.



MPCM301X, MPCM302X, MPCM305X Series ***SOP4, DC Input, Random-Phase Photo TRIAC Photo Coupler***

DISCLAIMER

- Our company is continually improving the quality, reliability, function and design. Our company reserves the right to make changes without further notices.
- The characteristic curves shown in this datasheet are representing typical performance which are not guaranteed.
- This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or lifesaving applications or any other application which can result in human injury or death.
- Immerge unit's body in solder paste is not recommended.
- Discoloration might be occurred on the package surface after soldering, reflow or long-time use. It neither impacts the performance nor reliability.

■ Revision History

Version	Date	Subjects (major changes since last revision)
1.0	2018-12-21	Datasheet Complete
1.1	2023-07-05	Upgrade Datasheet

代理商:

安迪斯智控(深圳)有限公司

Dave Pan:18665870722

Tel: 0755-86088477

Fax: 0755-86088479

Email: Dave.pan@adstech.cn

公司地址: 深圳市南山区西丽街道九祥岭工业区5栋201





MPCM301X, MPCM302X, MPCM305X Series
SOP4, DC Input, Random-Phase Photo TRIAC Photo Coupler



Miracle Technology Co., Ltd.
美祿科技股份有限公司

經銷商授權證書

本公司特此授權美祿之經銷商
於指定授權地區進行
合約內指定產品之推廣銷售與服務

公司名稱：安迪斯智控（深圳）有限公司

營業據點：中国广东省深圳市

授權地區：中国

授權期限：2025/12/25

授權產品：GaN(氮化镓)器件/MOSFET 管/光耦合器/IGBT 器件

美祿科技股份有限公



西元 2022 年 12 月 25 日