



### Features

- ◆ 650V, 7A,  $R_{DS(ON)}$ (Typ.) = 1.15Ω@ $V_{GS}$  = 10V.
- ◆ Low Crss
- ◆ Fast Switching
- ◆ 100% Avalanche Tested



### Application

- ◆ Adapter
- ◆ LCD Panel Power
- ◆ E-Bike Charger
- ◆ Switching Mode Power Supply



### Absolute Maximum Ratings $T_c = 25^\circ C$ unless otherwise noted

Symbol	Parameter	Limit	Unit
$V_{DS}$	Drain-Source Voltage <sup>a</sup>	650	V
$V_{GS}$	Gate-Source Voltage	$\pm 30$	V
$I_D$	Drain Current-Continuous, $T_c = 25^\circ C$	7	A
	Drain Current-Continuous, $T_c = 100^\circ C$	4	A
$I_{DM}$	Drain Current-Pulsed <sup>b</sup>	28	A
$P_D$	Maximum Power Dissipation @ $T_J = 25^\circ C$	69	W
EAS	Single Pulsed Avalanche Energy <sup>d</sup>	125	mJ
$T_J, T_{STG}$	Operating and Store Temperature Range	-55 to 150	°C

### Thermal Characteristics

Symbol	Parameter	Value	Unit
$R_{\theta JC}$	Thermal Resistance, Junction-Case Max.	1.8	°C/W
$R_{\theta JA}$	Thermal Resistance Junction-Ambient Max.	60	°C/W

### Electrical Characteristics $T_J = 25^\circ C$ unless otherwise noted

#### ■ Off Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
$BV_{DSS}$	Drain-Source Breakdown Voltage	$V_{GS} = 0V, I_D = 250\mu A$	650	-	-	V
$I_{DSS}$	Zero Gate Voltage Drain Current	$V_{DS} = 650V, V_{GS} = 0V$	-	-	1	μA
$I_{GSS}$	Forward Gate Body Leakage Current	$V_{DS} = 0V, V_{GS} = \pm 30V$	-	-	$\pm 100$	nA



# MPD07N65A

## N-Channel Power MOSFET

### ■ On Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
V <sub>GS(th)</sub>	Gate Threshold Voltage	V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =250μA	2	-	4	V
R <sub>DS(on)</sub>	Static Drain-Source On-Resistance <sup>c</sup>	V <sub>GS</sub> = 10V, I <sub>D</sub> =3.5A	-	1.15	1.35	Ω

### ■ Dynamic Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
C <sub>iss</sub>	Input Capacitance	V <sub>DS</sub> = 25V, V <sub>GS</sub> = 0V, f = 1.0MHz	-	1089	-	pF
C <sub>oss</sub>	Output Capacitance		-	100	-	pF
C <sub>rss</sub>	Reverse Transfer Capacitance		-	14	-	pF

### ■ On Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
t <sub>d(on)</sub>	Turn-On Delay Time	V <sub>DD</sub> = 325V, I <sub>D</sub> =7A, R <sub>G</sub> = 10Ω, V <sub>GS</sub> =10V	-	19	-	ns
t <sub>r</sub>	Turn-On Rise Time		-	29	-	ns
t <sub>d(off)</sub>	Turn-Off Delay Time		-	78	-	ns
t <sub>f</sub>	Turn-Off Fall Time		-	35	-	ns
Q <sub>g</sub>	Total Gate Charge	V <sub>DS</sub> = 520V, I <sub>D</sub> =7A, V <sub>GS</sub> = 10V	-	27	-	nC
Q <sub>gs</sub>	Gate-Source Charge		-	6	-	nC
Q <sub>gd</sub>	Gate-Drain Charge		-	11	-	nC

### ■ Drain-Source Diode Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
I <sub>s</sub>	Drain-Source Diode Forward Continuous Current	V <sub>GS</sub> = 0V	-	-	7	A
I <sub>SM</sub>	Maximum Pulsed Current	V <sub>GS</sub> = 0V	-	-	28	A
V <sub>SD</sub>	Drain-Source Diode Forward Voltage	V <sub>GS</sub> = 0V, I <sub>s</sub> = 7A	-		1.4	V
T <sub>rr</sub>	Body Diode Reverse Recovery Time	di/dt=100A/us I <sub>s</sub> =7A,V <sub>GS</sub> =0V	-	340	-	ns
Q <sub>rr</sub>	Reverse Recovery Charge		-	2900	-	nC

Notes:

- a. T<sub>J</sub>=-55 °C to +150 °C.
- b. Repetitive rating; pulse width limited by maximum junction temperature.
- c. Pulse width≤ 300us; duty cycle≤ 2%.
- d. L=10mH, V<sub>DD</sub>=50V,I<sub>as</sub>=5A,R<sub>G</sub>=25Ω Starting T<sub>J</sub>=25 °C.

### ■ Characteristic Curve




Figure 1. Typical Output Characteristics




Figure 2. Typical Transfer Characteristics




Figure 3. On- Resistance vs. Drain Current




Figure 4. Body-Diode Characteristics




Figure 5. Gate-Charge Characteristics





Figure 6. Capacitance Characteristics

### ■ Characteristic Curve



■ Package Information

# TO-252

