




MPF10N65A

N-Channel Power MOSFET

Features

- ◆ 650V, 10A, $R_{DS(ON)}$ (Typ.) = 0.80Ω@VGS = 10V.
- ◆ Low Crss
- ◆ Fast Switching
- ◆ 100% Avalanche Tested



Application

- ◆ Adaptor
- ◆ Standby Power
- ◆ Switching power supply
- ◆ LED Power

Absolute Maximum Ratings $T_c = 25^\circ C$ unless otherwise noted

| Symbol | Parameter | Rating | Unit |
|----------------|--|-----------------|------|
| V_{DS} | Drain-Source Voltage ^a | 650 | V |
| V_{GS} | Gate-Source Voltage | ± 30 | V |
| I_D | Drain Current-Continuous, $T_c = 25^\circ C$ | 10 | A |
| | Drain Current-Continuous, $T_c = 100^\circ C$ | 6.5 | A |
| I_{DM} | Drain Current-Pulsed ^b | 40 | A |
| P_D | Maximum Power Dissipation @ $T_j = 25^\circ C$ | 40 | W |
| E_{AS} | Single Pulsed Avalanche Energy ^c | 405 | mJ |
| T_j, T_{STG} | Operating and Store Temperature Range | 150, -55 to 150 | °C |

Thermal Characteristics

| Symbol | Parameter | Value | Unit |
|-----------------|---|-------|------|
| $R_{\theta JC}$ | Thermal Resistance, Junction to Case | 3.12 | °C/W |
| $R_{\theta JA}$ | Thermal Resistance, Junction to Ambient | 62.5 | °C/W |

Electrical Characteristics $T_j = 25^\circ C$ unless otherwise noted

■ Off Characteristics

| Symbol | Parameter | Test Condition | Min. | Typ. | Max. | Unit |
|------------|-----------------------------------|---------------------------------|------|------|-----------|------|
| BV_{DSS} | Drain-Source Breakdown Voltage | $V_{GS} = 0V, I_D = 250\mu A$ | 650 | - | - | V |
| I_{DSS} | Zero Gate Voltage Drain Current | $V_{DS} = 650V, V_{GS} = 0V$ | - | - | 1 | μA |
| I_{GSS} | Forward Gate Body Leakage Current | $V_{DS} = 0V, V_{GS} = \pm 30V$ | - | - | ± 100 | nA |



MPF10N65A

N-Channel Power MOSFET

■ On Characteristics

| Symbol | Parameter | Test Condition | Min. | Typ. | Max. | Unit |
|--------------|-----------------------------------|--------------------------------------|------|------|------|----------|
| $V_{GS(th)}$ | Gate Threshold Voltage | $V_{DS} = V_{GS}$, $I_D = 250\mu A$ | 2 | - | 4 | V |
| $R_{DS(on)}$ | Static Drain-Source On-Resistance | $V_{GS} = 10V$, $I_D = 5A$ | - | 0.80 | 0.95 | Ω |

■ Dynamic Characteristics

| Symbol | Parameter | Test Condition | Min. | Typ. | Max. | Unit |
|-----------|------------------------------|---|------|------|------|------|
| C_{iss} | Input Capacitance | $V_{DS} = 25V$, $V_{GS} = 0V$, $f = 1.0MHz$ | - | 1357 | - | pF |
| C_{oss} | Output Capacitance | | - | 127 | - | pF |
| C_{rss} | Reverse Transfer Capacitance | | - | 12 | - | pF |

■ On Characteristics

| Symbol | Parameter | Test Condition | Min. | Typ. | Max. | Unit |
|--------------|---------------------|--|------|------|------|------|
| $t_{d(on)}$ | Turn-On Delay Time | $V_{DD} = 325V$, $I_D = 10A$, $V_{GS}=10V$, $R_{GEN}=25\Omega$ | - | 20 | - | ns |
| t_r | Turn-On Rise Time | | - | 13 | - | ns |
| $t_{d(off)}$ | Turn-Off Delay Time | | - | 85 | - | ns |
| t_f | Turn-Off Fall Time | | - | 26 | - | ns |
| Q_g | Total Gate Charge | $V_{DS} = 520V$, $I_D = 10A$, $V_{GS} = 10V$ | - | 34 | - | nC |
| Q_{gs} | Gate-Source Charge | | - | 6.5 | - | nC |
| Q_{gd} | Gate-Drain Charge | | - | 15.5 | - | nC |


■ Drain-Source Diode Characteristics

| Symbol | Parameter | Test Condition | Min. | Typ. | Max. | Unit |
|----------|---|---|------|------|------|---------|
| I_s | Drain-Source Diode Forward Continuous Current | $V_{GS} = 0V$ | - | - | 10 | A |
| I_{SM} | Maximum Pulsed Current | $V_{GS} = 0V$ | - | - | 40 | A |
| V_{SD} | Drain-Source Diode Forward Voltage | $V_{GS} = 0V$, $I_s = 10A$ | - | - | 1.4 | V |
| T_{rr} | Body Diode Reverse Recovery Time | $I_s=10A$, $V_{GS} = 0V$ $dI_F/dt=100A/\mu s$ | - | 320 | - | ns |
| Q_{rr} | Body Diode Reverse Recovery Charge | | - | 3.7 | - | μC |


Notes:

- $T_J = +25^\circ C$ to $+150^\circ C$
- Repetitive rating; pulse width limited by maximum junction temperature.
- $L = 10mH$, $V_{DD}=50V$, $I_{AS} = 9A$, $R_G=25\Omega$ Starting $T_J=25^\circ C$.

■ Characteristic Curve



■ Characteristic Curve



■ Package Information

