



MPW03NA5



N-Channel Power MOSFET

Features

- ◆ 1500V, 3A, $R_{DS(ON)}$ (Typ.) = $5\Omega @ V_{GS} = 10V$.
- ◆ Low ON Resistance
- ◆ Fast Switching
- ◆ Low Gate Charge
- ◆ 100% Single Pulse avalanche energy Test

Application

- ◆ Power switch circuit of adaptor and charger



Absolute Maximum Ratings $T_c = 25^\circ C$ unless otherwise noted

Symbol	Parameter	Limit	Unit
V_{DS}	Drain-Source Voltage ^a	1500	V
V_{GS}	Gate-Source Voltage	± 30	V
I_D	Drain Current-Continuous, $T_c = 25^\circ C$	3	A
	Drain Current-Continuous, $T_c = 100^\circ C$	1.8	A
I_{DM}	Drain Current-Pulsed ^b	12	A
P_D	Maximum Power Dissipation @ $T_J = 25^\circ C$	32	W
EAS	Single Pulsed Avalanche Energy ^d	245	mJ
T_J, T_{STG}	Operating and Store Temperature Range	-55 to 150	$^\circ C$

Thermal Characteristics

Symbol	Parameter	Value	Unit
$R_{\theta JC}$	Thermal Resistance, Junction-Case Max.	3.8	$^\circ C/W$
$R_{\theta JA}$	Thermal Resistance Junction-Ambient Max.	40	$^\circ C/W$

Electrical Characteristics $T_J = 25^\circ C$ unless otherwise noted

Off Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS} = 0V, I_D = 250\mu A$	1500	-	-	V
I_{DSS}	Zero Gate Voltage Drain Current	$V_{DS} = 1500V$ $V_{GS} = 0V$	-	-	1	μA
I_{GSS}	Forward Gate Body Leakage Current	$V_{DS} = 0V, V_{GS} = \pm 30V$	-	-	± 100	nA



MPW03NA5

N-Channel Power MOSFET

On Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS} = V_{GS}, I_D = 250\mu A$	3	-	5	V
$R_{DS(on)}$	Static Drain-Source On-Resistance ^c	$V_{GS} = 10V, I_D = 1.5A$	-	5.0	6.5	Ω

Dynamic Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
C_{iss}	Input Capacitance	$V_{DS} = 25V,$ $V_{GS} = 0V,$ $f = 1.0MHz$	-	2036	-	pF
C_{oss}	Output Capacitance		-	98	-	pF
C_{rss}	Reverse Transfer Capacitance		-	12.8	-	pF

On Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
$t_{d(on)}$	Turn-On Delay Time	$V_{DD} = 750V, I_D = 3A,$ $R_G = 10\Omega,$	-	35.8	-	ns
t_r	Turn-On Rise Time		-	19.4	-	ns
$t_{d(off)}$	Turn-Off Delay Time		-	56	-	ns
t_f	Turn-Off Fall Time		-	31.2	-	ns
Q_g	Total Gate Charge	$V_{DD} = 750V, I_D = 3A,$ $V_{GS} = 10V$	-	37.6	-	nC
Q_{gs}	Gate-Source Charge		-	9.9	-	nC
Q_{gd}	Gate-Drain Charge		-	14.4	-	nC

Drain-Source Diode Characteristics

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Unit
I_S	Drain-Source Diode Forward Continuous Current	$V_{GS} = 0V$	-	-	3	A
I_{SM}	Maximum Pulsed Current	$V_{GS} = 0V$	-	-	12	A
V_{SD}	Drain-Source Diode Forward Voltage	$V_{GS} = 0V, I_S = 3A$	-	-	1.5	V
t_{rr}	Reverse Recovery Time	$I_S = 3A, T_j = 25^\circ C$ $dI_F/dt = 100A/\mu s,$ $V_{GS} = 0V$	-	882	-	ns
Q_{rr}	Reverse Recovery Charge		-	6.5	-	μC

Notes:

- $T_J = +25^\circ C$ to $+150^\circ C$
- Repetitive rating; pulse width limited by maximum junction temperature.
- Pulse width $\leq 300\mu s$; duty cycle $\leq 2\%$
- $L = 10mH, V_{DD} = 50V, I_{as} = 7A, R_G = 25\Omega$ Starting $T_J = 25^\circ C$




Figure 1. Maximum Safe Operating Area




Figure 2. Normalized On-Resistance Variation with Temperature




Figure 3. Gate Threshold Variation with Temperature




Figure 4. Maximum Drain Current with Case Temperature




Figure 5. Typical Drain to Source ON Resistance vs Drain Current




Figure 6. On-State Characteristics




Figure 7. Body Diode Forward Voltage Variation with Source Current




Figure 8. Transfer Characteristics Variation with Source Current




Figure 9. Capacitance Characteristics




Figure 10. Gate Charge Characteristics




Figure 11. Maximum Continuous Drain VS Case Temperature





Figure 12. Normalized Effective Transient Thermal Impedance With Pulse Duration

■ Package Information



Symbol	单位 mm			Symbol	单位 mm		
	Min	Nom	Max		Min	Nom	Max
A	5.35	5.55	5.75	E1	9.80	10.0	10.2
A1	2.80	3.00	3.20	E2	3.80	4.00	4.20
A2	1.90	2.10	2.30	H	24.3	24.5	24.7
A3	1.00	1.20	1.40	H1	9.80	10.0	10.2
b	0.80	0.90	1.00	H2	14.3	14.5	14.7
b1	1.80	2.00	2.20	H3	18.5	19.0	19.5
b2	1.80	2.00	2.20	H4	2.00	2.20	2.40
c	0.70	0.90	1.10	H5	24.0	24.5	25.0
e	5.25	5.45	5.65	G	4.3	4.5	4.7
E	15.2	15.4	15.6	ΦP	3.30	3.50	3.70