
SLVS050D - JUNE 1976 - REVISED JANUARY 2005

- Temperature Compensated
- Programmable Output Voltage
- Low Output Resistance
- Low Output Noise
- Sink Capability up to 100 mA

description/ordering information



The TL430 is a 3-terminal adjustable shunt regulator, featuring excellent temperature stability, wide operating current range, and low output noise. The output voltage can be set by two external resistors to any desired value between 3 V and 30 V. The TL430 can replace Zener diodes in many applications, providing improved performance.

The TL430C is characterized for operation from 0°C to 70°C.

	KING	
Bulk of 1000 TL430CLP	TL430C	
0°C to 70°C TO-226 / TO-92 (LP) Reel of 2000 TL430CLPR TL4300	C	

ORDERING INFORMATION

[†] Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.

symbol





Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.



Copyright © 2005, Texas Instruments Incorporated

SLVS050D - JUNE 1976 - REVISED JANUARY 2005

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)[†]

Regulator voltage (see Note 1)	30 V
Continuous regulator current	150 mA
Package thermal impedance, θ_{JA} (see Notes 2 and 3)	140°C/W
Operating virtual junction temperature, T _J	150°C
Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds	260°C
Storage temperature range, T _{stg}	–65°C to 150°C

[†] Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- NOTES: 1. All voltage values are with respect to the anode terminal.
 - 2. Maximum power dissipation is a function of $T_J(max)$, θ_{JA} , and T_A . The maximum allowable power dissipation at any allowable ambient temperature is $P_D = (T_J(max) T_A)/\theta_{JA}$. Operating at the absolute maximum T_J of 150°C can impact reliability.
 - 3. The package thermal impedance is calculated in accordance with JESD 51-7.

recommended operating conditions

			MIN	MAX	UNIT
VZ	Regulator voltage		Vref	30	V
ΙZ	Regulator current		2	100	mA
Т _А	Operating free-air temperature range	TL430C	0	70	°C

electrical characteristics over recommended operating conditions, T_{A} = 25 $^{\circ}C$ (unless otherwise noted)

	PARAMETER	TEST	TEST CONDI	٦	UNIT			
	FARAMETER	FIGURE	TEST CONDI	MIN	TYP	MAX	UNIT	
V _{I(ref)}	Reference input voltage	1	$V_Z = V_{I(ref)}$,	I _Z = 10 mA	2.5	2.75	3	V
$\alpha V_{I(ref)}$	Temperature coefficient of reference input voltage	1	$V_Z = V_{I(ref)},$ $T_A = 0^{\circ}C \text{ to } 70^{\circ}C$	I <u>Z</u> = 10 mA,		120		ppm/°C
II(ref)	Reference input current	2	I <u>Z</u> = 10 mA, R2 = ∞	R1 = 10 kΩ,		3	10	μΑ
IZK	Regulator current near lower knee of regulation range	1	$V_Z = V_{I(ref)}$			0.5	2	mA
	Regulator current at maximum	1	$V_Z = V_{I(ref)}$		50			
lzκ	limit of regulation range	2	$V_Z = 5 V$ to 30 V,	See Note 4	100			mA
rz	Differential regulator resistance (see Note 5)	1	$V_Z = V_{I(ref)},$ $\Delta I_Z = (52 - 2) \text{ mA}$			1.5	3	Ω
	Noise voltage			V _Z = 3 V		50		
Vn		2	f = 0.1 Hz to 10 Hz	V _Z = 12 V		200		μV
				V _Z = 30 V		650		1


NOTES: 4. The average power dissipation, V_Z • I_Z • duty cycle, must not exceed the maximum continuous rating in any 10-ms interval.
 5. The regulator resistance for V_Z > V_{I(ref)}, r_z, is given by:

$$\mathbf{r_Z}' = \mathbf{r_Z} \left(1 + \frac{\mathbf{R1}}{\mathbf{R2}} \right)$$



SLVS050D - JUNE 1976 - REVISED JANUARY 2005

PARAMETER MEASUREMENT INFORMATION







Figure 1. Test Circuit for V_Z = V_{I(ref)}






SLVS050D - JUNE 1976 - REVISED JANUARY 2005



TYPICAL CHARACTERISTICS

APPLICATION INFORMATION



 $V_{O} \approx \left(1 + \frac{R1}{R2}\right) V_{I(ref)}$

Figure 5. Shunt Regulator




Figure 6. Series Regulator



SLVS050D – JUNE 1976 – REVISED JANUARY 2005

APPLICATION INFORMATION




Figure 7. Current Limiter




Figure 9. Higher-Current Applications




Figure 8. Output Control of a 3-Terminal Fixed Regulator




Figure 10. Crowbar




Figure 11. V_{CC} Monitor





PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
TL430CLP	LIFEBUY	TO-92	LP	3	1000	RoHS & Green	SN	N / A for Pkg Type	0 to 70	TL430C	
TL430CLPE3	LIFEBUY	TO-92	LP	3	1000	RoHS & Green	SN	N / A for Pkg Type	0 to 70	TL430C	

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

⁽⁶⁾ Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

GENERIC PACKAGE VIEW

TO-92 - 5.34 mm max height TRANSISTOR OUTLINE



Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.




LP0003A



PACKAGE OUTLINE

TO-92 - 5.34 mm max height

TO-92



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M. 2. This drawing is subject to change without notice.
- Lead dimensions are not controlled within this area.
 Reference JEDEC TO-226, variation AA.
- 5. Shipping method:

 - a. Straight lead option available in bulk pack only.b. Formed lead option available in tape and reel or ammo pack.
 - c. Specific products can be offered in limited combinations of shipping medium and lead options.
 - d. Consult product folder for more information on available options.



LP0003A

EXAMPLE BOARD LAYOUT

TO-92 - 5.34 mm max height

TO-92





LP0003A

TAPE SPECIFICATIONS

TO-92 - 5.34 mm max height

TO-92





IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023, Texas Instruments Incorporated