

# SN54HCT658, SN54HCT659, SN74HCT658, SN74HCT659 OCTAL BUS TRANSCEIVERS WITH PARITY

D2839, MARCH 1984 - REVISED SEPTEMBER 1987

- Inputs are TTL-Voltage Compatible
- Bus Transceivers with Inverting Outputs ('HCT658) or True Outputs ('HCT659)
- Generates a Parity Bit for A Bus and B Bus
- Easily Cascadable
- Internal Active Pull-Ups and Pull-Downs
- High-Current 3-State Outputs Can Drive Up to 15 LSTTL Loads
- Package Options Include Plastic "Small Outline" Packages, Ceramic Chip Carriers, and Standard Plastic and Ceramic 300-mil DIPs
- Dependable Texas Instruments Quality and Reliability

## description


These octal bus transceivers are designed for asynchronous, bidirectional communication between data buses. The devices transmit data from the A Bus to the B Bus or from the B Bus to the A Bus, depending on the levels at the direction control inputs, GAB and  $\bar{G}BA$ . These devices also generate parity outputs, APO and BPO, which reflect the number of high levels at the A Bus and B Bus, respectively, taking into account the parity inputs API and BPI.

The bidirectional I/O ports feature active circuits on the input stage that, when the output shared by that pin is disabled, will maintain the input in the last state taken by the output. This state will be maintained until changed by activity on the bus. The advantage of this arrangement is that when all outputs on the bus are disabled, the inputs will be prevented from floating, resulting in minimum power dissipation and minimum susceptibility to noise. This eliminates any need for external pull-up or pull-down resistors. The parity inputs API and BPI have similar circuits. For further information, see Typical Application Data in 'HC658 series data sheet.


The SN54HCT658 and SN54HCT659 are characterized for operation over the full military temperature range of  $-55^{\circ}\text{C}$  to  $125^{\circ}\text{C}$ . The SN74HCT658 and SN74HCT659 are characterized for operation from  $-40^{\circ}\text{C}$  to  $85^{\circ}\text{C}$ .

SN54HCT658, SN54HCT659 . . . JT PACKAGE  
SN74HCT658, SN74HCT659 . . . DW-OR NT PACKAGE

(TOP VIEW)



SN54HCT658, SN54HCT659 . . . FK PACKAGE  
(TOP VIEW)



NC — No internal connection

2

HCMOS Devices

**PRODUCTION DATA** documents contain information current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

Copyright © 1984, Texas Instruments Incorporated

**TEXAS  
INSTRUMENTS**

POST OFFICE BOX 655012 • DALLAS, TEXAS 75265

2-609

# SN54HCT658, SN54HCT659, SN74HCT658, SN74HCT659 OCTAL BUS TRANSCEIVERS WITH PARITY



## 2

## HCMOS Devices

FUNCTION TABLE

CONTROL INPUTS		NUMBER OF HIGH INPUTS ON A BUS AND API	NUMBER OF HIGH INPUTS ON B BUS AND BPI	OUTPUTS		OPERATION	
$\bar{G}BA$	GAB	X	0, 2, 4, 6, 8 1, 3, 5, 7, 9	APO	BPO	'HCT658	'HCT659
L	L	X	0, 2, 4, 6, 8 1, 3, 5, 7, 9	Z	H	$\bar{B}$ Data to A Bus	B Data to A Bus
H	H	0, 2, 4, 6, 8 1, 3, 5, 7, 9	X	H	Z	$\bar{A}$ Data to B Bus	A Data to B Bus
H	L	X	X	Z	Z	Isolation	Isolation
L	H	X	0, 2, 4, 6, 8 1, 3, 5, 7, 9	H			
		X	0, 2, 4, 6, 8 1, 3, 5, 7, 9	L			
		0, 2, 4, 6, 8 1, 3, 5, 7, 9	X	H		$\bar{B}$ Data to A Bus, $\bar{A}$ Data to B Bus	B Data to A Bus, A Data to B Bus


logic symbols<sup>†</sup>



<sup>†</sup>These symbols are in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

Pin numbers shown are for DW, JT, and NT packages.

**logic diagram (positive logic)**



Pin numbers shown are for DW, JT, and NT packages.

**absolute maximum ratings over operating free-air temperature range<sup>†</sup>**

Supply voltage, V <sub>CC</sub> .....	-0.5 V to 7 V
Input clamp current, I <sub>IK</sub> (V <sub>I</sub> < 0 or V <sub>I</sub> > V <sub>CC</sub> ) .....	±20 mA
Output clamp current, I <sub>OK</sub> (V <sub>O</sub> < 0 or V <sub>O</sub> > V <sub>CC</sub> ) .....	±20 mA
Continuous output current, I <sub>O</sub> (V <sub>O</sub> = 0 to V <sub>CC</sub> ) .....	±35 mA
Continuous current through V <sub>CC</sub> or GND pins .....	±70 mA
Lead temperature 1.6 mm (1/16 in) from case for 60 s: FK or JT package .....	300°C
Lead temperature 1.6 mm (1/16 in) from case for 10 s: DW or NT package .....	260°C
Storage temperature range .....	-65°C to 150°C

<sup>†</sup>Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

# SN54HCT658, SN54HCT659, SN74HCT658, SN74HCT659 OCTAL BUS TRANSCEIVERS WITH PARITY

2

**HCMOS Devices**

## recommended operating conditions

			SN54HCT658			SN74HCT658			UNIT
			SN54HCT659			SN74HCT659			
	MIN	NOM	MAX	MIN	NOM	MAX	MIN	NOM	MAX
V <sub>CC</sub> Supply voltage	4.5	5	5.5	4.5	5	5.5			V
V <sub>IH</sub> High-level input voltage	V <sub>CC</sub> = 4.5 V to 5.5 V	2		2					V
V <sub>IL</sub> Low-level input voltage	V <sub>CC</sub> = 4.5 V to 5.5 V	0	0.8	0	0	0.8	0	0.8	V
V <sub>I</sub> Input voltage		0	V <sub>CC</sub>	0	V <sub>CC</sub>		0	V <sub>CC</sub>	V
V <sub>O</sub> Output voltage		0	V <sub>CC</sub>	0	V <sub>CC</sub>		0	V <sub>CC</sub>	V
t <sub>tr</sub> Input transition (rise and fall) times		0	500	0	0	500	0	500	ns
T <sub>A</sub> Operating free-air temperature	-55	125		-40	85				°C

## electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER	TEST CONDITIONS	V <sub>CC</sub>	T <sub>A</sub> = 25°C			SN54HCT658		SN74HCT658		UNIT
			MIN	TYP	MAX	MIN	MAX	MIN	MAX	
V <sub>OH</sub>	V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> , I <sub>OH</sub> = -20 μA	4.5 V	4.4	4.499		4.4		4.4		V
V <sub>OH</sub>	All outputs except APO & BPO	V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> , I <sub>OH</sub> = -6 mA	4.5 V	3.98	4.30		3.7		3.84	
	APO and BPO	V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> , I <sub>OH</sub> = -4 mA	4.5 V	3.98	4.30		3.7		3.84	
V <sub>OL</sub>	V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> , I <sub>OL</sub> = 20 μA	4.5 V	0.001	0.1		0.1		0.1		V
V <sub>OL</sub>	All outputs except APO & BPO	V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> , I <sub>OL</sub> = 6 mA	4.5 V	0.17	0.26		0.4		0.33	
	APO and BPO	V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> , I <sub>OL</sub> = 4 mA	4.5 V	0.17	0.26		0.4		0.33	
I <sub>I</sub>	GAB, GBA, API OR BPI	V <sub>I</sub> = V <sub>CC</sub> or 0	5.5 V	±0.1	±100		±1000		±1000	nA
I <sub>OZ</sub>	A or B	V <sub>O</sub> = V <sub>CC</sub> or 0, V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>	5.5 V	±0.01	±0.5		±10		±5	μA
I <sub>CC</sub>		V <sub>I</sub> = V <sub>CC</sub> or 0, I <sub>O</sub> = 0	5.5 V		8		160		80	μA
ΔI <sub>CC</sub> †		One input at 0.5 or 2.4 V Other inputs at 0 V or V <sub>CC</sub>	5.5 V	1.4	2.4		3		2.9	mA
C <sub>i</sub> ‡			4.5 to 5.5 V		3	10		10	10	pF

†This is the increase in supply current for each input that is at one of the specified TTL voltage levels rather than 0 V or V<sub>CC</sub>.

‡This parameter, C<sub>i</sub>, does not apply to I/O ports.

**SN54HCT658, SN74HCT658**  
**OCTAL BUS TRANSCEIVERS WITH PARITY**

switching characteristics over recommended operating free-air temperature range (unless otherwise noted),  $C_L = 50 \text{ pF}$  (see Note 1)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	V <sub>CC</sub>	T <sub>A</sub> = 25°C			SN54HCT658		SN74HCT658		UNIT
				MIN	TYP	MAX	MIN	MAX	MIN	MAX	
t <sub>pd</sub>	A or B	B or A	4.5 V	15	30		45		38		ns
			5.5 V	13	27		41		34		
t <sub>pd</sub>	A or B	APO or BPO	4.5 V	23	46		69		58		ns
			5.5 V	20	41		62		52		
t <sub>pd</sub>	API or BPI	APO or BPO	4.5 V	15	31		47		39		ns
			5.5 V	14	28		42		35		
t <sub>en</sub>	GAB or $\bar{G}BA$	APO or BPO	4.5 V	24	47		71		59		ns
			5.5 V	21	42		64		53		
t <sub>dis</sub>	GAB or $\bar{G}BA$	APO or BPO	4.5 V	24	47		71		59		ns
			5.5 V	21	42		64		53		
t <sub>t</sub>		Any	4.5 V	8	12		18		15		ns
			5.5 V	7	11		16		14		

C <sub>pd</sub>	Power dissipation capacitance	No load, T <sub>A</sub> = 25°C	62 pF typ
-----------------	-------------------------------	--------------------------------	-----------

switching characteristics over recommended operating free-air temperature range (unless otherwise noted),  $C_L = 150 \text{ pF}$  (see Note 1)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	V <sub>CC</sub>	T <sub>A</sub> = 25°C			SN54HCT658		SN74HCT658		UNIT
				MIN	TYP	MAX	MIN	MAX	MIN	MAX	
t <sub>pd</sub>	A or B	B or A	4.5 V	23	47		71		59		ns
			5.5 V	21	42		64		53		
t <sub>pd</sub>	A or B	APO or BPO	4.5 V	31	63		95		79		ns
			5.5 V	28	56		85		71		
t <sub>pd</sub>	API or BPI	APO or BPO	4.5 V	24	48		73		60		ns
			5.5 V	21	43		65		54		
t <sub>en</sub>	GAB or $\bar{G}BA$	APO or BPO	4.5 V	32	64		97		80		ns
			5.5 V	28	57		87		72		
t <sub>t</sub>		Any	4.5 V	17	42		63		53		ns
			5.5 V	14	38		57		48		

NOTE 1: Load circuits and voltage waveforms are shown in Section 1.

For typical application data and a description of the unique input structure, see the 'HC658 series data sheet.

2

HCMOS Devices

TEXAS  
INSTRUMENTS

POST OFFICE BOX 655012 • DALLAS, TEXAS 75265

2-613

# SN54HCT659, SN74HCT659 OCTAL BUS TRANSCEIVERS WITH PARITY

2

HC MOS Devices

switching characteristics over recommended operating free-air temperature range (unless otherwise noted),  $C_L = 50 \text{ pF}$  (see Note 1)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	V <sub>CC</sub>	$T_A = 25^\circ\text{C}$			SN54HCT659		SN74HCT659		UNIT	
				MIN	typ	MAX	MIN	MAX	MIN	MAX		
$t_{pd}$	A or B	B or A	4.5 V		14	28		61		50	ns	
			5.5 V		12	25		42		35		
$t_{pd}$	A or B	APO or BPO	4.5 V		23	46		69		58	ns	
			5.5 V		20	41		62		52		
$t_{pd}$	API or BPI	APO or BPO	4.5 V		15	31		47		39	ns	
			5.5 V		14	28		42		35		
$t_{en}$	GAB or $\overline{\text{G}}\text{BA}$	APO or BPO	4.5 V		24	47		71		59	ns	
			5.5 V		21	42		64		53		
$t_{dis}$	GAB or $\overline{\text{G}}\text{BA}$	APO or BPO	4.5 V		24	47		71		59	ns	
			5.5 V		21	42		64		53		
$t_t$		Any	4.5 V			8	12		18		15	ns
			5.5 V			7	11		16		14	
$C_{pd}$	Power dissipation capacitance			No load, $T_A = 25^\circ\text{C}$				62 pF typ				

switching characteristics over recommended operating free-air temperature range (unless otherwise noted),  $C_L = 150 \text{ pF}$  (see Note 1)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	V <sub>CC</sub>	$T_A = 25^\circ\text{C}$			SN54HCT659		SN74HCT659		UNIT	
				MIN	typ	MAX	MIN	MAX	MIN	MAX		
$t_{pd}$	A or B	B or A	4.5 V		23	45		84		67	ns	
			5.5 V		20	40		68		56		
$t_{pd}$	A or B	APO or BPO	4.5 V		32	63		95		79	ns	
			5.5 V		28	56		85		71		
$t_{pd}$	API or BPI	APO or BPO	4.5 V		24	48		73		60	ns	
			5.5 V		21	43		65		54		
$t_{en}$	GAB or $\overline{\text{G}}\text{BA}$	APO or BPO	4.5 V		32	64		97		80	ns	
			5.5 V		29	57		87		72		
$t_t$		Any	4.5 V			21	42		63		53	ns
			5.5 V			19	38		57		48	

NOTE 1: Load circuits and voltage waveforms are shown in Section 1.

For typical application data and a description of the unique input structure, see the 'HC658 series data sheet.