

SN54HC377, SN54HC378, SN54HC379  
SN74HC377, SN74HC378, SN74HC379

## OCTAL, HEX, AND QUAD D-TYPE FLIP-FLOPS WITH CLOCK ENABLE

D2684, DECEMBER 1982—REVISED JUNE 1989

- 'HC377 and 'HC378 Contain Eight and Six Flip-Flops, Respectively, with Single-Rail Outputs
- 'HC379 Contains Four Flip-Flops with Double-Rail Outputs
- Clock Enable Latched to Avoid False Clocking
- Applications Include:  
Buffer/Storage Registers  
Shift Registers  
Pattern Generators
- Package Options Include Plastic "Small Outline" Packages, Ceramic Chip Carriers, and Standard Plastic and Ceramic 300-mil DIPs
- Dependable Texas Instruments Quality and Reliability

**description**


These circuits are positive-edge-triggered D-type flip-flops with an enable input. The 'HC377, 'HC378, and 'HC379 devices are similar to 'HC273, 'HC174, and 'HC175 respectively, but feature a latched clock enable ( $\bar{G}$ ) instead of a common clear.

Information at the D inputs meeting the setup time requirements is transferred to the Q outputs on the positive-going edge of the clock pulse if  $\bar{G}$  is low. Clock triggering occurs at a particular voltage level and is not directly related to the transition time of the positive-going pulse. When the clock input is at either the high or low level, the D input signal has no effect at the output. The circuits are designed to prevent false clocking by transitions at the  $\bar{G}$  input.

The SN54HC377, SN54HC378, and SN54HC379 are characterized for operation over the full military temperature range of  $-55^{\circ}\text{C}$  to  $125^{\circ}\text{C}$ . The SN74HC377, SN74HC378, and SN74HC379 are characterized for operation from  $-40^{\circ}\text{C}$  to  $85^{\circ}\text{C}$ .

**NOTICE**

SEE ORDER OF DATA FOR ERRATA INFORMATION




SN54HC377 . . . J PACKAGE  
SN74HC377 . . . DW OR N PACKAGE

T-46-07-09

T-46-07-10

T-46-07-11

2

SN54HC377 . . . FK PACKAGE  
(TOP VIEW)SN54HC378 . . . J PACKAGE  
SN74HC378 . . . D OR N PACKAGESN54HC378 . . . FK PACKAGE  
(TOP VIEW)

NC—No internal connection

HCMOS Devices

PRODUCTION DATA documents contain information current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

TEXAS  
INSTRUMENTS  
POST OFFICE BOX 655012 • DALLAS, TEXAS 75265


Copyright © 1989, Texas Instruments Incorporated

2-431

SN54HC377, SN54HC379, SN74HC377, SN74HC379  
OCTAL AND QUAD D-TYPE FLIP-FLOPS WITH CLOCK ENABLE

T-46-07-09


T-46-07-10

SN54HC379... J PACKAGE  
SN74HC379... D, J, OR N PACKAGE  
(TOP VIEW)

SN54HC379... FK PACKAGE


(TOP VIEW)

T-46-07-11



2

## HC377 logic symbol†



† This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.  
Pin numbers shown are for DW, J, and N packages.



FUNCTION TABLE  
(EACH FLIP-FLOP)

INPUTS		OUTPUT	
G	CLOCK	DATA	Q
H	X	X	Q <sub>0</sub>
L	↑	H	H
L	↑	L	L
X	L	X	Q <sub>0</sub>

H = high level, L = low level, X = irrelevant

NC—No internal connection

## HC377 logic diagram (positive logic)




Pin numbers shown are for DW, J, and N packages.

T-46-07-09

SN54HC378, SN54HC379, SN74HC378, SN74HC379  
HEX AND QUAD D-TYPE FLIP-FLOPS WITH CLOCK ENABLE


T-46-07-10

'HC378 logic symbol†

FUNCTION TABLE  
(EACH FLIP-FLOP)

INPUTS			OUTPUT
G	CLOCK	DATA	Q
H	X	X	Q <sub>0</sub>
L	t	H	H
L	t	L	L
X	L	X	Q <sub>0</sub>

'HC379 logic symbol†

FUNCTION TABLE  
(EACH FLIP-FLOP)

INPUTS			OUTPUTS	
G	CLOCK	DATA	Q	$\bar{Q}$
H	X	X	Q <sub>0</sub>	$\bar{Q}_0$
L	t	H	H	L
L	t	L	L	H
X	L	X	Q <sub>0</sub>	$\bar{Q}_0$

†These symbols are in accordance with ANSI/IEEE Std 91-1984  
and IEC Publication 617-12.

Pin numbers are for D, J, and N packages.

SN54HC377, SN54HC378, SN54HC379

SN74HC377, SN74HC378, SN74HC379

OCTAL, HEX, AND QUAD D-TYPE FLIP-FLOPS WITH CLOCK ENABLE

T-46-07-09

T-46-07-10

T-46-07-11

## absolute maximum ratings over operating free-air temperature range†

Supply voltage, V <sub>CC</sub> .....	-0.5 V to 7 V
Input clamp current, I <sub>IK</sub> (V <sub>I</sub> < 0 or V <sub>I</sub> > V <sub>CC</sub> ) .....	±20 mA
Output clamp current, I <sub>OK</sub> (V <sub>O</sub> < 0 or V <sub>O</sub> > V <sub>CC</sub> ) .....	±20 mA
Continuous output current, I <sub>O</sub> (V <sub>O</sub> = 0 to V <sub>CC</sub> ) .....	±25 mA
Continuous current through V <sub>CC</sub> or GND pins .....	±50 mA
Lead temperature 1.6 mm (1/16 in) from case for 60 s: FK or J package .....	300°C
Lead temperature 1.6 mm (1/16 in) from case for 10 s: D, DW, or N package .....	260°C
Storage temperature range .....	-65°C to 150°C

† Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

2

HCMOS Devices

## recommended operating conditions

		SN54HC377			SN74HC377			UNIT
		MIN	NOM	MAX	MIN	NOM	MAX	
V <sub>CC</sub>	Supply voltage	2	5	6	2	5	6	V
V <sub>IH</sub>	High-level input voltage	V <sub>CC</sub> = 2 V	1.5		1.5			
		V <sub>CC</sub> = 4.5 V	3.15		3.15			
		V <sub>CC</sub> = 6 V	4.2		4.2			
V <sub>IL</sub>	Low-level input voltage	V <sub>CC</sub> = 2 V	0	0.3	0	0.3		
		V <sub>CC</sub> = 4.5 V	0	0.9	0	0.9		
		V <sub>CC</sub> = 6 V	0	1.2	0	1.2		
V <sub>I</sub>	Input voltage		0	V <sub>CC</sub>	0	V <sub>CC</sub>		V
V <sub>O</sub>	Output voltage		0	V <sub>CC</sub>	0	V <sub>CC</sub>		V
t <sub>t</sub>	Input transition (rise and fall) times	V <sub>CC</sub> = 2 V	0	1000	0	1000		
		V <sub>CC</sub> = 4.5 V	0	500	0	500		ns
		V <sub>CC</sub> = 6 V	0	400	0	400		
T <sub>A</sub>	Operating free-air temperature		-55	125	-40	85		°C

## electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER	TEST CONDITIONS	V <sub>CC</sub>	T <sub>A</sub> = 25°C			SN54HC377			SN74HC377			UNIT
			MIN	TYP	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
V <sub>OH</sub>	V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> , I <sub>OH</sub> = -20 μA	2 V	1.9	1.998		1.9		1.9				V
		4.5 V	4.4	4.499		4.4		4.4				
		6 V	5.9	5.999		5.9		5.9				
V <sub>OL</sub>	V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> , I <sub>OL</sub> = -4 mA	4.5 V	3.98	4.30		3.7		3.84				V
		6 V	5.48	5.80		5.2		5.34				
	V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> , I <sub>OL</sub> = 20 μA	2 V	0.002	0.1		0.1		0.1				
		4.5 V	0.001	0.1		0.1		0.1				V
		6 V	0.001	0.1		0.1		0.1				
	V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> , I <sub>OL</sub> = 4 mA	4.5 V	0.17	0.26		0.4		0.33				
I <sub>I</sub>	V <sub>I</sub> = V <sub>CC</sub> or 0	6 V	0.15	0.26		0.4		0.33				nA
	V <sub>I</sub> = V <sub>CC</sub> or 0, I <sub>O</sub> = 0	6 V		8		160		80				
	C <sub>I</sub>	2 to 6 V	3	10		10		10				pF

T-46-07-09

T-46-07-10

T-46-07-11

SN54HC377, SN54HC378, SN74HC379  
SN74HC377, SN74HC378, SN74HC379

## OCTAL, HEX, AND QUAD D-TYPE FLIP-FLOPS WITH CLOCK ENABLE

timing requirements over recommended operating free-air temperature range (unless otherwise noted)

		V <sub>CC</sub>	T <sub>A</sub> = 25°C		SN54HC377		SN74HC377		UNIT		
			MIN	MAX	SN54HC378	SN74HC378	SN54HC379	SN74HC379			
f <sub>clock</sub>	Clock frequency		2 V	0	5	0	3	0	4		
			4.5 V	0	25	0	16	0	20		
			6 V	0	29	0	19	0	23		
t <sub>w</sub>	Pulse duration, CLK high or low		2 V	100	150	125	125	125	MHz		
			4.5 V	20	30	25	25	25			
			6 V	17	25	21	21	21			
t <sub>su</sub>	D	Set up time before CLK†	2 V	100	150	125	125	125	ns		
			4.5 V	20	30	25	25	25			
	G high or low		6 V	17	25	21	21	21	ns		
			2 V	100	150	125	125	125			
t <sub>h</sub>	G inactive or active, data	G inactive or active, data	4.5 V	20	30	25	25	25	ns		
			6 V	17	25	21	21	21			
			2 V	5	5	5	5	5			
t <sub>h</sub>			4.5 V	5	5	5	5	5	ns		
			6 V	5	5	5	5	5			

switching characteristics over recommended operating free-air temperature range (unless otherwise noted). C<sub>L</sub> = 50 pF (see Note 1)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	V <sub>CC</sub>	T <sub>A</sub> = 25°C			SN54HC377		SN74HC377		UNIT
				MIN	TYP	MAX	MIN	MAX	MIN	MAX	
f <sub>max</sub>			2 V	5	11	3	4	4	200	200	MHz
				4.5 V	25	54	16	16	20	20	
				6 V	29	64	19	19	23	23	
t <sub>pd</sub>	CLK	Any	2 V	56	160	240	240	240	200	200	ns
				4.5 V	15	32	48	48	40	40	
				6 V	12	27	41	41	34	34	
t <sub>t</sub>		Any	2 V	38	75	110	110	110	95	95	ns
				4.5 V	8	15	22	22	19	19	
				6 V	.8	13	19	19	16	16	

C <sub>pd</sub>	Power dissipation capacitance	No load, T <sub>A</sub> = 25°C	30 pF typ
-----------------	-------------------------------	--------------------------------	-----------

Note 1: Load circuits and voltage waveforms are shown in Section 1.

2

HCMOS Devices


  
**TEXAS  
INSTRUMENTS**  
POST OFFICE BOX 655012 • DALLAS, TEXAS 75265

2-435