
- **Member of the Texas Instruments** Widebus™ Family
- **EPIC™** (Enhanced-Performance Implanted **CMOS) Submicron Process**
- **DOC**[™] (Dynamic Output Control) Circuit **Dynamically Changes Output Impedance, Resulting in Noise Reduction Without Speed Degradation**
- **Dynamic Drive Capability Is Equivalent to** Standard Outputs With IOH and IOL of \pm 24 mA at 2.5-V V_{CC}
- Overvoltage-Tolerant Inputs/Outputs Allow **Mixed-Voltage-Mode Data Communications**

- I_{off} Supports Partial-Power-Down Mode Operation
- **ESD Protection Exceeds JESD 22**
 - 2000-V Human-Body Model (A114-A)
 - 200-V Machine Model (A115-A)
- Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II
- **Package Options Include Plastic Thin** Shrink Small-Outline (DGG) and Thin Very Small-Outline (DGV) Packages

description

A Dynamic Output Control (DOC) circuit is implemented, which, during the transition, initially lowers the output impedance to effectively drive the load and, subsequently, raises the impedance to reduce noise. Figure 1 shows typical V_{OI} vs I_{OI} and V_{OH} vs I_{OH} curves to illustrate the output impedance and drive capability of the circuit. At the beginning of the signal transition, the DOC circuit provides a maximum dynamic drive that is equivalent to a high-drive standard-output device. For more information, refer to the TI application reports, AVC Logic Family Technology and Applications, literature number SCEA006, and Dynamic Output Control (DOC™) Circuitry Technology and Applications, literature number SCEA009.






Figure 1. Output Voltage vs Output Current

This 16-bit edge-triggered D-type flip-flop is operational at 1.2-V to 3.6-V V_{CC}, but is designed specifically for 1.65-V to 3.6-V V_{CC} operation.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

DOC, EPIC, and Widebus are trademarks of Texas Instruments Incorporated.



description (continued)

The SN74AVC16374 is particularly suitable for implementing buffer registers, I/O ports, bidirectional bus drivers, and working registers. It can be used as two 8-bit flip-flops or one 16-bit flip-flop. On the positive transition of the clock (CLK) input, the Q outputs of the flip-flop take on the logic levels at the data (D) inputs. $\overline{\text{OE}}$ can be used to place the eight outputs in either a normal logic state (high or low logic levels) or the high-impedance state. In the high-impedance state, the outputs neither load nor drive the bus lines significantly. The high-impedance state and the increased drive provide the capability to drive bus lines without need for interface or pullup components.

OE does not affect internal operations of the flip-flop. Old data can be retained or new data can be entered while the outputs are in the high-impedance state.

To ensure the high-impedance state during power up or power down, \overline{OE} should be tied to V_{CC} through a pullup resistor; the minimum value of the resistor is determined by the current-sinking capability of the driver.

This device is fully specified for partial-power-down applications using I_{off} . The I_{off} circuitry disables the outputs, preventing damaging current backflow through the device when it is powered down.

The SN74AVC16374 is characterized for operation from -40°C to 85°C.

terminal assignments


DGG OR DGV PACKAGE (TOP VIEW) 10E 48 🛮 1CLK 1Q1 **2** 47 1 1D1 1Q2 **[**]3 46 1 1D2 GND 4 45 GND 1Q3 🛮 5 44 🛮 1D3 1Q4 **[**] 6 43 1D4 V_{CC} 47 42 V_{CC} 1Q5 🛮 8 41 1 1D5 1Q6 🛮 9 40 1 1D6 GND 110 39 GND 1Q7 **1**11 38 🛮 1D7 1Q8 🛮 12 37 D8 2Q1 13 36 2D1 2Q2 114 35 2D2 GND 15 34 GND 2Q3 16 33 2D3 32 2D4 2Q4 [] 17 V_{CC} **□** 18 31 V_{CC} 2Q5 🛮 19 30 2D5 2Q6 **1**20 29 2D6 GND [] 21 28 GND 2Q7 [] 22 27 **∏** 2D7 26 2D8 2Q8 L 23 20E 24 25 2CLK



FUNCTION TABLE (each 8-bit flip-flop)


	INPUTS	OUTPUT	
OE	CLK	D	Q
L	\uparrow	Н	Н
L	\uparrow	L	L
L	H or L	Χ	Q ₀
Н	Χ	Χ	Z

logic symbol†



[†] This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

logic diagram (positive logic)





SN74AVC16374 16-BIT EDGE-TRIGGERED D-TYPE FLIP-FLOP WITH 3-STATE OUTPUTS

SCES158E - DECEMBER 1998 - REVISED DECEMBER 1999

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)†

Supply voltage range, V _{CC}	–0.5 V to 4.6 V
Input voltage range, V _I (see Note 1)	–0.5 V to 4.6 V
Voltage range applied to any output in the high-impedance or power-off state, VO	
(see Note 1)	–0.5 V to 4.6 V
Voltage range applied to any output in the high or low state, VO	
(see Notes 1 and 2)	$0.5 \text{ V to V}_{CC} + 0.5 \text{ V}$
Input clamp current, I _{IK} (V _I < 0)	–50 mA
Output clamp current, I _{OK} (V _O < 0)	–50 mA
Continuous output current, I _O	±50 mA
Continuous current through each V _{CC} or GND	±100 mA
Package thermal impedance, θ _{JA} (see Note 3): DGG package	70°C/W
DGV package	58°C/W
Storage temperature range, T _{stq}	–65°C to 150°C

[†] Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- NOTES: 1. The input and output negative-voltage ratings may be exceeded if the input and output current ratings are observed.
 - 2. The output positive-voltage rating may be exceeded up to 4.6 V maximum if the output current rating is observed.
 - 3. The package thermal impedance is calculated in accordance with JESD 51.



SN74AVC16374 16-BIT EDGE-TRIGGERED D-TYPE FLIP-FLOP WITH 3-STATE OUTPUTS SCES158E - DECEMBER 1998 - REVISED DECEMBER 1999

recommended operating conditions (see Note 4)

			MIN	MAX	UNIT			
V/00	Supply voltage	Operating	1.4	3.6	V			
VCC	Su pp iy voltage	Data retention only	1.2		V			
		V _{CC} = 1.2 V	Vcc					
		$V_{CC} = 1.4 \text{ V to } 1.6 \text{ V}$	0.65 × V _{CC}					
V_{IH}	High-level input voltage	$V_{CC} = 1.65 \text{ V to } 1.95 \text{ V}$	0.65 × V _{CC}		V			
		$V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$	1.7					
		$V_{CC} = 3 \text{ V to } 3.6 \text{ V}$	2					
		V _{CC} = 1.2 V		GND				
		V _{CC} = 1.4 V to 1.6 V		0.35 × V _{CC}				
V_{IL}	Low-level input voltage	$V_{CC} = 1.65 \text{ V to } 1.95 \text{ V}$		$0.35 \times V_{CC}$	V			
		V _{CC} = 2.3 V to 2.7 V		0.7				
		V _{CC} = 3 V to 3.6 V		0.8				
٧ _I	Input voltage		0	3.6	V			
\/a	Output voltage	Active state	0	Vcc	V			
VO	Output voltage	3-state	0	3.6	V			
		$V_{CC} = 1.4 \text{ V to } 1.6 \text{ V}$		-2				
lavia	Static high level cutout current	$V_{CC} = 1.65 \text{ V to } 1.95 \text{ V}$		-4	1 . !			
IOHS	Static high-level output current [†]	V _{CC} = 2.3 V to 2.7 V		-8	mA			
		V _{CC} = 3 V to 3.6 V		-12				
		V _{CC} = 1.4 V to 1.6 V		2				
lors	Charlie lave lavel autout average †	V _{CC} = 1.65 V to 1.95 V		4				
	Static low-level output current [†]	V _{CC} = 2.3 V to 2.7 V		8	mA			
		V _{CC} = 3 V to 3.6 V		12	1			
Δt/Δν	Input transition rise or fall rate	V _{CC} = 1.4 V to 3.6 V		5	ns/V			
TA	Operating free-air temperature		-40	85	°C			

[†] Dynamic drive capability is equivalent to standard outputs with IOH and IOL of ±24 mA at 2.5-V VCC. See Figure 1 for VOL vs IOL and VOH vs IOH characteristics. Refer to the TI application reports, AVC Logic Family Technology and Applications, literature number SCEA006, and Dynamic Output Control (DOC™) Circuitry Technology and Applications, literature number SCEA009.

NOTE 4: All unused inputs of the device must be held at V_{CC} or GND to ensure proper device operation. Refer to the TI application report, Implications of Slow or Floating CMOS Inputs, literature number SCBA004.



SN74AVC16374 16-BIT EDGE-TRIGGERED D-TYPE FLIP-FLOP WITH 3-STATE OUTPUTS

SCES158E - DECEMBER 1998 - REVISED DECEMBER 1999

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

	PARAMETER	TEST COND	OITIONS	Vcc	MIN	TYP	MAX	UNIT	
		I _{OHS} = -100 μA		1.4 V to 3.6 V	V _{CC} -0.	2			
	$I_{OHS} = -2 \text{ mA},$	/ _{IH} = 0.91 V	1.4 V	1.05					
Vон		$I_{OHS} = -4 \text{ mA},$	/ _{IH} = 1.07 V	1.65 V	1.2			V	
		$I_{OHS} = -8 \text{ mA},$	/ _{IH} = 1.7 V	2.3 V	1.75				
		$I_{OHS} = -12 \text{ mA},$	/ _{IH} = 2 V	3 V	2.3				
		I _{OLS} = 100 μA		1.4 V to 3.6 V			0.2		
		$I_{OLS} = 2 \text{ mA},$	/ _{IL} = 0.49 V	1.4 V			0.4		
VOL		$I_{OLS} = 4 \text{ mA},$	/ _{IL} = 0.57 V	1.65 V			0.45	V	
		$I_{OLS} = 8 \text{ mA},$	/ _{IL} = 0.7 V	2.3 V			0.55		
		$I_{OLS} = 12 \text{ mA},$	/ _{IL} = 0.8 V	3 V			0.7		
П	Control inputs	$V_I = V_{CC}$ or GND		3.6 V			±2.5	μΑ	
I _{off}		V_I or $V_O = 3.6 V$		0			±10	μΑ	
loz		$V_O = V_{CC}$ or GND		3.6 V			±10	μΑ	
ICC		$V_I = V_{CC}$ or GND,	O = 0	3.6 V			40	μΑ	
	Control inputs	V _I = V _{CC} or GND		2.5 V		3			
Ci	Control inputs	Al = ACC of QIAD		3.3 V		3		pF	
	Data inputs	V _I = V _{CC} or GND		2.5 V		2.5		рі	
	Data Inputs	AI = ACC OL QIAD		3.3 V		2.5			
Co	Outputs	VO = VCC or GND		2.5 V		6.5		pF	
	Catputs	10 - 400 01 014D		3.3 V		6.5		рі	

[†] Typical values are measured at V_{CC} = 2.5 V and 3.3 V, T_A = 25°C.

timing requirements over recommended operating free-air temperature range (unless otherwise noted) (see Figures 2 through 5)

		V _{CC} = 1.2 V		V _{CC} = 1.5 V ± 0.1 V		V _{CC} = 1.8 V ± 0.15 V		V _{CC} = 2.5 V ± 0.2 V		V _{CC} = 3.3 V ± 0.3 V		UNIT
		MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
fclock	Clock frequency						160		200		200	MHz
t _W	Pulse duration, CLK high or low					3.1		2.5		2.5		ns
t _{su}	Setup time, data before CLK↑	4.1		2.7		1.9		1.4		1.4		ns
th	Hold time, data after CLK↑	1.7		1.3		1.2		1.1		1.1		ns

switching characteristics over recommended operating free-air temperature range (unless otherwise noted) (see Figures 2 through 5)


PARAMETER	FROM TO (INPUT)		V _{CC} = 1.2 V	V _{CC} = 1.5 V ± 0.1 V		V _{CC} = 1.8 V ± 0.15 V		V _{CC} = 2.5 V ± 0.2 V		V _{CC} = 3.3 V ± 0.3 V		UNIT
	(IIVI O1)	(001101)	TYP	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	
f _{max}						160		200		200		MHz
^t pd	CLK	Q	7.3	1.5	8.4	1.2	6.7	0.8	4.1	0.7	3.3	ns
t _{en}	ŌĒ	Q	7.4	1.6	8.5	1.6	6.7	0.9	4.3	0.7	3.4	ns
^t dis	ŌĒ	Q	8.4	2.5	9.4	2.3	7.8	1	4.2	1.5	3.9	ns





operating characteristics, T_A = 25°C


PARAMETER		TEST CONDITIONS	V _{CC} = 1.8 V	$V_{CC} = 2.5 \text{ V}$	V _{CC} = 3.3 V	UNIT	
		TEST CONDITIONS	TYP	TYP	TYP	ONIT	
<u> </u>	Power dissipation	Outputs enabled	Cı = 0. f = 10 MHz	74	81	89	рF
C _{pd} capacitance	Outputs disabled	$C_L = 0$, $f = 10 MHz$	52	57	63	pr	


PARAMETER MEASUREMENT INFORMATION V_{CC} = 1.2 V AND 1.5 V \pm 0.1 V












PROPAGATION DELAY TIMES




NOTES: A. C_L includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: PRR \leq 10 MHz, Z $_{\mbox{O}}$ = 50 Ω , $t_{\mbox{f}}$ \leq 2 ns.
- D. The outputs are measured one at a time with one transition per measurement.
- E. tpLZ and tpHZ are the same as tdis.
- F. tpzL and tpzH are the same as ten.
- G. tplH and tpHL are the same as tpd.

Figure 2. Load Circuit and Voltage Waveforms



PARAMETER MEASUREMENT INFORMATION $V_{CC} = 1.8 \text{ V} \pm 0.15 \text{ V}$




NOTES: A. C_I includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: PRR \leq 10 MHz, $Z_O = 50~\Omega$, $t_f \leq$ 2 ns, $t_f \leq$ 2 ns.
- D. The outputs are measured one at a time with one transition per measurement.
- E. tpLZ and tpHZ are the same as tdis.
- F. tpzL and tpzH are the same as ten.
- G. tpl H and tpHI are the same as tpd.

Figure 3. Load Circuit and Voltage Waveforms




PARAMETER MEASUREMENT INFORMATION $V_{CC} = 2.5 \text{ V} \pm 0.2 \text{ V}$



- NOTES: A. C_L includes probe and jig capacitance.
 - B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
 - C. All input pulses are supplied by generators having the following characteristics: PRR \leq 10 MHz, $Z_O = 50 \ \Omega$, $t_f \leq 2 \ ns$.
 - D. The outputs are measured one at a time with one transition per measurement.
 - E. tpLZ and tpHZ are the same as tdis.
 - F. tpzL and tpzH are the same as ten.
 - G. tpLH and tpHL are the same as tpd.

Figure 4. Load Circuit and Voltage Waveforms

PARAMETER MEASUREMENT INFORMATION $V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$



- NOTES: A. C_I includes probe and jig capacitance.
 - B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
 - C. All input pulses are supplied by generators having the following characteristics: PRR \leq 10 MHz, $Z_Q = 50 \ \Omega$, $t_f \leq$ 2 ns, $t_f \leq$ 2 ns.
 - D. The outputs are measured one at a time with one transition per measurement.
 - E. tpl 7 and tpH7 are the same as tdis.
 - F. tpzL and tpzH are the same as ten.
 - G. tplH and tpHL are the same as tpd.

Figure 5. Load Circuit and Voltage Waveforms



IMPORTANT NOTICE

Texas Instruments and its subsidiaries (TI) reserve the right to make changes to their products or to discontinue any product or service without notice, and advise customers to obtain the latest version of relevant information to verify, before placing orders, that information being relied on is current and complete. All products are sold subject to the terms and conditions of sale supplied at the time of order acknowledgement, including those pertaining to warranty, patent infringement, and limitation of liability.

TI warrants performance of its semiconductor products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are utilized to the extent TI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except those mandated by government requirements.

CERTAIN APPLICATIONS USING SEMICONDUCTOR PRODUCTS MAY INVOLVE POTENTIAL RISKS OF DEATH, PERSONAL INJURY, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE ("CRITICAL APPLICATIONS"). TI SEMICONDUCTOR PRODUCTS ARE NOT DESIGNED, AUTHORIZED, OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT DEVICES OR SYSTEMS OR OTHER CRITICAL APPLICATIONS. INCLUSION OF TI PRODUCTS IN SUCH APPLICATIONS IS UNDERSTOOD TO BE FULLY AT THE CUSTOMER'S RISK.

In order to minimize risks associated with the customer's applications, adequate design and operating safeguards must be provided by the customer to minimize inherent or procedural hazards.

TI assumes no liability for applications assistance or customer product design. TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right of TI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used. TI's publication of information regarding any third party's products or services does not constitute TI's approval, warranty or endorsement thereof.

Copyright © 1999, Texas Instruments Incorporated