- 3-State Outputs Drive Bus Lines or Buffer Memory Address Registers
- Package Options Include Plastic Small-Outline (DB) Packages and Plastic 300-mil DIPs (N)

### description

The SN74F2245 is designed for asynchronous communication between data buses. The devices transmit data from the A bus to the B bus or from the B bus to the A bus depending upon the logic level at the direction-control (DIR) input. The output-enable ( $\overline{OE}$ ) input disables the device so the buses are effectively isolated.


DB OR N PACKAGE (TOP VIEW)				
DIR   A1   A2   A3   A4   A5   A6   A7   A8   GND	1 2 3 4 5 6 7 8 9 10	1 1 1 1 1 1 1	0 9 8 7 6 5 4 3 2	] <u>V</u> <sub>C</sub> C ] OE ] B1 ] B2 ] B3 ] B4 ] B5 ] B6 ] B7 ] B8

Both A and B outputs can sink up to 12 mA; 25- $\Omega$  resistors are included in the lower output circuit to reduce overshoot and undershoot.

The SN74F2245 is characterized for operation from 0°C to 70°C.

FUNCTION TABLE					
INPUTS		OPERATION			
OE	DIR	OPERATION			
L	L	B data to A bus			
L	Н	A data to B bus			
Н	Х	Isolation			


### logic symbol<sup>†</sup>



# 

logic diagram (positive logic)

 $DIR - \frac{1}{2}$ 



To Seven Other Channels

<sup>†</sup> This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.



Copyright © 1995, Texas Instruments Incorporated

19

OE

### SN74F2245 25-Ω OCTAL BUS TRANSCEIVER WITH 3-STATE OUTPUTS

SDFS099 – MAY 1995

### absolute maximum ratings over operating free-air temperature range (unless otherwise noted)<sup>†</sup>

Supply voltage range, V <sub>CC</sub>	–0.5 V to 7 V
Input voltage range, V <sub>I</sub> (except I/O ports) (see Note 1)	–1.2 V to 7 V
Input current range	30 mA to 5 mA
Voltage range applied to any output in the disabled or power-off state	−0.5 V to 5.5 V
Voltage range applied to any output in the high state	$\dots -0.5$ V to V <sub>CC</sub>
Current into any output in the low state	30 mA
Operating free-air temperature range, T <sub>A</sub>	0°C to 70°C
Storage temperature range, T <sub>stg</sub>	. −65°C to 150°C

<sup>†</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

NOTE 1: The input voltage ratings may be exceeded provided the input current ratings are observed.

### recommended operating conditions

		MIN	NOM	MAX	UNIT
Vcc	Supply voltage	4.5	5	5.5	V
VIH	High-level input voltage	2			V
VIL	Low-level input voltage			0.8	V
I <sub>IK</sub>	Input clamp current			-18	mA
IОН	High-level output current			- 3	mA
IOL	Low-level output current			12	mA
TA	Operating free-air temperature	0		70	°C

### electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

	PARAMETER	TEST CONDITIONS		MIN	TYP‡	MAX	UNIT	
VIK		V <sub>CC</sub> = 4.5 V,	I <sub>I</sub> = -18 mA			-1.2	V	
			I <sub>OH</sub> = - 1 mA	2.5	3.4			
Vон	Any output	V <sub>CC</sub> = 4.5 V	$I_{OH} = -3 \text{ mA}$	2.4	3.3		V	
		V <sub>CC</sub> = 4.75 V,	$I_{OH} = -1 \text{ mA to} - 3 \text{ mA}$	2.7				
Val	Any output		I <sub>OL</sub> = 1 mA		0.2	0.5	V	
VOL	Any output	$V_{CC} = 4.5 V$	I <sub>OL</sub> = 12 mA		0.5	0.75	v	
ı.	A and B		V <sub>I</sub> = 5.5 V			1	mA	
1	DIR and OE	V <sub>CC</sub> = 5.5 V	V <sub>I</sub> = 7 V			0.1	ША	
	A and B					70		
Ι <sub>ΙΗ</sub> §	DIR and OE	V <sub>CC</sub> = 5.5 V,	V <sub>I</sub> = 2.7 V			20	μA	
	A and B					-0.5		
IIL§	DIR and OE	V <sub>CC</sub> = 5.5 V,	V <sub>I</sub> = 0.5 V			- 0.5	mA	
los¶	A and B	V <sub>CC</sub> = 5.5 V,	$V_{O} = 0$	-50		-120	mA	
			Outputs high		62	90		
ICC		V <sub>CC</sub> = 5.5 V	Outputs low		73	105	mA	
			Outputs disabled		72	100		

<sup>‡</sup> All typical values are at  $V_{CC} = 5 \text{ V}$ ,  $T_A = 25^{\circ}\text{C}$ .

§ For I/O ports, the parameters IIH and IIL include the off-state output current.

I Not more than one output should be shorted at a time, and the duration of the short circuit should not exceed one second.



### SN74F2245 25-Ω OCTAL BUS TRANSCEIVER WITH 3-STATE OUTPUTS SDFS099 – MAY 1995

### switching characteristics (see Figure 1)

PARAMETER	FROM (INPUT)	то (оитрит)	CL R1 R2 T <sub>A</sub>	c = 5 V, = 50 pF = 500 Ω = 500 Ω = 25°C	; ), ),	$C_{L} = 50 \text{ pF}$ $R1 = 500 \Omega$ $R2 = 500 \Omega$ $T_{A} = MIN t$	2, 2, to MAX†	UNIT	
			MIN	TYP	MAX	MIN	MAX		
<sup>t</sup> PLH	A or B	B or A	2.5	3.9	5.5	2.1	6.6	ns	
<sup>t</sup> PHL	AUD	BOIA	3.1	4.6	6.6	2.9	7.1	115	
<sup>t</sup> PZH	ŌĒ	A or B	2.4	4.8	7.3	1.6	8.5		
<sup>t</sup> PZL	UE	AUB	3.6	6.6	10.6	3	12	ns	
<sup>t</sup> PHZ	ŌĒ	A or B	2.3	4.3	6.3	2	7.5		
<sup>t</sup> PLZ		AUD	2	4	5.8	1.9	6.8	ns	


<sup>†</sup> For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.



### SN74F2245 **25-** $\Omega$ **OCTAL BUS TRANSCEIVER** WITH 3-STATE OUTPUTS


SDFS099 - MAY 1995

### PARAMETER MEASUREMENT INFORMATION



NOTES: A. CI includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  1 MHz, t<sub>f</sub> = t<sub>f</sub>  $\leq$  2.5 ns, duty cycle = 50%.
- D. When measuring propagation delay times of 3-state outputs, switch S1 is open.
- E. The outputs are measured one at a time with one transition per measurement.





#### **IMPORTANT NOTICE**

Texas Instruments and its subsidiaries (TI) reserve the right to make changes to their products or to discontinue any product or service without notice, and advise customers to obtain the latest version of relevant information to verify, before placing orders, that information being relied on is current and complete. All products are sold subject to the terms and conditions of sale supplied at the time of order acknowledgement, including those pertaining to warranty, patent infringement, and limitation of liability.

TI warrants performance of its semiconductor products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are utilized to the extent TI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except those mandated by government requirements.

CERTAIN APPLICATIONS USING SEMICONDUCTOR PRODUCTS MAY INVOLVE POTENTIAL RISKS OF DEATH, PERSONAL INJURY, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE ("CRITICAL APPLICATIONS"). TI SEMICONDUCTOR PRODUCTS ARE NOT DESIGNED, AUTHORIZED, OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT DEVICES OR SYSTEMS OR OTHER CRITICAL APPLICATIONS. INCLUSION OF TI PRODUCTS IN SUCH APPLICATIONS IS UNDERSTOOD TO BE FULLY AT THE CUSTOMER'S RISK.

In order to minimize risks associated with the customer's applications, adequate design and operating safeguards must be provided by the customer to minimize inherent or procedural hazards.

TI assumes no liability for applications assistance or customer product design. TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right of TI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used. TI's publication of information regarding any third party's products or services does not constitute TI's approval, warranty or endorsement thereof.

Copyright © 1998, Texas Instruments Incorporated

1 of 2

🐺 Texas Instruments	THE WORLD LEADER IN DSP AND ANALOG
Products GO	Development Tools Applications GO
Search GO	□ Advanced Search □ TI Home □ TI&ME □ Employment □ Tech Support □ Comments □ Site Map □ TI Global

# PRODUCT FOLDER | PRODUCT INFO: FEATURES | DESCRIPTION | DATASHEETS | PRICING/AVAILABILITY | APPLICATION NOTES | RELATED DOCUMENTS

PRODUCT SUPPORT: TRAINING

### SN74F2245, Octal bus transceivers with series damping resistors DEVICE STATUS: ACTIVE

PARAMETER NAME	SN74F2245
Voltage Nodes (V)	5
Vcc range (V)	4.5 to 5.5
Input Level	TTL
Output Level	TTL
Output Drive (mA)	-3/12
No. of Outputs	8
Logic	True
Static Current	97.5
tpd(max) (ns)	7.1

### FEATURES

Back to Top

- 3-State Outputs Drive Bus Lines or Buffer Memory Address Registers
- Package Options Include Plastic Small-Outline (DB) Packages and Plastic 300-mil DIPs (N)

### DESCRIPTION

Back to Top

The SN74F2245 is designed for asynchronous communication between data buses. The devices transmit data from the A bus to the B bus or from the B bus to the A bus depending upon the logic level at the direction-control (DIR) input. The output-enable ( $\overline{OE}$ ) input disables the device so the buses are effectively isolated.

Both A and B outputs can sink up to 12 mA; 25-  $\Omega$  resistors are included in the lower output circuit to reduce overshoot and undershoot.

The SN74F2245 is characterized for operation from 0°C to 70°C.

## TECHNICAL DOCUMENTS

To view the following documents, <u>Acrobat Reader 3.x</u> is required. To download a document to your hard drive, right-click on the link and choose 'Save'.

### DATASHEET

Full datasheet in Acrobat PDF: <u>sdfs099.pdf</u> (84 KB) (Updated: 05/01/1995) Full datasheet in Zipped PostScript: <u>sdfs099.psz</u> (78 KB)

### APPLICATION NOTES

View Application Reports for Digital Logic

- Bus-Interface Devices With Output-Damping Resistors Or Reduced-Drive
   Outputs (SCBA012A Updated: 08/01/1997)
- Designing With Logic (SDYA009C Updated: 06/01/1997)
- Input and Output Characteristics of Digital Integrated Circuits (SDYA010 Updated: 10/01/1996)
- LVT-to-LVTH Conversion (SCEA010 Updated: 12/08/1998)
- Logic Solutions For IEEE Std 1284 (SCEA013 Updated: 06/01/1999)

### RELATED DOCUMENTS

- <u>Documentation Rules (SAP) And Ordering Information</u> (SZZU001B, 4 KB Updated: 05/06/1999)
- Logic Selection Guide Second Half 2000 (SDYU001N, 5035 KB Updated: 04/17/2000)
- MicroStar Junior BGA Design Summary (SCET004, 167 KB Updated: 07/28/2000)
- More Power In Less Space Technical Article (SCAU001A, 850 KB Updated: 03/01/1996)

### PRICING/AVAILABILITY

BUDGETARY ORDERABLE TEMP PRICE PACK PACKAGE PINS STATUS PRICING/AVAILABILITY DEVICE (°C) US\$/UNIT QTY QTY=1000+ SN74F2245DBR DB 20 0 TO 70 ACTIVE 0.43 2000 Check stock or order 0 TO 70 SN74F2245DW DW 20 ACTIVE 0.43 25 Check stock or order DW 0 TO 70 ACTIVE Check stock or order SN74F2245DWR 20 0.50 2000 0 TO 70 ACTIVE 0.43 SN74F2245N 20 20 Check stock or order Ν

### Table Data Updated on: 11/15/2000

© Copyright 2000 Texas Instruments Incorporated. All rights reserved. <u>Trademarks | Privacy Policy</u> | Important Notice

<u>Back to Top</u>

Back to Top

Back to Top

Back to Top

<u>Back to Top</u>