# DS36276

DS36276 FAILSAFE Multipoint Transceiver



Literature Number: SNLS085A

July 1998

DS36276 FAILSAFE Multipoint Transceiver



# DS36276 FAILSAFE Multipoint Transceiver

#### **General Description**

The DS36276 FAILSAFE Multipoint Transceiver is designed for use on bi-directional differential busses. It is compatible with existing TIA/EIA-485 transceivers, however, it offers an additional feature not supported by standard transceivers.


The FAILSAFE feature guarantees the receiver output to a known state when the Interface is in the following conditions: Floating Line, Idle Line (no active drivers), and Line Fault conditions (open or short). The receiver output is in a HIGH state for the following conditions: OPEN Inputs, Terminated Inputs ( $50\Omega$ ), and SHORTED Inputs.

FAILSAFE is a highly desirable feature when the transceivers are used with Asynchronous Controllers such as UARTs.

#### Features

- FAILSAFE receiver, RO = HIGH for:
  - OPEN inputs
  - Terminated inputs
  - SHORTED inputs
- Compatible with popular interface standards:
  - TIA/EIA-485 (RS-485)
  - TIA/EIA-422-A (RS-422-A)
- CCITT Recommendation V.11
- Bi-Directional Transceiver
- Designed for multipoint transmission
- Separate driver input, driver enable, receiver enable, and receiver output for maximum flexibility
- Wide bus common mode range — (-7V to +12V)
- Pin compatible with: DS75176B, DS96176, DS3695 and SN75176A and B
- Available in SOIC package

# Connection and Logic Diagram



Order Number DS36276M See NS Package Number M08A

#### Driver

Inputs			Outputs		
RE	DE	DI	DO/RI	DO /RI	
Х	Н	Н	Н	L	
X	н	L	L	н	
X	L	Х	Z	Z	

#### Receiver

	Output		
RE	DE	RI– <del>R</del> I	RO
L	L	≥0V	Н
L	L	≤–500 mV	L
н	Х	Х	Z

#### **Receiver FAILSAFE**

	Output		
RE	DE	RI– <del>R</del> I	RO
L	L	SHORTED	Н
L	L	OPEN	Н
н	Х	Х	Z

#### TRI-STATE® is a registered trademark of National Semiconductor Corporation.

### Absolute Maximum Ratings (Note 1)

If Military/Aerospace specified devices are required, please contact the National Semiconductor Sales Office/ Distributors for availability and specifications.

Supply Voltage (V <sub>CC</sub> )	7V
Input Voltage (DE, RE , and DI)	5.5V
Driver Output Voltage/	
Receiver Input Voltage	-10V to +15V
Receiver Output Voltage (RO)	5.5V
Maximum Package Power Dissipation @	+25°C
M Package (derate 5.8 mW/°C above	700
+25°C)	726 mW
Storage Temperature Range	–65°C to +150°C

Lead Temperature (Soldering 4	
sec.)	260°C
Max Junction Temperature	150°C
ESD Rating (HBM, 1.5 kΩ, 100	
pF)	$\geq$ 6.0 kV

# Recommended Operating Conditions

	Min	Max	Units
Supply Voltage, V <sub>CC</sub>	4.75	5.25	V
Bus Voltage	-7	+12	V
Operating Temperature (T <sub>A</sub> )			
DS36276	0	+70	°C

### Electrical Characteristics (Notes 2, 4)

Over recommended Supply Voltage and Operating Temperature ranges, unless otherwise specified.

Symbol	Parameter	Conditions			Min	Тур	Max	Units
DRIVER O	CHARACTERISTICS							
V <sub>OD</sub>	Differential Output Voltage	I <sub>O</sub> = 0 mA (No Load	)		1.5	4.8	6.0	V
V <sub>oDO</sub>	Output Voltage	$I_{O} = 0 \text{ mA}$ (Output t	o GND)		0		6.0	V
V <sub>oDO</sub>	Output Voltage	-			0		6.0	V
V <sub>T1</sub>	Differential Output Voltage	$R_{L} = 54\Omega$ (485)	(Figure 1)		1.5	2.0	5.0	V
	(Termination Load)	R <sub>L</sub> = 100Ω (422)	1		2.0	2.3	5.0	V
$\Delta V_{T1}$	Balance of V <sub>T1</sub>	$R_L = 54\Omega$	(Note 3)		-0.2	0.07	+0.2	V
	$ V_{T1}  -  \overline{V_{T1}} $	R <sub>L</sub> = 100Ω			-0.2	0.07	+0.2	V
Vos	Driver Common Mode	$R_L = 54\Omega$	(Figure 1)		0	2.5	3.0	V
	Output Voltage	R <sub>L</sub> = 100Ω	1		0	2.3	3.0	V
$\Delta V_{OS}$	Balance of V <sub>os</sub>	$R_L = 54\Omega$	(Note 3)		-0.2	0.08	+0.2	V
	$ V_{OS}  -  \overline{V_{OS}} $	R <sub>L</sub> = 100Ω		-0.2	0.08	+0.2	V	
I <sub>OSD</sub>	Driver Short-Circuit	V <sub>O</sub> = +12V	(Figure 3)			134	290	mA
	Output Current	$V_{O} = V_{CC}$				140		mA
		$V_{O} = 0V$				-140		mA
		$V_{O} = -7V$	-			-180	-290	mA
RECEIVE	R CHARACTERISTICS		1		1	1		
$V_{TH}$	Differential Input High Threshold Voltage (Note 5)	$V_{O} = V_{OH}, I_{O} = -0.4$ -7V $\leq V_{CM} \leq +12V$	l mA			-0.18	0	V
$V_{TL}$	Differential Input Low Threshold Voltage (Note 5)	$V_{O} = V_{OL}, I_{O} = 8.0 \text{ I}$ -7V $\leq V_{CM} \leq +12 \text{ V}$	mA		-0.5	-0.23		V
V <sub>HST</sub>	Hysteresis (Note 6)	$V_{CM} = 0V$				50		mV
I <sub>IN</sub>	Line Input Current	Other Input = 0V	V <sub>I</sub> = +12V			0.7	1.0	mA
	(V <sub>CC</sub> = 4.75V, 5.25V, 0V)	$DE = V_{IH}$ (Note 7)	$V_1 = -7V$			-0.5	-0.8	mA
I <sub>OSR</sub>	Short Circuit Current	$V_{O} = 0V$	1	RO	-5.0	-30	-85	mA
I <sub>oz</sub>	TRI-STATE <sup>®</sup> Leakage Current	$V_{\rm O} = 0.4$ to 2.4V		1	-20		+20	μA
V <sub>он</sub>	Output High Voltage	$V_{ID} = 0V, I_{OH} = -0.4$	1 mA	1	2.5	3.5		V
	(Figure 12)	V <sub>ID</sub> = OPEN, I <sub>OH</sub> =	–0.4 mA	1	2.5	3.5		V
V <sub>OL</sub>	Output Low Voltage	$V_{\rm ID} = -0.5V, I_{\rm OL} = +$		1		0.25	0.6	V
	(Figure 12)	$V_{\rm ID} = -0.5V, I_{\rm OL} = +$		1		0.35	0.7	V
R <sub>IN</sub>	Input Resistance			1	12	19		kΩ

#### Electrical Characteristics (Notes 2, 4) (Continued)

Over recommended Supply Voltage and Operating Temperature ranges, unless otherwise specified.

Symbol	Parameter	Conditions		Min	Тур	Max	Units
DEVICE CHARACTERISTICS							
V <sub>IH</sub>	High Level Input Voltage		DE,	2.0		V <sub>cc</sub>	V
VIL	Low Level Input Voltage		RE,	GND		0.8	V
I <sub>IH</sub>	High Level Input Current	V <sub>IH</sub> = 2.4V	or			20	μA
I	Low Level Input Current	$V_{IL} = 0.4V$	- DI			-100	μA
V <sub>CL</sub>	Input Clamp Voltage	$I_{CL} = -18 \text{ mA}$			-0.75	-1.5	V
I <sub>cc</sub>	Output Low Voltage	$DE = 3V, \overline{RE} = 0V, DI = 0V$			42	60	mA
I <sub>CCR</sub>	Supply Current	$DE = 0V, \overline{RE} = 0V, DI = 0V$			28	45	mA
I <sub>CCD</sub>	(No Load)	$DE = 3V, \overline{RE} = 3V, DI = 0V$			43	60	mA
I <sub>ccx</sub>		$DE = 0V, \overline{RE} = 3V, DI = 0V$			31	50	mA

#### Switching Characteristics (Note 4)

Over recommended Supply Voltage and Operating Temperature ranges, unless otherwise specified.

Symbol	Parameter	Conditions	Min	Тур	Max	Units
DRIVER CH	ARACTERISTICS		1	1		
t <sub>PLHD</sub>	Diff. Prop. Delay Low to High	$R_{L} = 54\Omega$	7	21	60	ns
t <sub>PHLD</sub>	Diff. Prop. Delay High to Low	C <sub>L</sub> = 50 pF	7	19	60	ns
t <sub>skD</sub>	Diff. Skew ( t <sub>PLHD</sub> -t <sub>PHLD</sub>  )	$C_{\rm D} = 50  \rm pF$		2	10	ns
t <sub>r</sub>	Diff. Rise Time	(Figures 4, 5)		12	50	ns
t <sub>f</sub>	Diff. Fall Time			12	50	ns
t <sub>PLH</sub>	Prop. Delay Low to High	$R_{L} = 27\Omega, C_{L} = 15 \text{ pF}$		22	45	ns
t <sub>PHL</sub>	Prop. Delay High to Low	(Figures 6, 7)		22	45	ns
t <sub>PZH</sub>	Enable Time Z to High	R <sub>L</sub> = 110Ω		32	55	ns
t <sub>PZL</sub>	Enable Time Z to Low	$C_{L} = 50 \text{ pF}$ (Figure 8 – Figure 11)		32	65	ns
t <sub>PHZ</sub>	Disable Time High to Z			22	55	ns
t <sub>PLZ</sub>	Disable Time Low to Z			16	55	ns
RECEIVER	CHARACTERISTICS	1				
t <sub>PLH</sub>	Prop. Delay Low to High	$V_{ID} = -1.5V$ to +1.5V	15	40	70	ns
t <sub>PHL</sub>	Prop. Delay High to Low	C <sub>L</sub> = 15 pF	15	42	70	ns
t <sub>sk</sub>	Skew ( t <sub>PLH</sub> -t <sub>PHL</sub>  )	(Figures 13, 14)		2	15	ns
t <sub>PZH</sub>	Enable Time Z to High	C <sub>L</sub> = 15 pF		15	50	ns
t <sub>PZL</sub>	Enable Time Z to Low	(Figures 15, 16)		17	50	ns
t <sub>PHZ</sub>	Disable Time High to Z			24	50	ns
t <sub>PLZ</sub>	Disable Time Low to Z			19	50	ns

Note 1: "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be guaranteed. They are not meant to imply that the devices should be operated at these limits. The tables of "Electrical Characteristics" specify conditions for device operation.

Note 2: Current into device pins is defined as positive. Current out of device pins is defined as negative. All voltages are referenced to ground unless otherwise specified.

Note 3:  $\Delta$  |V<sub>T1</sub>| and  $\Delta$  |V<sub>OS</sub>| are changes in magnitude of V<sub>T1</sub> and V<sub>OS</sub>, respectively, that occur when the input changes state.

**Note 4:** All typicals are given for V  $_{CC}$  = 5.0V and T<sub>A</sub> = +25°C.

Note 5: Threshold parameter limits specified as an algebraic value rather than by magnitude.

**Note 6:** Hysteresis defined as  $V_{HST} = V_{TH} - V_{TL}$ .

Note 7:  $I_{\text{IN}}$  includes the receiver input current and driver TRI-STATE leakage current.

# DS36276

### **Parameter Measurement Information**




FIGURE 1. Driver  $V_{\text{T1}}$  and  $V_{\text{OS}}$  Test Circuit




FIGURE 2. Driver  $V_{\rm OH}$  and  $V_{\rm OL}$  Test Circuit




FIGURE 3. Driver Short Circuit Test Circuit




FIGURE 4. Driver Differential Propagation Delay and Transition Time Test Circuit

#### Parameter Measurement Information (Continued)








FIGURE 5. Driver Differential Propagation Delays and Transition Times











S1 to DO for DI = 3V S1 to  $\overline{DO}$  for DI = 0V



#### Parameter Measurement Information (Continued)





FIGURE 9. Driver TRI-STATE Delays (t<sub>PZH</sub>, t<sub>PHZ</sub>)



S1 to DO for DI = 0V S1 to  $\overline{DO}$  for DI = 3V

FIGURE 10. Driver TRI-STATE Test Circuit ( $t_{PZL}$ ,  $t_{PLZ}$ )




FIGURE 11. Driver TRI-STATE Delays (t<sub>PZL</sub>, t<sub>PLZ</sub>)




FIGURE 12. Receiver  $V_{\rm OH}$  and  $V_{\rm OL}$ 





FIGURE 13. Receiver Propagation Delay Test Circuit




**Note 9:**  $C_L$  includes probe and stray capacitance.

Note 10: Diodes are 1N916 or equivalent.


FIGURE 16. Receiver Enable and Disable Timing




## **Typical Performance Characteristics**





Differential Output Voltage vs Output Current






Driver V<sub>OH</sub> vs I<sub>OH</sub> vs Temperature








Driver VoL vs IoL vs Temperature





#### Typical Performance Characteristics (Continued)













#### Supply Currrent vs Supply Voltage



#### Supply Current vs Temperature





#### Receiver V<sub>OH</sub> vs I<sub>OH</sub> vs Temperature

# DS36276

## Typical Performance Characteristics (Continued)

Voltage Output vs Voltage Input (Hysteresis)





#### LIFE SUPPORT POLICY

NATIONAL'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT AND GENERAL COUNSEL OF NATIONAL SEMICONDUCTOR CORPORATION. As used herein:

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
- 2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

	National Semiconductor	National Semiconductor	National Semiconductor	National Semiconductor
	Corporation	Europe	Asia Pacific Customer	Japan Ltd.
V	Americas	Fax: +49 (0) 180-530 85 86	Response Group	Tel: 81-3-5639-7560
	Email: support@nsc.com	Email: europe.support@nsc.com	Tel: 65-2544466	Fax: 81-3-5639-7507
		Deutsch Tel: +49 (0) 69 9508 6208	Fax: 65-2504466	
		English Tel: +44 (0) 870 24 0 2171	Email: ap.support@nsc.com	
www.	national.com	Français Tel: +33 (0) 1 41 91 8790		

National does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and National reserves the right at any time without notice to change said circuitry and specifications.

#### **IMPORTANT NOTICE**

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Audio	www.ti.com/audio	Communications and Telecom	www.ti.com/communications
Amplifiers	amplifier.ti.com	Computers and Peripherals	www.ti.com/computers
Data Converters	dataconverter.ti.com	Consumer Electronics	www.ti.com/consumer-apps
DLP® Products	www.dlp.com	Energy and Lighting	www.ti.com/energy
DSP	dsp.ti.com	Industrial	www.ti.com/industrial
Clocks and Timers	www.ti.com/clocks	Medical	www.ti.com/medical
Interface	interface.ti.com	Security	www.ti.com/security
Logic	logic.ti.com	Space, Avionics and Defense	www.ti.com/space-avionics-defense
Power Mgmt	power.ti.com	Transportation and Automotive	www.ti.com/automotive
Microcontrollers	microcontroller.ti.com	Video and Imaging	www.ti.com/video
RFID	www.ti-rfid.com		
OMAP Mobile Processors	www.ti.com/omap		
Wireless Connectivity	www.ti.com/wirelessconnectivity		
		u Hama Dawa	a O a Al a a m

**TI E2E Community Home Page** 

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2011, Texas Instruments Incorporated