

- Meets EIA Standards RS-422-A and RS-485 and CCITT Recommendations V.11 and X.27
- Designed for Multipoint Transmission on Long Bus Lines in Noisy Environments
- 3-State Outputs
- Bus Voltage Range . . . –7 V to 12 V
- Positive and Negative Current Limiting
- Driver Output Capability . . . 60 mA Max
- Driver Thermal Shutdown Protection
- Receiver Input Impedance . . . 12 kΩ Min
- Receiver Input Sensitivity . . . ±200 mV
- Receiver Input Hysteresis . . . 50 mV Typ
- Operates From Single 5-V Supply
- Low Power Requirements

SN75177B . . . D OR P PACKAGE (TOP VIEW)



SN75178B . . . P PACKAGE (TOP VIEW)



THE SN75177B IS NOT RECOMMENDED FOR NEW DESIGN

description

The SN75177B and SN75178B differential bus repeaters are monolithic integrated devices each designed for one-way data communication on multipoint bus transmission lines. These devices are designed for balanced transmission bus line applications and meet EIA Standard RS-422-A and RS-485 and CCITT Recommendations V.11 and X.27. Each device is designed to improve the performance of the data communication over long bus lines. The SN75177B and SN75178B are identical except for the complementary enable inputs, which allow the devices to be used in pairs for bidirectional communication.

The SN75177B and SN75178B feature positive- and negative-current limiting 3-state outputs for the receiver and driver. The receiver features high input impedance, input hysteresis for increased noise immunity, and input sensitivity of ± 200 mV over a common-mode input voltage range of -7 V to 12 V. The driver features thermal shutdown for protection from line fault conditions. Thermal shutdown is designed to occur at a junction temperature of approximately 150°C. The driver is designed to drive current loads up to 60 mA maximum.

The SN75177B and SN75178B are designed for optimum performance when used on transmission buses employing the SN75172 and SN75174 differential line drivers, SN75173 and SN75175 differential line receivers, or SN75176B bus transceiver.

Function Tables

SN75177B

DIFFERENTIAL INPUTS	ENABLE	OUTPUTS		
A – B	EN	Т	Υ	Z
V _{ID} ≥ 0.2 V	Н	Н	Н	L
$-0.2 \text{ V} < \text{V}_{1D} < 0.2 \text{ V}$	Н	?	?	?
V _{ID} ≤ 0.2 V	Н	L	L	Н
X	L	Z	Z	Z


SN75178B

DIFFERENTIAL INPUTS	ENABLE		OUTPUTS	
A – B	EN	Т	Υ	Z
V _{ID} ≥ 0.2 V	L	Н	Н	L
$-0.2 \text{ V} < \text{V}_{1D} < 0.2 \text{ V}$	L	?	?	?
V _{ID} ≤ 0.2 V	L	L	L	Н
X	Н	Z	Z	Z

H = high level, L = low level, ? = indeterminate, X = irrelevant, Z = impedance (off)





logic symbols†




† These symbols are in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

logic diagrams (positive logic)





schematics of inputs and outputs



SLLS002C - D2606, JULY 1985 - REVISED FEBRUARY 1993

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)

Supply voltage, V _{CC} (see Note 1)	7 V
Voltage range at any bus terminal	
Differential input voltage (see Note 2)	±25 V
Enable input voltage	5.5 V
Continuous total dissipation	See Dissipation Rating Table
Continuous total dissipation	, ,
•	0°C to 70°C

NOTES: 1. All voltage values, except differential input voltage, are with respect to network ground terminal.

2. Differential input voltage is measured at the noninverting input with respect to the corresponding inverting input.

DISSIPATION RATING TABLE

PACKAGE	$T_{\mbox{A}} \le 25^{\circ}\mbox{C}$ POWER RATING	DERATING FACTOR ABOVE T _A = 25°C	T _A = 70°C POWER RATING
D	725 mW	5.8 mW/°C	464 mW
Р	1000 mW	8.0 mW/°C	640 mW

recommended operating conditions

		MIN	NOM	MAX	UNIT
Supply voltage, V _{CC}		4.75	5	5.25	V
High-level input voltage, V _{IH}	EN or EN	2			V
low-level input voltage, V _{IL}	EN or EN			0.8	V
Common-mode input voltage, V _{IC}		-7 [†] 12		V	
Differential input voltage, V _{ID}				±12	V
High level cutout current leve	Driver			-60	mA
High-level output current, IOH	Receiver			-400	μΑ
Low lovel output ourrent I	Driver			60	mΛ
Low-level output current, IOL	Receiver			8	mA
Operating free-air temperature, TA		C		70	°C

[†] The algebraic convention, where the less-positive (more-negative) limit is designated minimum, is used in this data sheet for common-mode input voltage and threshold voltage.

DRIVER SECTION

electrical characteristics over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted)

	PARAMETER	TEST CO	ONDITIONS	MIN	TYP†	MAX	UNIT
VIK	Input clamp voltage	I _I = -18 mA				-1.5	V
۷o	Output voltage	IO = 0		0		6	V
V _{OD1}	Differential output voltage	I _O = 0		1.5		6	V
VOD2	Differential output voltage	$R_L = 100 \Omega$,	See Figure 1	1/2 V _{OD1} or 2§			V
		$R_L = 54 \Omega$,	See Figure 1	1.5	2.5	5	
VOD3	Differential output voltage	See Note 3		1.5		5	V
$\Delta V_{OD} $	Change in magnitude of diferential output voltage‡	B 54.0 × 400.0				±0.2	V
Voc	Common-mode output voltage	$R_L = 54 \Omega \text{ or } 100 \Omega,$	$R_L = 54 \Omega \text{ or } 100 \Omega,$ See Figure 1			3 -1	V
Δ V _{OC}	Change in magnitude of common-mode output voltage‡					±0.2	٧
lo	Output current	$V_{CC} = 0$,	$V_0 = -7 \text{ V to } 12 \text{ V}$			±100	μΑ
loz	High-impedance-state output current	$V_0 = -7 \text{ V to } 12 \text{ V}$				±100	μΑ
l _{IH}	High-level input current	V _I = 2.4 V				20	μΑ
I _I L	Low-level input current	V _I = 0.4 V				-400	μΑ
		V _O = -7 V	V _O = -7 V			-250	
los	Short-circuit output current	$V_{O} = V_{CC}$				250	mA
		V _O = 12 V				250	
loo	Supply surrent (total package)	No load	Outputs enabled		57	70	mA
ICC	Supply current (total package)	INUIUAU	Outputs disabled		26	35	IIIA

[†] All typical values are at $V_{CC} = 5 \text{ V}$ and $T_A = 25^{\circ}\text{C}$.

NOTE 3: See Figure 3.5 of EIA Standard RS-485.

switching characteristics, $V_{CC} = 5 \text{ V}$, $T_A = 25^{\circ}\text{C}$

	PARAMETER	TEST C	MIN	TYP	MAX	UNIT	
t _{dD}	Differential-output delay time	$R_L = 54 \Omega$, See Figure 3			15	20	ns
t _{tD}	Differential-output transition time				20	30	ns
tPZH	Output enable time to high level	$R_L = 110 \Omega$,	See Figure 4		85	120	ns
tPZL	Output enable time to low level	$R_L = 110 \Omega$,	See Figure 5		40	60	ns
^t PHZ	Output disable time from high level	$R_L = 110 \Omega$,	See Figure 4		150	250	ns
tPLZ	Output disable time from low level	$R_L = 110 \Omega$,	See Figure 5		20	30	ns

[‡]Δ|V_{OD}| and Δ|V_{OC}| are the changes in magnitude of V_{OD} and V_{OC}, respectively, that occur when the input is changed from a high level to a low level

[§] The minimum V_{OD2} with a 100- Ω load is either 1/2 V_{OD1} or 2, whichever is greater.

SYMBOL EQUIVALENTS

DATA SHEET PARAMETER	RS-422-A	RS-485
V _O	V _{oa,} V _{ob}	V _{oa} , V _{ob}
VOD1	Vo	Vo
IV _{OD2} I	$V_t (R_L = 100 \Omega)$	$V_t (R_L = 54 \Omega)$
IVOD3		V _t (Test Termination) Measurement 2)
Δ V _{OD}	$ V_t - \overline{V}_t $	$ V_t - \overline{V}_t $
Voc	V _{OS}	V _{OS}
Δ V _{OC}	V _{OS}	VOS - VOS
los	$ I_{sa} , I_{sb} $	
IO	I _{xa} , I _{xb}	l _{ia} ,l _{ib}

RECEIVER SECTION

electrical characteristics over recommended ranges of common-mode input voltage, supply voltage, and operating free-air temperature (unless otherwise noted)

	PARAMETER	TEST CON	IDITIONS	MIN	TYP [†]	MAX	UNIT
V _{T+}	Positive-going input threshold voltage	$V_0 = 2.7 V$,	$I_{O} = -0.4 \text{ mA}$			0.2	V
V _T _	Negative-going input threshold voltage	V _O = 0.5 V,	IO = 8 mA	-0.2‡			V
V _{hys}	Input hysteresis (V _{T+} – V _{T-})				50		mV
٧ _{IK}	Input clamp voltage at EN	$I_{ } = -18 \text{ mA}$				-1.5	V
Vон	High-level output voltage	V _{ID} = 200 mV, See Figure 2	$I_{OH} = -400 \mu A,$	2.7			V
VOL	Low-level output voltage	V _{ID} = -200 mV, See Figure 2	I _{OL} = 8 mA,			0.45	V
1	High impedance state output ourrent	V- 0.4 V to 2.4 V				20	^
loz	High-impedance-state output current	$V_0 = 0.4 \text{ V to } 2.4 \text{ V}$				-400	μΑ
1.	Line input current	Other input at 0 V,	V _I = 12 V			1	A
"	Line input current	See Note 4	V _I = -7 V			-0.8	mA
lін	High-level enable-input current	V _{IH} = 2.7 V				20	μΑ
I _I L	Low-level enable-input current	V _{IL} = 0.4 V				-200	μΑ
rį	Input resistance			12			kΩ
los	Short-circuit output current			-15		-85	mA
loo	Supply current (total package)	No load	Outputs enabled		57	70	mA
ICC	oupply outform (total package)	I NO IOGU	Outputs disabled		26	35	111/7

 $[\]uparrow$ All typical values are at V_{CC} = 5 V, T_A = 25°C.

switching characteristics, $V_{CC} = 5 \text{ V}$, $T_A = 25^{\circ}\text{C}$


	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
tPLH	Propagation delay time, low-to-high level output	$V_{ID} = -1.5 \text{ V to } 1.5 \text{ V},$		19	35	
tPHL	Propagation delay time, high-to-low level output	C _L = 15 pF, See Figure 6		30	40	ns
^t PZH	Output enable time to high level	C: 45 pF Coo Figure 7		10	20	
tPZL	Output enable time to high level	C _L = 15 pF, See Figure 7		12	20	ns
^t PHZ	Output disable time from high level	C _I = 15 pF, See Figure 8		25	35	
tPLZ	Output disable time from low level	C _L = 15 pF, See Figure 8		17	25	ns



[‡] The algebraic convention, where the less-positive (more-negative) limit is designated minimum, is used in this data sheet for common-mode input voltage and threshold voltage levels only.

NOTE 4: Refer to EIA Standard RS-422 for exact conditions.

PARAMETER MEASUREMENT INFORMATION






Figure 1. Driver V_{OD} and V_{OC}

Figure 2. Receiver VOH and VOL




Figure 3. Driver Differential-Output Test Circuit and Voltage Waveforms




Figure 4. Driver Enable and Disable Times




Figure 5. Driver Enable and Disable Times

NOTES: A. The input pulse is supplied by a generator having the following characteristics: PRR \leq 1 MHz, 50% duty cycle, $t_{f} \leq$ 6 ns, $t_{f} \leq$ 7 ns, $t_{f} \leq$ 8 ns, $t_{f} \leq$ 8 ns, $t_{f} \leq$ 9 ns, $t_$

B. CL includes probe and jig capacitance.



PARAMETER MEASUREMENT INFORMATION




Figure 6. Receiver Propagation Delay Times




Figure 7. Receiver Output Enable and Disable Times

NOTES: A. The input pulse is supplied by a generator having the following characteristics: PRR \leq 1 MHz, 50% duty cycle, $t_{\Gamma} \leq$ 6 ns, $t_{\Gamma} \leq$ 7 ns, $t_{\Gamma} \leq$ 8 ns, $t_{\Gamma} \leq$ 8 ns, $t_{\Gamma} \leq$ 9 ns, $t_$

- B. C_L includes probe and jig capacitance.
- C. All diodes are 1N916 or equivalent.



TYPICAL CHARACTERISTICS

DRIVER HIGH-LEVEL OUTPUT VOLTAGE vs




Figure 8

DRIVER DIFFERENTIAL OUTPUT VOLTAGE




Figure 10

DRIVER LOW-LEVEL OUTPUT VOLTAGE vs




Figure 9

RECEIVER OUTPUT VOLTAGE vs




Figure 11

TYPICAL CHARACTERISTICS

RECEIVER HIGH-LEVEL OUTPUT VOLTAGE

HIGH-LEVEL OUTPUT CURRENT





Figure 12

RECEIVER LOW-LEVEL OUTPUT VOLTAGE

LOW-LEVEL OUTPUT CURRENT



0.1

0

0

5

Figure 14

15

IOL - Low-Level Output Current - mA

20

25

30

10

RECEIVER HIGH-LEVEL OUTPUT VOLTAGE

FREE-AIR TEMPERATURE




Figure 13

RECEIVER LOW-LEVEL OUTPUT VOLTAGE vs

FREE-AIR TEMPERATURE





Figure 15

APPLICATION INFORMATION



NOTE: The line should be terminated at both ends in its characteristic impedance. Stub lengths off the main line should be kept as short as possible.

Figure 16. Typical Application Circuit



IMPORTANT NOTICE

Texas Instruments (TI) reserves the right to make changes to its products or to discontinue any semiconductor product or service without notice, and advises its customers to obtain the latest version of relevant information to verify, before placing orders, that the information being relied on is current and complete.

TI warrants performance of its semiconductor products and related software to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are utilized to the extent TI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except those mandated by government requirements.

Certain applications using semiconductor products may involve potential risks of death, personal injury, or severe property or environmental damage ("Critical Applications").

TI SEMICONDUCTOR PRODUCTS ARE NOT DESIGNED, INTENDED, AUTHORIZED, OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT APPLICATIONS, DEVICES OR SYSTEMS OR OTHER CRITICAL APPLICATIONS.

Inclusion of TI products in such applications is understood to be fully at the risk of the customer. Use of TI products in such applications requires the written approval of an appropriate TI officer. Questions concerning potential risk applications should be directed to TI through a local SC sales office.

In order to minimize risks associated with the customer's applications, adequate design and operating safeguards should be provided by the customer to minimize inherent or procedural hazards.

TI assumes no liability for applications assistance, customer product design, software performance, or infringement of patents or services described herein. Nor does TI warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right of TI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used.

Copyright © 1998, Texas Instruments Incorporated

🍎 Texas Instru	MENTS	THE WORL	LEADER	IN DSP AND	ANALOG
Products		Development Tools	GO	Applications	GO
Search	0	☐ Advanced Search☐ Tech Support	☐ TI Home ☐ Comments	□ TI&ME □ Site Map	□ Employment □ Tl Global

>> <u>Semiconductor Home</u> > <u>Products</u> > <u>Analog & Mixed-Signal</u> > <u>Interface Products</u> > <u>Transmitters and Receivers</u> >

SN75178B, DIFFERENTIAL BUS REPEATERS

Device Status: Active

- > Description
- > Features
- > Datasheets
- > Pricing/Samples/Availability
- > Application Notes
- > Related Documents
- > Applications

Description

The SN75177B and SN75178B differential bus repeaters are monolithic integrated devices each designed for one-way data communication on multipoint bus transmission lines. These devices are designed for balanced transmission bus line applications and meet EIA Standard RS-422-A and RS-485 and CCITT Recommendations V.11 and X.27. Each device is designed to improve the performance of the data communication over long bus lines. The SN75177B and SN75178B are identical except for the complementary enable inputs, which allow the devices to be used in pairs for bidirectional communication.

The SN75177B and SN75178B feature positive- and negative-current limiting 3-state outputs for the receiver and driver. The receiver features high input impedance, input hysteresis for increased noise immunity, and input sensitivity of ±200 mV over a common-mode input voltage range of -7 V to 12 V. The driver features thermal shutdown for protection from line fault conditions. Thermal shutdown is designed to occur at a junction temperature of approximately 150°C. The driver is designed to drive current loads up to 60 mA maximum.

The SN75177B and SN75178B are designed for optimum performance when used on transmission buses employing the SN75172 and SN75174 differential

line drivers, SN75173 and SN75175 differential line receivers, or SN75176B bus transceiver.

Features

- Meets EIA Standards RS-422-A and RS-485 and CCITT Recommendations V.11 and X.27
- Designed for Multipoint Transmission on Long Bus Lines in Noisy Environments
- 3-State Outputs
- Bus Voltage Range . . . -7 V to 12 V
- Positive and Negative Current Limiting
- Driver Output Capability . . . 60 mA Max
- Driver Thermal Shutdown Protection
- Receiver Input Impedance . . . 12 kΩ Min
- Receiver Input Sensitivity . . . ±200 mV
- Receiver Input Hysteresis . . . 50 mV Typ
- Operates From Single 5-V Supply
- Low Power Requirements

To view the following documents, <u>Acrobat Reader 3.x</u> is required.

To download a document to your hard drive, right-click on the link and choose 'Save'.

Datasheets

Full datasheet in Acrobat PDF: stls002c.pdf (165 KB)
Full datasheet in Zipped PostScript: stls002c.psz (151 KB)

Pricing/Samples/Availability

Orderable Device	<u>Package</u>	Pins	<u>Temp</u> (°C)	<u>Status</u>	Price/unit <u>USD</u> (100-999)	Pack Oty	<u>Availability /</u> <u>Samples</u>
SN75178BD	D	8	0 TO 70	NRND	1.80	75	Check stock or order
SN75178BDR	D	8		ACTIVE	1.54	2500	Check stock or order
SN75178BP	<u>P</u>	8	0 TO 70	ACTIVE	1.80	50	Check stock or order
SN75178BPS	<u>PS</u>	8		OBSOLETE			_

Application Reports

- 422 AND 485 STANDARDS OVERVIEW AND SYSTEM CONFIGURATIONS (SLLA070A Updated: 05/25/2000)
- COMPARING BUS SOLUTIONS (SLLA067 Updated: 03/06/2000)
- <u>ELECTROSTATIC DISCHARGE APPLICATION NOTE</u> (SSYA008 Updated: 05/05/1999)
- JITTER ANALYSIS (SLLA075 Updated: 03/31/2000)

- SKEW DEFINITIONS (SLLA060 Updated: 08/13/1999)
- THERMAL CHARACTERISTICS OF LINEAR AND LOGIC PACKAGES USING JEDEC PCB DESIGNS (SZZA017A Updated: 09/10/1999)

Related Documents

• <u>A STATISTICAL SURVEY OF COMMON-MODE NOISE</u> (SLLA057, 131 KB - Updated: 12/23/1999)

Table Data Updated on: 8/3/2000

© Copyright 2000 Texas Instruments Incorporated. All rights reserved. <u>Trademarks | Privacy Policy</u>

