# National Semiconductor is now part of Texas Instruments.

Search <a href="http://www.ti.com/">http://www.ti.com/</a> for the latest technical information and details on our current products and services.

April 1998

## LM123/LM323A/LM323 3-Amp, 5-Volt Positive Regulator

### **General Description**

The LM123 is a three-terminal positive regulator with a preset 5V output and a load driving capability of 3 amps. New circuit design and processing techniques are used to provide the high output current without sacrificing the regulation characteristics of lower current devices.

The LM323A offers improved precision over the standard LM323. Parameters with tightened specifications include output voltage tolerance, line regulation, and load regulation.

The 3 amp regulator is virtually blowout proof. Current limiting, power limiting, and thermal shutdown provide the same high level of reliability obtained with these techniques in the LM109 1 amp regulator.

No external components are required for operation of the LM123. If the device is more than 4 inches from the filter capacitor, however, a 1  $\mu F$  solid tantalum capacitor should be used on the input. A 0.1  $\mu F$  or larger capacitor may be used on the output to reduce load transient spikes created by fast switching digital logic, or to swamp out stray load capacitance

An overall worst case specification for the combined effects of input voltage, load currents, ambient temperature, and power dissipation ensure that the LM123 will perform satisfactorily as a system element.

For applications requiring other voltages, see LM150 series adjustable regulator data sheet.


Operation is guaranteed over the junction temperature range -55°C to +150°C for LM123, -40°C to +125°C for LM323A, and 0°C to +125°C for LM323. A hermetic TO-3 package is used for high reliability and low thermal resistance.

#### **Features**

- Guaranteed 1% initial accuracy (A version)
- 3 amp output current
- Internal current and thermal limiting
- 0.01Ω typical output impedance
- 7.5V minimum input voltage
- 30W power dissipation
- P+ Product Enhancement tested

## **Connection Diagram**


#### Metal Can Package



Order Number LM123K STEEL, LM323AK STEEL or LM323K STEEL
See NS Package Number K02A
Order Number LM123K/883
See NS Package Number K02C

#### **Typical Applications**

#### **Basic 3 Amp Regulator**



\*Required if LM123 is more than 4" from filter capacitor.
†Regulator is stable with no load capacitor into resistive loads.

## **Absolute Maximum Ratings** (Note 1)

If Military/Aerospace specified devices are required, please contact the National Semiconductor Sales Office/ Distributors for availability and specifications.

(Note 5)

Input Voltage 20V Power Dissipation Internally Limited

Operating Junction Temperature Range

Lead Temperature (Soldering, 10 sec.) 300°C ESD Tolerance (Note 5) 2000V

## LM123 Electrical Characteristics (Note 2)

Conditions		Units		
	Min	Тур	Max	
$T_j = 25^{\circ}C$	4.7	5	5.3	V
$V_{IN} = 7.5V, I_{OUT} = 0A$				
$7.5V \le V_{IN} \le 15V$	4.6		5.4	V
$0A \le I_{OUT} \le 3A, P \le 30W$				
$T_j = 25^{\circ}C$		5	25	mV
$7.5V \le V_{IN} \le 15V$				
$T_j = 25^{\circ}C, V_{IN} = 7.5V,$		25	100	mV
0A ≤ I <sub>OUT</sub> ≤ 3A				
$7.5V \le V_{IN} \le 15V$ ,		12	20	mA
0A ≤ I <sub>OUT</sub> ≤ 3A				
$T_j = 25^{\circ}C$		40		μVrms
10 Hz ≤ f ≤ 100 kHz				
$T_j = 25^{\circ}C$				
V <sub>IN</sub> = 15V		3	4.5	A
V <sub>IN</sub> = 7.5V		4	5	A
			35	mV
		2		°C/W
	$\begin{split} T_j &= 25^{\circ}\text{C} \\ V_{IN} &= 7.5\text{V}, \ I_{OUT} = 0\text{A} \\ 7.5\text{V} &\leq V_{IN} \leq 15\text{V} \\ 0\text{A} &\leq I_{OUT} \leq 3\text{A}, \ P \leq 30\text{W} \\ T_j &= 25^{\circ}\text{C} \\ 7.5\text{V} &\leq V_{IN} \leq 15\text{V} \\ T_j &= 25^{\circ}\text{C}, \ V_{IN} = 7.5\text{V}, \\ 0\text{A} &\leq I_{OUT} \leq 3\text{A} \\ 7.5\text{V} &\leq V_{IN} \leq 15\text{V}, \\ 0\text{A} &\leq I_{OUT} \leq 3\text{A} \\ T_j &= 25^{\circ}\text{C} \\ 10 \ \text{Hz} &\leq f \leq 100 \ \text{kHz} \\ T_j &= 25^{\circ}\text{C} \\ V_{IN} &= 15\text{V} \end{split}$	$\begin{array}{c} \text{Min} \\ T_{j} = 25\text{°C} \\ V_{IN} = 7.5\text{V},  I_{OUT} = 0\text{A} \\ \hline 7.5\text{V} \leq V_{IN} \leq 15\text{V} \\ 0\text{A} \leq I_{OUT} \leq 3\text{A},  P \leq 30\text{W} \\ \hline T_{j} = 25\text{°C} \\ 7.5\text{V} \leq V_{IN} \leq 15\text{V} \\ \hline T_{j} = 25\text{°C},  V_{IN} = 7.5\text{V}, \\ 0\text{A} \leq I_{OUT} \leq 3\text{A} \\ \hline 7.5\text{V} \leq V_{IN} \leq 15\text{V}, \\ 0\text{A} \leq I_{OUT} \leq 3\text{A} \\ \hline T_{j} = 25\text{°C} \\ 10  \text{Hz} \leq f \leq 100  \text{kHz} \\ \hline T_{j} = 25\text{°C} \\ 10  \text{Hz} \leq f \leq 100  \text{kHz} \\ \hline \end{array}$	$\begin{array}{c ccccccccccccccccccccccccccccccccccc$	$\begin{array}{c ccccccccccccccccccccccccccccccccccc$

## LM323A/LM323 Electrical Characteristics (Note 2)

Parameter	Conditions	LM323A			LM323			Units
		Min	Тур	Max	Min	Тур	Max	1
Output Voltage	$T_j = 25^{\circ}C$	4.95	5	5.05	4.8	5	5.2	V
	$V_{IN} = 7.5V, I_{OUT} = 0A$							
	$7.5V \le V_{IN} \le 15V$	4.85		5.15	4.75		5.25	V
	$0A \le I_{OUT} \le 3A, P \le 30W$							
Line Regulation (Note 4)	$T_j = 25^{\circ}C$		5	10		5	25	mV
	$7.5V \le V_{IN} \le 15V$							
Load Regulation (Note 4)	$T_j = 25^{\circ}C, V_{IN} = 7.5V,$		25	50		25	100	mV
	$0A \le I_{OUT} \le 3A$							
Quiescent Current	$7.5V \le V_{IN} \le 15V$ ,		12	20		12	20	mA
	$0A \le I_{OUT} \le 3A$							
Output Noise Voltage	$T_j = 25^{\circ}C$		40			40		μVrms
	10 Hz ≤ f ≤ 100 kHz							
Short Circuit Current Limit	T <sub>j</sub> = 25°C							
	V <sub>IN</sub> = 15V		3	4.5		3	4.5	Α
	V <sub>IN</sub> = 7.5V		4	6		4	5	Α
Long Term Stability				35			35	mV
Thermal Resistance Junction to Case (Note 3)			2			2		°C/W

www.national.com

#### LM323A/LM323 Electrical Characteristics (Note 2) (Continued)

Note 1: "Absolute Maximum Ratings" indicate limits beyond which damage to the device may occur. Operating Ratings indicate conditions for which the device is functional, but do not guarantee specific performance limits.

Note 2: Unless otherwise noted, specifications apply for  $-55^{\circ}\text{C} \le T_j \le +150^{\circ}\text{C}$  for the LM123,  $-40^{\circ}\text{C} \le T_j \le +125^{\circ}\text{C}$  for the LM323A, and  $0^{\circ}\text{C} \le T_j \le +125^{\circ}\text{C}$  for the LM323. Although power dissipation is internally limited, specifications apply only for P  $\le$  30W.

Note 3: Without a heat sink, the thermal resistance of the TO-3 package is about 35°C/W. With a heat sink, the effective thermal resistance can only approach the specified values of 2°C/W, depending on the efficiency of the heat sink.


Note 4: Load and line regulation are specified at constant junction temperature. Pulse testing is required with a pulse width ≤ 1 ms and a duty cycle ≤ 5%.

Note 5: Refer to RETS123K drawing for LM123K military specifications.


Note 6: Human body model, 1.5 k $\Omega$  in series with 100 pF.

### **Typical Performance Characteristics**


## Maximum Average Power Dissipation for LM123




## Maximum Average Power Dissipation for LM323A, LM323




#### **Output Impedance**




#### **Peak Available Output Current**




#### **Short Circuit Current**




Ripple Rejection




#### **Dropout Voltage**



Line Transient Response




Output Voltage




DS007771-17

## Typical Performance Characteristics (Continued)


#### **Quiescent Current**



#### Load Transient Response




### Output Noise Voltage



## **Typical Applications**


### 10 Amp Regulator with Complete Overload Protection



\*Select for 20 mA Current from Unregulated Negative Supply

## Typical Applications (Continued)


## Adjustable Regulator 0V-10V @ 3A




\*R6 = 
$$\frac{V^{-}}{12 \text{ mA}}$$

 $\rm A_1-LM101A$   $\rm C_1-2~\mu F$  Optional — Improves Ripple Rejection, Noise, and Transient Response

#### Trimming Output to 5V




### Adjustable Output 5V-10V 0.1% Regulation




\*Select to Set Output Voltage


\*\*Select to Draw 25 mA from V-



www.national.com



Metal Can Package (K)
Order Number LM123K STEEL, LM323AK STEEL or LM323K STEEL
NS Package Number K02A



### LIFE SUPPORT POLICY

NATIONAL'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT AND GENERAL COUNSEL OF NATIONAL SEMICONDUCTOR CORPORATION. As used herein:

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
- 2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.



National Semiconductor Corporation

Tel: 1-800-272-9959 Fax: 1-800-737-7018 Email: support@nsc.com

www.national.com

National Semiconductor Europe

Fax: +49 (0) 1 80-530 85 86

Fax: +49 (0) 1 80-530 85 86
Email: europe.support@nsc.com
Deutsch Tel: +49 (0) 1 80-530 85 85
English Tel: +49 (0) 1 80-532 78 32
Français Tel: +49 (0) 1 80-532 93 58
Italiano Tel: +49 (0) 1 80-534 16 80

National Semiconductor Asia Pacific Customer Response Group Tel: 65-2544466 Fax: 65-2504466

Email: sea.support@nsc.com

National Semiconductor Japan Ltd. Tel: 81-3-5639-7560 Fax: 81-3-5639-7507