
SLLS061 - D3407, JANUARY 1990


- Bidirectional Transceiver
- Designed for Multipoint Transmission in Noisy Environments Such as Automotive Applications
- 3-State Driver and Receiver Outputs
- Individual Driver and Receiver Enables
- Wide Positive and Negative Input/Output Bus Voltage Ranges
- Driver Output Capability . . . ±10 mA Max
- Thermal Shutdown Protection
- Driver Positive and Negative Current Limiting
- Receiver Input Impedance . . . 12 k $\Omega$  Min
- Receiver Input Sensitivity . . . ±200 mV
- Receiver Input Hysteresis . . . 50 mV Typ
- Operates From Single 5-V Supply
- Low Power Requirements

#### description

The SN65076B and SN75076B differential bus transceivers are monolithic integrated circuits designed for bidirectional data communication on multipoint bus transmission lines. They are designed for noisy environments, where a low-impedance termination to ground is required.




#### logic symbol<sup>†</sup>



<sup>†</sup> This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

#### logic diagram (positive logic)



The SN65076B and SN75076B combine a differential line driver and a differential input line receiver, both of which operate from a single 5-V power supply. The receiver has an active-low enable. The driver differential outputs and the receiver differential inputs are connected internally to form differential input/output (I/O) bus ports that are designed to offer minimum loading to the bus whenever the driver is disabled or  $V_{CC} = 0$ . These ports feature wide positive and negative common-mode voltage ranges making the device suitable for party-line applications.

#### **Function Tables**

#### DRIVER

INPUT	OUT	PUTS
D	Α	В
H L	Н ∟†	L H†

<sup>†</sup> These levels assume that the open-collector outputs (A) and the open-emitter outputs (B) are connected to a pullup and pulldown resistor, respectively. RECEIVER

DIFFERENTIAL INPUTS A – B	ENABLE RE	OUTPUT R
V <sub>ID</sub> ≥ 0.2 V	L	L
-0.2 V < V <sub>ID</sub> < 0.2 V	L	?
$V_{ID} \leq -0.2 V$	L	Н
X	Н	Z

H = high level, L = low level, ? = indeterminate; X = irrelevant, Z = high impedance (off)

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.




2–1

SLLS061 – D3407, JANUARY 1990

#### description (continued)

The driver is designed to handle loads up to 10 mA of sink and source current. The driver features positive- and negative-current limiting and thermal shutdown for protection from line fault conditions. Thermal shutdown is designed to occur at a junction temperature of approximately 150°C in the P package and 170°C in the D package. The receiver features a minimum input impedance of 12 k $\Omega$ , an input sensitivity of ±200 mV, and a typical input hysteresis of 50 mV.

The SN65076B is characterized for operation from  $-40^{\circ}$ C to  $105^{\circ}$ C and the SN75076B is characterized for operation from  $0^{\circ}$ C to  $70^{\circ}$ C.





SLLS061 – D3407, JANUARY 1990

#### absolute maximum ratings over operating free-air temperature range (unless otherwise noted)

Supply voltage, V <sub>CC</sub> (see Note 1)	
Enable input voltage	
Continuous total power dissipation	
Operating free-air temperature range: SN65076B	
SN75076B	0°C to 70°C
Storage temperature range	–65°C to 150°C
Lead temperature 1,6 mm (1/16 inch) from the case for 10 seconds	260°C

NOTE 1: All voltage values, except differential input/output bus voltage, are with respect to network ground terminal.

DISSIPATION RATING TABLE							
PACKAGE	T <sub>A</sub> ≤ 25°C POWER RATING	DERATING FACTOR ABOVE T <sub>A</sub> = 25°C	T <sub>A</sub> = 70°C POWER RATING	T <sub>A</sub> = 105°C POWER RATING			
D	725 mW	5.8 mW/°C	464 mW	261 mW			
Р	1100 mW	8.8 mW/°C	702 mW	396 mW			

### recommended operating conditions

			MIN	NOM	MAX	UNIT
Supply voltage, V <sub>CC</sub>			4.75	5	5.25	V
Veltage et envirus terminel (concretely er commen mede) V( er V( -					12	V
Voltage at any bus terminal (separately or common mode), VI or VIC				-7	v	
High-level input voltage, $V_{IH}$		D and RE	2			V
Low-level input voltage, VIL		D and RE			0.8	V
Differential input voltage, VID (see Note 2)					±12	V
High lovel output ourrent love		Driver (A)			-10	mA
High-level output current, I <sub>OH</sub>		Receiver			-400	μA
		Driver (B)			10	
Low-level output current, IOL		Receiver			8	mA
Operating free-air temperature, $T_A$	SN65076B		-40		105	°C
	SN75076B		0		70	C

NOTE 2: Differential-input/output bus voltage is measured at the noninverting terminal A with respect to the inverting terminal B.



SLLS061 – D3407, JANUARY 1990

### **DRIVER SECTION**

# electrical characteristics over recommended ranges of supply voltage and operating free-air temperature

	PARAMETER	TE	ST CONDITIONS	MIN	MAX	UNIT	
VIK	Input clamp voltage	lj = -18 mA			-1.5	V	
VO	Output voltage	V <sub>I</sub> = 2 V,	IO = 0	0	6	V	
V <sub>OD1</sub>	Differential output voltage	I <sub>O</sub> = 0		1.5	6	V	
VOD2	Differential output voltage	See Figure 1		1.5	5	V	
1.0	Output ourroat	VI. 0.9.V	V <sub>O</sub> = 12 V		1	~^^	
10	Output current	V <sub>1</sub> = 0.8 V	$V_0 = -7 V$		-0.8	mA	
Iн	High-level input current	V <sub>I</sub> = 2.4 V	V <sub>1</sub> = 2.4 V		20	μA	
۱ <sub>IL</sub>	Low-level input current	V <sub>I</sub> = 0.4 V			-400	μA	
		V <sub>O</sub> = -7 V	$V_{O} = -7 V$ $V_{O} = 0$		-250		
1	Short-circuit output current	$V_{O} = 0$			-150	mA	
los		VO = VCC	V <sub>O</sub> = V <sub>CC</sub>		250	0 114	
		V <sub>O</sub> = 12 V	V <sub>O</sub> = 12 V		250		
ICC	Supply current (total package)	No load			30	mA	

### switching characteristics, V<sub>CC</sub> = 5 V, T<sub>A</sub> = $25^{\circ}$ C

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
ton	Differential-output turn-on time			60	90	ns
toff	Differential-output turn-off time	See Figure 3		75	110	ns



SLLS061 - D3407, JANUARY 1990

### **RECEIVER SECTION**

# electrical characteristics over recommended ranges of common-mode input voltage, supply voltage, and operating free-air temperature (unless otherwise noted)

	PARAMETER	TEST COND	ITIONS	MIN	TYP†	MAX	UNIT
V <sub>T+</sub>	Positive-going input threshold voltage	V <sub>O</sub> = 2.7 V,	$I_{O} = -0.4 \text{ mA}$			0.2	V
$V_{T-}$	Negative-going input threshold voltage	V <sub>O</sub> = 0.5 V,	IO = 8 mA	-0.2‡			V
V <sub>hys</sub>	Hysteresis (V <sub>T+</sub> – V <sub>T</sub> _)				50		mV
VIK	Enable-input clamp voltage	lj = – 18 mA				-1.5	V
Vон	High-level output voltage	V <sub>ID</sub> = −200 mV, See Figure 2	I <sub>OH</sub> = -400 μA,	2.7			V
VOL	Low-level output voltage	V <sub>ID</sub> = −200 mV, See Figure 2	I <sub>OL</sub> = 8 mA,			0.45	V
IOZ	High-impedance-state output current	V <sub>O</sub> = 0.4 V to 2.4 V				±20	μΑ
tı -	Line input current		VI = 12 V, See Note 3			1 -0.8	mA
IIН	High-level enable-input current	V <sub>IH</sub> = 2.7 V				20	μΑ
IIL	Low-level enable-input current	V <sub>IL</sub> = 0.4 V				-100	μΑ
ri	Input resistance			12			kΩ
los	Short-circuit output current			-15		-85	mA
ICC	Supply current (total package)	No load				30	mA

<sup>†</sup> All typical values are at  $V_{CC} = 5 \text{ V}$ ,  $T_A = 25^{\circ}\text{C}$ .

<sup>‡</sup> The algebraic convention, in which the less-positive (more-negative) limit is designated minimum, is used in this data sheet for threshold voltage levels only.


NOTE 3: This applies for both power on and power off.

### switching characteristics, V<sub>CC</sub> = 5 V, C<sub>L</sub> = 15 pF, T<sub>A</sub> = 25°C


	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
<sup>t</sup> PLH	Propagation delay time, low-to-high level output	VID = 0 to 3 V, See Figure 4		21	35	ns
<sup>t</sup> PHL	Propagation delay time, high-to-low level output	V D = 0.03 V, See Figure 4		23	35	ns
<sup>t</sup> PZH	Output enable time to high level	Soo Eiguro E		10	20	ns
<sup>t</sup> PZL	Output enable time to low level	See Figure 5		12	20	ns
<sup>t</sup> PHZ	Output disable time from high level	Soo Eiguro E		20	35	ns
<sup>t</sup> PLZ	Output disable time from low level	See Figure 5		17	25	ns




SLLS061 – D3407, JANUARY 1990







**TEST CIRCUIT** 






Input 1.5 V 1.5 V 0 Vton  $t_{0}$  0 V 1.5 V 0 V1.5 V -1 V

VOLTAGE WAVEFORMS

Figure 3. Driver Differential-Output Delay Times




#### Figure 4. Receiver Test Circuit and Voltage Waveforms Propagation Delay Times

- NOTES: A. The input pulse is supplied by a generator having the following characteristics: PRR  $\leq$  500 kHz, 50% duty cycle, t<sub>f</sub>  $\leq$  6 ns, t<sub>f</sub>  $\leq$  6 ns, Z<sub>O</sub> = 50  $\Omega$ .
  - B. CL includes probe and jig capacitance.



SLLS061 – D3407, JANUARY 1990





- NOTES: A. The input pulse is supplied by a generator having the following characteristics: PRR  $\leq$  500 kHz, 50% duty cycle, t<sub>f</sub>  $\leq$  6 ns, t<sub>f</sub>  $\leq$  6 ns, Z<sub>O</sub> = 50  $\Omega$ .
  - B. CL includes probe and jig capacitance.



SLLS061 – D3407, JANUARY 1990


#### **RECEIVER HIGH-LEVEL OUTPUT VOLTAGE RECEIVER HIGH-LEVEL OUTPUT<sup>†</sup>** vs vs **HIGH-LEVEL OUTPUT CURRENT** FREE-AIR TEMPERATURE 5 5 $V_{CC} = 5 V$ $V_{ID} = 0.2 V$ V<sub>ID</sub> = 200 mV T<sub>A</sub> = 25°C V<sub>OH</sub> – High-Level Output Voltage – V V<sub>OH</sub> – High-Level Output Voltage – V **I**OH = - 440 μA 4 4 3 3 V<sub>CC</sub> = 5.25 V 2 2 $V_{CC} = 5 V$ V<sub>CC</sub> = 4.75 V 1 1 0 0 0 - 10 - 20 - 30 - 40 - 50 -40 -20 0 20 40 60 80 100 120 T<sub>A</sub> – Free-Air Temperature – °C IOH - High-Level Output Current - mA Figure 7 Figure 6 **RECEIVER LOW-LEVEL OUTPUT VOLTAGE RECEIVER LOW-LEVEL OUTPUT VOLTAGE<sup>†</sup>** VS vs **RECEIVER LOW-LEVEL OUTPUT CURRENT** FREE-AIR TEMPERATURE 0.6 0.6 $V_{CC} = 5 V$ $V_{CC} = 5 V$ T<sub>A</sub> = 25°C $V_{ID} = -200 \text{ mV}$ V<sub>OL</sub> – Low-Level Output Voltage – V V<sub>OL</sub> – Low-Level Output Voltage – V 0.5 0.5 IOL = 8 mA 0.4 0.4 0.3 0.3 0.2 0.2 0.1 0.1 0 0 0 5 10 15 20 25 30 - 40 - 20 40 80 100 120 0 20 60 IOL - Low Level Output Current - mA T<sub>A</sub> – Free-Air Temperature – °C Figure 8 Figure 9

**TYPICAL CHARACTERISTICS** 


<sup>†</sup>Only the 0°C to 70°C portion of the curve applies for the SN75076B.



SLLS061 - D3407, JANUARY 1990



## APPLICATION INFORMATION



#### Figure 12. Typical Application Circuit



#### PACKAGING INFORMATION

Orderable Device	Status <sup>(1)</sup>	Package Type	Package Drawing	Pins Package Qty	Eco Plan <sup>(2)</sup>	Lead/Ball Finish	MSL Peak Temp <sup>(3)</sup>
SN75076BP	OBSOLETE	PDIP	Р	8	TBD	Call TI	Call TI

<sup>(1)</sup> The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS) or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details. TBD: The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

<sup>(3)</sup> MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

#### **IMPORTANT NOTICE**

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DSP	dsp.ti.com	Broadband	www.ti.com/broadband
Interface	interface.ti.com	Digital Control	www.ti.com/digitalcontrol
Logic	logic.ti.com	Military	www.ti.com/military
Power Mgmt	power.ti.com	Optical Networking	www.ti.com/opticalnetwork
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
		Telephony	www.ti.com/telephony
		Video & Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless

Mailing Address:

Texas Instruments

Post Office Box 655303 Dallas, Texas 75265

Copyright © 2005, Texas Instruments Incorporated