

- Choice of Open-Collector, Open-Emitter, or 3-State Outputs
- High-Impedance Output State for Party-Line Applications
- Single-Ended or Differential AND/NAND Outputs
- Single 5-V Supply
- Dual Channel Operation
- Compatible With TTL
- Short-Circuit Protection
- High-Current Outputs
- Common and Individual Output Controls
- Clamp Diodes at Inputs and Outputs
- Easily Adaptable to SN55114 and SN75114 Applications
- Designed for Use With SN55115 and SN75115


#### description

The SN55113 and SN75113 dual differential line drivers with 3-state outputs are designed to provide all the features of the SN55114 and SN75114 line drivers with the added feature of driver output controls. Individual controls are provided for each output pair, as well as a common control for both output pairs. If any output





# SN55113 . . . FK PACKAGE (TOP VIEW)



NC - No internal connection

is low, the associated output is in a high-impedance state and the output can neither drive nor load the bus. This permits many devices to be connected together on the same transmission line for party-line applications.

The output stages are similar to TTL totem-pole outputs, but with the sink outputs, YS and ZS, and the corresponding active pullup terminals, YP and ZP, available on adjacent package pins.

The SN55113 is characterized for operation over the full military temperature range of –55°C to 125°C. The SN75113 is characterized for operation over the temperature range of 0°C to 70°C.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.




#### **FUNCTION TABLE**

	OUTPUTS				
OUTPUT	CONTROL	D/	ATA	AND	NAND
С	CC	Α	в†	Y	Z
L	Х	Х	Х	Z	Z
Х	L	Х	Χ	Z	Z
Н	Н	L	Χ	L	Н
Н	Н	Х	L	L	Н
Н	Н	Н	Н	Н	L

H = high level, L = low level, X = irrelevant,


# logic symbol‡



<sup>&</sup>lt;sup>‡</sup> This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

Pin numbers shown are for the J, N, and W packages.


# logic diagram (positive logic)



Z = high impedance (off)

<sup>†</sup>B input and 4th line of function table are applicable only to driver number 1.

#### schematic



<sup>†</sup> These components are common to both drivers. Resistor values shown are nominal and in ohms.

# absolute maximum ratings over operating free-air temperature range (unless otherwise noted)‡

Supply voltage, V <sub>CC</sub> (see Note 1)	7 V
Input voltage, V <sub>I</sub>	
Off-state voltage applied to open-collector outputs	12 V
Continuous total power dissipation (see Note 2)	See Dissipation Rating Table
Operating free-air temperature range, T <sub>A</sub> : SN55113	–55°C to 125°C
SN75113	0°C to 70°C
Storage temperature range, T <sub>stq</sub>	65°C to 150°C
Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds: N package .	260°C
Case temperature for 60 seconds: FK package	260°C
Lead temperature 1,6 mm (1/16 inch) from case for 60 seconds: J or W packa	ge 300°C

<sup>‡</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

#### DISSIPATION RATING TABLE

PACKAGE	$T_{\mbox{A}} \le 25^{\circ}\mbox{C}$ POWER RATING			T <sub>A</sub> = 125°C POWER RATING
FK	1375 mW	11.0 mW/°C	880 mW	275 mW
J	1375 mW	11.0 mW/°C	880 mW	275 mW
N	1150 mW	9.2 mW/°C	736 mW	N/A
W	1000 mW	8.0 mW/°C	640 mW	200 mW



# SN55113, SN75113 **DUAL DIFFERENTIAL LINE DRIVERS**

SLLS070C - SEPTEMBER 1973 - REVISED MARCH 1997

## recommended operating conditions

	;	SN55113			SN75113		
	MIN	NOM	MAX	MIN	NOM	MAX	UNIT
Supply voltage, V <sub>CC</sub>	4.5	5	5.5	4.75	5	5.25	V
High-level input voltage, VIH	2			2			V
Low-level input voltage, V <sub>IL</sub>			8.0			0.8	V
High-level output current, IOH			- 40			- 40	mA
Low-level output current, IOL			40			40	mA
Operating free-air temperature, TA	-55		125	0		70	°C

## electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

	PARAMETER		PARAMETER TEST CONDITIONS†		uo.t		SN55113			SN75113			
			'5	SI CONDITION	181	MIN	TYP <sup>‡</sup>	MAX	MIN	TYP <sup>‡</sup>	MAX	UNIT	
۷ıĸ	Input clamp vo	ltage	V <sub>CC</sub> = MIN,	I <sub>I</sub> = -12 mA			-0.9	-1.5		-0.9	-1.5	V	
V0	High-level outp	out	V <sub>CC</sub> = MIN,	V <sub>IH</sub> = 2 V,	$I_{OH} = -10 \text{ mA}$	2.4	3.4		2.4	3.4		V	
VOH	voltage		V <sub>IL</sub> = 0.8 V		$I_{OH} = -40  \text{mA}$	2	3.0		2	3.0		V	
VOL	Low-level outp	out	$V_{CC} = MIN,$ $I_{OL} = 40 \text{ mA}$	V <sub>IH</sub> = 2 V,	V <sub>IL</sub> = 0.8 V,		0.23	0.4		0.23	0.4	V	
Vок	Output clamp	voltage	$V_{CC} = MAX$ ,	$I_{O} = -40 \text{ mA}$			-1.1	-1.5		-1.1	-1.5	V	
				V <sub>OH</sub> = 12 V	T <sub>A</sub> = 25°C		1	10					
10, 00	Off-state	autaut	V <sub>CC</sub> = MAX	VOH = 12 V	T <sub>A</sub> = 125°C			200					
<sup>I</sup> O(off)	open-collector current	output	ACC = MAX	V <sub>OH</sub> = 5.25 V	T <sub>A</sub> = 25°C					1	10	10 μA	
				VOH = 5.25 V	T <sub>A</sub> = 70°C						20		
				$T_A = 25^{\circ}C$ ,	$V_O = 0$ to $V_{CC}$			±10			±10		
	Off-state		-state $V_{CC} = MAX$ ,		V <sub>O</sub> = 0			-150			-20	J l	
loz		' Controls at 1	Controls at $T_A = MAX$		$V_0 = 0.4 \text{ V}$			±80			±20	μΑ	
	output current		0.8 V	I IA - WIAX	V <sub>O</sub> = 2.4 V			±80			±20		
					AO = ACC			80			20		
<b>.</b>	Input current	A, B, C		\/ E = \/				1			1	^	
†¡	at maximum input voltage	СС	$V_{CC} = MAX,$	V <sub>I</sub> = 5.5 V				2			2	mA	
1	High-level	A, B, C	V <sub>CC</sub> = MAX,	\\. 2.4\\				40			40		
ΊΗ	input current	CC	VCC = MAX	V  = 2.4 V	Î			80			80	μΑ	
1	Low-level	A, B, C	\/00 - MAY	V MAY V 0.4V				-1.6			-1.6	mA	
ΊL	input current	CC	$V_{CC} = MAX, V_I = 0.4 V$					-3.2			-3.2	IIIA	
los	Short-circuit output current	§	V <sub>CC</sub> = MAX,	V <sub>O</sub> = 0,	T <sub>A</sub> = 25°C	-40	-90	-120	-40	-90	-120	mA	
loo	Supply current	t	All inputs at 0 \	/, No load,	$V_{CC} = MAX$		47	65		47	65	m A	
ICC	(both drivers)		$T_A = 25^{\circ}C$		V <sub>CC</sub> = 7 V		65	85		65	85	mA	

<sup>†</sup> All parameters with the exception of off-state open-collector output current are measured with the active pullup connected to the sink output. For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.




 $<sup>\</sup>ddagger$  All typical values are at TA = 25°C and VCC = 5 V, with the exception of VCC at 7 V.


<sup>§</sup> Only one output should be shorted at a time, and duration of the short-circuit should not exceed one second.

# switching characteristics, $V_{CC}$ = 5 V, $C_L$ = 30 pF, $T_A$ = 25°C

PARAMETER		TEST CONDITIONS	S	N55113	}	S	UNIT		
		TEST CONDITIONS	MIN	TYP	MAX	MIN	TYP	MAX	ONIT
tPLH	Propagation delay time, low-to-high level output	See Figure 1		13	20		13	30	ns
tPHL	Propagation delay time, high-to-low-level output	See Figure 1		12	20		12	30	ns
<sup>t</sup> PZH	Output enable time to high level	$R_L$ = 180 Ω, See Figure 2		7	15		7	20	ns
tPZL	Output enable time to low level	$R_L$ = 250 Ω, See Figure 3		14	30		14	40	ns
t <sub>PHZ</sub>	Output disable time from high level	$R_L$ = 180 Ω, See Figure 2		10	20		10	30	ns
t <sub>PLZ</sub>	Output disable time from low level	$R_L$ = 250 Ω, See Figure 3		17	35		17	35	ns

## PARAMETER MEASUREMENT INFORMATION






NOTES: A. The pulse generator has the following characteristics:  $Z_0 = 50 \Omega$ , PRR  $\leq 500 \text{ kHz}$ ,  $t_W = 100 \text{ ns}$ .

B. C<sub>L</sub> includes probe and jig capacitance.

Figure 1. Test Circuit and Voltage Waveforms t<sub>PLH</sub> and t<sub>PHL</sub>



### PARAMETER MEASUREMENT INFORMATION



**VOLTAGE WAVEFORMS** 

NOTES: A. The pulse generator has the following characteristics:  $Z_O = 50 \ \Omega$ , PRR  $\leq 500 \ kHz$ ,  $t_W = 100 \ ns$ .


B. C<sub>I</sub> includes probe and jig capacitance.


Figure 2. Test Circuit and Voltage Waveforms tpzH and tpHZ

<sup>t</sup>PHZ

 $V_{off}\approx 0~V$ 

### PARAMETER MEASUREMENT INFORMATION






**VOLTAGE WAVEFORMS** 

NOTES: A. The pulse generator has the following characteristics:  $Z_O$  = 50  $\Omega$ , PRR  $\leq$  500 kHz,  $t_W$  = 100 ns.

B. C<sub>L</sub> includes probe and jig capacitance.

Figure 3. Test Circuit and Voltage Waveforms,  $t_{\mbox{\scriptsize PZL}}$  and  $t_{\mbox{\scriptsize PLZ}}$ 


#### TYPICAL CHARACTERISTICS<sup>†</sup>



<sup>†</sup> Data for temperatures below 0°C and above 70°C and for supply voltages below 4.75 V and above 5.25 V are applicable to SN55113 circuits only. These parameters were measured with the active pullup connected to the sink output.




#### TYPICAL CHARACTERISTICS†



<sup>†</sup> Data for temperatures below 0°C and above 70°C and for supply voltages below 4.75 V and above 5.25 V are applicable to SN55113 circuits only. These parameters were measured with the active pullup connected to the sink output.




### TYPICAL CHARACTERISTICS†




<sup>†</sup> Data for temperatures below 0°C and above 70°C and for supply voltages below 4.75 V and above 5.25 V are applicable to SN55113 circuits only. These parameters were measured with the active pullup connected to the sink output.



#### TYPICAL CHARACTERISTICS<sup>†</sup>



<sup>†</sup> Data for temperatures below 0°C and above 70°C and for supply voltages below 4.75 V and above 5.25 V are applicable to SN55113 circuits only. These parameters were measured with the active pullup connected to the sink output.



 $\ddagger R_T = Z_O$ . A capacitor may be connected in series with  $R_T$  to reduce power dissipation.

Figure 18. Basic Party-Line or Data-Bus Differential Data Transmission



#### **IMPORTANT NOTICE**

Texas Instruments and its subsidiaries (TI) reserve the right to make changes to their products or to discontinue any product or service without notice, and advise customers to obtain the latest version of relevant information to verify, before placing orders, that information being relied on is current and complete. All products are sold subject to the terms and conditions of sale supplied at the time of order acknowledgement, including those pertaining to warranty, patent infringement, and limitation of liability.

TI warrants performance of its semiconductor products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are utilized to the extent TI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except those mandated by government requirements.

CERTAIN APPLICATIONS USING SEMICONDUCTOR PRODUCTS MAY INVOLVE POTENTIAL RISKS OF DEATH, PERSONAL INJURY, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE ("CRITICAL APPLICATIONS"). TI SEMICONDUCTOR PRODUCTS ARE NOT DESIGNED, AUTHORIZED, OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT DEVICES OR SYSTEMS OR OTHER CRITICAL APPLICATIONS. INCLUSION OF TI PRODUCTS IN SUCH APPLICATIONS IS UNDERSTOOD TO BE FULLY AT THE CUSTOMER'S RISK.

In order to minimize risks associated with the customer's applications, adequate design and operating safeguards must be provided by the customer to minimize inherent or procedural hazards.

TI assumes no liability for applications assistance or customer product design. TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right of TI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used. TI's publication of information regarding any third party's products or services does not constitute TI's approval, warranty or endorsement thereof.

Copyright © 1998, Texas Instruments Incorporated



>> Semiconductor Home > Products > Analog & Mixed-Signal > Interface Products > Transmitters and Receivers >

#### SN75113, DUAL DIFFERENTIAL LINE DRIVER

**Device Status: Active** 

- > Description
- > Features
- > Datasheets
- > Pricing/Samples/Availability
- > Application Notes
- > Related Documents
- > Development Tools
- > Applications

Parameter Name	SN75113
Drivers Per Package	2
Driver tpd (ns)	30
Driver (RL) (Ohms)	100
Supply Voltage(s) (V)	5
ICC (max) (mA)	65
Footprint	SN75113

## **Description**

The SN55113 and SN75113 dual differential line drivers with 3-state outputs are designed to provide all the features of the SN55114 and SN75114 line drivers with the added feature of driver output controls. Individual controls are provided for each output pair, as well as a common control for both output pairs. If any output is low, the associated output is in a high-impedance state and the output can neither drive nor load the bus. This permits many devices to be connected together on the same transmission line for party-line applications.

The output stages are similar to TTL totem-pole outputs, but with the sink outputs, YS and ZS, and the corresponding active pullup terminals, YP and ZP, available on adjacent package pins.

The SN55113 is characterized for operation over the full military temperature range of -55° C to 125°C. The SN75113 is characterized for operation over the temperature range of 0°C to 70°C.

### **Features**

- Choice of Open-Collector, Open-Emitter, or 3-State Outputs
- High-Impedance Output State for Party-Line Applications
- Single-Ended or Differential AND/NAND Outputs
- Single 5-V Supply
- Dual Channel Operation
- Compatible With TTL

- Short-Circuit Protection
- High-Current Outputs
- Common and Individual Output Controls
- Clamp Diodes at Inputs and Outputs
- Easily Adaptable to SN55114 and SN75114 Applications
- Designed for Use With SN55115 and SN75115

To view the following documents, <u>Acrobat Reader 3.x</u> is required.

To download a document to your hard drive, right-click on the link and choose 'Save'.

#### **Datasheets**

Full datasheet in Acrobat PDF: <a href="style="style-type: selso70c.pdf">slls070c.pdf</a> (213 KB)
Full datasheet in Zipped PostScript: <a href="style-type: selso70c.psz">slls070c.psz</a> (186 KB)

## Pricing/Samples/Availability

Orderable Device	<u>Package</u>	<u>Pins</u>	Temp (°C)	<u>Status</u>	Price/unit USD (100-999)	Pack Qty	Availability / Samples
SN75113D	D	16	0 TO 70	ACTIVE	2.50	40	Check stock or order
SN75113DR	D	16	0 TO 70	ACTIVE	2.09	2500	Check stock or order
SN75113N	N	16	0 TO 70	ACTIVE	2.50	25	Check stock or order
SN75113NS	<u>NS</u>	16	0 TO 70	ACTIVE			Check stock or order

## **Application Reports**

- 422 AND 485 OVERVIEW AND SYSTEM CONFIGURATIONS (SLLA070 Updated: 02/15/2000)
- ANALOG APPLICATIONS JOURNAL, FEBRUARY 2000 (SLYT012A Updated: 03/23/2000)
- ANALOG APPLICATIONS JOURNAL, NOVEMBER 1999 (SLYT010A Updated: 03/23/2000)
- <u>COMPARING BUS SOLUTIONS</u> (SLLA067 Updated: 03/06/2000)
- ELECTROSTATIC DISCHARGE APPLICATION NOTE (SSYA008 Updated: 05/05/1999)
- JITTER ANALYSIS (SLLA075 Updated: 03/31/2000)
- SKEW DEFINITIONS (SLLA060 Updated: 08/13/1999)
- THERMAL CHARACTERISTICS OF LINEAR AND LOGIC PACKAGES USING JEDEC PCB DESIGNS (SZZA017A Updated: 09/15/1999)

## **Related Documents**

A STATISTICAL SURVEY OF COMMON-MODE NOISE (SLLA057, 131 KB - Updated: 12/23/1999)

Table Data Updated on: 6/2/2000

Search
 Tech Support
 Comments
 Site Map
 Tl&ME
 Home

(c) Copyright 2000 Texas Instruments Incorporated. All rights reserved. Trademarks, Important Notice!, Privacy Policy