SN74ALS29841 10-BIT BUS-INTERFACE D-TYPE LATCH WITH 3-STATE OUTPUTS

SDAS149A - JUNE 1988 - REVISED JANUARY 1995

 3-State Buffer-Type Outputs Drive Bus Lines Directly 	DW OR NT PACKAGE (TOP VIEW)
Bus-Structured Pinout	OE 1 VCC
Provides Extra Bus-Driving Latches	1D [2 23] 1Q
Necessary for Wider Address/Data Paths or	2D 🛮 3 22 🗓 2Q
Buses With Parity	3D 🛮 4 21 🗓 3Q
 Buffered Control Inputs Reduce dc Loading 	4D 🛛 5 20 🗍 4Q
Effects	5D 🛮 6 19 🗓 5Q
Power-Up High-Impedance State	6D 🛛 7 18 🖸 6Q
Package Options Include Plastic	7D 🛮 8 17 🗓 7Q
Small-Outline (DW) Packages and Standard	8D 🛮 9 16 🕽 8Q
Plastic (NT) 300-mil DIPs	9D 🛮 10 15 🕽 9Q
(, 2 5	10D 🛛 11 14 🗍 10Q
description	GND [12 13] LE

This 10-bit latch features 3-state outputs designed specifically for driving highly capacitive or relatively low-impedance loads. It is particularly suitable for implementing buffer registers, I/O ports, bidirectional bus drivers, and working registers.

The ten latches are transparent D-type latches. The SN74ALS29841 has noninverting data (D) inputs.

A buffered output-enable (\overline{OE}) input can place the ten outputs in either a normal logic state (high or low logic levels) or in a high-impedance state. The outputs also are in the high-impedance state during power-up and power-down conditions. The outputs remain in the high-impedance state while the device is powered down. In the high-impedance state, the outputs neither load nor drive the bus lines significantly. The high-impedance state and increased drive provide the capability to drive bus lines without interface or pullup components.

OE does not affect the internal operation of the latches. Old data can be retained or new data can be entered while the outputs are off.


The SN74ALS29841 is characterized for operation from 0°C to 70°C.

FUNCTION TABLE

	INPUTS	OUTPUT	
OE	LE	D	Q
L	Н	Н	Н
L	Н	L	L
L	L	Χ	Q_0
Н	X	Χ	Z


SDAS149A - JUNE 1988 - REVISED JANUARY 1995

logic symbol†



[†] This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

logic diagram (positive logic)



absolute maximum ratings over operating free-air temperature range (unless otherwise noted)‡

Supply voltage, V _{CC}	
Input voltage, V _I	/ V
Voltage applied to a disabled 3-state output	5.5 V
Operating free-air temperature range, T _A	\dots $$ 0°C to 70°C
Storage temperature range	. -65°C to 150°C

[‡] Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

recommended operating conditions

		MIN	NOM	MAX	UNIT
Vcc	Supply voltage	4.75	5	5.25	V
VIH	High-level input voltage	2			V
V_{IL}	Low-level input voltage			8.0	V
IOH	High-level output current			-24	mA
lOL	Low-level output current			48	mA
t _W	Pulse duration, LE high	6			ns
t _{su}	Setup time, data before LE↓	2.5			ns
t _h	Hold time, data after LE↓	4.5			ns
TA	Operating free-air temperature	0		70	°C

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER	TEST CO	MIN	TYP [†]	MAX	UNIT	
VIК	$V_{CC} = 4.75 V$,	I _I = –18 mA			-1.2	V
V	V 475 V	I _{OH} = -15 mA	2.4	3.3		V
Voн	V _{CC} = 4.75 V	$I_{OH} = -24 \text{ mA}$	2	3.1		
V _{OL}	$V_{CC} = 4.75 V$,	$I_{OL} = 48 \text{ mA}$		0.35	0.5	V
IOZH	$V_{CC} = 5.25 V$,	V _O = 2.7 V			20	μΑ
lozL	$V_{CC} = 5.25 V$,	V _O = 0.4 V			-20	μΑ
lį	$V_{CC} = 5.25 V$,	V _I = 5.5 V			0.1	mA
lіН	$V_{CC} = 5.25 V$,	V _I = 2.7 V			20	μΑ
I _{IL}	$V_{CC} = 5.25 V$,	V _I = 0.4 V			-0.2	mA
los [‡]	V _{CC} = 5.25 V,	V _O = 0	-75		-250	mA
Icc	V _{CC} = 5.25 V,	Outputs low		55	85	mA

[†] All typical values are at V_{CC} = 5 V, T_A = 25°C. ‡ Not more than one output should be shorted at a time, and the duration of the short circuit should not exceed one second.


SN74ALS29841 **10-BIT BUS-INTERFACE D-TYPE LATCH** WITH 3-STATE OUTPUTS SDAS149A - JUNE 1988 - REVISED JANUARY 1995

switching characteristics (see Figure 1)


PARAMETER	FROM	TO TEST CONDITIONS		V _{CC} = MIN T _A = MIN to	to MAX [†] , o MAX [†]	UNIT			
	(INPUT)	(OUTPUT)		MIN	MAX				
t _{PLH}	D	A O	0. 50.55	2	9.5	20			
t _{PHL}	U	Any Q	C _L = 50 pF	2	9.5	ns			
^t PLH	C	A O	O. 200 #F		14				
^t PHL	D	Any Q	C _L = 300 pF		14	ns			
^t PLH	-	A O	0. 50.55		12				
^t PHL	LE	Any Q	C _L = 50 pF		12 ns				
^t PLH	LE	A O	0 000 5		16				
t _{PHL}	LE	Any Q	C _L = 300 pF	16		ns			
^t PZH	ŌĒ	A O	0 50 5		14				
^t PZL	ÜE	Any Q	C _L = 50 pF		14	ns			
^t PZH	<u>OE</u>	A O	0 200 = 5		20				
^t PZL	ÜE	Any Q	C _L = 300 pF		23	ns			
t _{PHZ}	<u>OE</u>		0 50 5		15				
tPLZ	ÜE	Any Q	C _L = 50 pF		12	ns			
^t PHZ	OE Amir	40	A= O	OE Any Q C _I =	C 5 pE		9		
t _{PLZ}	OE	Ally Q	C _L = 5 pF		9	ns			


[†] For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.


PARAMETER MEASUREMENT INFORMATION




SWITCH POSITION TABLE							
TEST	S1	S2					
tPLH tPHL tPZH tPZL tPHZ tPHZ	Closed Closed Open Closed Closed Closed	Closed Closed Closed Open Closed Closed					









ENABLE AND DISABLE TIMES, 3-STATE OUTPUTS

NOTES: A. C_L includes probe and jig capacitance.

PROPAGATION DELAY TIMES

- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: PRR \leq 10 MHz, $Z_O = 50 \Omega$, $t_f \leq 2.5$ ns.

Figure 1. Load Circuit and Voltage Waveforms





PACKAGE OPTION ADDENDUM

7-Jun-2010

PACKAGING INFORMATION

Orderable Device	Status (1) P	ackage Typ	e Package Drawing	Pins	Package Qty	Eco Plan ⁽²⁾	Lead/ Ball Finish	MSL Peak Temp ⁽³⁾	Samples (Requires Login)
SN74ALS29841DW	OBSOLETE	SOIC	DW	24		TBD	Call TI	Call TI	Samples Not Available
SN74ALS29841NT	OBSOLETE	PDIP	NT	24		TBD	Call TI	Call TI	Samples Not Available

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Pb-Free (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

(3) MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.


Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

NT (R-PDIP-T**)

PLASTIC DUAL-IN-LINE PACKAGE

24 PINS SHOWN



NOTES: A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.

B. This drawing is subject to change without notice.

The 28 pin end lead shoulder width is a vendor option, either half or full width.



DW (R-PDSO-G24)

PLASTIC SMALL OUTLINE



NOTES: A. All linear dimensions are in inches (millimeters). Dimensioning and tolerancing per ASME Y14.5M-1994.

- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion not to exceed 0.006 (0,15).
- D. Falls within JEDEC MS-013 variation AD.



IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Audio	www.ti.com/audio	Communications and Telecom	www.ti.com/communications
Amplifiers	amplifier.ti.com	Computers and Peripherals	www.ti.com/computers
Data Converters	dataconverter.ti.com	Consumer Electronics	www.ti.com/consumer-apps
DLP® Products	www.dlp.com	Energy and Lighting	www.ti.com/energy
DSP	dsp.ti.com	Industrial	www.ti.com/industrial
Clocks and Timers	www.ti.com/clocks	Medical	www.ti.com/medical
Interface	interface.ti.com	Security	www.ti.com/security
Logic	logic.ti.com	Space, Avionics and Defense	www.ti.com/space-avionics-defense
Power Mgmt	power.ti.com	Transportation and Automotive	www.ti.com/automotive
Microcontrollers	microcontroller.ti.com	Video and Imaging	www.ti.com/video
RFID	www.ti-rfid.com	Wireless	www.ti.com/wireless-apps
RF/IF and ZigBee® Solutions	www.ti.com/lprf		

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2011, Texas Instruments Incorporated

e2e.ti.com

TI E2E Community Home Page