

**SN54HCT640, SN54HCT643, SN54HCT645
SN74HCT640, SN74HCT643, SN74HCT645
OCTAL BUS TRANSCEIVERS WITH 3-STATE OUTPUTS**

D2804, MARCH 1984—REVISED SEPTEMBER 1987

- Inputs are TTL-Voltage Compatible
- Choice of True or Inverting Logic
- High-Current 3-State Outputs Can Drive Up to 15 LSTTL Loads
- Package Options Include Plastic "Small Outline" Packages, Ceramic Chip Carriers, and Standard Plastic and Ceramic 300-mil DIPs
- Dependable Texas Instruments Quality and Reliability


DEVICE	LOGIC
'HCT640	Inverting
'HCT643	True and Inverting
'HCT645	True

description


These octal bus transceivers are designed for asynchronous two-way communication between data buses. The devices transmit data from the A bus to the B bus or from the B bus to the A bus depending upon the level at the direction control (DIR) input. The enable input (\bar{G}) can be used to disable the device so the buses are effectively isolated.

The SN54HCT640, SN54HCT643, and SN54HCT645 are characterized for operation over the full military temperature range of -55°C to 125°C . The SN74HCT640, SN74HCT643 and SN74HCT645 are characterized for operation from -40°C to 85°C .

SN54HCT' ... J PACKAGE
SN74HCT' ... DW OR N PACKAGE
(TOP VIEW) T-52-31



SN54HCT' ... FK PACKAGE
(TOP VIEW)



FUNCTION TABLE

CONTROL INPUTS	OPERATION		
	'HCT640	'HCT643	'HCT645
\bar{G} DIR			
L L	B data to A bus	B data to A bus	B data to A bus
L H	\bar{A} data to B bus	\bar{A} data to B bus	A data to B bus
H X	isolation	isolation	isolation

PRODUCTION DATA documents contain information current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.



POST OFFICE BOX 655012 • DALLAS, TEXAS 75265

Copyright © 1984, Texas Instruments Incorporated

2-553


2
HCMOS Devices

**SN54HCT640, SN54HCT643, SN54HCT645
SN74HCT640, SN74HCT643, SN74HCT645
OCTAL BUS TRANSCEIVERS WITH 3-STATE OUTPUTS**

T-52-31


logic symbols†

2 HCMOS Devices



†These symbols are in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

logic diagrams (positive logic)



**SN54HCT640, SN54HCT643, SN54HCT645
SN74HCT640, SN74HCT643, SN74HCT645
OCTAL BUS TRANSCEIVERS WITH 3-STATE OUTPUTS**

T-52-31

absolute maximum ratings over operating free-air temperature range†

Supply voltage, V_{CC}	-0.5 V to 7 V
Input clamp current, I_{IK} ($V_I < 0$ or $V_I > V_{CC}$)	± 20 mA
Output clamp current, I_{OK} ($V_O < 0$ or $V_O > V_{CC}$)	± 20 mA
Continuous output current, I_O ($V_O = 0$ to V_{CC})	± 35 mA
Continuous current through V_{CC} or GND pins	± 70 mA
Lead temperature 1,6 mm (1/16 in) from case for 60 s: FK or J package	300°C
Lead temperature 1,6 mm (1/16 in) from case for 10 s: DW or N package	260°C
Storage temperature range	-65°C to 150°C

2

HCMOS Devices

† Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

recommended operating conditions

	SN54HCT640 SN54HCT643 SN54HCT645			SN74HCT640 SN74HCT643 SN74HCT645			UNIT
	MIN	NOM	MAX	MIN	NOM	MAX	
V_{CC} Supply voltage	4.5	5	5.5	4.5	5	5.5	V
V_{IH} High-level input voltage	$V_{CC} = 4.5$ V to 5.5 V			2			V
V_{IL} Low-level input voltage	$V_{CC} = 4.5$ V to 5.5 V			0			V
V_I Input voltage	0			V_{CC}			V
V_O Output voltage	0			V_{CC}			V
t_t Input transition (rise and fall) times	0			500			ns
T_A Operating free-air temperature	-55			125			°C

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted).

PARAMETER	TEST CONDITIONS	V_{CC}	$T_A = 25^\circ\text{C}$			SN54HCT640 SN54HCT643 SN54HCT645		SN74HCT640 SN74HCT643 SN74HCT645		UNIT
			MIN	TYP	MAX	MIN	MAX	MIN	MAX	
			V_{OH}	$V_I = V_{IH}$ or V_{IL} , $I_{OH} = -20 \mu\text{A}$	4.5 V	4.4	4.499	4.4	4.4	
	$V_I = V_{IH}$ or V_{IL} , $I_{OH} = -8 \text{ mA}$	4.5 V	3.98	4.30	3.7	3.84			V	
V_{OL}	$V_I = V_{IH}$ or V_{IL} , $I_{OL} = 20 \mu\text{A}$	4.5 V	0.001	0.1	0.1	0.1			V	
	$V_I = V_{IH}$ or V_{IL} , $I_{OL} = 8 \text{ mA}$	4.5 V	0.17	0.28	0.4	0.33			V	
I_I	DIR or \bar{G}	$V_I = V_{CC}$ or 0	5.5 V	± 0.1	± 100	± 1000	± 1000		nA	
I_{OZ}	A or B	$V_O = V_{CC}$ or 0	5.5 V	± 0.01	± 0.5	± 10	± 5		μA	
I_{CC}		$V_I = V_{CC}$ or 0, $I_O = 0$	5.5 V		8	160	80		μA	
ΔI_{CC}^\ddagger		One input at 0.5 V or 2.4 V Other inputs at 0 V or V_{CC}	5.5 V	1.4	2.4	3	2.9		mA	
C_I	DIR or \bar{G}		4.5 to 5.5 V	3	10	10	10		pF	

‡ This is the increase in supply current for each input that is at one of the specified TTL voltage levels rather than 0 V or V_{CC} .



SN54HCT640, SN54HCT643
SN74HCT640, SN74HCT643
OCTAL BUS TRANSCEIVERS WITH 3-STATE OUTPUTS

T-52-31

switching characteristics over recommended operating free-air temperature range (unless otherwise noted), $C_L = 50$ pF (see Note 1)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	V _{CC}	T _A = 25°C						UNIT	
				SN54HCT640 SN54HCT643			SN74HCT640 SN74HCT643				
				MIN	TYP	MAX	MIN	MAX	MIN		MAX
t _{pd}	A or B	B or A	4.5 V	14	21		32		25	ns	
			5.5 V	12	18		27		23		
t _{en}	\bar{G}	A or B	4.5 V		27	35		53		44	ns
			5.5 V		24	32		47		39	
t _{dls}	\bar{G}	A or B	4.5 V		20	30		45		38	ns
			5.5 V		18	26		41		34	
t _t		A or B	4.5 V		9	12		18		15	ns
			5.5 V		8	11		16		14	

C _{pd}	Power dissipation capacitance per transceiver	No load, T _A = 25°C	40 pF typ
-----------------	---	--------------------------------	-----------

switching characteristics over recommended operating free-air temperature range (unless otherwise noted), $C_L = 150$ pF (see Note 1)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	V _{CC}	T _A = 25°C						UNIT	
				SN54HCT640 SN54HCT643			SN74HCT640 SN74HCT643				
				MIN	TYP	MAX	MIN	MAX	MIN		MAX
t _{pd}	A or B	B or A	4.5 V	17	27		41		34	ns	
			5.5 V	15	24		37		30		
t _{en}	\bar{G}	A or B	4.5 V		31	45		68		56	ns
			5.5 V		28	41		61		51	
t _t		A or B	4.5 V		17	42		63		53	ns
			5.5 V		14	38		57		48	

NOTE 1: Load circuits and voltage waveforms are shown in Section 1.

2 HCMOS Devices

SN54HCT645, SN74HCT645
OCTAL BUS TRANSCEIVERS WITH 3-STATE OUTPUTS

T-52-31

switching characteristics over recommended operating free-air temperature range (unless otherwise noted), $C_L = 50$ pF (see Note 1)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	V _{CC}	T _A = 25°C			SN54HCT645		SN74HCT645		UNIT
				MIN	TYP	MAX	MIN	MAX	MIN	MAX	
t _{pd}	A or B	B or A	4.5 V		16	22		33		28	ns
			5.5 V		14	20		30		25	
t _{en}	0	A or B	4.5 V		25	46		69		58	ns
			5.5 V		22	41		62		52	
t _{dis}	0	A or B	4.5 V		26	40		60		50	ns
			5.5 V		23	36		54		45	
t _t		A or B	4.5 V		9	12		18		15	ns
			5.5 V		8	11		16		14	

C _{pd}	Power dissipation capacitance per transceiver	No load, T _A = 25°C	40 pF typ
-----------------	---	--------------------------------	-----------

switching characteristics over recommended operating free-air temperature range (unless otherwise noted), $C_L = 150$ pF (see Note 1)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	V _{CC}	T _A = 25°C			SN54HCT645		SN74HCT645		UNIT
				MIN	TYP	MAX	MIN	MAX	MIN	MAX	
t _{pd}	A or B	B or A	4.5 V		20	30		45		38	ns
			5.5 V		18	27		41		34	
t _{en}	0	A or B	4.5 V		36	59		89		74	ns
			5.5 V		30	53		80		67	
t _t		A or B	4.5 V		17	42		63		53	ns
			5.5 V		14	38		57		48	

NOTE 1: Load circuits and voltage waveforms are shown in Section 1.

2

HCMOS Devices

TEXAS
INSTRUMENTS

POST OFFICE BOX 655012 • DALLAS, TEXAS 75285

2-557