SDAS214C - DECEMBER 1982 - REVISED AUGUST 1995

- 3-State Outputs Drive Bus Lines or Buffer Memory Address Registers
- pnp Inputs Reduce dc Loading
- Package Options Include Plastic Small-Outline (DW) Packages, Ceramic Chip Carriers (FK), and Standard Plastic (N) and Ceramic (J) 300-mil DIPs

description

These octal buffers/drivers are designed specifically to improve both the performance and density of 3-state memory address drivers, clock drivers, and bus-oriented receivers and transmitters. When these devices are used with the 'ALS241, 'AS241A, 'ALS244, and 'AS244A, the circuit designer has a choice of selected combinations of inverting and noninverting outputs, symmetrical active-low output-enable (OE) inputs, and complementary OE and OE inputs. These devices feature high fan-out and improved fan-in.

The -1 version of SN74ALS240A is identical to the standard version, except that the recommended maximum I_{OL} for the -1 version is 48 mA. There is no -1 version of the SN54ALS240A.

The SN54ALS240A and SN54AS240A are characterized for operation over the full military temperature range of -55° C to 125° C. The SN74ALS240A and SN74AS240A are characterized for operation from 0°C to 70°C.

SN54ALS240A, SN54AS240A J PACKAGE
SN74ALS240A, SN74AS240A DW OR N PACKAGE
(TOP VIEW)

(,	
[2 [3	20 19 18	V <u>CC</u> 20E 1Y1
	17	2A4
	16] 1Y2
6	15	2A3
[7	14] 1Y3
8]]	13	2A2
9	12] 1Y4
10) 11	2A1
		$\begin{bmatrix} 2 & 19 \\ 3 & 18 \\ 4 & 17 \\ 5 & 16 \\ 6 & 15 \\ 7 & 14 \\ 8 & 13 \end{bmatrix}$

SN54ALS240A, SN54AS240A . . . FK PACKAGE


FUNCTION TABLE	
(each buffer)	

(1.1.1.1.1.)							
INP	JTS	OUTPUT					
OE	Α	Y					
L	Н	L					
L	L	н					
н	Х	Z					

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.


SDAS214C - DECEMBER 1982 - REVISED AUGUST 1995


logic symbol[†]



[†] This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

logic diagram (positive logic)





absolute maximum ratings over operating free-air temperature range (unless otherwise noted)[‡]

Supply voltage, V _{CC}	
Input voltage, V ₁	
Voltage applied to a disabled 3-state output	
Operating free-air temperature range, T _A : SN54ALS240A	-55°C to 125°C
SN74ALS240A	0°C to 70°C
Storage temperature range	–65°C to 150°C

Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.



SDAS214C - DECEMBER 1982 - REVISED AUGUST 1995

recommended operating conditions

		SN54ALS240A			SN7	UNIT		
		MIN	NOM	MAX	MIN	NOM	MAX	UNIT
VCC	Supply voltage	4.5	5	5.5	4.5	5	5.5	V
VIH	High-level input voltage	2			2			V
VIL	Low-level input voltage			0.7			0.8	V
ЮН	High-level output current			-12			-15	mA
	Low-level output current			12			24	mA
OL							48†	ША
TA	Operating free-air temperature	-55		125	0		70	°C

[†] Applies only to the -1 version and only if V_{CC} is between 4.75 V and 5.25 V

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

	TEST CONDITIONS		SN	54ALS24	0A	SN7	74ALS24	0A	
PARAMETER			MIN	TYP‡	MAX	MIN	TYP‡	MAX	UNIT
VIK	V _{CC} = 4.5 V,	lı = -18 mA			-1.2			-1.2	V
	$V_{CC} = 4.5 V \text{ to } 5.5 V,$	I _{OH} = -0.4 mA	V _{CC} -2	2		V _{CC} -2	2		
Veri		$I_{OH} = -3 \text{ mA}$	2.4	3.2		2.4	3.2		V
VOH	$V_{CC} = 4.5 V$	I _{OH} = -12 mA	2						v
		I _{OH} = -15 mA				2			
		I _{OL} = 12 mA		0.25	0.4		0.25	0.4	
VOL	$V_{CC} = 4.5 V$	I _{OL} = 24 mA					0.35	0.5	V
		$I_{OL} = 48 \text{ mA}^{\dagger}$					0.35	0.5	
IOZH	$V_{CC} = 5.5 V,$	V _O = 2.7 V			20			20	μA
I _{OZL}	$V_{CC} = 5.5 V,$	V _O = 0.4 V			-20			-20	μΑ
lj	V _{CC} = 5.5 V,	V _I = 7 V			0.1			0.1	mA
Iн	V _{CC} = 5.5 V,	V _I = 2.7 V			20			20	μΑ
۱ _{IL}	V _{CC} = 5.5 V,	V _I = 0.4 V			-0.1			-0.1	mA
١ _O §	V _{CC} = 5.5 V,	V _O = 2.25 V	-20		-112	-30		-112	mA
		Outputs high		4	11		4	11	
ICC	V _{CC} = 5.5 V	Outputs low		13	23		13	23	mA
		Outputs disabled		14	25		14	25	

 † Applies only to the -1 version and only if V_{CC} is between 4.75 V and 5.25 V

[‡] All typical values are at $V_{CC} = 5 \text{ V}$, $T_A = 25^{\circ}\text{C}$. § The output conditions have been chosen to produce a current that closely approximates one half of the true short-circuit output current, I_{OS} .



SDAS214C - DECEMBER 1982 - REVISED AUGUST 1995

switching characteristics (see Figure 1)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	CL R1 R2	= 50 pF = 500 9 2 = 500 9	2,	3	UNIT	
				SN54ALS240A		SN74ALS240A		
			MIN	MAX	MIN	MAX		
^t PLH	А	v	2	22	2	9	ns	
^t PHL	A	Y	2	11	2	9	115	
^t PZH	OE	Y	4	34	5	13	ns	
tPZL	ÛE	Ϋ́	5	26	5	18	115	
^t PHZ	OE	V	1	15	2	10	ns	
^t PLZ	UE		3	24	3	12	115	

[†] For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)[‡]

Supply voltage, V _{CC}	
Input voltage, V ₁	
Voltage applied to a disabled 3-state output	
Operating free-air temperature range, T _A : SN54AS240A	-55°C to 125°C
SN74AS240A	0°C to 70°C
Storage temperature range	-65°C to 150°C

Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

recommended operating conditions

		SN	54AS24	DA	SN	74AS24	DA	UNIT
		MIN	NOM	MAX	MIN	NOM	MAX	UNIT
VCC	Supply voltage	4.5	5	5.5	4.5	5	5.5	V
VIH	High-level input voltage	2			2			V
V_{IL}	Low-level input voltage			0.8			0.8	V
IOH	High-level output current			-12			-15	mA
IOL	Low-level output current			48			64	mA
TA	Operating free-air temperature	-55		125	0		70	°C



SDAS214C - DECEMBER 1982 - REVISED AUGUST 1995

DADAMETED	TERTO	TEST CONDITIONS SN54AS240A			SN54AS240A		SN74AS240A		
PARAMETER	IESIC	ONDITIONS	MIN	TYP†	MAX	MIN	TYP [†]	MAX	UNIT
VIK	V _{CC} = 4.5 V,	lj = -18 mA			-1.2			-1.2	V
		$I_{OH} = -2 \text{ mA}$	V _{CC} -2	2		V _{CC} -2	2		
Varia	V_{CC} = 4.5 V to 5.5 V	$I_{OH} = -3 \text{ mA}$	2.4	3.4		2.4	3.4		V
VOH		I _{OH} = -12 mA	2.4						v
	$V_{CC} = 4.5 V$	I _{OH} = -15 mA				2.4			
Mai		I _{OL} = 48 mA		0.27	0.55				
Vol	$V_{CC} = 4.5 V$	I _{OL} = 64 mA					0.31	0.55 V	
IOZH	V _{CC} = 5.5 V,	V _O = 2.7 V			50			50	μΑ
IOZL	V _{CC} = 5.5 V,	$V_{O} = 0.4 V$			-50			-50	μΑ
li	V _{CC} = 5.5 V,	V _I = 7 V			0.1			0.1	mA
Ін	V _{CC} = 5.5 V,	V _I = 2.7 V			20			20	μΑ
A inputs					-1			-1	mA
	$V_{CC} = 5.5 V,$	$V_{I} = 0.4 V$			-0.5			-0.5	mA
IO [‡]	V _{CC} = 5.5 V,	V _O = 2.25 V	-50		-150	-50		-150	mA
		Outputs high		11	17		11	17	
ICC	V _{CC} = 5.5 V	Outputs low		51	75		51	75	mA
		Outputs disabled		24	38		24	38	

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

† All typical values are at V_{CC} = 5 V, T_A = 25°C.
 ‡ The output conditions have been chosen to produce a current that closely approximates one half of the true short-circuit output current, I_{OS}.


switching characteristics (see Figure 1)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	CL R1 R2	V _{CC} = 4.5 V to 5.5 V, C _L = 50 pF, R1 = 500 Ω, R2 = 500 Ω, T _A = MIN to MAX§			UNIT
			SN54AS240A		SN74AS240A		
			MIN	MAX	MIN	MAX	
^t PLH	A	Y	1	7	1	6.5	ns
^t PHL			1.2	6.5	1.2	6.5	115
^t PZH	OE	Υ	1	7	1	6.4	ns
t _{PZL}	ÛE		1.1	9.5	1.1	9	115
^t PHZ	OE	V	1.2	5.5	1.2	5	ns
^t PLZ	UL	I	1.5	12.5	1.5	9.5	115

§ For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.



SDAS214C - DECEMBER 1982 - REVISED AUGUST 1995



NOTES: A. CL includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
 C. When measuring propagation delay items of 3-state outputs, switch S1 is open.
- D. All input pulses have the following characteristics: PRR \leq 1 MHz, t_r = t_f = 2 ns, duty cycle = 50%.
- E. The outputs are measured one at a time with one transition per measurement.

Figure 1. Load Circuits and Voltage Waveforms



IMPORTANT NOTICE

Texas Instruments and its subsidiaries (TI) reserve the right to make changes to their products or to discontinue any product or service without notice, and advise customers to obtain the latest version of relevant information to verify, before placing orders, that information being relied on is current and complete. All products are sold subject to the terms and conditions of sale supplied at the time of order acknowledgement, including those pertaining to warranty, patent infringement, and limitation of liability.

TI warrants performance of its semiconductor products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are utilized to the extent TI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except those mandated by government requirements.

CERTAIN APPLICATIONS USING SEMICONDUCTOR PRODUCTS MAY INVOLVE POTENTIAL RISKS OF DEATH, PERSONAL INJURY, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE ("CRITICAL APPLICATIONS"). TI SEMICONDUCTOR PRODUCTS ARE NOT DESIGNED, AUTHORIZED, OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT DEVICES OR SYSTEMS OR OTHER CRITICAL APPLICATIONS. INCLUSION OF TI PRODUCTS IN SUCH APPLICATIONS IS UNDERSTOOD TO BE FULLY AT THE CUSTOMER'S RISK.

In order to minimize risks associated with the customer's applications, adequate design and operating safeguards must be provided by the customer to minimize inherent or procedural hazards.

TI assumes no liability for applications assistance or customer product design. TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right of TI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used. TI's publication of information regarding any third party's products or services does not constitute TI's approval, warranty or endorsement thereof.

Copyright © 1998, Texas Instruments Incorporated

😻 Texas Instruments	THE WORL	D LEADER	IN DSP AND	ANALOG
Products	Development Tools	▼	Applications	•
Search	☐ Advanced Search ☐ Tech Support		🗆 TI&ME 🗖 Site Map	🖬 Employment 🖿 Tl Global

>> Semiconductor Home > Products > Digital Logic > Buffers and Drivers > Inverting Buffers and Drivers >

SN54ALS240A, OCTAL BUFFERS/DRIVERS WITH 3-STATE OUTPUTS

Device Status: Active

- > Description
- Features
- Datasheets
- > Pricing/Samples/Availability
- Application Notes
- Related Documents

Parameter Name	SN54ALS240A			
Voltage Nodes (V)	5			
Vcc range (V)	4.5 to 5.5			
Input Level	TTL			
Output Level	TTL			
No. of Outputs	8			
Logic	Inv			

Description

These octal buffers/drivers are designed specifically to improve both the performance and density of 3-state memory address drivers, clock drivers, and bus-oriented receivers and transmitters. When these devices are used with the 'ALS241, 'AS241A, 'ALS244, and 'AS244A, the circuit designer has a choice of selected combinations of inverting and noninverting outputs, symmetrical active-low output-enable (OE\) inputs, and complementary OE and \overrightarrow{OE} inputs. These devices feature high fan-out and improved fan-in.

The -1 version of SN74ALS240A is identical to the standard version, except that the recommended maximum I_{OL} for the -1 version is 48 mA. There is no -1 version of the SN54ALS240A.

The SN54ALS240A and SN54AS240A are characterized for operation over the full military temperature range of -55°C to 125°C. The SN74ALS240A and SN74AS240A are characterized for operation from 0°C to 70°C.

Features

- pnp Inputs Reduce dc Loading
- Package Options Include Plastic Small-Outline (DW) Packages, Ceramic Chip Carriers (FK), and Standard Plastic (N) and Ceramic (J) 300-mil DIPs

To view the following documents, <u>Acrobat Reader 3.x</u> is required. To download a document to your hard drive, right-click on the link and choose 'Save'.

Datasheets

Full datasheet in Acrobat PDF: <u>sdas214c.pdf</u> (110 KB) Full datasheet in Zipped PostScript: <u>sdas214c.psz</u> (109 KB)

Pricing/Samples/Availability

Orderable Device	Package	<u>Pins</u>	<u>Temp</u> (° <u>C)</u>	<u>Status</u>	Price/unit USD (100- <u>999)</u>	<u>Pack</u> Qty	<u>DSCC</u> <u>Number</u>	<u>Availability /</u> <u>Samples</u>
JM38510/38301B2A	<u>FK</u>	20	-55 TO 125	ACTIVE	20.29	1		<u>Check stock or</u> <u>order</u>
JM38510/38301BRA	ī	20	-55 TO 125	ACTIVE	14.46	1		<u>Check stock or</u> <u>order</u>
SN54ALS240AJ	ī	20	-55 TO 125	ACTIVE	5.01	1		<u>Check stock or</u> <u>order</u>
SNJ54ALS240AFK	<u>FK</u>	20	-55 TO 125	ACTIVE	11.52	1		<u>Check stock or</u> order
SNJ54ALS240AJ	ī	20	-55 TO 125	ACTIVE	5.91	1		<u>Check stock or</u> <u>order</u>
SNJ54ALS240AW	W	20	-55 TO 125	ACTIVE	12.53	1	5962- 8859101SA	<u>Check stock or</u> <u>order</u>

Application Reports

View Application Reports for Digital Logic

- ADVANCED SCHOTTKY (ALS AND AS) LOGIC FAMILIES (SDAA010 Updated: 02/05/1999)
- BUS-INTERFACE DEVICES WITH OUTPUT-DAMPING RESISTORS OR REDUCED-DRIVE OUTPUTS (SCBA012A - Updated: 08/01/1997)
- DESIGNING WITH LOGIC (SDYA009C Updated: 06/01/1997)
- INPUT AND OUTPUT CHARACTERISTICS OF DIGITAL INTEGRATED CIRCUITS (SDYA010 Updated: 02/05/1999)
- <u>LIVE INSERTION</u> (SDYA012 Updated: 02/05/1999)

Related Documents

- DOCUMENTATION RULES (SAP) AND ORDERING INFORMATION (SZZU001B, 4 KB Updated: 05/06/1999)
- LOGIC SELECTION GUIDE SECOND HALF 2000 (SDYU001N, 5035 KB Updated: 04/17/2000)

• MORE POWER IN LESS SPACE - TECHNICAL ARTICLE (SCAU001A, 850 KB - Updated: 03/01/1996)

Table Data Updated on: 8/8/2000

© Copyright 2000 Texas Instruments Incorporated. All rights reserved. Trademarks | Privacy Policy



V Texas Instruments	THE WORL	D LEADER	IN DSP AND	ANALOG
Products 💌	Development Tools	▼	Applications	•
Search	■ Advanced Search ■ Tech Support	□ TI Home □ Comments	ロ TI&ME ロ Site Map	🗆 Employment 🖿 Tl Global

>> Semiconductor Home > Products > Digital Logic > Buffers and Drivers > Inverting Buffers and Drivers >

SN54AS240A, OCTAL BUFFERS/DRIVERS WITH 3-STATE OUTPUTS

Device Status: Active

- > Description
- Features
- Datasheets
- > Pricing/Samples/Availability
- Application Notes
- Related Documents

Parameter Name	SN54AS240A
Voltage Nodes (V)	5
Vcc range (V)	4.5 to 5.5
Input Level	TTL
Output Level	TTL
No. of Outputs	8
Logic	Inv

Description

These octal buffers/drivers are designed specifically to improve both the performance and density of 3-state memory address drivers, clock drivers, and bus-oriented receivers and transmitters. When these devices are used with the 'ALS241, 'AS241A, 'ALS244, and 'AS244A, the circuit designer has a choice of selected combinations of inverting and noninverting outputs, symmetrical active-low output-enable (OE\) inputs, and complementary OE and \overrightarrow{OE} inputs. These devices feature high fan-out and improved fan-in.

The -1 version of SN74ALS240A is identical to the standard version, except that the recommended maximum I_{OL} for the -1 version is 48 mA. There is no -1 version of the SN54ALS240A.

The SN54ALS240A and SN54AS240A are characterized for operation over the full military temperature range of -55°C to 125°C. The SN74ALS240A and SN74AS240A are characterized for operation from 0°C to 70°C.

Features

- 3-State Outputs Drive Bus Lines or Buffer Memory Address Registers
- pnp Inputs Reduce dc Loading
- Package Options Include Plastic Small-Outline (DW) Packages, Ceramic Chip Carriers (FK), and Standard Plastic (N) and Ceramic (J) 300-mil DIPs

To view the following documents, <u>Acrobat Reader 3.x</u> is required. To download a document to your hard drive, right-click on the link and choose 'Save'.

Datasheets

Full datasheet in Acrobat PDF: <u>sdas214c.pdf</u> (110 KB) Full datasheet in Zipped PostScript: <u>sdas214c.psz</u> (109 KB)

Pricing/Samples/Availability

<u>Orderable</u> <u>Device</u>	<u>Package</u>	<u>Pins</u>	<u>Temp</u> (<u>°C)</u>	<u>Status</u>	Price/unit USD (100- 999)	<u>Pack</u> <u>Qty</u>	DSCC Number	<u>Availability /</u> <u>Samples</u>
SNJ54AS240AFK	<u>FK</u>	20	-55 TO 125	ACTIVE	12.11	1		Check stock or order
SNJ54AS240AJ	ī	20	-55 TO 125	ACTIVE	6.60	1		Check stock or order
SNJ54AS240AW	W	20	-55 TO 125	ACTIVE	15.87	1		Check stock or order

Application Reports

View Application Reports for Digital Logic

- ADVANCED SCHOTTKY (ALS AND AS) LOGIC FAMILIES (SDAA010 Updated: 02/05/1999)
- ADVANCED SCHOTTKY LOAD MANAGEMENT (SDYA016 Updated: 02/05/1999)
- DESIGNING WITH LOGIC (SDYA009C Updated: 06/01/1997)
- INPUT AND OUTPUT CHARACTERISTICS OF DIGITAL INTEGRATED CIRCUITS (SDYA010 Updated: 02/05/1999)
- LIVE INSERTION (SDYA012 Updated: 02/05/1999)

Related Documents

- DOCUMENTATION RULES (SAP) AND ORDERING INFORMATION (SZZU001B, 4 KB Updated: 05/06/1999)
- LOGIC SELECTION GUIDE SECOND HALF 2000 (SDYU001N, 5035 KB Updated: 04/17/2000)
- MORE POWER IN LESS SPACE TECHNICAL ARTICLE (SCAU001A, 850 KB Updated: 03/01/1996)

Table Data Updated on: 8/8/2000

© Copyright 2000 Texas Instruments Incorporated. All rights reserved. Trademarks | Privacy Policy

