

### General Description

- Low  $R_{DS(ON)}$
- RoHS and Halogen-Free Compliant

### Applications




- Load switch
- PWM

### General Features

$V_{DS} = 60V$     $I_D = 3.0A$

$R_{DS(ON)} = 75\text{ m}\Omega(\text{Typ.}) @ V_{GS}=10V$

100% UIS Tested  
100%  $R_g$  Tested



Marking: ARDP OR 2310D

### Absolute Maximum Ratings: ( $T_a=25^\circ\text{C}$ unless otherwise noted)

Symbol	Parameter	Ratings	Units
$V_{DS}$	Drain-Source Voltage	60	V
$V_{GS}$	Gate-Source Voltage	$\pm 20$	V
$I_D$	Continuous Drain Current- $T_A=25^\circ\text{C}$	3.0	A
	Continuous Drain Current- $T_A=100^\circ\text{C}$	2.2	
$I_{DM}$	Pulse Drain Current Tested <sup>note1</sup>	14	A
$P_D$	Power Dissipation- $T_A=25^\circ\text{C}$	1.7	W
$T_J, T_{STG}$	Operating and Storage Junction Temperature Range	-55 to +150	°C

### Thermal Characteristics:

Symbol	Parameter	Max	Units
$R_{JA}$	Thermal Resistance,Junction to Ambient	73.5	°C/W


**Electrical Characteristics:** ( $T_c=25^\circ C$  unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Units
<b>Off Characteristics</b>						
$BV_{DSS}$	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=250 \mu A$	60	---	---	V
$I_{DSS}$	Zero Gate Voltage Drain Current	$V_{GS}=0V, V_{DS}=60V$	---	---	1	$\mu A$
$I_{GSS}$	Gate-Source Leakage Current	$V_{GS}=\pm 20V, V_{DS}=0A$	---	---	$\pm 100$	nA
<b>On Characteristics</b>						
$V_{GS(th)}$	GATE-Source Threshold Voltage	$V_{GS}=V_{DS}, I_D=250 \mu A$	1	1.5	2.5	V
$R_{DS(on)}$	Drain-Source on-Resistance <sup>note2</sup>	$V_{GS}=10V, I_D=3A$	---	75	105	$m \Omega$
		$V_{GS}=4.5V, I_D=2A$	---	85	110	
<b>Dynamic Characteristics</b>						
$C_{iss}$	Input Capacitance	$V_{DS}=25V, V_{GS}=0V, f=1MHz$	---	325	---	pF
$C_{oss}$	Output Capacitance		---	85	---	
$C_{rss}$	Reverse Transfer Capacitance		---	15	---	
<b>Switching Characteristics</b>						
$t_{d(on)}$	Turn-On Delay Time	$V_{DS}=30V, V_{GS}=10V,$ $I_D=2A, R_{GEN}=3 \Omega$	---	13	---	ns
$t_r$	Rise Time		---	51	---	ns
$t_{d(off)}$	Turn-Off Delay Time		---	19	---	ns
$t_f$	Fall Time		---	12	---	ns
$Q_g$	Total Gate Charge	$V_{GS}=10V, V_{DS}=30V,$ $I_D=3A$	---	5.1	---	nC
$Q_{gs}$	Gate-Source Charge		---	1.3	---	nC
$Q_{gd}$	Gate-Drain "Miller" Charge		---	1.7	---	nC
<b>Drain-Source Diode Characteristics</b>						
$I_s$	Continuous Source Current	---	---	---	3	A
$I_{SM}$	Pulsed Source Current	---	---	---	12	A
$V_{SD}$	Forward Voltage	$V_{GS}=0V, I_s=3A$	---	---	1.2	V


**Notes:**

- Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature
- Pulse Test: Pulse Width  $\leq 300\mu s$ , Duty Cycle  $\leq 0.5\%$


**Typical Characteristics:** ( $T_C=25^\circ\text{C}$  unless otherwise noted)




**Figure 1:** Output Characteristics




**Figure 2:** Typical Transfer Characteristics




**Figure 3:** On-resistance vs. Drain Current



**Figure 4:** Body Diode Characteristics




**Figure 5:** Gate Charge Characteristics




**Figure 6:** Capacitance Characteristics


**Figure 7:** Normalized Breakdown Voltage vs. Junction Temperature




**Figure 9:** Maximum Safe Operating Area




**Figure 11:** Maximum Effective Transient Thermal Impedance, Junction-to-Case




**Figure 8:** Normalized on Resistance vs. Junction Temperature



**Figure 10:** Maximum Continuous Drain Current vs. Case Temperature



## Package Information:SOT-23-3L



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E1	1.500	1.700	0.059	0.067
E	2.650	2.950	0.104	0.116
e	0.950(BSC)		0.037(BSC)	
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°