

Rochester Electronics Manufactured Components

Rochester branded components are manufactured using either die/wafers purchased from the original suppliers or Rochester wafers recreated from the original IP. All recreations are done with the approval of the OCM.

Parts are tested using original factory test programs or Rochester developed test solutions to guarantee product meets or exceed the OCM data sheet.

Quality Overview

- ISO-9001
- AS9120 certification
- Qualified Manufacturers List (QML) MIL-PRF-35835
 - Class Q Military
 - Class V Space Level
- Qualified Suppliers List of Distributors (QSLD)
- Rochester is a critical supplier to DLA and meets all industry and DLA standards.

Rochester Electronics, LLC is committed to supplying products that satisfy customer expectations for quality and are equal to those originally supplied by industry manufacturers.

The original manufacturer's datasheet accompanying this document reflects the performance and specifications of the Rochester manufactured version of this device. Rochester Electronics guarantees the performance of its semiconductor products to the original OEM specifications. 'Typical' values are for reference purposes only. Certain minimum or maximum ratings may be based on product characterization, design, simulation, or sample testing.

- Ceramic Chip Carriers in Addition to Plastic and Ceramic DIPs
- Dependable Texas Instruments Quality and Reliability

· Package Options Include Both Plastic and

description

These devices contain two independent 4-input AND gates.

The SN54H21 and SN54LS21 are characterized for operation over the full military temperature range of -55°C to 125°C. The SN74H21 and SN74LS21 are characterized for operation from 0 ° C to 70 °C.

FUNCTION TABLE (each gate)

	INP	UTS	OUTPUT				
A	В	С	٥	Y			
н	Н	н	н	н			
L	Х	X	x	Ĺ			
х	L	X	x	L			
х	X	L	X	L			
Х	X	Х	L.	L			


logic diagram (each gate)



positive logic

$$Y = A \cdot B \cdot C \cdot D$$
 or $Y = \overline{A + B + C + D}$


SN54H21 . . . J PACKAGE SN54LS21 . . . J OR W PACKAGE SN74H21 . . . J OR N PACKAGE SN74LS21 ... D. J OR N PACKAGE (TOP VIEW)



SN54H21 ... W PACKAGE (TOP VIEW)


1A	ф	U 14	1D
1Y	₫₂	13	1C
NC	□3	12	1B
Vcc	□4	11	GND
NC	ď۶	10	2Y
2A	Дe	фe	2D
2B	ď۶	8	2C


SN54LS21 . . . FK PACKAGE SN74LS21 ... FN PACKAGE (TOP VIEW)



NC - No internal connection

schematics (each gate)





Resistor values shown are nominal

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)

Supply voltage, Vcc (see Not	e 1)	7 V
Input voltage: 'H21	·	5.5 V
'l S21		7 V
Operating temperature range:	SN54'	55°C to 125°C
operating temperature range	SN74'	0°C to 70°C
Storage temperature range .		65°C to 150°C

NOTE 1: Voltage values are with respect to network ground terminal.



TYPES SN54H21, SN74H21 DUAL 4-INPUT POSITIVE-AND GATES

recommended operating conditions

		SN54H21				UNIT		
		MIN	NOM	MAX	MIN	NOM	MAX	UNII
Vcc	Supply voltage	4.5	5	5.5	4.75	5	5.25	٧
VIH	High-level input voltage	2			2			V
VIL	Low-level input voltage			0.8			8.0	٧
Іон	High-level output current			- 0.5			- 0.5	mΑ
IOL	Low-level output current			20			20	mA
TA	Operating free-air temperature	- 55		125	0		70	°c

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER	TEST CONDITIONS †			SN54H21			SN74H21			
PARAMETER				MIN	TYP‡	MAX	MIN	TYP‡	мах	UNIT
VIK	V _{CC} = MIN,	I ₁ = -8 mA				- 1.5			- 1.5	V
Vон	V _{CC} - MIN,	V _{IH} = 2 V,	IOH = ~ 0.5 mA	2.4	3.4		2.4	3.4		V
VOL	V _{CC} = MIN,	V1L = 0.8 V	IOL = 20 mA		0.2	0.4		0.2	0.4	V
11	V _{CC} - MAX,	V1 = 5.5 V				1			1	mA
ЧН	V _{CC} = MAX,	V _j = 2,4 V				50			50	μА
HL	V _{CC} = MAX,	V = 0.4 V				2			-2	mA
IOS §	V _{CC} MAX			-40		100	-40		-100	mA
І ссн	V _{CC} = MAX,	V ₁ = 4.5 V		l	12	20		12	20	mA
locu	V _{CC} MAX,	V = 0 V		l	20	32		20	32	mA

¹ For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.

switching characteristics, VCC = 5 V, TA = 25°C (see note 2)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	TEST CONDITIONS		MIN	TYP	MAX	UNIT
tPLH .	Any	V	R₁ = 280 Ω,	C ₁ ≈ 25 pF		7.6	12	ns
^t PHL	City		HL = 280 \O,	CL - 29 pF		8.8	12	ns

NOTE 2: See General Information Section for load circuits and voltage waveforms.

 $^{^{\}ddagger}$ All typical values are at $V_{CC} \simeq 5$ V, $T_{A} \simeq 25^{\circ}$ C. § Not more than one output should be shorted at a time, and the duration of the short-circuit should not exceed one second,

TYPES SN54LS21, SN74LS21 DUAL 4-INPUT POSITIVE-AND GATES

recommended operating conditions

		SN54LS21 SN74LS21			21	UNIT		
		MIN	NOM	MAX	MIN	NOM	MAX	ONT
Vcc	Supply voltage	4.5	5	5.5	4,75	5	5.25	٧
VIH	High-level input voltage	2			2			٧
VIL	Low-level input voltage			0.7			8.0	٧
ЮН	High-level output current			- 0.4			- 0.4	mA
İOL	Low-level output current			4			8	mA
TA	Operating free-air temperature	- 55		125	0		70	°C

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

DADAMETED	TEST CONDITIONS †		SN54LS21			SN74LS21			UNIT	
PARAMETER	!	TEST CONDIT	IONS	MIN	TYP‡	MAX	MIN	TYP‡	MAX	ONII
Vικ	V _{CC} = MIN, I _I = 18 mA					- 1.5			1.5	٧
Voн	VCC = MIN,	V _{IH} = 2 V,	I _{OH} = - 0.4 mA	2.5	3.4		2.7	3.4	-	٧
Va.	VCC = MIN,	VIL = MAX,	IOL = 4 mA		0.25	0.4		0.25	0.4	
VOL	V _{CC} = MIN,	VIL = MAX,	IOL = 8 mA					0.35	0.5	1 *
l _i	VCC = MAX,	V ₁ = 7 V				0.1			0,1	mA
ΙΉ	V _{CC} * MAX,	V ₁ = 2.7 V				20			20	μА
l _{IL}	V _{CC} = MAX,	V ₁ = 0.4 V				- 0.4			- 0.4	mA
IOSS	V _{CC} = MAX			- 20		- 100	- 20		- 100	mA
ССН	V _{CC} = MAX,	V ₁ = 4.5 V			1.2	2.4		1.2	2.4	mA
ICCL	V _{CC} = MAX,	V ₁ = 0 V			2.2	4.4		2.2	4.4	mΑ

[†] For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.

switching characteristics. $V_{CC} = 5 \text{ V}$. TA = 25°C (see note 2)

				1		_		
ı	PARAMETER	FROM TO TEST CONDITIONS		MIN	TYP	MAX	UNIT	
		(INPUT)	(OUTPUT)	TEST CONDITIONS	MIN	117	MAX	UNIT
	^t PLH	Δον		B 2k0 C 15 oF		8	15	ns
	tPHL	Any	1	R _L ≈ 2 kΩ, C _L = 15 pF		10	20	ns

NOTE 2: See General Information Section for load circuits and voltage waveforms.

[‡] All typical values are at $V_{CC} = 5 \text{ V}$, $T_A = 25 ^{\circ}\text{C}$

[§] Not more than one output should be shorted at a time, and the duration of the short-circuit should not exceed one second.