


DSS12 THRU DSS120

<u>SOD-123FL</u>		<u>FEATURES</u>												
 <p style="text-align: center;">Dimensions in millimeters</p>		<ul style="list-style-type: none"> ◆ The plastic package carries Underwriters Laboratory Flammability Classification 94V-0 ◆ Metal silicon junction, majority carrier conduction ◆ Low power loss, high efficiency ◆ High forward surge current capability ◆ High temperature soldering guaranteed: 250°C/10 seconds, 0.375" (9.5mm) lead length, 5 lbs. (2.3kg) tension 												
		<u>MECHANICAL DATA</u>												
		<p>Case: JEDEC SOD-123FL molded plastic body Terminals: Solderable per MIL-STD-750, Method 2026 Polarity: Color band denotes cathode end Mounting Position: Any Weight: 0.0007 ounce, 0.02 grams</p>												
<u>MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS</u>														
Ratings at 25°C ambient temperature unless otherwise specified. Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.														
Catalog Number	SYMBOLS	DSS12 K12	DSS13 K13	DSS14 K14	DSS15 K15	DSS16 K16	DSS17 K17	DSS18 K18	DSS19 K19	DSS110 K110	DSS115 K115	DSS120 K120	UNITS	
Maximum repetitive peak reverse voltage	V_{RRM}	20	30	40	50	60	70	80	90	100	150	200	VOLTS	
Maximum RMS voltage	V_{RMS}	14	21	28	35	42	49	56	63	70	105	140	VOLTS	
Maximum DC blocking voltage	V_{DC}	20	30	40	50	60	70	80	90	100	150	200	VOLTS	
Maximum average forward rectified current	$I_{(AV)}$	1.0											Amp	
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I_{FSM}	25.0											Amps	
Maximum instantaneous forward voltage at 1.0A	V_F	0.55			0.70			0.85			0.95		Volts	
Maximum DC reverse current $T_A=25^\circ\text{C}$ at rated DC blocking voltage $T_A=100^\circ\text{C}$	I_R	0.5					5.0					0.2 2.0		mA
Typical junction capacitance (NOTE 1)	C_J	110					80							pF
Operating junction temperature range	T_J	-65 to +125					-65 to +150							°C
Storage temperature range	T_{STG}	-65 to +150											°C	
Note: 1. Measured at 1MHz and applied reverse voltage of 4.0V D.C.														

DSS12 THRU DSS120

AVERAGE FORWARD RECTIFIED CURRENT,
AMPERES

FIG. 1- FORWARD CURRENT DERATING CURVE




FIG. 2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




FIG. 3-TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




FIG. 4-TYPICAL REVERSE CHARACTERISTICS




FIG. 5-TYPICAL JUNCTION CAPACITANCE

