SCLS157

- Package Options Include Plastic "Small Outline" Packages, Ceramic Chip Carriers, and Standard Plastic and Ceramic 300-mil DIPs
- Dependable Texas Instruments Quality and Reliability

#### description

These devices contain two independent 4-input positive NOR gates. They perform the Boolean functions:

 $Y = \overline{A} + \overline{B} + \overline{C} + \overline{D} \text{ or } Y = \overline{A} \cdot \overline{B} \cdot \overline{C} \cdot \overline{D}$ in positive logic.

The SN54HC4002 is characterized for operation over the full military temperature range of -55 °C to 125 °C. The SN74HC4002 is characterized for operation from -40 °C to 85 °C.

FUNCTION TABLE

|   | INP | OUTPUT |   |       |
|---|-----|--------|---|-------|
| A | B   | С      | D | Y     |
| н | Х   | Х      | Х | L     |
| х | н   | х      | х | L     |
| х | Х   | н      | х | ) L ' |
| х | х   | х      | н | L L   |
| L | L   | L      | L | н     |

logic symbol<sup>†</sup>



<sup>†</sup>This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

Pin numbers shown are for D, J, and N packages.

D2684, DECEMBER 1982-REVISED SEPTEMBER 1987

10 28

9 🗌 2 A

8 NC

| SN54HC4002 J PACKAGE<br>SN74HC4002 D OR N PACKAGE |                  |  |  |  |  |  |  |
|---------------------------------------------------|------------------|--|--|--|--|--|--|
| (T                                                | OP VIEW)         |  |  |  |  |  |  |
|                                                   |                  |  |  |  |  |  |  |
| ז או                                              |                  |  |  |  |  |  |  |
| 1A 🗌                                              | 2 13 🗋 2 Y       |  |  |  |  |  |  |
| 1В 🗌                                              | 3 12 <b>]</b> 2D |  |  |  |  |  |  |
| 1C 🗍                                              | 4 11 2C          |  |  |  |  |  |  |

| SN54HC4002 | FK PACKAGE |
|------------|------------|
| (TOP       | VIEW)      |

1D 🗍 5

NC 6

GND 7

|    |          | 1A     | 1   | Ŋ  | VCC<br>VCC    | 2Υ |      |    |
|----|----------|--------|-----|----|---------------|----|------|----|
| ſ  | $ \cap $ | 3      | 2   | Ţ  | 20            | 19 |      |    |
| 1B | ≱ן       |        |     |    |               |    | 18[  | 2D |
| NC | ]5       |        |     |    |               |    | 17 [ | NC |
| 1C | ]6       |        |     |    |               |    | 16   | 2C |
| NC | ٦D       |        |     |    |               |    | 15[  | NC |
| 1D | ] 8      |        |     |    |               |    | 14[  | 2B |
|    |          | Å      |     | 11 | <sup>12</sup> | 13 |      |    |
|    |          | ů<br>Z | GND | NC | NC            | 2A |      | -  |

NC-No internal connection

#### logic diagram (positive logic)



PRODUCTION DATA documents contain information current as of publication date. Products conform to specifications per the terms of Taxas leatruments standard warranty. Production processing does not necessarily include testing of all parameters.



Copyright © 1982, Texas Instruments Incorporated

### SN54HC4002, SN74HC4002 DUAL 4-INPUT POSITIVE-NOR GATES

#### absolute maximum ratings over operating free-air temperature range<sup>†</sup>

| Supply voltage range, VCC                                             | -0.5 | V to 7 V |
|-----------------------------------------------------------------------|------|----------|
| Input clamp current, IIK (VI < 0 or VI > VCC)                         |      | ± 20 mA  |
| Output clamp current, $IOK$ ( $VO < 0$ or $AO > ACC$ )                |      | ± 20 mA  |
| Continuous output current, $I_{O}$ (VO = 0 to VCC)                    |      | ± 25 mA  |
| Continuous current through VCC or GND pins                            |      | ± 50 mA  |
| Lead temperature 1,6 mm (1/16 in) from case for 60 s: FK or J package |      | . 300°C  |
| Lead temperature 1,6 mm (1/16 in) from case for 10 s: D or N package  |      | . 260°C  |
| Storage temperature range 6                                           | 5°C  | to 150°C |

<sup>†</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

|                |                                        |                         | SN54HC4002 |     |      | SN74HC4002 |     |                 |      |
|----------------|----------------------------------------|-------------------------|------------|-----|------|------------|-----|-----------------|------|
|                |                                        |                         | MIN        | NOM | MAX  | MIN        | NOM | MAX             | UNIT |
| Vcc            | Supply voltage                         |                         | 2          | 5   | 6    | 2          | 5   | 6               | V    |
|                |                                        | V <sub>CC</sub> = 2 V   | 1.5        |     |      | 1.5        |     |                 |      |
| VIH            | High-level input voltage               | $V_{CC} = 4.5 V$        | 3.15       |     |      | 3.15       |     |                 | V    |
|                |                                        | $V_{CC} = 6 V$          | 4.2        |     |      | 4.2        |     |                 |      |
|                |                                        | V <sub>CC</sub> = 2 V   | 0          |     | 0.3  | 0          |     | 0.3             |      |
| VIL            | Low-level input voltage                | V <sub>CC</sub> = 4.5 V | 0          |     | 0.9  | 0          |     | 0.9             | V    |
|                |                                        | V <sub>CC</sub> = 6 V   | 0          |     | 1.2  | 0          |     | 1.2             |      |
| Vi             | Input voltage                          |                         | 0          |     | Vcc  | 0          |     | V <sub>CC</sub> | V    |
| Vo             | Output voltage                         |                         | 0          |     | Vcc_ | 0          |     | Vcc             | V    |
|                |                                        | V <sub>CC</sub> = 2 V   | 0          |     | 1000 | 0          |     | 1000            |      |
| t <sub>t</sub> | Input transition (rise and fall) times | $V_{CC} = 4.5 V$        | 0          |     | 500  | 0          |     | 500             | ns   |
|                |                                        | $V_{CC} = 6 V$          | 0          |     | 400  | 0          |     | 400             |      |
| ΤΔ             | Operating free-air temperature         |                         | - 55       |     | 125  | - 40       |     | 85              | °C   |

#### recommended operating conditions

# electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

|                 |                                                                                  |          | TA = 25°C |     |      | SN54H | C4002 | SN74HC4002 |      | LINIT |
|-----------------|----------------------------------------------------------------------------------|----------|-----------|-----|------|-------|-------|------------|------|-------|
| PARAMETER       | TEST CONDITIONS                                                                  | VCC      | MIN T     | YP  | MAX  | MIN   | MAX   | MIN        | MAX  |       |
|                 |                                                                                  | 2 V      | 1.9 1.9   | 98  |      | 1.9   |       | 1.9        |      |       |
| ĺ               | $V_{\rm I} = V_{\rm IH}$ or $V_{\rm IL}$ , $I_{\rm OH} = -20 \ \mu A$            | 4.5 V    | 4,4 4,4   | 199 |      | 4.4   |       | 4.4        |      |       |
| ∨он             |                                                                                  | 6 V      | 5.9 5.9   | 999 |      | 5.9   |       | 5.9        |      | v     |
|                 | $V_{I} = V_{IH}$ or $V_{IL}$ , $I_{OH} = -4 \text{ mA}$                          | 4.5 V    | 3.98 4.   | .30 |      | 3.7   |       | 3.84       |      |       |
|                 | VI = VIH or VIL, IOH = -5.2 mA                                                   | 6 V      | 5.48 5.   | .80 |      | 5.2   |       | 5.34       |      |       |
|                 | $V_{I} = V_{IH}$ or $V_{IL}$ , $I_{OL} = 20 \ \mu A$                             | 2 V      | 0.0       | 002 | 0.1  |       | 0.1   |            | 0.1  |       |
|                 |                                                                                  | 4.5 V    | 0.0       | 001 | 0.1  |       | 0.1   |            | 0.1  |       |
| V <sub>OL</sub> |                                                                                  | 6 V      | 0.0       | 001 | 0.1  |       | 0.1   |            | 0.1  | v     |
|                 | $V_{\parallel} = V_{\parallel}$ or $V_{\parallel}$ , $I_{0\perp} = 4 \text{ mA}$ | 4.5 V    | 0.        | .17 | 0.26 |       | 0.4   |            | 0.33 |       |
|                 | $V_{I} = V_{IH}$ or $V_{IL}$ , $I_{OL} = 5.2 \text{ mA}$                         | 6 V      | 0.        | .15 | 0.26 |       | 0.4   |            | 0.33 |       |
|                 | $V_{I} = V_{CC} \text{ or } 0$                                                   | 6 V      | ±(        | 0.1 | ±100 |       | ±1000 | t ]        | 1000 | nA    |
| I'cc            | $V_I = V_{CC} \text{ or } 0,  I_O \neq 0$                                        | 6 V      |           |     | 2    |       | 40    |            | 20   | μA    |
| Ci              |                                                                                  | 2 to 6 V |           | 3   | 10   |       | 10    |            | 10   | рF    |



### SN54HC4002, SN74HC4002 DUAL 4-INPUT POSITIVE-NOR GATES

ć

.

# switching characteristics over recommended operating free-air temperature range (unless otherwise noted), $C_L = 50 \text{ pF}$ (see Note 1)

| PARAMETER       | FROM      | то                 | Vcc         | T <sub>A</sub> = 25°C        |         |     | SN54HC4002 |          | SN74HC4002 |           |      |
|-----------------|-----------|--------------------|-------------|------------------------------|---------|-----|------------|----------|------------|-----------|------|
|                 | (INPUT)   | (OUTPUT)           |             | MIN                          | TYP     | MAX | MIN        | MAX      | MIN        | MAX       | UNIT |
|                 |           |                    | 2 V         |                              | 44      | 110 | <u> </u>   | 165      |            | 140       |      |
| t <sub>pđ</sub> | A thru D  | Y                  | 4.5 V       |                              | 12      | 22  | 1          | 33       |            | 28        | ns   |
|                 |           |                    | 6 V         |                              | 11      | 19  |            | 28       |            | 24        |      |
|                 |           |                    | 2 V         |                              | 38      | 75  |            | 110      |            | 95        |      |
| tt              |           | Y                  | 4.5 V       |                              | 8       | 15  |            | 22       |            | 19        | กร   |
|                 |           |                    | 6 V         | <u> </u>                     | 6       | 13  |            | 19       |            | 16        |      |
|                 |           |                    |             |                              | Ate las | · - | 25.90      | <u> </u> |            | E aE tura |      |
| ∿pd             | Power dis | sipation capacitan | ce per gate | No load, $f_A = 25^{\circ}C$ |         | 1   | 25 pr typ  |          |            |           |      |

Note 1: Load circuits and voltage waveforms are shown in Section 1.



#### **IMPORTANT NOTICE**

Texas Instruments and its subsidiaries (TI) reserve the right to make changes to their products or to discontinue any product or service without notice, and advise customers to obtain the latest version of relevant information to verify, before placing orders, that information being relied on is current and complete. All products are sold subject to the terms and conditions of sale supplied at the time of order acknowledgement, including those pertaining to warranty, patent infringement, and limitation of liability.

TI warrants performance of its semiconductor products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are utilized to the extent TI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except those mandated by government requirements.

CERTAIN APPLICATIONS USING SEMICONDUCTOR PRODUCTS MAY INVOLVE POTENTIAL RISKS OF DEATH, PERSONAL INJURY, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE ("CRITICAL APPLICATIONS"). TI SEMICONDUCTOR PRODUCTS ARE NOT DESIGNED, AUTHORIZED, OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT DEVICES OR SYSTEMS OR OTHER CRITICAL APPLICATIONS. INCLUSION OF TI PRODUCTS IN SUCH APPLICATIONS IS UNDERSTOOD TO BE FULLY AT THE CUSTOMER'S RISK.

In order to minimize risks associated with the customer's applications, adequate design and operating safeguards must be provided by the customer to minimize inherent or procedural hazards.

TI assumes no liability for applications assistance or customer product design. TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right of TI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used. TI's publication of information regarding any third party's products or services does not constitute TI's approval, warranty or endorsement thereof.

Copyright © 1998, Texas Instruments Incorporated

| 🜵 Texas Instruments | THE WORLD LEADER IN DSP AND ANALOG                                                                   |
|---------------------|------------------------------------------------------------------------------------------------------|
| Products 💽          | Development Tools Applications GO                                                                    |
| Search GO           | □ Advanced Search □ TI Home □ TI&ME □ Employment<br>□ Tech Support □ Comments □ Site Map □ TI Global |

### PRODUCT FOLDER | PRODUCT INFO: FEATURES | DESCRIPTION | DATASHEETS | PRICING/AVAILABILITY | APPLICATION NOTES | RELATED DOCUMENTS

PRODUCT SUPPORT: TRAINING

# SN54HC4002, Dual 4-Input Positive-NOR Gates

DEVICE STATUS: ACTIVE

| PARAMETER NAME    | SN54HC4002 |  |  |  |  |
|-------------------|------------|--|--|--|--|
| Voltage Nodes (V) | 6, 5, 2    |  |  |  |  |
| Vcc range (V)     | 2.0 to 6.0 |  |  |  |  |
| Input Level       | CMOS       |  |  |  |  |
| Output Level      | CMOS       |  |  |  |  |
| No. of Gates      | 2          |  |  |  |  |

# FEATURES

Back to Top

- Package Options Include Plastic "Small Outline" Packages, Ceramic Chip carriers, and Standard Plastic and Ceramic 300-mil DIPs
- Dependable Texas Instruments Quality and Reliability

# DESCRIPTION

Back to Top

These devices contain two independent 4-input positive NOR gates. They perform the Boolean functions: Y = (A + B + C + D) or  $Y = A \cdot B \cdot C \cdot D$  in positive logic.

The SN54HC4002 is characterized for operation over the full military temperature range of -55°C to 125°C. The SN74HC4002 is characterized for operation from -40°c to 85°C.

### **TECHNICAL DOCUMENTS**

To view the following documents, Acrobat Reader 3.x is required. To download a document to your hard drive, right-click on the link and choose 'Save'.

# DATASHEET

Full datasheet in Acrobat PDF: scls157.pdf (76 KB) (Updated: 09/01/1987) Full datasheet in Zipped PostScript: scls157.psz (143 KB)

# **APPLICATION NOTES**

View Application Reports for Digital Logic

Back to Top

Back to Top

Back to Top

2 of 2

- CMOS Power Consumption and CPD Calculation (SCAA035B Updated: 06/01/1997)
- Designing With Logic (SDYA009C Updated: 06/01/1997)
- HCMOS Design Considerations (SCLA007 Updated: 04/01/1996)
- Implications of Slow or Floating CMOS Inputs (SCBA004C Updated: 02/01/1998)
- Input and Output Characteristics of Digital Integrated Circuits (SDYA010 Updated: 10/01/1996)
- Live Insertion (SDYA012 Updated: 10/01/1996)
- <u>SN54/74HCT CMOS Logic Family Applications And Restrictions</u> (SCLA011 Updated: 05/01/1996)
- Using High Speed CMOS and Advanced CMOS in Systems With Multiple Vcc (SCLA008 -Updated: 04/01/1996)

### RELATED DOCUMENTS

Back to Top

- Documentation Rules (SAP) And Ordering Information (SZZU001B, 4 KB Updated: 05/06/1999)
- Logic Selection Guide Second Half 2000 (SDYU001N, 5035 KB Updated: 04/17/2000)
- MicroStar Junior BGA Design Summary (SCET004, 167 KB Updated: 07/28/2000)
- More Power In Less Space Technical Article (SCAU001A, 850 KB Updated: 03/01/1996)

### PRICING/AVAILABILITY

Back to Top

| ORDERABLE<br>DEVICE | PACKAGE   | <u>PINS</u> | <u>TEMP</u><br>(°C) | <u>STATUS</u> | BUDGETARY<br>PRICE<br>US\$/UNIT<br>QTY=1000+ | <u>PACK</u><br><u>QTY</u> | <u>DSCC</u><br><u>NUMBER</u> | PRICING/AVAILABILITY |
|---------------------|-----------|-------------|---------------------|---------------|----------------------------------------------|---------------------------|------------------------------|----------------------|
| JM38510/65104BCA    | Ţ         | 14          | -55<br>TO<br>125    | ACTIVE        | 6.22                                         | 1                         |                              | Check stock or order |
| SN54HC4002J         | Ţ         | 14          | -55<br>TO<br>125    | ACTIVE        | 0.94                                         | 500                       |                              | Check stock or order |
| SNJ54HC4002FK       | <u>FK</u> | 20          | -55<br>TO<br>125    | ACTIVE        | 6.71                                         | 165                       | 84044012A                    | Check stock or order |
| SNJ54HC4002J        | Ţ         | 14          | -55<br>TO<br>125    | ACTIVE        | 1.12                                         | 1                         |                              | Check stock or order |

### Table Data Updated on: 11/21/2000

© Copyright 2000 Texas Instruments Incorporated. All rights reserved. <u>Trademarks | Privacy Policy</u> | Important Notice