
SCES130D - MARCH 1998 - REVISED MAY 2000

- EPIC™ (Enhanced-Performance Implanted CMOS) Process
- Unbuffered Outputs
- Typical V_{OLP} (Output Ground Bounce)
 <0.8 V at V_{CC} = 3.3 V, T_A = 25°C
- Typical V_{OHV} (Output V_{OH} Undershoot)
 >2.3 V at V_{CC} = 3.3 V, T_A = 25°C
- 2-V to 5.5-V V_{CC} Operation
- Support Mixed-Mode Voltage Operation on All Ports
- Latch-Up Performance Exceeds 250 mA Per JESD 17
- ESD Protection Exceeds 2000 V Per MIL-STD-883, Method 3015; Exceeds 200 V Using Machine Model (C = 200 pF, R = 0)
- Package Options Include Plastic Small-Outline (D, NS), Shrink Small-Outline (DB), Thin Very Small-Outline (DGV), and Thin Shrink Small-Outline (PW) Packages, Ceramic Flat (W) Packages, Chip Carriers (FK), and DIPs (J)


description

These hex inverters are designed for 2-V to 5.5-V V_{CC} operation.

SN54LVU04A . . . J OR W PACKAGE SN74LVU04A . . . D, DB, DGV, NS, OR PW PACKAGE (TOP VIEW)



SN54LVU04A . . . FK PACKAGE (TOP VIEW)



NC - No internal connection

The 'LVU04A devices contain six independent inverters with unbuffered outputs. These devices perform the Boolean function $Y = \overline{A}$.

The SN54LVU04A is characterized for operation over the full military temperature range of -55° C to 125° C. The SN74LVU04A is characterized for operation from -40° C to 85° C.

FUNCTION TABLE (each inverter)

INPUT	OUTPUT
Α	Υ
Н	L
L	Н




Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

EPIC is a trademark of Texas Instruments.

LINEESS OTHERWISE NOTED this document contains PRODUCTION



logic symbol[†]



[†] This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12. Pin numbers shown are for the D, DB, DGV, J, NS, PW, and W packages.

logic diagram, each inverter (positive logic)



absolute maximum ratings over operating free-air temperature range (unless otherwise noted)‡

Supply voltage range, V _{CC}		–0.5 V to 7 V
Input voltage range, V _I (see Note 1)		–0.5 V to 7 V
Output voltage range, V _O (see Notes 1 and 2)		$0.5 \text{ V to V}_{CC} + 0.5 \text{ V}$
Input clamp current, I_{IK} ($V_I < 0$)		–20 mA
Output clamp current, I _{OK} (V _O < 0 or V _O > V _{CO}	C)	±50 mA
Continuous output current, $I_O(V_O = 0 \text{ to } V_{CC})$	-	±25 mA
Continuous current through V _{CC} or GND		±50 mA
Package thermal impedance, θ _{JA} (see Note 3)	: D package	86°C/W
	DB package	96°C/W
	DGV package	127°C/W
	NS package	76°C/W
	PW package	113°C/W
Storage temperature range, T _{stg}		–65°C to 150°C

[‡] Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- NOTES: 1. The input and output voltage ratings may be exceeded if the input and output current ratings are observed.
 - 2. This value is limited to 5.5 V maximum.
 - 3. The package thermal impedance is calculated in accordance with JESD 51.



recommended operating conditions (see Note 4)

			SN54L	.VU04A	SN74L	VU04A	UNIT
			MIN	MAX	MIN	MAX	UNIT
Vcc	Supply voltage		2	5.5	2	5.5	V
		V _{CC} = 2 V	1.7		1.7		
VIH	High-level input voltage	$V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$	V _{CC} × 0.8		$V_{CC} \times 0.8$		V
VIH	r light-level input voltage	$V_{CC} = 3 V \text{ to } 3.6 V$	V _{CC} × 0.8		$V_{CC} \times 0.8$		ľ
		$V_{CC} = 4.5 \text{ V to } 5.5 \text{ V}$	V _{CC} × 0.8		$V_{CC} \times 0.8$		
		$V_{CC} = 2 V$		0.3		0.3	
VIL	Low-level input voltage	$V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$		$V_{CC} \times 0.2$		$V_{CC} \times 0.2$	V
۷IL	Low-level input voltage	$V_{CC} = 3 V \text{ to } 3.6 V$		$V_{CC} \times 0.2$		$V_{CC} \times 0.2$	ľ
		$V_{CC} = 4.5 \text{ V to } 5.5 \text{ V}$		$V_{CC} \times 0.2$	V _{CC} × 0.2		
VI	Input voltage		0	5.5	0	5.5	V
Vo	Output voltage		0	VCC	0	VCC	V
		V _{CC} = 2 V	1	– 50		-50	μΑ
lou	High-level output current	$V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$	5	-2		-2	
ЮН	r light-level output current	$V_{CC} = 3 V \text{ to } 3.6 V$	30	-6		-6	mA
		$V_{CC} = 4.5 \text{ V to } 5.5 \text{ V}$	Q	-12		-12	
		V _{CC} = 2 V		50		50	μΑ
lo:	Low-level output current	$V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$		2		2	
IOL	Low-level output current	$V_{CC} = 3 V \text{ to } 3.6 V$		6		6	mA
		$V_{CC} = 4.5 \text{ V to } 5.5 \text{ V}$		12		12	
		$V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$	0	200	0	200	
Δt/Δν	Input transition rise or fall rate	$V_{CC} = 3 V \text{ to } 3.6 V$	0	100	0	100	ns/V
		$V_{CC} = 4.5 \text{ V to } 5.5 \text{ V}$	0	20	0	20	
T_A	Operating free-air temperature		-55	125	-40	85	°C

NOTE 4: All unused inputs of the device must be held at V_{CC} or GND to ensure proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs*, literature number SCBA004.

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER	TEST CONDITIONS	,,	SN54	1LVU04A		SN74	LVU04A	١	UNIT
PARAMETER	TEST CONDITIONS	v _{CC}	MIN	TYP	MAX	MIN	TYP	MAX	UNIT
	IOH = -50 μA	2 V to 5.5 V	V _{CC} -0.1			V _{CC} -0.1			
Vou	I _{OH} = -2 mA	2.3 V	2			2			V
VOH	I _{OH} = -6 mA	3 V	2.48	, sh		2.48			V
	I _{OH} = -12 mA	4.5 V	3.8	, Z		3.8			
	I _{OL} = 50 μA	2 V to 5.5 V		BA	0.1			0.1	
V _{OL}	$I_{OL} = 2 \text{ mA}$	2.3 V			0.4			0.4	V
VOL.	I _{OL} = 6 mA	3 V	"/2)	0.44			0.44	v
	I _{OL} = 12 mA	4.5 V	0		0.55			0.55	
lį	$V_I = V_{CC}$ or GND	0 V to 5.5 V	Q		±1			±1	μΑ
Icc	$V_I = V_{CC}$ or GND, $I_O = 0$	5.5 V			20			20	μΑ
C _i	$V_I = V_{CC}$ or GND	3.3 V		4			4		pF

SCES130D - MARCH 1998 - REVISED MAY 2000

switching characteristics over recommended operating free-air temperature range, V_{CC} = 2.5 V \pm 0.2 V (unless otherwise noted) (see Figure 1)

PARAMETER	ER FROM TO (OUTPUT)	то	LOAD	T,	ղ = 25°C	;	SN54LVU04A	SN74L	VU04A	UNIT
PARAMETER		(OUTPUT)	CAPACITANCE	MIN	TYP	MAX	MIN MAX	MIN	MAX	UNIT
to a	Δ	V	C _L = 15 pF		3.2*	10.9*	1* 14*	1	14	no
^t pd	^	ī	C _L = 50 pF		6.6	13.4	1 16	1	16	ns

^{*} On products compliant to MIL-PRF-38535, this parameter is not production tested.

switching characteristics over recommended operating free-air temperature range, V_{CC} = 3.3 V \pm 0.3 V (unless otherwise noted) (see Figure 1)

PARAMETER	FROM	то	LOAD	T,	ղ = 25°C	;	SN54LVU04A	SN74L\	/U04A	UNIT
PARAMETER	(INPUT) (OUTPUT) CAPAC	CAPACITANCE	MIN	TYP	MAX	MIN MAX	MIN	MAX	UNIT	
foot	^		C _L = 15 pF		2.5*	8.9*	1* 10.5*	1	10.5	ns
^t pd	^	'	C _L = 50 pF		4.7	11.4	1 13	1	13	115

^{*} On products compliant to MIL-PRF-38535, this parameter is not production tested.

switching characteristics over recommended operating free-air temperature range, V_{CC} = 5 V \pm 0.5 V (unless otherwise noted) (see Figure 1)

PARAMETER	FROM	то	LOAD	T,	ղ = 25°C	;	SN54LVU04A	SN74L	VU04A	LINIT
PARAMETER	(INPUT) (OUTPUT) CAPAC	CAPACITANCE	MIN	TYP	MAX	MIN MAX	MIN	MAX	UNIT	
foot	^	V	C _L = 15 pF		2.2*	5.5*	1* 6.5	1	6.5	no
^t pd	^	ī	C _L = 50 pF		3.9	7	1 8	1	8	ns

^{*} On products compliant to MIL-PRF-38535, this parameter is not production tested.

noise characteristics, $V_{CC} = 3.3 \text{ V}$, $C_L = 50 \text{ pF}$, $T_A = 25^{\circ}\text{C}$ (see Note 5)

	PARAMETER			SN74LVU04A			
	PARAMETER	MIN	TYP	MAX	UNIT		
VOL(P)	Quiet output, maximum dynamic V _{OL}		0.5	0.8	V		
V _{OL(V)}	Quiet output, minimum dynamic V _{OL}		-0.1	-0.8	V		
V _{OH(V)}	Quiet output, minimum dynamic V _{OH}		3		V		
VIH(D)	High-level dynamic input voltage	2.31			V		
V _{IL(D)}	Low-level dynamic input voltage			0.99	V		


NOTE 5: Characteristics are for surface-mount packages only.

operating characteristics, T_A = 25°C

PARAMETER		TEST CO	VCC	TYP	UNIT	
Const	Dower dissination conscitance	C 50 pE	f = 10 MHz	3.3 V	5.6	n.E
C _{pd}	Power dissipation capacitance	$C_L = 50 \text{ pF},$	I = 10 WITZ	5 V	6.7	pΕ



PARAMETER MEASUREMENT INFORMATION



NOTES: A. C_L includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: PRR \leq 1 MHz, $Z_Q = 50 \Omega$, $t_f \leq 3$ ns, $t_f \leq 3$ ns.
- D. The outputs are measured one at a time with one input transition per measurement.
- E. tpLz and tpHz are the same as tdis.
- F. tpzL and tpzH are the same as ten.
- G. tpHL and tpLH are the same as tpd.

Figure 1. Load Circuit and Voltage Waveforms

IMPORTANT NOTICE

Texas Instruments and its subsidiaries (TI) reserve the right to make changes to their products or to discontinue any product or service without notice, and advise customers to obtain the latest version of relevant information to verify, before placing orders, that information being relied on is current and complete. All products are sold subject to the terms and conditions of sale supplied at the time of order acknowledgment, including those pertaining to warranty, patent infringement, and limitation of liability.

TI warrants performance of its semiconductor products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are utilized to the extent TI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except those mandated by government requirements.

Customers are responsible for their applications using TI components.

In order to minimize risks associated with the customer's applications, adequate design and operating safeguards must be provided by the customer to minimize inherent or procedural hazards.

TI assumes no liability for applications assistance or customer product design. TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right of TI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used. TI's publication of information regarding any third party's products or services does not constitute TI's approval, warranty or endorsement thereof.

Copyright © 2000, Texas Instruments Incorporated