

54F/74F32 Quad 2-Input OR Gate

General Description

Features

This device contains four independent gates, each of which performs the logic OR function.

■ Guaranteed 4000V minimum ESD protection


Commercial	Military	Package Number	Package Description
74F32PC		N14A	14-Lead (0.300" Wide) Molded Dual-In-Line
	54F32DM (Note 2)	J14A	14-Lead Ceramic Dual-In-Line
74F32SC (Note 1)		M14A	14-Lead (0.150" Wide) Molded Small Outline, JEDEC
74F32SJ (Note 1)		M14D	14-Lead (0.300" Wide) Molded Small Outline, EIAJ
	54F32FM (Note 2)	W14B	14-Lead Cerpack
	54F32LM (Note 2)	E20A	20-Lead Ceramic Leadless Chip Carrier, Type C


Note 1: Devices also available in 13" reel. Use suffix = SCX and SJX.


Note 2: Military grade device with environmental and burn-in processing. Use suffix = DMQB, FMQB and LMQB.

Logic Symbol

Connection Diagrams







Pin Assignment

TI /F/9463-1

Unit Loading/Fan Out

		54F/74F				
Pin Names	Description	U.L. HIGH/LOW	Input I _{IH} /I _{IL} Output I _{OH} /I _{OL}			
A _n , B _n O _n	Inputs Outputs	1.0/1.0 50/33.3	20 μA/ – 0.6 mA –1 mA/20 mA			

TRI-STATE® is a registered trademark of National Semiconductor Corporation

Absolute Maximum Ratings (Note 1)

If Military/Aerospace specified devices are required, please contact the National Semiconductor Sales Office/Distributors for availability and specifications.

 $\begin{array}{lll} \mbox{Storage Temperature} & -65^{\circ}\mbox{C to} + 150^{\circ}\mbox{C} \\ \mbox{Ambient Temperature under Bias} & -55^{\circ}\mbox{C to} + 125^{\circ}\mbox{C} \\ \mbox{Junction Temperature under Bias} & -55^{\circ}\mbox{C to} + 175^{\circ}\mbox{C} \\ \mbox{Plastic} & -55^{\circ}\mbox{C to} + 150^{\circ}\mbox{C} \\ \end{array}$

V_{CC} Pin Potential to

 Ground Pin
 −0.5V to +7.0V

 Input Voltage (Note 2)
 −0.5V to +7.0V

 Input Current (Note 2)
 −30 mA to +5.0 mA

Voltage Applied to Output

in HIGH State (with $V_{CC} = 0V$)

 $\begin{array}{ll} \text{Standard Output} & -0.5 \text{V to V}_{\text{CC}} \\ \text{TRI-STATE} \tiny{\circledR} \text{ Output} & -0.5 \text{V to } +5.5 \text{V} \end{array}$

Current Applied to Output in LOW State (Max) twice the rated I_{OL} (mA) ESD Last Passing Voltage (Min) 4000V

Note 1: Absolute maximum ratings are values beyond which the device may be damaged or have its useful life impaired. Functional operation under these conditions is not implied.

Note 2: Either voltage limit or current limit is sufficient to protect inputs.

Recommended Operating Conditions

Free Air Ambient Temperature

Supply Voltage

Military +4.5V to +5.5V Commercial +4.5V to +5.5V

DC Electrical Characteristics


Symbol	Parameter		54F/74F			Units	V _{CC}	Conditions	
Symbol			Min	Тур	Max	Ullits	▼CC	Conditions	
V _{IH}	Input HIGH Voltage		2.0			٧		Recognized as a HIGH Signal	
V _{IL}	Input LOW Voltage				0.8	V		Recognized as a LOW Signal	
V _{CD}	Input Clamp Diode Vo	oltage			-1.2	V	Min	$I_{\text{IN}} = -18 \text{ mA}$	
V _{OH}	Output HIGH Voltage	54F 10% V _{CC} 74F 10% V _{CC} 74F 5% V _{CC}	2.5 2.5 2.7			٧	Min	$I_{OH} = -1 \text{ mA}$ $I_{OH} = -1 \text{ mA}$ $I_{OH} = -1 \text{ mA}$	
V _{OL}	Output LOW 54F 10% V _{CC} Voltage 74F 10% V _{CC}				0.5 0.5	٧	Min	$I_{OL} = 20 \text{ mA}$ $I_{OL} = 20 \text{ mA}$	
I _{IH}	Input HIGH 54F Current 74F				20.0 5.0	μΑ	Max	$V_{IN} = 2.7V$	
I _{BVI}	Input HIGH Current Breakdown Test	54F 74F			100 7.0	μΑ	Max	$V_{IN} = 7.0V$	
ICEX	Output HIGH Leakage Current	54F 74F			250 50	μΑ	Max	$V_{OUT} = V_{CC}$	
V _{ID}	Input Leakage Test	74F	4.75			٧	0.0	$I_{\text{ID}} = 1.9 \ \mu\text{A}$ All Other Pins Grounded	
I _{OD}	Output Leakage 74F Circuit Current				3.75	μΑ	0.0	V _{IOD} = 150 mV All Other Pins Grounded	
I _{IL}	Input LOW Current				-0.6	mA	Max	$V_{IN} = 0.5V$	
los	Output Short-Circuit Current		-60		-150	mA	Max	$V_{OUT} = 0V$	
Icch	Power Supply Current			6.1	9.2	mA	Max	V _O = HIGH	
I _{CCL}	Power Supply Current	t		10.3	15.5	mA	Max	$V_O = LOW$	

AC Electrical Characteristics


			74F		5-	4F	74F		
Symbol Parameter		$\begin{aligned} \textbf{T}_{\textbf{A}} &= +25^{\circ}\textbf{C} \\ \textbf{V}_{\textbf{CC}} &= +5.0\textbf{V} \\ \textbf{C}_{\textbf{L}} &= 50\textbf{pF} \end{aligned}$			$ extsf{T}_{ extsf{A}}, extsf{V}_{ extsf{CC}} = extsf{Mil} \ extsf{C}_{ extsf{L}} = extsf{50 pF}$		T _A , V _{CC} = Com C _L = 50 pF		Units
		Min	Тур	Max	Min	Max	Min	Max	
t _{PLH}	Propagation Delay	3.0	4.2	5.6	3.0	7.5	3.0	6.6	ns
t _{PHL}	A_n , B_n to O_n	3.0	4.0	5.3	2.5	7.5	3.0	6.3	115

Ordering Information


The device number is used to form part of a simplified purchasing code where the package type and temperature range are defined as follows:




Physical Dimensions inches (millimeters)



Physical Dimensions inches (millimeters) (Continued) 0.785 (19.939) MAX 14 13 12 11 10 9 8 0.025 (0.635) 0.220-0.310 (5.588-7.874) 1 2 3 4 5 6 7 0.290-0.320 0.005 0.200 GLASS SEALANT (5.080) MAX 0.020-0.060 (D.127) MIN (7.366-8.128) 0.060 ± 0.005 (1.524 ±0.127) 0.180 MAX (0.508-1.524) (4.572) 0.008-0.012 10° MAX (0.203-0.305) 0.310-0.410 D.018 ±0.003 0.125-0.200 0.098 (7.874-10.41) (0.457 ±0,076) (3.175-5.080) (2.489) MAX BOTH ENDS 0.100 ±0.010 (2.540 ±0.254) (3.81) MIN J14A (REV G) 14-Lead Ceramic Dual-In-Line Package (D) NS Package Number J14A LEAD NO. 1 IDENT 0.010 (0.254) MAX $\frac{0.150 - 0.157}{(3.810 - 3.988)}$ $\frac{0.053 - 0.069}{(1.346 - 1.753)}$ 8° MAX TYP $\frac{0.004 - 0.010}{(0.102 - 0.254)}$ SEATING PLANE 0.014 (0.356) 0.008 - 0.010 (0.203 - 0.254) TYP ALL LEADS $\frac{0.014-0.020}{(0.356-0.508)}\,\mathrm{TYP}$ 0.016 - 0.050 (0.406 - 1.270) TYP ALL LEADS 0.004 (0.102) ALL LEAD TIPS 0.008 (0.203) TYP 14-Lead (0.150" Wide) Molded Small Outline Package, JEDEC (S) NS Package Number M14A



Physical Dimensions inches (millimeters) (Continued)



LIFE SUPPORT POLICY

NATIONAL'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF NATIONAL SEMICONDUCTOR CORPORATION. As used herein:

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
- A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.



National Semiconductor Corporation 2900 Semiconductor Drive P.O. Box 58090 Santa Clara, CA 95052-8090 Tel: 1(800) 272-9959 TWX: (910) 339-9240 National Semiconductor GmbH Livry-Gargan-Str. 10 D-82256 Fürstenfeldbruck Germany Tel: (81-41) 35-0 Telex: 527649 Fax: (81-41) 35-1 National Semiconductor Japan Ltd. Sumitomo Chemical Engineering Center Bldg. 7F 1-7-1, Nakase, Mihama-Ku Chiba-City, Ciba Prefecture 261

National Semiconductor Hong Kong Ltd. 13th Floor, Straight Block, Ocean Centre, 5 Canton Rd. Tsimshatsui, Kowloon Hong Kong Tel: (852) 2737-1600 Fax: (852) 2736-9960

National Semiconductores Do Brazil Ltda. Rue Deputado Lacorda Franco 120-3A Sao Paulo-SP Brazil 05418-000 Tel: (55-11) 212-5066 Telex: 391-1131931 NSBR BR Fax: (55-11) 212-1181 National Semiconductor (Australia) Pty, Ltd. Building 16 Business Park Drive Monash Business Park Nottinghilli, Melbourne Victoria 3168 Australia Tel: (3) 558-9999 Fax: (3) 558-9998

×	<u>Design</u>	Purchasing	<u>Quality</u>	Company	<u>Jobs</u>

Products > Military/Aerospace > Logic > FAST > 54F32



54F32 Quad 2-Input OR Gate

Contents

- General Description
- Features
- Datasheet
- Package Availability, Models, Samples
 & Pricing

General Description

This device contains four independent gates, each of which performs the logic OR function.

Features

• Guaranteed 4000V minimum ESD protection

Datasheet

Title	Size (in Kbytes)	Date	View Online	Download	Receive via Email
54F32 Quad 2-Input OR Gate		1	View Online	II Jownload I	Receive via Email
54F32 Mil-Aero Datasheet MN54F32-X	16 Kbytes		View Online	II Jownload I	Receive via Email

Please use <u>Adobe Acrobat</u> to view PDF file(s). If you have trouble printing, see <u>Printing Problems</u>.

Package Availability, Models, Samples & Pricing

	Package			Mod	els	Samples	Budgetary Pricing		Std
Part Number	Туре	# pins	Status	SPICE	IBIS	& Electronic Orders	Quantity	\$US each	Pacl Size
54F32LMQB	LCC	20	Full production	N/A	N/A		50+	\$3.3500	tube of 50
54F32DMQB	Cerdip	14	Full production	N/A	N/A	×	50+	\$1.6000	tube of 25
54F32DM	Cerdip	14	Full production	N/A	N/A	·	50+	\$7.5000	tube of 25
54F32FMQB	Cerpack	14	Full production	N/A	N/A		50+	\$2.6000	tube of 19
54F32DC	Cerdip	14	Full production	N/A	N/A	·			tube of N/A
JM38510/33501B2	LCC	20	Full production	N/A	N/A		50+	\$7.3000	tube of 50
JM38510/33501BC	Cerdip	14	Full production	N/A	N/A		50+	\$7.0000	tube of 25
JM38510/33501BD	Cerpack	14	Full production	N/A	N/A		50+	\$7.9000	tube of 19
JM38510/33501SC	Cerdip	14	Full production	N/A	N/A		50+	\$145.0000	tube of 25
JM38510/33501SD	Cerpack	14	Full production	N/A	N/A		50+	\$145.0000	tube of 19
54F32 MW8	wafe	er	Full production	N/A	N/A				N/A

[Information as of 28-Jul-2000]

Quick Search	Parametric	System	Product	Home
	Search	Diagrams	Tree	Home

About Languages . About the Site . About "Cookies"
National is QS 9000 Certified . Privacy/Security
Copyright © National Semiconductor Corporation
Preferences . Feedback