54/7477 011134

QUAD D-TYPE LATCH


CONNECTION DIAGRAM
PINOUT A

**DESCRIPTION** — The '77 contains four D-type latches used for temporary storage. Each latch shares an Enable input with one other latch. When the Enable input is HIGH, a latch is transparent, i.e., the Q output follows the D input each time it changes. When the Enable goes LOW, the information(that was present at the D input when the transition occurred) is retained at the Q output. For Truth Table, specifications, and logic diagrams, refer to the '75 data sheet, but note that  $\overline{\mathbf{Q}}$  is not available on the '77.

## ORDERING CODE: See Section 9

ONDERING CODE. See Section's				
PKGS	PIN OUT	V <sub>CC</sub> = +5.0 V ±5%, T <sub>A</sub> = 0°C to +70°C	MILITARY GRADE  V <sub>CC</sub> = +5.0 V ±10%,  T <sub>A</sub> = -55° C to +125° C	PKG TYPE
Ceramic DIP (D)	А	7477DC	5477DM	6A
Flatpak (F)	A	7477FC	5477FM	31

## LOGIC SYMBOL



## INPUT LOADING/FAN-OUT: See Section 3 for U.L. definitions

PIN NAMES	DESCRIPTION	<b>54/74 (U.L.)</b> HIGH/LOW	
D1 — D4	Data inputs	2.0/2.0	
E <sub>1,2</sub>	Enable Input, Latches 1, 2	4.0/4.0	
E3,4 Q1 Q4	Enable Input, Latches 3, 4	4.0/4.0	
Q1 — Q4	Latch Outputs	10/10	