


QUADRUPLE BUS TRANSCEIVERS

FEATURES

- Two-Way Asynchronous Communication Between Data Buses
- PNP Inputs Reduce D-C Loading
- Hysteresis (Typically 400 mV) at Inputs Improves Noise Margin

SN54LS243 . . . J OR W PACKAGE SN74LS243 . . . D, N, OR NS PACKAGE (TOP VIEW)



FUNCTION TABLE (EACH TRANSCEIVER)


| INP | UTS | Chlynd C242 |
|-----|-----|--------------------------|
| GAB | GBA | SNxxLS243 |
| L | L | A to B |
| Н | Н | B to A |
| Н | L | Isolation |
| L | Н | Latch A and B (A = B) |

DESCRIPTION

These four-data-line transceivers are designed for asynchronous two-way communications between data buses. SN74LS243 can be used to drive terminated lines down to $133~\Omega$.

SN54LS243 is characterized for operation over the full military temperature range of -55°C to 125°C. SN74LS243 is characterized for operation from 0°C to 70°C.

SCHEMATICS OF INPUTS AND OUTPUTS






Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.




LOGIC SYMBOL



A. These symbols are in accordance with ANSI/EEE Std. 91-1984 and IEC Publication 617-12.

LOGIC DIAGRAM (POSITIVE LOGIC)





ABSOLUTE MAXIMUM RATINGS(1)

| | | | MIN | MAX | UNIT |
|------------------|--------------------------------------|-----------|-----|-----|------|
| V _{CC} | Supply voltage ⁽²⁾ | | | 7 | V |
| V _{IN} | Input voltage | | 7 | V | |
| | OFF-state output voltage | | | 5.5 | V |
| _ | | SN54LS243 | -55 | 125 | 00 |
| T _A | Operating free-air temperature range | SN74LS243 | 0 | 70 | °C |
| T _{stg} | Storage temperature range | | -65 | 150 | °C |

⁽¹⁾ Stresses beyond those listed under absolute maximum ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions* is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

RECOMMENDED OPERATING CONDITIONS

over operating free-air temperature range (unless otherwise noted)

| | | SNS | SN54LS243 | | | | SN74LS243 | | | |
|-----------------|--------------------------------|-----|-----------|-----|------|-----|-----------|------|--|--|
| | | MIN | NOM | MAX | MIN | NOM | MAX | UNIT | | |
| V_{CC} | Supply voltage ⁽¹⁾ | 4.5 | 5 | 5.5 | 4.75 | 5 | 5.25 | V | | |
| V _{IH} | High-level input voltage | 2 | | | 2 | | | V | | |
| V _{IL} | Low-level input voltage | | | 0.7 | | | 0.8 | V | | |
| I _{OH} | High-level output voltage | | | -12 | | | -15 | mA | | |
| I _{OL} | Low-level output voltage | | | 12 | | | 24 | mA | | |
| T _A | Operating free-air temperature | -55 | | 125 | 0 | | 70 | °C | | |

⁽¹⁾ Voltage values are with respect to network ground terminal.

⁽²⁾ Voltage values are with respect to network ground terminal.



ELECTRICAL CHARACTERISTICS

over operating free-air temperature range (unless otherwise noted)

| DADAMETER | | _ | TEST CONDITIONS ⁽¹⁾ | | | 4LS243 | | SN | N74LS243 | 3 | |
|------------------|---|--------------------------------------|--------------------------------------|---|------------------------|--------|------|--------------------|----------|------|------|
| | PARAMETER TEST CONDITIONS ⁽¹⁾ | | ONS(") | MIN | MIN TYP ⁽²⁾ | | MIN | TYP ⁽²⁾ | MAX | UNIT | |
| V _{IK} | A or B | V _{CC} = MIN, | $I_1 = -18 \text{ mA}$ | | | | -1.5 | | | -1.5 | V |
| Hyster | esis (V _{T+} – V _{T-}) | $V_{CC} = MIN,$ | | | 0.2 | 0.4 | | 0.2 | 0.4 | | V |
| V | | V _{CC} = MIN, | V - 2 V | $V_{IL} = MAX,$ $I_{OH} = -3 \text{ mA}$ | 2.4 | 3.1 | | 2.4 | 3.1 | | ٧ |
| V _{OH} | | V _{CC} = IVIIIN, | v _{IH} = 2 v, | $V_{IL} = 0.5 \text{ V},$ $I_{OH} = \text{MAX}$ | 2 | | | 2 | | | |
| \/ | | $V_{CC} = MIN,$ | $V_{IH} = 2 V$, | I _{OL} = 12 mA | | 0.25 | 0.4 | | 0.25 | 0.4 | > |
| V_{OL} | | $V_{IL} = MAX$ | | I _{OL} = 24 mA | | | | | 0.35 | 0.5 | V |
| l _{ozh} | | $V_{CC} = MIN,$ $V_{IL} = MAX,$ | V _{IH} = 2 V, | V _O = 2.7 V | | | 40 | | | 40 | μΑ |
| l _{OZL} | | $V_{CC} = MIN,$ $V_{IL} = MAX,$ | V _{IH} = 2 V, | V _O = 0.4 V | | | -200 | | | -200 | μΑ |
| | A or B | | | V _I = 5.5 V | | | 0.1 | | | 0.1 | A |
| I _I | GAB or GBA | $V_{CC} = MAX,$ | | V _I = 7 V | | | 0.1 | | | 0.1 | mA |
| I _{IH} | | $V_{CC} = MAX,$ | | | | | 20 | | | 20 | μΑ |
| | A inputs | V _{CC} = MAX, GAB and GB | · · | | | | -0.2 | | | -0.2 | |
| I _{IL} | B inputs | V _{CC} = MAX, GAB and GB | · · | | | | -0.2 | | | -0.2 | mA |
| | GAB or GBA | V _{CC} = MAX, | V _I = 0.4 V, | | | | -0.2 | | | -0.2 | Ì |
| I _{OS} | | $V_{CC} = MAX$ | | | -40 | | -225 | -40 | | -225 | mA |
| | Outputs high | | | | | 22 | 38 | | 22 | 38 | |
| I _{CC} | Outputs low | $V_{CC} = MAX$ | V _{CC} = MAX, Outputs open, | | | 29 | 50 | | 29 | 50 | mA |
| •00 | All outputs disabled | Outputs open | | | | 32 | 54 | | 32 | 54 | 1117 |

⁽¹⁾ For conditions shown as MIN or MAX, use the appropriate value specified under "recommended operating conditions."

SWITCHING CHARACTERISTICS

 $V_{CC} = 5 \text{ V}, T_A = 25^{\circ}\text{C}$

| DADAMETED | ARAMETER TEST CONDITIONS | | SN5 | | SN7 | | UNIT | | |
|------------------|--------------------------|------------------------|-----|-----|-----|-----|------|-----|------|
| PARAMETER | | | MIN | TYP | MAX | MIN | TYP | MAX | UNII |
| t _{PLH} | | | | 9 | 14 | | 12 | 18 | ns |
| t _{PHL} | $R_1 = 667 \Omega$ | $C_1 = 45 \text{ pF}$ | | 12 | 18 | | 12 | 18 | ns |
| t _{PZL} | $R_L = 007 \Omega$ | C _L = 45 pr | | 20 | 30 | | 20 | 30 | ns |
| t _{PZH} | | | | 15 | 23 | | 15 | 23 | ns |
| t _{PLZ} | $R_1 = 667 \Omega$ | $C_1 = 5 pF$ | | 10 | 20 | | 10 | 20 | ns |
| t _{PHZ} | $N_L = 007 \Omega_2$ | $G_L = 5 \text{ pr}$ | | 15 | 25 | | 15 | 25 | ns |

Submit Documentation Feedback

 ⁽²⁾ All typical values are at V_{CC} = 5 V, T_A = 25°C.
 (3) I_{CC} is measured with transceivers eabled in one direction only, or with all transceivers disabled.







PACKAGING INFORMATION

| Orderable Device | Status ⁽¹⁾ | Package Type | Package Drawing | Pins | Package Qty | Eco Plan ⁽²⁾ | Lead/Ball Finish | MSL Peak Temp (3) |
|------------------|-----------------------|-----------------|--------------------|------|----------------|----------------------------|------------------|--------------------|
| 80020012A | OBSOLETE | LCCC | FK | 20 | | TBD | Call TI | Call TI |
| 8002001CA | OBSOLETE | CDIP | J | 14 | | TBD | Call TI | Call TI |
| 8002001DA | OBSOLETE | CFP | W | 14 | | TBD | Call TI | Call TI |
| 80020022A | OBSOLETE | | | 20 | | TBD | Call TI | Call TI |
| 8002002CA | ACTIVE | CDIP | J | 14 | 1 | TBD | A42 SNPB | N / A for Pkg Type |
| 8002002DA | ACTIVE | CFP | W | 14 | 1 | TBD | A42 | N / A for Pkg Type |
| SN54LS243J | ACTIVE | CDIP | J | 14 | 1 | TBD | A42 SNPB | N / A for Pkg Type |
| SN74LS242D | OBSOLETE | SOIC | D | 14 | | TBD | Call TI | Call TI |
| SN74LS242DR | OBSOLETE | SOIC | D | 14 | | TBD | Call TI | Call TI |
| SN74LS242N | OBSOLETE | PDIP | N | 14 | | TBD | Call TI | Call TI |
| SN74LS243D | ACTIVE | SOIC | D | 14 | 50 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| SN74LS243DE4 | ACTIVE | SOIC | D | 14 | 50 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| SN74LS243DG4 | ACTIVE | SOIC | D | 14 | 50 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| SN74LS243DR | ACTIVE | SOIC | D | 14 | 2500 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| SN74LS243DRE4 | ACTIVE | SOIC | D | 14 | 2500 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| SN74LS243DRG4 | ACTIVE | SOIC | D | 14 | 2500 | Green (RoHS & no Sb/Br) | CU NIPDAU | Level-1-260C-UNLIM |
| SN74LS243J | OBSOLETE | CDIP | J | 14 | | TBD | Call TI | Call TI |
| SN74LS243N | ACTIVE | PDIP | N | 14 | 25 | Pb-Free (RoHS) | CU NIPDAU | N / A for Pkg Type |
| SN74LS243N3 | OBSOLETE | PDIP | N | 14 | | TBD | Call TI | Call TI |
| SN74LS243NE4 | ACTIVE | PDIP | N | 14 | 25 | Pb-Free (RoHS) | CU NIPDAU | N / A for Pkg Type |
| SNJ54LS243FK | OBSOLETE | | | 20 | | TBD | Call TI | Call TI |
| SNJ54LS243J | ACTIVE | CDIP | J | 14 | 1 | TBD | A42 SNPB | N / A for Pkg Type |
| SNJ54LS243W | ACTIVE | CFP | W | 14 | 1 | TBD | A42 | N / A for Pkg Type |

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Pb-Free (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame

⁽²⁾ Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.



PACKAGE OPTION ADDENDUM

27-Jun-2008

retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

(3) MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.


Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



TAPE AND REEL INFORMATION





| A0 | Dimension designed to accommodate the component width |
|----|---|
| В0 | Dimension designed to accommodate the component length |
| K0 | Dimension designed to accommodate the component thickness |
| W | Overall width of the carrier tape |
| P1 | Pitch between successive cavity centers |

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

| Device | _ | Package Drawing | | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-------------|------|--------------------|----|------|--------------------------|--------------------------|---------|---------|---------|------------|-----------|------------------|
| SN74LS243DR | SOIC | D | 14 | 2500 | 330.0 | 16.4 | 6.5 | 9.0 | 2.1 | 8.0 | 16.0 | Q1 |





*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|-------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74LS243DR | SOIC | D | 14 | 2500 | 346.0 | 346.0 | 33.0 |

14 LEADS SHOWN



NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. This package is hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
- E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.

FK (S-CQCC-N**)

28 TERMINAL SHOWN

LEADLESS CERAMIC CHIP CARRIER



NOTES: A. All linear dimensions are in inches (millimeters).

- B. This drawing is subject to change without notice.
- C. This package can be hermetically sealed with a metal lid.
- D. The terminals are gold plated.
- E. Falls within JEDEC MS-004



D (R-PDSO-G14)

PLASTIC SMALL-OUTLINE PACKAGE



NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 (0,15) per end.
- Body width does not include interlead flash. Interlead flash shall not exceed .017 (0,43) per side.
- E. Reference JEDEC MS-012 variation AB.



W (R-GDFP-F14)

CERAMIC DUAL FLATPACK



NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. This package can be hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification only.
- E. Falls within MIL STD 1835 GDFP1-F14 and JEDEC MO-092AB



IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products Amplifiers amplifier.ti.com Data Converters dataconverter.ti.com DSP dsp.ti.com Clocks and Timers www.ti.com/clocks Interface interface.ti.com Logic logic.ti.com Power Mgmt power.ti.com Microcontrollers microcontroller.ti.com www.ti-rfid.com RF/IF and ZigBee® Solutions www.ti.com/lprf

| Applications | |
|--------------------|---------------------------|
| Audio | www.ti.com/audio |
| Automotive | www.ti.com/automotive |
| Broadband | www.ti.com/broadband |
| Digital Control | www.ti.com/digitalcontrol |
| Medical | www.ti.com/medical |
| Military | www.ti.com/military |
| Optical Networking | www.ti.com/opticalnetwork |
| Security | www.ti.com/security |
| Telephony | www.ti.com/telephony |
| Video & Imaging | www.ti.com/video |
| Wireless | www.ti.com/wireless |

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2008, Texas Instruments Incorporated