SDLS205 - DECEMBER 1983 - REVISED MARCH 1988


- Package Options Include Plastic "Small Outline" Packages, Ceramic Chip Carriers and Flat Packages, and Plastic and Ceramic DIPs
- Dependable Texas Instruments Quality and Reliability


description

These devices contain 4-2-3-2 input AND-OR-INVERT gates. They perform the Boolean function $Y = \overline{ABCD + EF + GHI + JK}$. The 'S64 has totem-pole outputs and the 'S65 has open-collector outputs.

The SN54S64 and the SN54S65 are characterized for operation over the full military temperature range of $-55\,^{\circ}\text{C}$ to 125 $^{\circ}\text{C}$. The SN74S64 and the SN74S65 are characterized for operation from 0 $^{\circ}\text{C}$ to 70 $^{\circ}\text{C}$.

logic symbols†







[†]These symbols are in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

Pin numbers shown are for D, J, N, and W packages.

SN54S64, SN54S65 . . . J OR W PACKAGE SN74S64, SN74S65 . . . D OR N PACKAGE (TOP VIEW)




SN54S64, SN54S65 . . . FK PACKAGE (TOP VIEW)




NC - No internal connection

logic diagram (each device) (positive logic)



SDLS205 - DECEMBER 1983 - REVISED MARCH 1988

schematics (each gate)



Resistor values shown are nominal and in ohms.

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)

Supply voltage, VCC (see Note 1)		
Input voltage	• • • • • • • • • • • • • • • • • • • •	5.5 V
Off-state output voltage, 'S65		
Operating free-air temperature range:	SN54'	
	SN74'	0°C to 70°C
Storage temperature range		



recommended operating conditions

		SN54S64			SN74S64		
	MIN	NOM	MAX	MIN	NOM	MAX	UNIT
V _{CC} Supply voltage	4.5	5	5,5	4.75	5	5.25	V
V _{IH} High-level input voltage	2			2			V
V _{IL} Low-level input voltage			8,0			8.0	V
IOH High-level output current			- 1			1	mA
IOL Low-level output current			20			20	mA
T _A Operating free-air temperature	– 55		125	0		70	°C

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER		TEST CONDIT	;							
		TEGT CONDIT	TONS I.	MIN	TYP‡	MAX	MIN	TYP‡	MAX	UNIT
VIK	V _{CC} = MIN,	$I_1 = -18 \text{ mA}$				-1,2			- 1.2	V
v _{oh}	V _{CC} = MIN,	V _{1L} = 0.8 V,	I _{OH} = -1 mA	2.5	3.4		2.7	3.4		V
VOL	V _{CC} = MIN,	V _{IH} = 2 V,	1 _{OL} = 20 mA			0,5			0.5	V
կ	$V_{CC} = MAX$,	V ₁ = 5.5 V				1			1	mA
ЧН	V _{CC} = MAX,	V ₁ = 2.7 V				50			50	μΑ
HL	V _{CC} = MAX,	V ₁ = 0.5 V				- 2			- 2	mA
loss	V _{CC} = MAX			- 40		-100	- 40		- 100	mA
Іссн	V _{CC} = MAX,	V1 = 0			7	12.5		7	12,5	mA
ICCL	V _{CC} = MAX,	V ₁ = 4.5 V			8.5	16		8.5	16	mA

[†] For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.

switching characteristics, $V_{CC} = 5 \text{ V}$, $T_A = 25^{\circ}\text{C}$ (see note 2)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	TEST CON	MIN TYP	MAX	UNIT	
^t PLH			B. = 200 O	0 - 15 - 5	3.5	5.5	ns
^t PHL	Any		$R_L = 280 \Omega$,	C _L = 15 pF	3.5	5.5	ns
t _{PLH}	. Ally	'	R _L = 280 Ω,	C. = 50 = 5	5		ns
t _{PHL}			nL - 200 12,	C _L = 50 pF	5.5		ns

NOTE 2: Load circuits and voltage waveforms are shown in Section 1.

[‡] All typical values are at $V_{CC} = 5 \text{ V}$, $T_A = 25^{\circ} \text{C}$. § Not more than one output should be shorted at a time, and the duration of the short-circuit should not exceed one second.

recommended operating conditions

		SN54S65			SN74S65			
	MIN	NOM	MAX	MIN	NOM	MAX	UNIT	
V _{CC} Supply voltage	4.5	5	5.5	4.75	5	5.25	V	
V _{IH} High-level input voltage	2			2			V	
V _{IL} Low-level input voltage			8.0			8.0	V	
VOH High-level output voltage			5.5			5.5	V	
OL Low-level output current			20			20	mA	
T _A Operating free-air temperature	– 55		125	0	·	70	°c	

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER	TEST CONDITIONS†		SN54S6	5	;	LINUT		
	TEST CONDITIONS.	MIN	TYP [‡]	MAX	MIN	TYP [‡]	MAX	UNIT
V _{IK}	$V_{CC} = MIN$, $I_{I} = -18 \text{ mA}$			1.2			1.2	V
ЮН	$V_{CC} = MIN$, $V_{IL} = 0.8 \text{ V}$, $V_{OH} = 5.5 \text{ V}$						0.25	
ЮП	$V_{CC} = MIN$, $V_{IL} = 0.7 \text{ V}$, $V_{OH} = 5.5 \text{ V}$		***************************************	0.25				mA
VOL	$V_{CC} = MIN$, $V_{IH} = 2 V$, $I_{OL} = 20 mA$		0.2	0.4		0.2	0.4	V
l _l	$V_{CC} = MAX$, $V_{\parallel} = 5.5 V$			1			1	mA
ItH .	$V_{CC} = MAX$, $V_{I} = 2.7 V$			50			50	μΑ
اړړ	$V_{CC} = MAX$, $V_1 = 0.5 V$			-2			- 2	mA
1ссн	$V_{CC} = MAX, V_I = 0$		6	11		6	11	mA
^I CCL	$V_{CC} = MAX$, $V_1 = 4.5 V$		8.5	16		8.5	16	mA

[†]For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.

switching characteristics, $V_{CC} = 5 \text{ V}$, $T_A = 25^{\circ}\text{C}$ (see note 2)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	TEST CON	MIN	TYP	MAX	UNIT	
t _{PLH}			$R_1 = 280 \Omega$,	C: -15 -F	2	5	7.5	ns
^t PHL	Any		n 200 12,	C _L = 15 pF	2	5.5	8.5	ns
^t PLH]	'	P. = 280 O	0. = 50 = 5		8		ns
t _{PHL}			R _L = 280 Ω,	C _L = 50 pF		6.5		ns

NOTE 2: Load circuits and voltage waveforms are shown in Section 1.



 $^{^{\}ddagger}$ All typical values are at V_{CC} = 5 V, T_A = 25 °C.



www.ti.com 25-Oct-2022

PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
JM38510/07402BCA	ACTIVE	CDIP	J	14	1	Non-RoHS & Green	(6) SNPB	N / A for Pkg Type	-55 to 125	JM38510/ 07402BCA	Samples
JM38510/07402BDA	ACTIVE	CFP	W	14	1	Non-RoHS & Green	SNPB	N / A for Pkg Type	-55 to 125	JM38510/ 07402BDA	Samples
M38510/07402BCA	ACTIVE	CDIP	J	14	1	Non-RoHS & Green	SNPB	N / A for Pkg Type	-55 to 125	JM38510/ 07402BCA	Samples
M38510/07402BDA	ACTIVE	CFP	W	14	1	Non-RoHS & Green	SNPB	N / A for Pkg Type	-55 to 125	JM38510/ 07402BDA	Samples
SN54S64J	ACTIVE	CDIP	J	14	1	Non-RoHS & Green	SNPB	N / A for Pkg Type	-55 to 125	SN54S64J	Samples
SNJ54S64J	ACTIVE	CDIP	J	14	1	Non-RoHS & Green	SNPB	N / A for Pkg Type	-55 to 125	SNJ54S64J	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.



PACKAGE OPTION ADDENDUM

www.ti.com 25-Oct-2022

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE MATERIALS INFORMATION

www.ti.com 10-Mar-2022

TUBE



*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (µm)	B (mm)
JM38510/07402BDA	W	CFP	14	1	506.98	26.16	6220	NA
M38510/07402BDA	W	CFP	14	1	506.98	26.16	6220	NA

W (R-GDFP-F14)

CERAMIC DUAL FLATPACK



NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. This package can be hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification only.
- E. Falls within MIL STD 1835 GDFP1-F14



CERAMIC DUAL IN LINE PACKAGE



Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.

4040083-5/G





CERAMIC DUAL IN LINE PACKAGE



NOTES:

- 1. All controlling linear dimensions are in inches. Dimensions in brackets are in millimeters. Any dimension in brackets or parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. This package is hermitically sealed with a ceramic lid using glass frit.
- His package is remitted by sealed with a ceramic its using glass mit.
 Index point is provided on cap for terminal identification only and on press ceramic glass frit seal only.
 Falls within MIL-STD-1835 and GDIP1-T14.



CERAMIC DUAL IN LINE PACKAGE



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated