



»Features

$V_{DS} = 20V$
 $I_D = 0.75A$
 $R_{DS(ON)} @ V_{GS} = 4.5V, \text{ Max } = 380m\Omega$
 $R_{DS(ON)} @ V_{GS} = 2.5V, \text{ Max } = 450m\Omega$
 $R_{DS(ON)} @ V_{GS} = 1.8V, \text{ Max } = 800m\Omega$

»Pin Configurations



»General Description

- Lead Free Product is Acquired
- Advanced trench process technology
- High Density Cell Design For Ultra Low On-Resistance
- SOT-723 for Surface Mount Package.

»Application

- Load/Power Switching
- Interfacing Switching
- Battery Management for Ultra Small Portable Electronics
- Logic Level Shift

»Absolute Maximum Ratings @ $T_A=25^\circ C$ unless otherwise noted

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	20	V
Typical Gate-Source Voltage	V_{GS}	± 12	V
Continuous Drain Current (note 1)	I_D	0.75	A
Pulsed Drain Current ($t_p=10\mu s$)	I_{DM}	1.8	A
Power Dissipation (note 1)	P_D	350	mW
Thermal Resistance from Junction to Ambient (note 1)	$R_{\theta JA}$	357	°C/W
Junction Temperature	T_J	150	°C
Storage Temperature	T_{STG}	-55~+150	°C
Lead Temperature for Soldering Purposes(1/8" duration for 10 s)	T_L	260	°C

»Electrical Characteristics @ $T_A=25^\circ\text{C}$ unless otherwise noted


Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
STATIC CHARACTERISTICS						
Drain-source breakdown voltage	$V_{(\text{BR})\text{DSS}}$	$V_{\text{GS}} = 0\text{V}, I_{\text{D}} = 250\mu\text{A}$	20			V
Zero gate voltage drain current	I_{DSS}	$V_{\text{DS}} = 20\text{V}, V_{\text{GS}} = 0\text{V}$			1	μA
Gate-body leakage current	I_{GSS}	$V_{\text{GS}} = \pm 10\text{V}, V_{\text{DS}} = 0\text{V}$			± 20	μA
Gate threshold voltage (note 2)	$V_{\text{GS}(\text{th})}$	$V_{\text{DS}} = V_{\text{GS}}, I_{\text{D}} = 250\mu\text{A}$	0.35	0.54	1.1	V
Drain-source on-resistance (note 2)	$R_{\text{DS}(\text{on})}$	$V_{\text{GS}} = 4.5\text{V}, I_{\text{D}} = 0.65\text{A}$		270	380	$\text{m}\Omega$
		$V_{\text{GS}} = 2.5\text{V}, I_{\text{D}} = 0.55\text{A}$		320	450	$\text{m}\Omega$
		$V_{\text{GS}} = 1.8\text{V}, I_{\text{D}} = 0.45\text{A}$		390	800	$\text{m}\Omega$
Forward transconductance (note 2)	g_{FS}	$V_{\text{DS}} = 10\text{V}, I_{\text{D}} = 0.8\text{A}$		1.6		S
Diode forward voltage	V_{SD}	$I_{\text{S}} = 0.15\text{A}, V_{\text{GS}} = 0\text{V}$			1.2	V
DYNAMIC CHARACTERISTICS (note 4)						
Input capacitance	C_{iss}	$V_{\text{DS}} = 16\text{V}, V_{\text{GS}} = 0\text{V}, f = 1\text{MHz}$		79	120	pF
Output capacitance	C_{oss}			13	20	pF
Reverse transfer capacitance	C_{rss}			9	15	pF
SWITCHING CHARACTERISTICS (note 4)						
Turn-on delay time (note 3)	$t_{\text{d}(\text{on})}$	$V_{\text{GS}} = 4.5\text{V}, V_{\text{DS}} = 10\text{V}, I_{\text{D}} = 500\text{mA}, R_{\text{GEN}} = 10\Omega$		6.7		ns
Turn-on rise time (note 3)	t_{r}			4.8		ns
Turn-off delay time (note 3)	$t_{\text{d}(\text{off})}$			17.3		ns
Turn-off fall time (note 3)	t_{f}			7.4		ns

Notes :


1. Surface mounted on FR4 board using the minimum recommended pad size.
2. Pulse Test : Pulse Width=300 μs , Duty Cycle=2%.
3. Switching characteristics are independent of operating junction temperatures.
4. Guaranteed by design, not subject to producing.

»Typical Performance Characteristics ($T_J = 25^\circ\text{C}$, unless otherwise noted)


Output Characteristics




Transfer Characteristics




$R_{DS(ON)}$ — I_D




$R_{DS(ON)}$ — V_{GS}



I_S — V_{SD}




Threshold Voltage




» Package Information

SOT-723



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.430	0.500	0.017	0.020
A1	0.000	0.050	0.000	0.002
b	0.170	0.270	0.007	0.011
b1	0.270	0.370	0.011	0.015
c	0.080	0.150	0.003	0.006
D	1.150	1.250	0.045	0.049
E	1.150	1.250	0.045	0.049
E1	0.750	0.850	0.030	0.033
e	0.800TYP.		0.031TYP.	
θ	7° REF.		7° REF.	

» Suggested Pad Layout



» Ordering information

Order code	Package	Marking	Base qty	Delivery mode
BM3134KE	SOT-723	34KE	8K	Tape and reel