


Description

We declare that the material of product compliance with Rohs requirements and Halogen Free.
 ESD protected
 Low RDS(on)

Product Summary

V _{DS}	60	V
R _{DS(ON),max}	2.3	Ω
I _D	0.3	A

SOT-363 Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V _{DS}	Drain-Source Voltage	60	V
V _{GS}	Gate-Source Voltage	±20	V
I _D @T _A =25°C	Continuous Drain Current, V _{GS} @ 10V ¹	300	mA
I _D @T _A =70°C	Continuous Drain Current, V _{GS} @ 10V ¹	190	mA
I _{DM}	Pulsed Drain Current ²	0.65	A
P _D @T _A =25°C	Total Power Dissipation ³	0.35	W
T _{STG}	Storage Temperature Range	-55 to 150	°C
T _J	Operating Junction Temperature Range	-55 to 150	°C

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
R _{θJA}	Thermal Resistance Junction-Ambient ¹	---	300	°C/W

Electrical Characteristics ($T_J=25^\circ C$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=250\mu A$	60	---	---	V
$\Delta BV_{DSS}/\Delta T_J$	BV_{DSS} Temperature Coefficient	Reference to $25^\circ C, I_D=1mA$	---	0.054	---	$V/^\circ C$
$R_{DS(ON)}$	Static Drain-Source On-Resistance ²	$V_{GS}=10V, I_D=200mA$	---	1.8	2.3	Ω
		$V_{GS}=4.5V, I_D=100mA$	---	2.3	3.0	
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}, I_D=250\mu A$	1.0	1.4	2.5	V
$\Delta V_{GS(th)}$	$V_{GS(th)}$ Temperature Coefficient		---	-4.96	---	$mV/^\circ C$
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=48V, V_{GS}=0V, T_J=25^\circ C$	---	---	1	μA
		$V_{DS}=48V, V_{GS}=0V, T_J=55^\circ C$	---	---	5	
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V, V_{DS}=0V$	---	---	± 10	μA
g_{fs}	Forward Transconductance	$V_{DS}=50V, I_D=200mA$	---	0.16	---	S
Q_g	Total Gate Charge (4.5V)	$V_{DS}=0.5V, V_{GS}=10V, I_D=200mA$	---	0.5	---	nC
Q_{gs}	Gate-Source Charge		---	0.2	---	
Q_{gd}	Gate-Drain Charge		---	0.15	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DD}=30V, V_{GEN}=10V, R_G=25\Omega$, $I_D=500mA, RL=60\Omega$,	---	6.7	---	ns
T_r	Rise Time		---	12	---	
$T_{d(off)}$	Turn-Off Delay Time		---	13	---	
T_f	Fall Time		---	15	---	
C_{iss}	Input Capacitance	$V_{DS}=30V, V_{GS}=0V, f=1MHz$	---	18.5	---	pF
C_{oss}	Output Capacitance		---	7.5	---	
C_{rss}	Reverse Transfer Capacitance		---	4.2	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_s	Continuous Source Current ^{1,4}	$V_G=V_D=0V$, Force Current	---	---	300	mA
I_{SM}	Pulsed Source Current ^{2,4}		---	---	0.65	A
V_{SD}	Diode Forward Voltage ²	$V_{GS}=0V, I_s=0.5A, T_J=25^\circ C$	---	---	1.2	V

Note :

1. The data tested by surface mounted on a 1 inch² FR-4 board with 2OZ copper.
2. The data tested by pulsed , pulse width $\leq 300\mu s$, duty cycle $\leq 2\%$
3. The power dissipation is limited by $150^\circ C$ junction temperature.
4. The data is theoretically the same as I_D and I_{DM} , in real applications , should be limited by total power dissipation.





HUASHUO
SEMICONDUCTOR


HSSK2N7002

DUAL N-Ch 60V Fast Switching MOSFETs




Typical Characteristics



On-Resistance VS Temperature



Capacitance Characteristic








HUASHUO
SEMICONDUCTOR

HSSK2N7002

DUAL N-Ch 60V Fast Switching MOSFETs





HUASHUO
SEMICONDUCTOR

HSSK2N7002

DUAL N-Ch 60V Fast Switching MOSFETs

Ordering Information

Part Number	Package code	Packaging
HSSK2N7002	SOT-363	3000/Tape&Reel

