National Semiconductor is now part of Texas Instruments.

Search http://www.ti.com/ for the latest technical information and details on our current products and services.



LP395

Ultra Reliable Power Transistor

General Description

The LP395 is a fast monolithic transistor with complete overload protection. This very high gain transistor has included on the chip, current limiting, power limiting, and thermal overload protection, making it difficult to destroy from almost any type of overload. Available in an epoxy TO-92 transistor package this device is guaranteed to deliver 100 mA.

Thermal limiting at the chip level, a feature not available in discrete designs, provides comprehensive protection against overload. Excessive power dissipation or inadequate heat sinking causes the thermal limiting circuitry to turn off the device preventing excessive die temperature.

The LP395 offers a significant increase in reliability while simplifying protection circuitry. It is especially attractive as a small incandescent lamp or solenoid driver because of its low drive requirements and blowout-proof design.

The LP395 is easy to use and only a few precautions need be observed. Excessive collector to emitter voltage can destroy the LP395 as with any transistor. When the device is used as an emitter follower with a low source impedance, it is necessary to insert a 4.7 $k\Omega$ resistor in series with the base lead to prevent possible emitter follower oscillations. Also since it has good high frequency response, supply by-passing is recommended.

Areas where the LP395 differs from a standard NPN transistor are in saturation voltage, leakage (quiescent) current and

in base current. Since the internal protection circuitry requires voltage and current to function, the minimum voltage across the device in the on condition (saturated) is typically 1.6 Volts, while in the off condition the quiescent (leakage) current is typically 200 µA. Base current in this device flows out of the base lead, rather than into the base as is the case with conventional NPN transistors. Also the base can be driven positive up to 36 Volts without damage, but will draw current if driven negative more than 0.6 Volts. Additionally, if the base lead is left open, the LP395 will turn on.


The LP395 is a low-power version of the 1-Amp LM195/LM295/LM395 Ultra Reliable Power Transistor.

The LP395 is rated for operation over a -40° C to $+125^{\circ}$ C range.

Features

- Internal thermal limiting
- Internal current and power limiting
- Guaranteed 100 mA output current
- 0.5 µA typical base current
- Directly interfaces with TTL or CMOS
- +36 Volts on base causes no damage
- 2 µs switching time


Connection Diagram



Order Number LP395Z See NS Package Z03A

Typical Applications

Fully Protected Lamp Driver



Absolute Maximum Ratings (Note 1)

Collector to Emitter Voltage 36V
Collector to Base Voltage 36V
Base to Emitter Voltage (Forward) 36V
Base to Emitter Voltage (Reverse) 10V
Base to Emitter Current (Reverse) 20 mA

Collector Current Limit

Power Dissipation

Operating Temperature Range

Storage Temperature Range

Lead Temp. (Soldering, 10 seconds)

Internally Limited

Internally

Electrical Characteristics

				Tested	Design	Units
Symbol	Parameter	Conditions	Typical	Limit	Limit	(Limit)
				(Note 3)	(Note 4)	
V _{CE}	Collector to Emitter	0.5 mA ≤ I _C ≤ 100 mA		36	36	V(Max)
	Operating Voltage				(Note 2)	
I _{CL}	Collector Current Limit	V _{BE} = 2V, V _{CE} = 36V	45	25	20	mA(Min)
	(Note 5)	$V_{BE} = 2V, V_{CE} = 15V$	90	60	50	mA(Min)
		$V_{BE} = 2V, 2V \le V_{CE} \le 6V$	130	100	100	mA(Min)
I _B	Base Current	0 ≤ I _C ≤ 100 mA	-0.3	-2.0	-2.5	μA(Max)
IQ	Quiescent Current	$V_{BE} = 0V, \ 0 \le V_{CE} \le 36V$	0.24	0.50	0.60	mA(Max)
V _{CE(SAT)}	Saturation Voltage	$V_{BE} = 2V, I_{C} = 100 \text{ mA}$	1.82	2.00	2.10	V(Max)
BV _{BE}	Base to Emitter Break-	$0 \le V_{CE} \le 36V, I_{B} = 2 \mu A$		36	36	V(Min)
	down Voltage (Note 5)					
V _{BE}	Base to Emitter Voltage	I _C = 5 mA	0.69	0.79	0.90	V(Max)
	(Note 6)	I _C = 100 mA (Note 5)	1.02		1.40	V (Max)
t _S	Switching Time	$V_{CE} = 20V, R_{L} = 200\Omega$	2			μs
		$V_{BE} = 0V, +2V, 0V$				
θ_{JA}	Thermal Resistance	0.4" leads soldered to	150		180	°C/W
	Junction to Ambient	printed circuit board				(Max)
		0.125" leads soldered to	130		160	°C/W
		printed circuit board				(Max)

Note 1: Absolute Maximum Ratings indicate limits beyond which damage to the device may occur. Operating Ratings indicate conditions for which the device is functional, but do not guarantee specific performance limits.

Note 2: Parameters identified with boldface type apply at temp. extremes. All other numbers, unless noted apply at +25°C.


Note 3: Guaranteed and 100% production tested.

Note 4: Guaranteed (but not 100% production tested) over the operating temperature and supply voltage ranges. These limits are not used to calculate outgoing quality levels.

Note 5: These numbers apply for pulse testing with a low duty cycle.

Note 6: Base positive with respect to emitter.

Simplified Circuit



www.national.com 2


Applications Information

One failure mode incandescent lamps may experience is one in which the filament resistance drops to a very low value before it actually blows out. This is especially rough on most solid-state lamp drivers and in most cases a lamp failure of this type will also cause the lamp driver to fail.

Because of its high gain and blowout-proof design, the LP395 is an ideal candidate for reliably driving small incandescent lamps. Additionally, the current limiting characteristics of the LP395 are advantageous as it serves to limit the cold filament inrush current, thus increasing lamp life.


Typical Performance Characteristics

5 Volt Transfer Function




00552510

Collector Characteristics




Quiescent Collector Current




00552514

36 Volt Transfer Function




00552511

Available Collector Current



00552513


Saturation Voltage



00552515


Typical Performance Characteristics (Continued)

Collector Current Threshold




Typical Applications


Lamp Flasher (Short Circuit Proof)




Two Terminal Current Limiter




Optically Isolated Switch



Composite PNP



Physical Dimensions inches (millimeters) unless otherwise noted



Order Number LP395Z NS Package Z03A

National does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and National reserves the right at any time without notice to change said circuitry and specifications.

For the most current product information visit us at www.national.com.

LIFE SUPPORT POLICY

NATIONAL'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT AND GENERAL COUNSEL OF NATIONAL SEMICONDUCTOR CORPORATION. As used herein:

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
- 2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

ZOSA (Rev G)

BANNED SUBSTANCE COMPLIANCE

National Semiconductor manufactures products and uses packing materials that meet the provisions of the Customer Products Stewardship Specification (CSP-9-111C2) and the Banned Substances and Materials of Interest Specification (CSP-9-111S2) and contain no "Banned Substances" as defined in CSP-9-111S2.



National Semiconductor Americas Customer Support Center

Email: new.feedback@nsc.com

Tel: 1-800-272-9959

www.national.com

National Semiconductor Europe Customer Support Center Fax: +49 (0) 180-530 85 86

Email: europe.support@nsc.com
Deutsch Tel: +49 (0) 69 9508 6208
English Tel: +44 (0) 870 24 0 2171 Français Tel: +33 (0) 1 41 91 8790

National Semiconductor Asia Pacific Customer Support Center Email: ap.support@nsc.com **National Semiconductor** Japan Customer Support Center Fax: 81-3-5639-7507 Email: jpn.feedback@nsc.com Tel: 81-3-5639-7560