# MSKSEMI 美森科







TVS



TSS



MOV



GDT



PIFF

# 2N7002KT1G-MS

**Product specification** 





## **Features**

- 60V,0.3A, RDS(ON) =2.2Ω@VGS=10V
- Improved dv/dt capability
- Fast switching
- Green Device Available
- G-S ESD Protection Diode Embedded
- ESD protected up to 2KV

# **Application**

- Motor Drive
- Power Tools
- LED Lighting

BVDSS	RDSON	ID
60V	2.2Ω	0.3A

## **Reference News**

PACKAGE OUTLINE	Pin Configuration	Marking
SOT-23	G	704*

## **Absolute Maximum Ratings** (TA=25 ℃ unless otherwise noted)

Symbol	Parameter	Rating	Units
VDS	Drain- Source Voltage	60	V
Vgs	Gate- Sou₁ce Voltage	±20	V
I <sub>D</sub>	Drain Current – Continuous (T <sub>C</sub> =25°C)	0.3	А
lu lu	Drain Current – Continuous (T <sub>C</sub> =100 ℃)	0.1	А
Ірм	Drain Current – Pulsed <sup>1</sup>	0.8	А
P <sub>D</sub>	Power Dissipation (T <sub>C</sub> =25 °c)	0.35	W
1.0	Power Dissipation – Derate above 25 ℃	0.003	W/℃
Тѕтс	Storage Temperature Range	-50 to 150	$^{\circ}$
Tu	Operating Junction Temperature Range	-50 to 150	$^{\circ}$



## **Thermal Characteristics**

Symbol	Parameter	Тур.	Max.	Unit
Reja	Thermal Resistance Junction to ambient		357	°C/W

## **Electrical Characteristics**(TJ=25 °C , unless otherwise noted)

#### **Off Characteristics**

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
BVDSS	Drain- Source Breakdown Voltage	V <sub>GS</sub> =0V , I <sub>D</sub> =250uA	60			V
1	Drain- Source Leakage Current	V <sub>DS</sub> =60V , V <sub>GS</sub> =0V , T <sub>J</sub> =25℃			1	ŭΑ
IDSS	1	V <sub>DS</sub> =48V , V <sub>GS</sub> =0V , T <sub>J</sub> =125℃			10	uА
Igss	Gate- Source Leakage Current	V <sub>GS</sub> ±20V , V <sub>DS</sub> =0V			±10	uА

### On Characteristics

RDS/OND Static Drain-Source On-Resistance		V <sub>GS</sub> =10V , I <sub>D</sub> =0.3A		2.2	2.8	Ω
R <sub>DS(ON)</sub> Static Drain-Source On-Resistance	V <sub>GS</sub> =4.5V , I <sub>D</sub> =0.2A		2 4	3 0	Ω	
V <sub>GS(th)</sub>	Gate Threshold Voltage	$V_{GS}=V_{DS}$ , $I_D=250uA$	1	1.6	2.5	V
gfs	Forward Transconductance	V <sub>DS</sub> =10V , I <sub>D</sub> =0.3A		0.5	I	S

## **Dynamic and switching Characteristics**

Qg	Total Gate Charge <sup>2 , 3</sup>		 3.7	5.6	
Qgs	Gate-Source Charge <sup>2</sup> , <sup>3</sup>	V <sub>DS</sub> =30V , V <sub>GS</sub> =10V , I <sub>D</sub> =1A	 0.9	1.4	nC
Qgd	Gate-Drain Charge <sup>2, 3</sup>		 0.4	0.6	
T <sub>d(on)</sub>	Turn-On Delay Time <sup>2, 3</sup>		 3	6	
Tr	Rise Time <sup>2 , 3</sup>	$V_{DD}$ =30V , $V_{GS}$ =10V , $R_{G}$ =6 $\Omega$	 5	10	ns
$T_{d(off)}$	Turn-Off Delay Time <sup>2, 3</sup>	I <sub>D</sub> =0.2A	 14	27	113
Tf	Fall Time <sup>2, 3</sup>		 9	17	
Ciss	Input Capacitance		 25.5	38	
Coss	Output Capacitance	$V_{DS}$ =30V , $V_{GS}$ =0V , F=1MHz	 17	26	рF
Crss	Reverse Transfer Capacitance		 7.8	12	

#### **Drain-Source Diode Characteristics and Maximum Ratings**

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
Is	Continuous Source Current	V <sub>G</sub> =V <sub>D</sub> =0V , Force Current			0.3	Α
lsм	Pulsed Source Current	VG-VD-UV, Force Current			1.2	Α
VsD	Diode Forward Voltage	V <sub>GS</sub> =0V , I <sub>S</sub> =1A , T <sub>J</sub> =25℃			1	V
trr	Reverse Recovery Time	V <sub>GS</sub> =50V, I <sub>S</sub> =1A , dI/dt=100A/μs		3.4		ns
Qrr	Reverse Recovery Charge	T <sub>J</sub> =25℃		0.7		nC

#### Note:

- 1.Repetitive Rating: Pulsed width limited by maximum junction temperature.
- $2\,.$  The data tested by pulsed , pulse width  $\leqq 300\,us$  , duty cycle  $\leqq 2\,\%\,.$
- 3. Essentially independent of operating temperature.

### **ELECTRICAL CHARACTERISTICS CURVE**




Fig.1 Continuous Drain Current vs. Tc




Fig.3 Normalized V<sub>th</sub> vs. T<sub>J</sub>




Fig.5 Normalized Transient Impedance




Fig.2 Normalized RDSON vs. TJ




Fig.4 Gate Charge Waveform







Fig.6 Maximum Safe Operation Area



## PACKAGE MECHANICAL DATA








Symbol	Dimensions	Dimensions In Millimeters		ns In Inches	
Syllibol	Min	Max	Min	Max	
Α	0.900	1.150	0.035	0.045	
A1	0.000	0.100	0.000	0.004	
A2	0.900	1.050	0.035	0.041	
b	0.300	0.500	0.012	0.020	
С	0.080	0.150	0.003	0.006	
D	2.800	3.000	0.110	0.118	
E	1.200	1.400	0.047	0.055	
E1	2.250	2.550	0.089	0.100	
е	0.950	0 TYP	0.03	7 TYP	
e1	1.800	2.000	0.071	0.079	
L	0.550 REF		0.022	2 REF	
L1	0.300	0.500	0.012	0.020	
θ	0°	8°	0°	8°	

# **Suggested Pad Layout**



### Note:

- 1.Controlling dimension:in millimeters.
- 2.General tolerance:±0.05mm.
- 3. The pad layout is for reference purposes only.

## **REEL SPECIFICATION**

P/N	PKG	QTY
2N7002KT1G-MS	SOT-23	3000



## **Attention**

- Any and all MSKSEMI Semiconductor products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your MSKSEMI Semiconductor representative nearest you before using any MSKSEMI Semiconductor products described or contained herein in such applications.
- MSKSEMI Semiconductor assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specificationsof any andall MSKSEMI Semiconductor products described or contained herein.
- Specifications of any and all MSKSEMI Semiconductor products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer'sproducts or equipment.
- MSKSEMI Semiconductor. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with someprobability. It is possiblethat these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits anderror prevention circuitsfor safedesign, redundant design, and structural design.
- In the event that any or all MSKSEMI Semiconductor products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from theauthorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of MSKSEMI Semiconductor.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. MSKSEMI Semiconductor believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. Whendesigning equipment, referto the "Delivery Specification" for the MSKSEMI Semiconductor productthat you intend to use.