

3.0 AMP SURFACE MOUNT BRIDGE RECTIFIERS

FEATURES:

- Glass Passivated Chip Junction
- Reverse Voltage - 50 to 1000 V
- Forward Current - 3.0 A
- High Surge Current Capability
- Designed for Surface Mount Application

MECHANICAL DATA

- Case: UMSB
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 0.234g / 0.00825oz

Marking

Marking code
MB30A --- MB30M


VOLTAGE RANGE

50 to 1000 Volts

CURRENT

3.0 Ampere

UMSB



UNIT		A	C	D	E	E ₁	L	e	b	z
mm	max	1.5	0.29	7.0	7.6	8.9	1.6	5.3	1.15	10°
	min	1.3	0.17	6.2	7.1	8.4	1.0	4.9	0.95	
mil	max	59	12	276	299	350	55	209	45	
	min	51	7	244	280	331	31.5	193	37	

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating 25°C ambient temperature unless otherwise specified.
 Single phase half wave, 60Hz, resistive or inductive load.
 For capacitive load, derate current by 20%.

TYPE NUMBER	MSB30A	MSB30B	MSB30D	MSB30G	MSB30J	MSB30K	MSB30M	UNIT	
Maximum Recurrent Peak Reverse Voltage	50	100	200	400	600	800	1000	V	
Maximum RMS Voltage	35	70	140	280	420	560	700	V	
Maximum DC Blocking Voltage	50	100	200	400	600	800	1000	V	
Maximum Average Forward Rectified Current at Ta=40°C (Note 1)								3.0	A
Peak Forward Surge Current, 8.3 ms single half sine-wave superimposed on rated load (JEDEC method)								8.0	A
I ² t Rating for Fusing (1ms < t < 8.3ms)								42	A ² S
Maximum Forward Voltage Drop per Bridge Element at 3.0A								1.1	V
Maximum DC Reverse Current Ta=25°C								5.0	µA
at Rated DC Blocking Voltage Ta=125°C								200	µA
Typical Thermal Resistance R _{JA} (Note 2)								30	°C/W
Operating Temperature Range, T _J								-55 — +150	°C
Storage Temperature Range, T _{stg}								-55 — +150	°C

NOTES: 1. Mounted on P.C. Board.
 2. Thermal Resistance Junction to Ambient.

RATING AND CHARACTERISTIC CURVES

FIG.1-TYPICAL FORWARD CURRENT DERATING CURVE




FIG.2-MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG.3-TYPICAL FORWARD CHARACTERISTICS




FIG.4-TYPICAL REVERSE CHARACTERISTICS

