

General Description

The MAX1823 is a dual, current-limited switch with autoreset specifically made for USB applications. The autoreset feature latches the switch off if the output is shorted, saving system power. The switch reactivates when the short circuit is removed. Each channel is guaranteed to supply 720mA and meet USB specifications. Low quiescent supply current (50µA) and standby current (3μA) conserve battery power in portable applications.


The MAX1823 has multiple safety features to ensure that the USB port is protected. Built-in thermal-overload protection limits power dissipation and junction temperature. Accurate internal current-limiting circuitry protects the input supply against both overload and short-circuit conditions. Independent fault signals (FAULTA and FAULTB) notify the microprocessor (µP) when a thermal-overload, current-limit, undervoltagelockout (UVLO), or short-circuit fault occurs. A 20ms fault-blanking feature ignores momentary faults, such as those caused when hot swapping a capacitive load, preventing false alarms to the host system. The MAX1823A/MAX1823B also block reverse current (current from OUT_ to IN_) while in shutdown.

The MAX1823 is available in a space-saving 10-pin µMAX package. The MAX1823/MAX1823A are enabled with an active-low signal, and the MAX1823B/MAX1823H are enabled with an active-high signal. For a single version of this device, refer to the MAX1946 data sheet. For a triple version, refer to the MAX1940 data sheet.

Applications

USB Ports and Hubs Notebook and Desktop Computers PDAs and Palmtop Computers **Docking Stations**

Pin Configuration



MIXIM


Features

- ◆ Dual USB Switch in Tiny 10-Pin uMAX Package
- ♦ Autoreset Feature Saves Power
- ♦ Guaranteed 720mA Load per Channel
- ♦ Built-In 20ms Fault Blanking
- ♦ Compliant to USB Specification
- **♦ Blocks Reverse Current in Shutdown** (MAX1823A/MAX1823B)
- ♦ 4V to 5.5V Input Voltage Range
- **♦ Independent Shutdown Control** (MAX1823/MAX1823A—Active Low) (MAX1823B/MAX1823H—Active High)
- ♦ Independent FAULT Indicator Outputs
- ♦ Thermal-Overload Protection
- ♦ 50µA Quiescent Current (Both Switches On)
- ♦ 3µA Standby Current
- ♦ UL Recognized

Ordering Information

PART	TEMP RANGE	PIN-PACKAGE
MAX1823EUB	-40°C to +85°C	10 μMAX
MAX1823AEUB	-40°C to +85°C	10 μMAX
MAX1823BEUB	-40°C to +85°C	10 μMAX
MAX1823HEUB	-40°C to +85°C	10 μMAX

Typical Operating Circuit



Maxim Integrated Products 1

ABSOLUTE MAXIMUM RATINGS

IN, INA, INB, ONA, ONB, ONA, ONB	
OUTA, OUTB to GND	0.3V to +6V
FAULTA, FAULTB to GNDC	0.3V to $(V_{IN} + 0.3V)$
MAX1823/MAX1823H, INA, IN to OUTA;	_
INB, IN to OUTB	0.3V to +6V
MAX1823A/MAX1823B, INA, IN to OUTA;	
INB, IN to OUTB (when disabled, Note 3)	6V to +6V
INA, IN to OUTA; INB, IN to OUTB	
(when enabled, Note 4)	1.5A to +1.5ARMS

Ī	FAULTA, FAULTB Current	20mA
(Continuous Power Dissipation ($T_A = +70^{\circ}C$)	
	10-Pin µMAX (derate 5.6mW/°C above +70°C))444mW
(Operating Temperature Range	-40°C to +85°C
,	Junction Temperature	+150°C
	Storage Temperature Range6	
	Lead Temperature (soldering, 10s)	+300°C

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

ELECTRICAL CHARACTERISTICS

(Circuit of Figure 1, $V_{IN} = V_{INB} = 5V$, $\overline{ONA} = \overline{ONB} = GND$ (MAX1823/MAX1823A), ONA = ONB = IN (MAX1823B/MAX1823H), $T_A = 0^{\circ}C$ to +85°C, unless otherwise noted. Typical values are at $T_A = +25^{\circ}C$.)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS	
Supply Voltage Range			4.0		5.5	V	
		T _A = +25°C, each switch, MAX1823/MAX1823H		75	105		
Switch On-Resistance	Box	T _A = +25°C, each switch, MAX1823A/MAX1823B		90	120	mΩ	
Switch On-nesistance	Ron	T _A = 0°C to +85°C, each switch, MAX1823/MAX1823H			135	11152	
		$T_A = 0$ °C to +85°C, each switch, MAX1823A/MAX1823B			165		
Standby Supply Current		ON_ = IN_ (MAX1823/MAX1823A), ON_ = GND (MAX1823B/MAX1823H)		3	10	μΑ	
Quiescent Supply Current		IOUTA = IOUTB = 0A, one channel on		40	80	μΑ	
		IOUTA = IOUTB = 0A, both channels on		50	100	<u> </u>	
OUT_ Off-Leakage Current		ON_ = IN_ (MAX1823/MAX1823A), ON_ = GND (MAX1823B/MAX1823H), V _{OUTA} = V _{OUTB} = 0V, T _A = +25°C		0.02	1.00		
OOT_OII-Leakage Current		ON_ = IN_ (MAX1823/MAX1823A), ON_ = GND (MAX1823B/MAX1823H), VOUTA = VOUTB = 0V, TA = 0°C to +85°C		0.02	10.00	μΑ	
Undervoltage-Lockout Threshold	V _{UVLO}	Rising edge, 3% hysteresis	3.0	3.4	3.8	V	
Continuous Load Current			720			mA	
Continuous Current Limit	I _{LIM}	$V_{IN} - V_{OUT} = 0.5V$	0.72	0.90	1.20	А	
Short-Circuit Current Limit	ISHORT	Vout_ = 0V (Iout pulsing)	0.8	1.2	1.6	APEAK	
Sherr Should Surface Emili	.3110111	V _{OUT} = 0V (I _{OUT} pulsing)		0.35		ARMS	

ELECTRICAL CHARACTERISTICS (continued)

(Circuit of Figure 1, $V_{IN} = V_{INA} = V_{INB} = 5V$, $\overline{ONA} = \overline{ONB} = GND$ (MAX1823/MAX1823A), ONA = ONB = IN (MAX1823B/MAX1823H), $T_A = 0^{\circ}C$ to +85°C, unless otherwise noted. Typical values are at $T_A = +25^{\circ}C$.)

PARAMETER	SYMBOL	CON	NDITIONS	MIN	TYP	MAX	UNITS
Short-Circuit Detect Threshold		(Note 1)			1		V
Continuous Current-Limit Blanking Timeout Period		From continuous cui	rrent-limit condition to	10	20	35	ms
Short-Circuit Blanking Timeout Period		From short-circuit cu FAULT_ assertion	urrent-limit condition to	7.5	18	35.0	ms
T 0 D 1		$R_{OUT} = 10k\Omega$,	MAX1823/MAX1823H	0.5	1.2	4.0	
Turn-On Delay	ton	does not include rise time	MAX1823A/MAX1823B	0.3	0.8	3.0	ms
Output Rise Time	trise	$R_{OUT} = 10\Omega$, from	10% to 90% of V _{OUT} _		2.5		ms
Time Off Delegi from ON		$\frac{\text{R}_{\text{OUT}} = 10\Omega, \text{ does}}{\text{ON}_{}}$ (MAX1823) or 0 deasserted to V _{OUT}	_ ` ,		0.8	3.0	
Turn-Off Delay from ON	tOFF	R _{OUT} = 10Ω, does ON (MAX1823A) or deasserted to V _{OUT}			0.1	3.0	ms
Output Fall Time	+	$R_{OUT} = 10\Omega$, from 9 (MAX1823/MAX1823	90% to 10% of V _{OUT} _ 3H)		2.5		
Output Fall Time	^t FALL	$R_{OUT} = 10\Omega$, from 90% to 10% of V_{OUT} (MAX1823A/MAX1823B)			2.8		ms
Thermal-Shutdown Threshold		15°C hysteresis			+160		°C
Logic Input High Voltage		$V_{IN} = 4V \text{ to } 5.5V$		2			V
Logic Input Low Voltage		V_{IN} = 4V to 5.5V				0.8	V
Logic Input Current		ON_ = GND or IN_ (MAX1823/MAX1823A), ON_ = GND or IN_ (MAX1823B/MAX1823H)		-1		+1	μΑ
FAULT_ Output Low Voltage		I _{SINK} = 1mA, V _{IN} _ = 4V				0.4	V
FAULT_ Output High Leakage Current		V _{IN} _ = V _{FAULT} _ = 5.5V				1	μΑ
Autoreset OUT_ Current		In latched-off state, V _{OUT} = 0V		10	30	45	mA
Autoreset Threshold		In latched-off state,	rising	0.4	0.5	0.6	V
Autoreset Blanking Time		In latched-off state,	V _{OUT_} > 0.5V	10	20	35	ms

ELECTRICAL CHARACTERISTICS

(Circuit of Figure 1, $V_{IN} = V_{IN} = V_{ON} = 5V$ (MAX1823B/MAX1823H); $V_{IN} = V_{IN} = 5V$, $ON_{} = GND$ (MAX1823/MAX1823A), $T_A = -40^{\circ}C$ to $+85^{\circ}C$, unless otherwise noted.) (Note 2)

PARAMETER	SYMBOL	cc	ONDITIONS	MIN	TYP	MAX	UNITS
Supply Voltage Range				4.0		5.5	V
Switch On-Resistance	Dou	Each switch, MAX1823/MAX1823H				135	m0
Switch On-Resistance	Ron	Each switch, MAX	1823A/MAX1823B			165	mΩ
Standby Supply Current		ON_ = IN_ (MAX18 ON_ = GND (MAX	823/MAX1823A), 1823B/MAX1823H)			10	μΑ
Quiescent Supply Current		IOUTA = IOUTB = C	A, one channel on			80	^
Quiescent Supply Current		IOUTA = IOUTB = C	A, both channels on			100	μΑ
OUT_ Off-Leakage Current		ON_ = IN_ (MAX1823/MAX1823A), ON_ = GND (MAX1823B/MAX1823H), VOUTA = VOUTB = 0V				10	μΑ
Undervoltage-Lockout Threshold	V _U VLO	Rising edge, 3% h	ysteresis	3.0		3.8	V
Continuous Load Current				720			mA
Continuous Current Limit	ILIM	V _{IN} V _{OUT} _ = 0.5	ίV	0.72		1.20	А
Current Limit into Short Circuit	ISHORT	V _{OUT} = 0V (I _{OUT}	pulsing)	0.8		1.6	APEAK
Continuous Current-Limit Blanking Timeout Period		From continuous of FAULT_ assertion	current-limit condition to	10		35	ms
Short-Circuit Blanking Timeout Period		From short-circuit FAULT_ assertion	current-limit condition to	7.5		35.0	ms
Turn-On Delay	ton	$R_{OUT} = 10k\Omega$, does not include	MAX1823/MAX1823H	0.5		4.0	ms
Tuiti-Off Delay	ton	rise time	MAX1823A/MAX1823B	0.3		3.0	1115
Turn-Off Delay from ON	toff	R_{OUT} = 10 Ω , does not include fall time (from \overline{ON} (MAX1823/MAX1823A) or ON (MAX1823B/MAX1823H) deasserted to V_{OUT} = 90% V_{IN})				3	ms

! ______ N/IXI/N

ELECTRICAL CHARACTERISTICS (continued)

(Circuit of Figure 1, $V_{IN} = V_{IN} = V_{ON} = 5V$ (MAX1823B/MAX1823H); $V_{IN} = V_{IN} = 5V$, $ON_{} = GND$ (MAX1823/MAX1823A), $T_{A} = -40^{\circ}C$ to $+85^{\circ}C$, unless otherwise noted.) (Note 2)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
Logic Input High Voltage		V _{IN} _= 4V to 5.5V	2			V
Logic Input Low Voltage		V _{IN} _= 4V to 5.5V			8.0	V
Logic Input Current		$V_{\overline{ON}} = OV \text{ or } V_{\overline{IN}}$	-1		+1	μΑ
FAULT_ Output Low Voltage		I _{SINK} = 1mA, V _{IN} _ = 4V			0.4	V
FAULT_ Output High Leakage Current		V _{IN} _ = V FAULT _ = 5.5V			1	μΑ
Autoreset OUT_Current		In latched-off state, V _{OUT} = 0V	10		50	mA
Autoreset Threshold		In latched-off state, rising	0.4		0.6	V
Autoreset Blanking Time		In latched-off state, V _{OUT} > 0.5V	10	•	35	ms

Note 1: The output voltage at which the device transitions from short-circuit current limit to continuous current limit.


Note 2: Specifications to -40°C are guaranteed by design, not production tested.


Note 3: Reverse current (current from OUT_ to IN_) is blocked when disabled.


Note 4: Forward current (current from IN_ to OUT_) is internally limited. Reverse current, from OUT_ to IN_, is not limited when the device is enabled and must be kept below 1.5A_{RMS} to prevent permanent device damage. When the MAX1823A/MAX1823B are disabled, the switch turns off and reverse current is internally blocked.

Typical Operating Characteristics

(Circuit of Figure 1, $V_{INA} = V_{INA} = V_{INB} = 5V$, $\overline{ON}_- = GND$ (MAX1823/MAX1823A), $ON_- = IN_-$ (MAX1823B/MAX1823H), $T_A = +25^{\circ}C$, unless otherwise noted.)









Typical Operating Characteristics (continued)

(Circuit of Figure 1, $V_{INA} = V_{INA} = V_{INB} = 5V$, $\overline{ON}_- = GND$ (MAX1823/MAX1823A), $ON_- = IN_-$ (MAX1823B/MAX1823H), $T_A = +25$ °C, unless otherwise noted.)




Typical Operating Characteristics (continued)


(Circuit of Figure 1, $V_{IN} = V_{INA} = V_{INB} = 5V$, $\overline{ON}_{-} = GND$ (MAX1823/MAX1823A), $ON_{-} = IN_{-}$ (MAX1823B/MAX1823H), $T_{A} = +25^{\circ}C_{+}$ unless otherwise noted.)



Typical Operating Characteristics (continued)

(Circuit of Figure 1, $V_{INA} = V_{INA} = V_{INB} = 5V$, $\overline{ON}_- = GND$ (MAX1823/MAX1823A), $ON_- = IN_-$ (MAX1823B/MAX1823H), $T_{A} = +25^{\circ}C$, unless otherwise noted.)





Pin Description

PIN	NAME	FUNCTION
1	ONA *(ONA)	Control Input for Switch A. Can be driven higher than IN_ without damage. A logic low turns switch A on for the MAX1823/MAX1823A, and a logic high turns switch A on for the MAX1823B/MAX1823H.
2, 3, 4	INA, IN, INB	Power Input. Connect all IN_ pins together, and bypass with a 0.1µF capacitor to ground. Load conditions may require additional bulk capacitance to prevent the input from being pulled down.
5	ONB *(ONB)	Control Input for Switch B. Can be driven higher than IN_ without damage. A logic low turns switch B on for the MAX1823/MAX1823A, and a logic high turns switch B on for the MAX1823B/MAX1823H.
6	FAULTB	Fault-Indicator Output for Switch B. This open-drain output goes low when switch B is in thermal shutdown or UVLO or in a sustained (>20ms) current-limit or short-circuit condition.
7	OUTB	Power Output for Switch B. Connect a 1µF capacitor from OUTB to ground. Load condition may require additional bulk capacitance.
8	GND	Ground
9	OUTA	Power Output for Switch A. Connect a 1µF capacitor from OUTA to ground. Load condition may require additional bulk capacitance.
10	FAULTA	Fault-Indicator Output for Switch A. This open-drain output goes low when switch A is in thermal shutdown or UVLO or in a sustained (>20ms) current-limit or short-circuit condition.

^{*()} are for the MAX1823B/MAX1823H only.

Detailed Description

The MAX1823 is a dual, current-limited switch designed for USB applications. It has two independent switches, each with its own enable control input and autoreset function. Each switch has an error-flag output to notify the USB controller when the current-limit, short-circuit, undervoltage-lockout, or thermal-shutdown threshold is reached (Figure 2).

The MAX1823 operates from a 4V to 5.5V input voltage range and guarantees a minimum 720mA output current. A built-in 0.9A current limit limits the current in the event of a heavy-overload condition. The MAX1823 has independent thermal shutdown for each switch in the event of a prolonged overload or short-circuit condition. The autoreset function monitors the overload and automatically turns the switch on when the overload is removed.

Use of low-R_{ON} NMOS switches enables the MAX1823 to provide two switches in the ultra-small 10-pin μ MAX package. An internal micropower charge pump generates the high-side supply needed for driving the gates of these high-side switches. Separate current-limiting and thermal-shutdown circuits permit each switch to operate independently, improving system robustness.

Undervoltage-Lockout and Input-Voltage Requirements

The MAX1823 includes a UVLO circuit to prevent erroneous switch operation when the input voltage goes low during startup and brownout conditions. Operation is inhibited when V_{IN} is less than 3.4V.

Output Fault Protection

The MAX1823 senses the switch output voltage and selects continuous current limiting when V_{OUT} is greater than 1V or short-circuit current limiting when V_{OUT} is less than 1V. When V_{OUT} is greater than 1V, the device operates in a continuous current-limit mode that sets the output current limit to 0.9A. When V_{OUT} is less than 1V, the device operates in short-circuit current-limit mode, sourcing 0.35A_{RMS} current pulses to the load.

Autoreset Mode

If an output fault is detected for more than the 20ms blanking time, the output latches off, the $\overline{\text{FAULT}}$ output goes low, and a 25mA current is forced at the output. If the voltage on the output exceeds 0.5V for 20ms, the fault resets, the 25mA current source shuts down, and the output turns on. The device monitors the output voltage so that a short-circuit condition can be detected. Active loads are not expected to have measurable currents when the supply is below 0.5V. The MAX1823/MAX1823A can also be reset from fault manually by toggling $\overline{\text{ON}}$ _(ON_ for the MAX1823B/MAX1823H) for that channel.

Thermal Shutdown

The MAX1823 features independent thermal shutdown for each switch channel, allowing one switch to deliver power even if the other switch has a fault condition. When the junction temperature exceeds +160°C, the switch turns off and the FAULT_ output goes low immediately; fault blanking does not occur during thermal limit. When the junction cools by 15°C, the switch turns on again. If the fault overload condition continues, the switch cycles on and off, resulting in a pulsed output, saving battery power.

Reverse Current Blocking

The USB specification does not allow an output device to source current back into the USB port. However, the MAX1823A/MAX1823B are designed to safely power noncompliant devices. When disabled, each output is switched to a high-impedance state, blocking reverse current flow from the output back to the input. However, during normal operation with the device enabled, the MAX1823A/MAX1823B are bidirectional switches.

Fault Indicators

The MAX1823 provides an open-drain fault output (FAULT_) for each switch. For most applications, connect FAULT_ to $\overline{\text{IN}}$ through a 100k Ω pullup resistor. FAULT_ goes low when any of the following conditions occur:

- The input voltage is below the UVLO threshold.
- The switch junction temperature exceeds the +160°C thermal-shutdown temperature limit.
- The switch is in current-limit or short-circuit limit mode after the fault-blanking period is exceeded.
- The switch is in autoreset mode.




Figure 1. Typical Application Circuit

After the fault condition is removed, the FAULT_ output deasserts after a 20ms delay. Ensure that the MAX1823 has adequate input bypass capacitance to prevent glitches from triggering FAULT_ outputs. Input glitches greater than 0.2V/µs may cause erroneous FAULT_ indications.

Behavior During Current Limit and Fault Blanking

The MAX1823 limits switch current in three ways. When ON_ is deasserted (high for MAX1823/MAX1823A, low for MAX1823B/MAX1823H), the switch is off and leakage dominates the residual output current. When ON_ is asserted (low for MAX1823/MAX1823A, high for MAX1823B/MAX1823H), the switch supplies a continuous output current of at least 720mA. When the output current exceeds the 0.9A threshold, the MAX1823 limits the current depending on the output voltage. For VOUT_ greater than 1V (current-limit mode), the MAX1823 regulates the output current to 0.9A. For

VOUT_ less than 1V (short-circuit mode), the MAX1823 pulses the switch, decreasing the current to 0.35ARMS (Table 1). Note that a thermal overload may result from either of these high-current conditions.

The MAX1823 switches may enter current limit in normal operation when powering up or driving heavy capacitive loads. To differentiate these conditions from short circuits or sustained overloads that may damage the device, the MAX1823 has an independent fault-blanking circuit in each switch. When a load transient causes the device to enter current limit, an internal counter starts to monitor the duration of the fault. For load faults exceeding 20ms fault-blanking time, the switch turns off, the FAULT_ signal asserts low, and the device enters autoreset mode (see the *Autoreset Mode* section). Only current-limit and short-circuit faults are blanked. Thermal-overload faults and input voltage drops below the UVLO threshold immediately cause the switch to turn off and FAULT_ to assert low.




Figure 2. Functional Diagram

Table 1. MAX1823 Current Limiting and Fault Behavior

CONDITION	MAX1823 BEHAVIOR
Output short circuit (Vout < 1V)	 An output short circuit ramps the current to I_{SHORT} in 2ms to 3ms, the switch shuts off, the blanking timer turns on, FAULT_ stays high, and the output current pulses at 0.35A_{RMS}. Removing the short circuit before the 15ms short-circuit blanking timeout period allows the next ramped current pulse to soft-start the output. The FAULT_ flag stays high. A short circuit exceeding 15ms to 20ms forces FAULT_ low at 20ms, enables autoreset mode, and sources 25mA at the output. An output voltage above 0.5V for 20ms resets the switch, turns on the output, and forces FAULT_ high.
Output overload current (Vout > 1V)	 An output overload regulates the current at I_{LIM} (0.9A), and FAULT_ stays high until the overload is removed, a thermal fault occurs, or the 20ms continuous current-limit timeout period is reached. An overcurrent condition still present at 20ms forces FAULT_ low, enables autoreset, and sources 25mA at the output. An output voltage above 0.5V for 20ms resets the switch, turns on the output, and forces FAULT_ high.
Thermal fault (T _J > +160°C)	 A junction temperature of +160°C immediately forces FAULT_ low (the blanking timer does not apply to thermal faults) and turns off the switch. The junction cooling 15°C removes the thermal fault condition, enables autoreset mode, and sources 25mA at the output. FAULT_ remains low while a thermal fault condition is present. An output voltage above 0.5V for 20ms resets the switch, turns on the output, and forces FAULT_ high.

Fault blanking allows the MAX1823 to handle USB loads that may not be fully compliant with the USB specifications. USB loads with additional bypass capacitance and/or large startup currents can be successfully powered even while protecting the upstream power source. No fault is indicated if the switch is able to bring up the load within the 20ms blanking period.

Applications Information

Input Power Source

IN, INA, and INB provide the power for all control and charge-pump circuitry. All three IN_ pins must be connected together externally. The input-voltage slew rate should be less than 0.2V/µs to prevent erroneous FAULT_ indications. This condition should not occur under normal USB applications.

Input Capacitor

Connect a capacitor from IN_ to ground to limit the input voltage drop during momentary output short-circuit conditions. A 0.1µF ceramic capacitor is required for local decoupling; higher capacitor values further reduce the voltage drop at the input (see the Typical Application Circuit (Figure 1)). When driving inductive loads, a larger capacitance prevents voltage spikes from exceeding the MAX1823's absolute maximum ratings.

Output Capacitor

Place a 1µF or greater capacitor at each output for noise immunity. When starting up into very large capacitive loads, the switch pulses the output current at 0.35ARMS until the output voltage rises above 1V, then the capacitor continues to charge at the full 0.9A current limit. There is no limit to the output capacitor size, but to prevent a startup fault assertion, the capacitor must charge up within the fault-blanking delay period. Typically, starting up into a 330µF or smaller capacitor does not trigger a fault output. In addition to bulk capacitance, small-value (0.1µF or greater) ceramic capacitors improve the output's resilience to electrostatic discharge (ESD).

Driving Inductive Loads

A wide variety of devices (mice, keyboards, cameras, and printers) can load the USB port. These devices commonly connect to the port with cables, which can add an inductive component to the load. This inductance causes the output voltage at the USB port to ring during a load step. The MAX1823 is capable of driving inductive loads, but avoids exceeding the device's absolute maximum ratings. Usually the load inductance is relatively small, and the MAX1823's input includes a substantial bulk capacitance from an upstream regulator as well as local bypass capacitors, limiting overshoot. If severe ringing occurs due to large load inductance, clamp the MAX1823's output below 6V and above -0.3V.

Turn-On and Turn-Off Behavior

In the absence of faults, the MAX1823's internal switches turn on and off slowly under the control of the ON_inputs. Transition times for both edges are provided in the *Electrical Characteristics* table. The slow charge-pump switch drive minimizes load transients on the upstream power source. Under thermal fault and UVLO, the power device turns off rapidly (100ns) to protect the power device.

Layout and Thermal Dissipation

To optimize the switch response time to output short-circuit conditions, keep all traces as short as possible to reduce the effect of undesirable parasitic inductance. Place input and output capacitors no more than 5mm from device leads. All IN_ and OUT_ pins must be connected with short traces to the power bus. Wide power-bus planes provide superior heat dissipation through the switch IN_ and OUT_ pins.

While the switches are on, power dissipation is small, and the package temperature change is minimal. Calculate the power dissipation for this condition as follows:

$$P = (IOUT)^2 RON$$

For the normal operating current (I_{OUT} = 0.5A), and the maximum on-resistance of the switch (135m Ω), the power dissipation is:

$$P = (0.5A)^2 \times 0.135\Omega = 34mW$$
 per switch

The worst-case power dissipation occurs when the switch is in current limit and the output is greater than 1V. In this case, the power dissipated in each switch is the voltage drop across the switch multiplied by the current limit:

$$P = (I_{LIM})(V_{IN} - V_{OUT})$$

For a 5V input and 1V output, the maximum power dissipation per switch is:

$$P = (1.2A) (5V - 1V) = 4.8W$$

Since the package power dissipation is only 444mW, the MAX1823 die temperature exceeds the thermal-shutdown threshold, and the switch output shuts down until the junction temperature cools by 15°C. The duty cycle and period are strong functions of the ambient temperature and the PC board layout.

A short circuit at the output causes the power dissipated across the switch and the junction temperature to increase. If the fault condition persists, the thermal-overload-protection circuitry activates, and the output shuts down until the junction temperature decreases by 15°C (see the *Thermal Shutdown* section).

Since the output short-circuit current is 25mA (typ), and with $V_{IN} = 5V$, calculate the power dissipation for a short-circuited output as follows:

$$P = (0.025A)(5) = 0.125W$$


Chip Information

TRANSISTOR COUNT: 3227

PROCESS: BiCMOS

Package Information

(The package drawing(s) in this data sheet may not reflect the most current specifications. For the latest package outline information, go to **www.maxim-ic.com/packages**.)



Maxim cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim product. No circuit patent licenses are implied. Maxim reserves the right to change the circuitry and specifications without notice at any time.







WHAT'S NEW PRODUCTS SOLUTIONS

DESIGN

APPNOTES

SUPPORT

Maxim > Products > Power and Battery Management

MAX1823, MAX1823A, MAX1823B, MAX1823H

Dual USB Switch with Fault Blanking and Autoreset

QuickView

Technical Documents

Ordering Info

More Information

AII

Ordering Information

Notes:

- 1. Other options and links for purchasing parts are listed at: http://www.maxim-ic.com/sales.
- 2. Didn't Find What You Need? Ask our applications engineers. Expert assistance in finding parts, usually within one business day.
- 3. Part number suffixes: T or T&R = tape and reel; + = RoHS/lead-free; # = RoHS/lead-exempt. More: SeeFull Data Sheet or Part Naming Conventions.
- 4. * Some packages have variations, listed on the drawing. "PkgCode/Variation" tells which variation the product

Devices: 1-16 of 16

MAX1823	Free Sample	Buy	Package: TYPE PINS FOOTPRINT DRAWING CODE/VAR *	Temp	RoHS/Lead-Free? Materials Analysis
MAX1823EUB+T			uMAX;10 pin;15 mm Dwg: 21-0061J (PDF) Use pkgcode/variation: U10+2*	-40C to +85C	RoHS/Lead-Free: Lead Free Materials Analysis
MAX1823EUB+			uMAX;10 pin;15 mm Dwg: 21-0061J (PDF) Use pkgcode/variation: U10+2*	-40C to +85C	RoHS/Lead-Free: Lead Free Materials Analysis
MAX1823EUB			uMAX;10 pin;15 mm Dwg: 21-0061J (PDF) Use pkgcode/variation: U10-2*	-40C to +85C	RoHS/Lead-Free: No Materials Analysis
MAX1823EUB-T			uMAX;10 pin;15 mm Dwg: 21-0061J (PDF) Use pkgcode/variation: U10-2*	-40C to +85C	RoHS/Lead-Free: No Materials Analysis
MAX1823A	Free Sample	Buy	Package: TYPE PINS FOOTPRINT DRAWING CODE/VAR *	Temp	RoHS/Lead-Free? Materials Analysis
MAX1823AEUB			uMAX;10 pin;15 mm Dwg: 21-0061J (PDF) Use pkgcode/variation: U10-2*	-40C to +85C	RoHS/Lead-Free: No Materials Analysis
MAX1823AEUB-T			uMAX;10 pin;15 mm Dwg: 21-0061J (PDF) Use pkgcode/variation: U10-2*	-40C to +85C	RoHS/Lead-Free: No Materials Analysis
MAX1823AEUB+T			uMAX;10 pin;15 mm Dwg: 21-0061J (PDF) Use pkgcode/variation: U10+2*	-40C to +85C	RoHS/Lead-Free: Lead Free Materials Analysis
MAX1823AEUB+			uMAX;10 pin;15 mm Dwg: 21-0061J (PDF) Use pkgcode/variation: U10+2*	-40C to +85C	RoHS/Lead-Free: Lead Free Materials Analysis
MAX1823B	Free Sample	Buy	Package: TYPE PINS FOOTPRINT DRAWING CODE/VAR *	Temp	RoHS/Lead-Free? Materials Analysis
MAX1823BEUB+T			uMAX;10 pin;15 mm Dwg: 21-0061J (PDF) Use pkgcode/variation: U10+2*	-40C to +85C	RoHS/Lead-Free: Lead Free Materials Analysis
MAX1823BEUB+			uMAX;10 pin;15 mm Dwg: 21-0061J (PDF) Use pkgcode/variation: U10+2*	-40C to +85C	RoHS/Lead-Free: Lead Free Materials Analysis
MAX1823BEUB-T			uMAX;10 pin;15 mm Dwg: 21-0061J (PDF) Use pkgcode/variation: U10-2*	-40C to +85C	RoHS/Lead-Free: No Materials Analysis

MAX1823BEUB			uMAX;10 pin;15 mm Dwg: 21-0061J (PDF) Use pkgcode/variation: U10-2*	-40C to +85C	RoHS/Lead-Free: No Materials Analysis
MAX1823H	Free Sample	Buy	Package: TYPE PINS FOOTPRINT DRAWING CODE/VAR *	Temp	RoHS/Lead-Free? Materials Analysis
MAX1823HEUB+T			uMAX;10 pin;15 mm Dwg: 21-0061J (PDF) Use pkgcode/variation: U10+2*	-40C to +85C	RoHS/Lead-Free: Lead Free Materials Analysis
MAX1823HEUB-T			uMAX;10 pin;15 mm Dwg: 21-0061J (PDF) Use pkgcode/variation: U10-2*	-40C to +85C	RoHS/Lead-Free: No Materials Analysis
MAX1823HEUB+			uMAX;10 pin;15 mm Dwg: 21-0061J (PDF) Use pkgcode/variation: U10+2*	-40C to +85C	RoHS/Lead-Free: Lead Free Materials Analysis
MAX1823HEUB			uMAX;10 pin;15 mm Dwg: 21-0061J (PDF) Use pkgcode/variation: U10-2*	-40C to +85C	RoHS/Lead-Free: No Materials Analysis

Didn't Find What You Need?

- Next Day Product Selection Assistance from Applications Engineers
- Parametric Search
- Applications Help

QuickView

Description
Key Features
Applications/Uses
Key Specifications
Diagram

Technical Documents

Data Sheet
Application Notes
Design Guides
Engineering Journals
Reliability Reports
Software/Models
Evaluation Kits

Ordering Info

Price and Availability Samples Buy Online Package Information Lead-Free Information

More Information

Related Products Notes and Comments Evaluation Kits

Document Ref.: 19-1903; Rev 3; 2003-11-11 This page last modified: 2007-06-14

CONTACT US: SEND US AN EMAIL

Copyright 2007 by Maxim Integrated Products, Dallas Semiconductor • Legal Notices • Privacy Policy