



Energy & Power > Power Cable Accessories > Joints & Splices



Joints & Splice Product Availability: **AMERICAS**

Installation Instruction: **English**

Joints & Splice Technology: **Cold Applied, Cold Shrink**

Joints & Splice Voltage Class: **≤ 1 kV**

Joints & Splice Product Type: **Motor Connection Kit**

## Features

### Product Type Features

Component Design	PowerGel Sealing Gel
Adhesive Coating	Silicone Gel
Joints & Splice Technology	Cold Applied, Cold Shrink
Joints & Splice Product Type	Motor Connection Kit

### Electrical Characteristics

Joints & Splice Voltage Class	≤ 1 kV
-------------------------------	--------

### Body Features

Flexibility	Semi-Flexible
-------------	---------------

### Mechanical Attachment

Mechanical Reinforcement	Molded Cap Clamp
--------------------------	------------------

### Dimensions

Bolt Width (Max)	10 mm[.375 in]
Lug Barrel Length (Max)	13 mm[.5 in]
Bolt Length (Max)	13 mm[.5 in]
GelCap Length (Nominal)	71 mm[2.8 in]
Lug Overall Length (Max)	25 mm[1 in]
Conductor Range (Main)	16 – 10 AWG



Cross-Section Range	1.5 – 5 mm <sup>2</sup>
Cable Cross-Section (Max) (Main)	5 mm <sup>2</sup>
Cable Cross-Section (Min) (Main)	1.5 mm <sup>2</sup>

### Usage Conditions

Environmental Resistance	ASTM D1149, 168 Hours @40°C, 50 ppm
Operating Temperature Range	-40 – 105 °C
Chemical Resistance	ASTM D543, Sulfuric Acid, Sodium Hydroxide, Transformer & Motor Oil

### Operation/Application

Thermal Resistance	Applicable for Low Temperatures, Applicable for High Temperatures, Flame-Retardant
Mechanical Resistance	Abrasion Resistant (2040 gm wt, 4000 cycles, 5% max thickness loss), Against Mechanical Impact or Damage
UV-Stabilized	ASTM G53, UVB, 4000 hours, 4 hour on/off cycle

### Industry Standards

Standards	ANSI C119.1
UL Rating	UL 486A-486B

### Product Availability

Joints & Splice Product Availability	AMERICAS
--------------------------------------	----------

### Packaging Features

Standard Pack	5
Packaging Quantity	1
Packaging Method	Bag

### Other

Product Use	PowerGel-filled cap for motor lead and stub splice connections
Installation Instruction	English

### Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # 292284-000  
GELCAP-4(B5)



TE Part # 632692-000  
GELCAP-3(B5)



TE Part # 986734-000  
GELCAP-2(B5)



TE Part # F40658-000  
GELCAP-SL-2/0-3HOLE(B10)




TE Part # CP1967-000  
GELCAP-SL-2/0-3HOLE-B100



TE Part # 1710501-1  
GELPACT-SMY

Also in the Series | **RAYCHEM GelCap**



Joints & Splices(4)



Street Lighting Connectors(2)

## Customers Also Bought



TE Part #322225  
TERMINAL,SOLIS R 2/0 3/4



TE Part #DT04-12PA-BL08  
REC, 12P, BLK, N, ENH KEY, FLANGE, A



TE Part #718495-055  
RSRB-4046



TE Part #712836-000  
MCK-3V



TE Part #464364-000  
AFSJ-1C-BASIC



TE Part #063838-000  
HVT-152-G




TE Part #1-1904005-4  
V23374A1601X008-EV-144



TE Part #4-1393306-6  
VF711F11S01/X836



TE Part #C52938-000  
WCSF-070-6/2-12N-B50



TE Part #603275-000  
HKPE-1853F

## Documents

### Datasheets & Catalog Pages

[GELCAP-MOTOR-CONNECTION-CABLE-ACCESSORIES](#)

English

### Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English