SIEMENS

Data sheet 6XV1850-2JH10


product type designation

product description

IE TP Cord 9/RJ45, 2x2

Patch cable, preferred length, preassembled with one 9-pole D-sub connector and one RJ45 connector

Industrial Ethernet TP Cord 9/RJ45, TP cord pre-assembled with 1x RJ45 connector and 1x 9-pole ITP connector length 1 m.



suitability for use	Easy connection of terminal devices to the IE FC cabling system
cable designation	LI 02YSCY 2x2x0,15/0,98 PIMF ICCS GN
wire length	1 m
electrical data	
number of electrical connections	2
attenuation factor per length	
• at 10 MHz / maximum	0.085 dB/m
at 100 MHz / maximum	0.278 dB/m
• at 300 MHz / maximum	0.5 dB/m
• at 600 MHz / maximum	0.733 dB/m
impedance	
• at 1 MHz 100 MHz	100 Ω
● at 10 MHz 600 MHz	100 Ω
relative symmetrical tolerance	
 of the characteristic impedance at 1 MHz 100 MHz 	15 %
 of the characteristic impedance at 10 MHz 600 MHz 	6 %
transfer impedance per length / at 10 MHz	10 mΩ/m
loop resistance per length / maximum	300 mΩ/m
insulation resistance coefficient	500 GΩ·m
operating voltage	
RMS value	80 V
mechanical data	
number of electrical cores	4
design of the shield	Overlapped aluminum-clad foil, sheathed in a braided screen of tin- plated copper wires
core diameter	
 of AWG26 insulated conductor 	0.48 mm
outer diameter	
 of inner conductor 	0.48 mm
of the wire insulation	0.98 mm
width / of cable sheath	5.8 mm
symmetrical tolerance of width / of cable sheath	0.2 mm
thickness / of cable sheath	3.7 mm
symmetrical tolerance of thickness / of cable sheath	0.2 mm

	and attended a (DE)
of the wire insulation	polyethylene (PE)
of cable sheath	PVC
color	
 of the insulation of data wires 	white/blue, white/orange
of cable sheath	green
bending radius	
with single bend / minimum permissible	24 mm
with multiple bends / minimum permissible	42 mm
weight per length	32 kg/km
ambient conditions	
ambient temperature	
 during operation 	-40 +70 °C
during storage	-40 +70 °C
during transport	-40 +70 °C
during installation	-40 +70 °C
fire behavior	flame resistant according to IEC 60332-1
chemical resistance	, and the second
• to mineral oil	oil resistant according to IEC 60811-2-1 (4 h / 70°C)
• to grease	Conditional resistance
protection class IP	IP20
·	
product features, product functions, product components	/ general
product feature	
• halogen-free	No
• silicon-free	Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	No
UL/ETL style / 600 V Rating	No
certificate of suitability	
 EAC approval 	Yes
UL approval	Yes
standard for structured cabling	Cat5
Marine classification association	
 American Bureau of Shipping Europe Ltd. (ABS) 	No
 French marine classification society (BV) 	No
Det Norske Veritas (DNV)	No
Germanische Lloyd (GL)	No
 Lloyds Register of Shipping (LRS) 	No
Nippon Kaiji Kyokai (NK)	No
Polski Rejestr Statkow (PRS)	No
reference code	
according to IEC 81346-2	WG
 according to IEC 81346-2:2019 	WGB
further information / internet-Links	
Internet-Link	http://www.cigmons.com/tic.collection.tegl
to web page: selection aid TIA Selection Tool to web page: selection aid TIA Selection Tool	http://www.siemens.com/tia-selection-tool
to website: Industrial communication	http://www.siemens.com/simatic-net
to website: Industry Mall	https://mall.industry.siemens.com
to website: Information and Download Center	http://www.siemens.com/industry/infocenter
 to website: Selection guide for cables and connectors 	https://sie.ag/2QdlxcP
to website: Image database	http://automation.siemens.com/bilddb
to website: CAx-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

last modified: 1/14/2022 🖸