



Product: [8504](#)

Lead Wire, #24 Str TC, PVC Ins, TYPE B MIL-W-16878/1

Request Sample

### Product Description

Low Temp Plastic Lead Wire, 24AWG (7x32) Tinned Copper, PVC Insulation, TYPE B MIL-W-16878/1 600V 105C

### Technical Specifications

#### Product Overview

Suitable Applications:	inter-connection circuits, internal wiring of computer and electronic equipments, (Type B) MIL-W-16878/1-Low Temp applications
------------------------	--

#### Construction Details

##### Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	1	24	7x32	TC - Tinned Copper

##### Insulation

Material	Nom. Thickness	Nom. Insulation Diameter
PVC - Polyvinyl Chloride	0.01 in (0.25 mm)	0.044 in (1.1 mm)

Overall Cable Diameter (Nominal):	0.044 in (1.1 mm)
-----------------------------------	-------------------

#### Electrical Characteristics

##### Voltage

<b>UL Voltage Rating</b>
600 V RMS

#### Mechanical Characteristics

##### Bend Radius

Stationary Min.	Installation Min.
0.18 in (4.6 mm)	0.18 in (4.6 mm)

Max. Pull Tension:	5.5 lbs (2.5 kg)
Bulk Cable Weight:	2 lbs/1000ft

#### Standards and Compliance

Sustainability:	CA Prop 65
Military Compliance:	MIL-W-16878/1
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

#### History

Update and Revision:	Revision Number: 0.438 Revision Date: 01-20-2023
----------------------	--

#### Part Numbers

##### Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8504 010100	Black	Reel	100 ft	612825210313	

8504 0101000	Black	Reel	1,000 ft	612825210320	P
8504 006100	Blue, Light	Reel	100 ft	612825210207	
8504 0061000	Blue, Light	Reel	1,000 ft	612825210214	P
8504 001100	Brown	Reel	100 ft	612825210054	
8504 0011000	Brown	Reel	1,000 ft	612825210061	P
8504 008100	Gray	Reel	100 ft	612825210238	
8504 0081000	Gray	Reel	1,000 ft	612825210245	P
8504 005100	Green, Dark	Reel	100 ft	612825210177	
8504 0051000	Green, Dark	Reel	1,000 ft	612825210184	P
8504 003100	Orange	Reel	100 ft	612825210115	
8504 0031000	Orange	Reel	1,000 ft	612825210122	P
8504 002100	Red	Reel	100 ft	612825210085	
8504 0021000	Red	Reel	1,000 ft	612825210092	P
8504 0071000	Violet	Reel	1,000 ft	612825210221	P
8504 009100	White	Reel	100 ft	612825210269	
8504 0091000	White	Reel	1,000 ft	612825210276	P
8504 004100	Yellow	Reel	100 ft	612825210146	
8504 0041000	Yellow	Reel	1,000 ft	612825210153	P

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.