



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	SEE DETAIL	"A" +/- .062	MARKER ACROSS	TUBING COLOR	MARKERS PER ROLL
H050X084H1T	C	0.50 [12.70]	4	WHITE	2000
H100X084H1T	A	1.00 [25.40]	2		1000
H200X084H1T	B	2.00 [50.80]	1		500
H100X084H2T	A	1.00 [25.40]	2	YELLOW	1000
H200X084H2T	B	2.00 [50.80]	1		500
H100X084H3T	A	1.00 [25.40]	2	BLACK	1000
H200X084H3T	B	2.00 [50.80]	1		500
H100X084H4T	A	1.00 [25.40]	2	RED	1000
H200X084H4T	B	2.00 [50.80]	1		500



NOTE:
1. DIMENSIONS IN () ARE IN MILLIMETERS.

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
10	4/30/15	RVU	SEWH	JHAC	ADD NEW COLUMN OF MARKERS PER ROLL.	GAECN02785
9	1/16/15	RVU	SEWH	MSAD	ADD NEW PN, H050X084H1T. ADD NEW DETAIL C WITH 4 COLUMNS FOR H050X084H1T.	GAECN02538
8	4/12/12	RVU			REVISED ON DETAIL A, B, DESIGN TO SHOW ALL MARKERS.	6731
7	12/1/10	RVU			CHANGE BOX DESIGN.	6230
6	5/21/09	RVU			+/- .12, +/- .062, +/- .020 WAS +/- .03, +/- .032, +/- .010. HT: .84 +/- .062 WAS .840. MAT'L, HSK TUBING GMUHS31, 3.5 WIDE LINER WAS GMUHS. ADD "A" +/- .062.	5593

TITLE H***X084H*T OPTIMUM COMPUTER PRINTABLE MIL. SPEC. HEAT SHRINK MARKERS CUSTOMER DRAWING	
ITEM REVISION NAME 100923NK/13	PANDUIT
DATASET FILE NAME 100923NK_DC_C10436/13L	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .x ± .12 [3.05] .xxx ± .020 [.508] .xx ± .062 [1.57] ANGLES ±	
THIRD ANGLE PROJECTION	
DRAWN BY RVU	DATE 8/2/06
CHK MSAD	SCALE NTS
DRAWING NUMBER: C10436	
SHT 1 OF 1	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	DRAWING NUMBER	SHT	SIZE
							RVU	8/2/06	MSAD	NTS	C10436	1 OF 1	A