
DATE
 REV
 ECN
 APP'D. BY

 10/15/19
 A0
 RELEASED
 ADB





ט

NOTES:

1. M12 CONNECTOR COMPONENTS:

HOUSING: THERMOPLASTIC UL94 V-0

CONTACTS: COPPER ALLOY

SHELL: COPPER ALLOYS AND ZINC ALLOY

SEALING: NBR

CONTACT PLATING: UNDERPLATE: 50u"~70u" NICKEL

CONTACT AREA: 10u" GOLD

2

RJ45 CONNECTOR COMPONENTS: HOUSING: CLEAR POLYCARBONATE

CONTACTS: COPPER ALLOY STRAIN RELIEF OVERMOLD: PVC SHIELD: NICKEL PLATED BRASS

CONTACT PLATING: UNDERPLATE: 100u" NICKEL PLATING: 2u" GOLD FLASH CONTACT AREA: 50u" GOLD

CABLE CONSTRUCTION: STRANDED, TIN PLATED COPPER 4PR, SF/UTP, TYPE CMX

TPE JACKET


2. ELECTRICAL TESTING:

100% TRANSMISSION TESTED FOR PERFORMANCE

3. PACKAGING:

ONE CABLE PER BAG

PIN ASSIGNMENT




568B STANDARD WIRING MAP


Part Numbers Reference Table			
LENGTH	Part Number		
3 FT	BM-MYRM003F		
7 FT	BM-MYRM007F		
15 FT	BM-MYRM015F		
30 FT	BM-MYRM030F		

P/N STRUCTURE:

BM-MYRMxxxF







206 Van Vorst Street Jersey City, NJ 07302 +1 201 432 0463 http://www.belfuse.com

DO NOT SCALE DRAWING
DRAWING IS SUBJECT TO
CHANGE WITHOUT NOTICE

DIMENSIONS: INCHES [METRIC]

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ±.005 [0.13] ANGLES ARE ± 1'

SHEET NO. 1 OF 1

THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF BEL FUSE, INC. AND SHALL NOT BE REPRODUCED, COPIED. OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN

CONSENT OF BEL FUSE, INC.

M12 X-CODE MALE TO RJ45 MALE

	DRN BY:		DATE 09/18/19		
ı	APPD BY:	ADB	DATE 10,	/15/19	
	DWG NO.	CT999201		REV. AO	

AutoCAD

- M = M12

- CABLE ASSEMBLY FAMILY

Α