



HX-CT

TE Internal #: EL8206-000

Printable Tubing, Continuous, Low Fire Hazard, 2:1 Shrink Ratio, Yellow, .25in [6.4mm] Expanded Inside Diameter, HX-CT

[View on TE.com >](#)

Identification & Labeling > Printable Tubing > Continuous Tube, Low Fire Hazard HX-CT



Printable Tubing Type: **Continuous**

Printable Tubing Grade: **Low Fire Hazard**

Shrink Ratio: **2:1**

Primary Product Color: **Yellow**

Expanded Inside Diameter (Min): **6.4 mm [.25 in]**

[All Continuous Tube, Low Fire Hazard HX-CT \(18\)](#)

Features

Product Type Features

| | |
|------------------------|-----------------|
| Printable Tubing Type | Continuous |
| Printable Tubing Grade | Low Fire Hazard |

Body Features

| | |
|-----------------------|--------|
| Shrink Ratio | 2:1 |
| Primary Product Color | Yellow |

Dimensions

| | |
|---------------------------------|-------------------------------|
| Expanded Inside Diameter (Min) | 6.4 mm[.25 in] |
| Recovered Inside Diameter (Max) | 3.2 mm[.125 in] |
| Compatible Cable Diameter Range | 3.2 – 5.12 mm[.125 – .201 in] |

Usage Conditions

| | |
|-----------------------------|----------------------------|
| Operating Temperature Range | -40 – 105 °C[-40 – 221 °F] |
|-----------------------------|----------------------------|

Printer/Label Features

| | |
|--------------------|------------------|
| Printer Technology | Thermal Transfer |
|--------------------|------------------|

Packaging Features

| | |
|--------------------|----|
| Packaging Quantity | 50 |
|--------------------|----|



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



| | | | |
|--|--|--|--|
|  <p>TE Part # 1-2186500-1 T3212-PRINTER</p> |  <p>TE Part # 1-2186502-1 T3224-PRINTER</p> |  <p>TE Part # 1-2186503-1 T3224-SWARE-PRINTER</p> |  <p>TE Part # 1-2186501-1 T3212-SWARE-PRINTER</p> |
|--|--|--|--|



Also in the Series | HX-CT



Customers Also Bought





Documents

Product Drawings

[HX-CT-50M-6.4-OUT-4](#)

English

Datasheets & Catalog Pages

[Printable Continuous Tubing](#)

English

[HX-CT, Low Fire Hazard Continuous Heat Shrink Identification Tube](#)

English

Product Specifications

[Product Specification](#)

English

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English