



REPRESENTATIVE IMAGE

Product: [1817P](#)

Audio Snake Cable, 8 Pr #22 Str TC, Ind. Shielded & Jacketed, PVDF Jkt, CMP

Product Description

Audio Snake Cable, 8 pair 22 AWG (7 x 30) Tinned Copper, FEP insulation, Individually Foil Shielded and PVDF jacketed, Overall PVDF Jacket, Ripcord, CMP

Technical Specifications

Product Overview

Suitable Applications:	Multi-channel interconnect between audio equipment such as microphones, speakers, amplifiers, mixing consoles; Live events or studio sound; Analog audio
------------------------	----------------------------------------------------------------------------------------------------------------------------------------------------------

Construction Details

Conductor

Element	Number of Element	Size	Stranding	Material
Pair(s)	8	22 AWG	7x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	FEP - Fluorinated Ethylene Propylene	0.010 in (0.25 mm)	0.05 in (1.3 mm)	Black, Red

Inner Shield

Element	Shield Type	Material	Coverage	Drainwire Type
Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC

Inner Jacket

Element	Material	Nom. Thickness	Nom. Diameter
Pair(s)	PVDF - Polyvinylidene Fluoride	0.009 in (0.23 mm)	0.119 in (3.02 mm)

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVDF - Polyvinylidene Fluoride	0.015 in (0.38 mm)	0.424 in (10.8 mm)	Yes

Overall Cable Diameter (Nominal):	0.424 in (10.8 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
Pair(s)	14.8 Ohm/1000ft (48.6 Ohm/km)	31 pF/ft (100 pF/m)	56 pF/ft (180 pF/m)	50 Ohm	66%	1.45 Amps per conductor @ 25°C

Voltage

UL Voltage Rating
300 V (CMP)

Mechanical Characteristics

Temperature

UL Temperature	Operating
150°C	-40°C to +150°C

Bend Radius

Stationary Min.	Installation Min.
4.2 in (110 mm)	4.2 in (110 mm)

Max. Pull Tension:	243 lbs (110 kg)
Bulk Cable Weight:	98 lbs/1000ft (150 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor
Flammability / Reaction to Fire:	NFPA 262, UL 910 (Plenum)
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	1817R

History

Update and Revision:	Revision Number: 0.337 Revision Date: 11-09-2022
----------------------	--------------------------------------------------

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
1817P 010500	Black	Reel	500 ft	612825123590
1817P 0101000	Black	Reel	1,000 ft	612825123583

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.