## **SIEMENS**

Data sheet 6XV1850-2HH60


## product type designation

product description

## IE TP XP cord RJ45/RJ45, crossed

Crossover patch cable, preferred length, preassembled with two RJ45 connectors (10/100MB)

Industrial Ethernet TP XP Cord RJ45/RJ45, TP cord pre-assembled with 2 RJ45 plug, send and receive line crossed, length 6 m.



suitability for use	Easy connection of terminal devices to the IE FC cabling system
cable designation	LI 02YSCY 2x2x0,15/0,98 PIMF ICCS GN
wire length	6 m
electrical data	
number of electrical connections	2
attenuation factor per length	
<ul><li>at 10 MHz / maximum</li></ul>	0.09 dB/m
<ul><li>at 100 MHz / maximum</li></ul>	0.285 dB/m
<ul><li>at 300 MHz / maximum</li></ul>	0.495 dB/m
at 600 MHz / maximum	0.75 dB/m
impedance	
• at 1 MHz 100 MHz	100 Ω
• at 10 MHz 600 MHz	100 Ω
relative symmetrical tolerance	
<ul> <li>of the characteristic impedance at 1 MHz 100 MHz</li> </ul>	15 %
<ul> <li>of the characteristic impedance at 10 MHz 600 MHz</li> </ul>	6 %
transfer impedance per length / at 10 MHz	10 mΩ/m
loop resistance per length / maximum	300 mΩ/m
insulation resistance coefficient	150 GΩ·m
operating voltage	
<ul> <li>RMS value</li> </ul>	80 V
mechanical data	
number of electrical cores	4
design of the shield	Overlapped aluminum-clad foil, sheathed in a braided screen of tin- plated copper wires
core diameter	
<ul> <li>of AWG26 insulated conductor</li> </ul>	0.48 mm
outer diameter	
<ul> <li>of inner conductor</li> </ul>	0.48 mm
of the wire insulation	0.98 mm
width / of cable sheath	5.8 mm
symmetrical tolerance of width / of cable sheath	0.2 mm
thickness / of cable sheath	3.7 mm
symmetrical tolerance of thickness / of cable sheath	0.2 mm
material	

- of the wire inculation	nelvethylene (DE)
of the wire insulation	polyethylene (PE)
of cable sheath	PVC
color	
<ul> <li>of the insulation of data wires</li> </ul>	white/blue, white/orange
of cable sheath	green
bending radius	
<ul><li>with single bend / minimum permissible</li></ul>	24 mm
with multiple bends / minimum permissible	42 mm
weight per length	32 kg/km
ambient conditions	
ambient temperature	
<ul> <li>during operation</li> </ul>	-40 +70 °C
during storage	-40 +70 °C
during transport	-40 +70 °C
during installation	-40 +70 °C
fire behavior	flame resistant according to IEC 60332-2-1
chemical resistance	, and the second
• to mineral oil	oil resistant according to IEC 60811-2-1 (4 h / 70°C)
• to grease	Conditional resistance
protection class IP	IP20
product features, product functions, product components	/ general
product feature	N.
• halogen-free	No
• silicon-free	Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	No
UL/ETL style / 600 V Rating	No
certificate of suitability	
<ul> <li>EAC approval</li> </ul>	Yes
UL approval	Yes
standard for structured cabling	Cat5
Marine classification association	
<ul> <li>American Bureau of Shipping Europe Ltd. (ABS)</li> </ul>	No
<ul> <li>French marine classification society (BV)</li> </ul>	No
<ul> <li>Det Norske Veritas (DNV)</li> </ul>	No
<ul> <li>Germanische Lloyd (GL)</li> </ul>	No
<ul> <li>Lloyds Register of Shipping (LRS)</li> </ul>	No
<ul> <li>Nippon Kaiji Kyokai (NK)</li> </ul>	No
Polski Rejestr Statkow (PRS)	No
reference code	
• according to IEC 81346-2	WG
• according to IEC 81346-2:2019	WGB
further information / internet-Links	
Internet-Link	
to web page: selection aid TIA Selection Tool	http://www.siemens.com/tia-selection-tool
to web page: selection and TIA Selection Tool     to website: Industrial communication	http://www.siemens.com/simatic-net
	https://mall.industry.siemens.com
to website: Industry Mall     to website: Information and Download Center	
	http://www.siemens.com/industry/infocenter
<ul> <li>to website: Selection guide for cables and connectors</li> </ul>	https://sie.ag/2QdlxcP
to website: Image database	http://automation.siemens.com/bilddb
to website: Mage database     to website: CAx-Download-Manager	http://www.siemens.com/cax
to website: Industry Online Support	https://support.industry.siemens.com
- 13 Hosoito. Hisabily Chillio Cupport	The state of the s

last modified: 7/7/2022 🖸